

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709349

Luminaire Tested: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

Issue Date: 3/5/2020

Test Information

Test Method: LM-79-2019
Report Number: P709349
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-3, G3-2104-222-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4892.8 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 41.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	98	94	91	88	89	86	84	81	72	70	68	59	57	56	46	46	45	39
2	90	84	79	74	83	77	73	69	65	62	59	53	51	50	43	42	40	36
3	84	75	69	64	77	70	64	60	59	55	52	49	46	44	40	38	36	32
4	77	68	61	56	71	63	57	52	53	49	46	45	42	39	36	35	33	29
5	72	61	54	49	66	57	51	46	49	44	40	41	38	35	34	32	30	27
6	66	56	48	43	61	52	45	41	44	40	36	38	34	32	31	29	27	24
7	62	51	44	39	57	47	41	37	41	36	33	35	31	29	29	27	25	22
8	58	46	39	35	53	43	37	33	38	33	29	32	29	26	27	24	23	20
9	54	43	36	31	50	40	34	30	35	30	27	30	26	24	25	23	21	19
10	50	39	33	28	47	37	31	27	32	28	24	28	24	22	23	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	21632	21632	21632	21632	21632
5°	21840	21644	21870	21644	21840
10°	22076	21940	22123	21940	22076
15°	22121	22272	22539	22272	22121
20°	21780	22215	22656	22215	21780
25°	21178	21643	22137	21643	21178
30°	19939	20517	21052	20517	19939
35°	17895	18557	18920	18557	17895
40°	14779	15220	15548	15220	14779
45°	8873	10988	9839	10988	8873
50°	3504	6059	3818	6059	3504
55°	1869	2749	1841	2749	1869
60°	807	1371	869	1371	807
65°	734	833	772	833	734
70°	727	779	774	779	727
75°	661	774	717	774	661
80°	623	716	716	716	623
85°	537	704	704	704	537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
 Vertical Angle: 45°
 Luminance: 11061 cd/sqm

TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	2.6
10°-20°	376.4	7.7
20°-30°	557.4	11.4
30°-40°	577.4	11.8
40°-50°	347.0	7.1
50°-60°	82.9	1.7
60°-70°	22.6	0.5
70°-80°	12.6	0.3
80°-90°	8.0	0.2
90°-100°	75.8	1.5
100°-110°	221.0	4.5
110°-120°	360.6	7.4
120°-130°	457.6	9.4
130°-140°	489.7	10.0
140°-150°	457.2	9.3
150°-160°	376.3	7.7
160°-170°	252.3	5.2
170°-180°	89.6	1.8
0°-30°	1062.1	21.7
0°-40°	1639.5	33.5
0°-60°	2069.4	42.3
0°-90°	2112.6	43.2
90°-120°	657.4	13.4
90°-150°	2062.0	42.1
90°-180°	2780.0	56.8
0°-180°	4892.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1340	1340	1340	1340	1340	
5°	1348	1335	1349	1335	1348	129
15°	1323	1332	1348	1332	1323	372
25°	1189	1215	1243	1215	1189	543
35°	908	942	960	942	908	559
45°	389	481	431	481	389	306
55°	66	98	65	98	66	64
65°	19	22	20	22	19	20
75°	11	12	12	12	11	12
85°	3	4	4	4	3	4
90°	21	19	3	26	41	10
95°	22	29	30	96	130	37
105°	225	169	140	252	310	210
115°	373	374	269	400	460	369
125°	592	572	398	498	564	525
135°	774	737	542	559	624	593
145°	892	862	692	595	638	558
155°	970	946	821	676	662	448
165°	1011	986	908	794	762	285
175°	990	974	949	907	894	95
180°	952	952	952	952	952	

TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8
2.5°	1341.3	1342.7	1344.1	1340.3	1334.8	1334.5	1339.3	1343.4	1345.4	1347.5	1345.4
5°	1347.5	1348.3	1349.2	1343.6	1335.9	1334.9	1340.4	1345.1	1347.3	1349.4	1347.3
7.5°	1347.3	1348.6	1349.9	1345.4	1339.0	1338.1	1342.8	1346.7	1348.0	1349.4	1348.0
10°	1346.5	1347.8	1349.1	1344.6	1338.2	1338.2	1344.6	1349.4	1349.4	1349.4	1349.4
12.5°	1340.4	1342.3	1344.3	1341.3	1336.6	1338.6	1347.4	1353.6	1351.9	1350.2	1351.9
15°	1323.4	1326.4	1329.4	1329.8	1329.4	1335.4	1347.8	1356.1	1352.3	1348.4	1352.3
17.5°	1292.3	1296.4	1300.5	1304.0	1307.3	1317.6	1334.7	1346.0	1340.0	1334.0	1340.0
20°	1267.6	1271.1	1274.5	1280.2	1286.6	1299.2	1318.0	1330.6	1324.6	1318.6	1324.6
22.5°	1238.4	1242.2	1245.9	1251.4	1257.5	1270.6	1290.8	1304.3	1298.0	1291.7	1298.0
25°	1188.8	1192.2	1195.6	1201.6	1208.4	1221.3	1240.1	1252.9	1247.8	1242.6	1247.8
27.5°	1123.4	1127.1	1130.9	1136.7	1143.1	1154.4	1170.6	1182.2	1179.9	1177.6	1179.9
30°	1069.5	1074.6	1079.8	1087.2	1095.3	1105.7	1118.6	1128.3	1128.7	1129.2	1128.7
32.5°	1008.7	1015.6	1022.4	1030.0	1037.7	1047.5	1059.3	1068.0	1067.4	1066.8	1067.4
35°	907.9	915.2	922.5	930.1	937.8	945.2	952.5	958.2	959.0	959.9	959.0
37.5°	791.2	794.0	796.8	803.7	812.0	820.1	827.9	833.5	832.9	832.3	832.9
40°	701.2	701.6	702.0	708.8	717.8	726.4	734.5	740.3	739.0	737.7	739.0
42.5°	605.0	606.8	608.6	616.0	625.3	633.0	639.1	641.3	631.8	622.3	631.8
45°	388.6	420.2	451.8	467.8	478.4	484.0	484.4	478.8	454.8	430.9	454.8
47.5°	203.3	234.5	265.7	297.3	329.0	336.5	319.6	299.5	269.6	239.7	269.6
50°	139.5	150.1	160.8	195.2	237.6	244.8	217.0	191.3	171.6	152.0	171.6
52.5°	101.8	108.3	114.9	141.6	175.1	178.1	150.6	127.6	117.9	108.1	117.9
55°	66.4	68.1	69.8	81.8	97.1	98.2	85.0	74.0	69.7	65.4	69.7
57.5°	39.6	43.2	46.8	52.3	58.3	58.5	52.8	47.5	43.8	40.0	43.8
60°	25.0	27.6	30.1	35.6	42.0	42.9	38.2	33.8	30.4	26.9	30.4
62.5°	22.7	23.6	24.4	28.1	32.9	33.2	29.2	25.9	24.9	23.9	24.9
65°	19.2	19.7	20.1	20.8	21.7	21.9	21.5	21.1	20.6	20.2	20.6
67.5°	16.9	17.4	17.8	18.1	18.5	18.7	18.8	18.7	18.3	17.9	18.3
70°	15.4	15.8	16.2	16.4	16.4	16.6	17.0	17.2	16.8	16.4	16.8
72.5°	13.8	13.9	14.0	14.3	14.6	14.9	14.9	15.0	14.9	14.8	14.9
75°	10.6	11.0	11.4	11.9	12.3	12.5	12.5	12.4	12.0	11.5	12.0
77.5°	8.3	8.7	9.1	9.2	9.2	9.4	9.7	9.9	9.6	9.2	9.6
80°	6.7	7.2	7.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
82.5°	5.2	5.6	6.0	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
85°	2.9	3.3	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	5.0	5.0	4.8	4.9	5.2	5.2	4.6	3.8	2.9	2.1	2.9
90°	21.2	21.2	20.2	19.2	19.2	18.3	15.4	11.5	6.7	2.9	6.7
92.5°	25.0	25.0	24.0	23.9	22.3	20.6	16.9	16.9	16.7	10.6	18.3
95°	22.1	22.1	22.1	22.1	26.0	32.7	48.1	49.1	32.7	29.8	42.3
97.5°	50.6	53.5	59.8	71.2	87.3	90.4	85.6	63.9	61.2	56.9	77.5
100°	102.9	105.8	110.6	125.0	136.6	113.5	89.4	88.5	82.7	80.8	102.9
102.5°	169.1	169.7	172.9	177.4	137.3	124.3	118.7	114.6	105.8	104.6	126.8
105°	225.1	218.3	187.6	168.3	169.3	169.3	165.4	157.7	141.4	140.4	165.4
107.5°	220.3	219.5	220.6	223.5	228.5	227.4	222.9	202.4	183.1	178.7	201.2
110°	262.6	262.6	264.5	267.4	269.3	267.4	260.6	234.7	211.6	204.9	225.1

TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	306.4	304.9	306.8	308.9	313.2	307.4	296.0	266.2	240.1	230.3	250.5
115°	373.2	373.2	374.1	374.1	375.1	372.2	349.1	318.4	283.7	269.3	286.6
117.5°	441.1	439.2	440.3	441.5	437.6	429.9	403.2	367.4	328.5	305.5	319.1
120°	481.9	483.8	481.9	483.8	479.9	468.4	442.4	402.0	357.8	330.9	341.4
122.5°	524.2	525.3	524.9	524.6	519.9	506.9	476.3	434.3	390.9	357.8	362.2
125°	591.5	586.7	584.8	583.8	580.0	564.6	532.8	489.6	438.6	398.2	392.4
127.5°	647.9	645.8	641.7	639.6	633.6	615.0	582.5	540.7	484.7	439.0	426.1
130°	684.8	685.8	681.0	678.1	667.5	647.3	615.5	576.1	519.4	467.4	449.2
132.5°	721.7	720.4	718.7	710.4	701.3	679.6	650.2	609.2	551.7	497.4	472.2
135°	774.2	771.4	766.6	758.9	747.3	726.2	698.3	657.9	600.2	541.5	506.9
137.5°	816.0	813.7	808.7	800.6	787.5	769.2	741.2	705.2	649.8	587.8	544.2
140°	840.6	840.6	834.8	825.2	813.7	795.4	770.4	732.9	679.0	619.4	570.3
142.5°	862.9	862.9	856.4	849.1	836.8	820.0	798.1	760.6	708.3	649.4	597.3
145°	892.5	892.5	888.7	882.9	869.5	854.1	835.8	798.3	750.2	691.5	639.6
147.5°	918.7	920.8	916.0	911.4	900.8	882.7	867.3	831.4	787.5	735.6	682.3
150°	934.9	937.8	932.9	929.1	918.5	901.2	885.8	852.2	809.8	761.7	710.8
152.5°	950.3	952.4	949.1	945.3	933.1	915.8	902.7	871.4	832.9	787.1	735.4
155°	969.5	974.3	970.5	965.6	954.1	937.8	926.2	897.4	861.8	821.4	777.1
157.5°	989.1	991.2	987.4	981.4	970.6	956.6	944.3	917.7	886.8	852.0	813.3
160°	998.3	1001.2	997.4	990.7	979.1	966.6	955.1	930.1	902.2	870.4	834.8
162.5°	1004.5	1008.2	1004.3	998.3	984.5	973.5	963.5	940.8	914.5	885.8	854.1
165°	1010.8	1014.7	1011.8	1005.1	990.7	982.0	973.3	954.1	931.0	907.9	881.0
167.5°	1011.2	1016.0	1012.4	1006.8	992.4	983.9	977.6	961.0	942.4	924.7	903.7
170°	1008.9	1013.7	1010.8	1006.0	991.6	983.9	979.1	965.6	949.3	933.9	917.6
172.5°	1003.5	1007.6	1005.5	1000.7	987.0	980.8	978.3	966.4	953.1	941.6	927.6
175°	989.7	995.5	991.6	987.8	976.2	972.4	973.3	965.6	956.0	949.3	940.6
177.5°	969.1	972.2	971.4	969.1	960.6	960.6	963.7	959.1	956.0	952.9	949.1
180°	952.2	952.2	952.2	952.2	952.2	952.2	952.2	952.2	952.2	952.2	952.2

TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8	1339.8
2.5°	1343.4	1339.3	1334.5	1334.8	1340.3	1344.1	1342.7	1341.3
5°	1345.1	1340.4	1334.9	1335.9	1343.6	1349.2	1348.3	1347.5
7.5°	1346.7	1342.8	1338.1	1339.0	1345.4	1349.9	1348.6	1347.3
10°	1349.4	1344.6	1338.2	1338.2	1344.6	1349.1	1347.8	1346.5
12.5°	1353.6	1347.4	1338.6	1336.6	1341.3	1344.3	1342.3	1340.4
15°	1356.1	1347.8	1335.4	1329.4	1329.8	1329.4	1326.4	1323.4
17.5°	1346.0	1334.7	1317.6	1307.3	1304.0	1300.5	1296.4	1292.3
20°	1330.6	1318.0	1299.2	1286.6	1280.2	1274.5	1271.1	1267.6
22.5°	1304.3	1290.8	1270.6	1257.5	1251.4	1245.9	1242.2	1238.4
25°	1252.9	1240.1	1221.3	1208.4	1201.6	1195.6	1192.2	1188.8
27.5°	1182.2	1170.6	1154.4	1143.1	1136.7	1130.9	1127.1	1123.4
30°	1128.3	1118.6	1105.7	1095.3	1087.2	1079.8	1074.6	1069.5
32.5°	1068.0	1059.3	1047.5	1037.7	1030.0	1022.4	1015.6	1008.7
35°	958.2	952.5	945.2	937.8	930.1	922.5	915.2	907.9
37.5°	833.5	827.9	820.1	812.0	803.7	796.8	794.0	791.2
40°	740.3	734.5	726.4	717.8	708.8	702.0	701.6	701.2
42.5°	641.3	639.1	633.0	625.3	616.0	608.6	606.8	605.0
45°	478.8	484.4	484.0	478.4	467.8	451.8	420.2	388.6
47.5°	299.5	319.6	336.5	329.0	297.3	265.7	234.5	203.3
50°	191.3	217.0	244.8	237.6	195.2	160.8	150.1	139.5
52.5°	127.6	150.6	178.1	175.1	141.6	114.9	108.3	101.8
55°	74.0	85.0	98.2	97.1	81.8	69.8	68.1	66.4
57.5°	47.5	52.8	58.5	58.3	52.3	46.8	43.2	39.6
60°	33.8	38.2	42.9	42.0	35.6	30.1	27.6	25.0
62.5°	25.9	29.2	33.2	32.9	28.1	24.4	23.6	22.7
65°	21.1	21.5	21.9	21.7	20.8	20.1	19.7	19.2
67.5°	18.7	18.8	18.7	18.5	18.1	17.8	17.4	16.9
70°	17.2	17.0	16.6	16.4	16.4	16.2	15.8	15.4
72.5°	15.0	14.9	14.9	14.6	14.3	14.0	13.9	13.8
75°	12.4	12.5	12.5	12.3	11.9	11.4	11.0	10.6
77.5°	9.9	9.7	9.4	9.2	9.2	9.1	8.7	8.3
80°	7.7	7.7	7.7	7.7	7.7	7.6	7.2	6.7
82.5°	6.2	6.2	6.2	6.2	6.2	6.0	5.6	5.2
85°	3.8	3.8	3.8	3.8	3.8	3.7	3.3	2.9
87.5°	3.7	5.0	6.0	7.1	8.1	8.7	9.4	9.0
90°	10.6	17.3	22.1	28.9	35.6	39.4	43.3	41.4
92.5°	26.0	37.3	44.4	55.8	64.1	71.0	74.1	73.7
95°	59.6	75.0	89.4	102.9	116.4	126.0	131.8	129.8
97.5°	94.6	119.5	137.9	156.0	171.0	180.0	185.8	189.7
100°	119.3	143.3	170.2	187.6	204.9	215.4	225.1	228.9
102.5°	149.3	169.5	196.4	219.1	237.9	249.3	257.4	261.2
105°	191.4	216.4	239.5	263.5	283.7	298.2	306.8	309.7
107.5°	232.4	259.9	282.6	307.4	326.0	342.0	352.6	358.8
110°	257.8	287.6	316.4	336.6	356.8	371.3	381.8	385.7

TEST NUMBER: P709349

CATALOG NUMBER: DL2W-WB-M-075U-050D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	283.9	314.5	344.9	367.4	387.6	402.0	414.1	419.5
115°	317.4	351.1	384.7	414.5	432.8	446.3	454.9	459.7
117.5°	351.6	386.3	417.8	449.0	469.0	479.4	483.4	486.9
120°	373.2	407.8	438.6	467.4	490.5	504.0	508.8	510.7
122.5°	391.6	425.5	457.8	485.1	507.4	524.0	531.9	533.8
125°	417.4	452.0	484.7	510.7	533.8	550.1	558.8	563.6
127.5°	441.8	473.6	508.2	536.3	557.5	572.3	580.7	584.6
130°	458.8	486.7	521.3	550.1	571.3	587.7	595.4	599.2
132.5°	476.5	498.2	531.3	561.7	583.6	598.4	606.9	610.7
135°	503.0	515.5	543.4	575.2	598.2	612.7	620.4	624.2
137.5°	531.3	536.1	554.0	582.8	606.9	622.1	629.0	631.5
140°	552.1	549.2	561.7	586.7	610.7	625.2	632.9	633.8
142.5°	573.6	566.9	571.7	591.3	612.3	626.7	634.4	636.1
145°	608.8	594.4	589.6	601.1	615.5	629.0	635.7	637.7
147.5°	644.2	625.6	612.1	615.7	623.2	632.1	638.6	640.0
150°	670.4	646.3	629.0	628.1	630.9	636.7	642.5	641.5
152.5°	695.0	670.2	648.3	642.7	642.5	645.2	647.9	647.7
155°	734.8	706.9	681.0	670.4	664.6	662.7	662.7	661.7
157.5°	772.9	744.4	716.9	702.1	693.5	688.8	687.5	685.4
160°	798.3	767.5	741.5	725.2	716.5	708.8	706.0	703.1
162.5°	822.1	793.7	764.6	749.0	739.6	732.7	729.8	725.4
165°	855.0	832.0	802.1	785.8	775.2	769.4	765.6	761.7
167.5°	883.3	864.1	839.6	821.8	814.8	808.3	804.6	797.7
170°	900.2	884.9	862.7	846.4	842.5	836.8	830.0	822.3
172.5°	914.9	902.5	882.7	871.8	867.9	862.2	860.0	853.9
175°	932.9	926.2	911.8	903.1	903.1	902.2	899.3	893.5
177.5°	946.8	944.5	936.0	931.4	934.5	934.5	933.7	928.3
180°	952.2	952.2	952.2	952.2	952.2	952.2	952.2	952.2

(END OF REPORT)