

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1427770

Luminaire Tested: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1427770
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-20)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9359.1 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	87	92	88	85	81	76	73	71	65	63	61	54	53	52	47				
2	90	82	76	71	83	77	71	67	66	62	58	57	54	51	48	45	43	39				
3	82	72	65	59	76	67	61	55	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	52	47	52	46	42	44	40	36	37	34	32	28				
5	69	57	48	42	64	53	46	40	46	40	36	40	35	32	34	30	27	24				
6	63	51	43	37	59	48	40	35	42	36	31	36	31	28	31	27	24	21				
7	59	46	38	32	54	43	36	31	38	32	27	33	28	24	28	24	21	19				
8	54	42	34	28	50	39	32	27	34	28	24	30	25	22	26	22	19	17				
9	51	38	30	25	47	36	29	24	31	26	22	27	23	19	24	20	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30197	30197	30197	30197
5°	30013	30355	30013	30355
10°	29907	30251	29907	30251
15°	29743	30117	29743	30117
20°	29554	29848	29554	29848
25°	29236	29494	29236	29494
30°	28925	29123	28925	29123
35°	28556	28737	28556	28737
40°	28232	28314	28232	28314
45°	27818	27818	27818	27818
50°	27261	27326	27261	27326
55°	26620	26657	26620	26657
60°	25901	25901	25901	25901
65°	25058	24958	25058	24958
70°	23877	23627	23877	23627
75°	22264	21771	22264	21771
80°	19842	18856	19842	18856
85°	15857	13412	15857	13412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°
 Vertical Angle: 45°
 Luminance: 28005 cd/sqm

TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	1.9
10°-20°	505.6	5.4
20°-30°	761.1	8.1
30°-40°	910.2	9.7
40°-50°	939.9	10.0
50°-60°	847.7	9.1
60°-70°	649.4	6.9
70°-80°	375.3	4.0
80°-90°	103.3	1.1
90°-100°	111.5	1.2
100°-110°	325.1	3.5
110°-120°	530.5	5.7
120°-130°	673.2	7.2
130°-140°	720.3	7.7
140°-150°	672.6	7.2
150°-160°	553.5	5.9
160°-170°	371.2	4.0
170°-180°	131.8	1.4
0°-30°	1443.7	15.4
0°-40°	2353.9	25.2
0°-60°	4141.5	44.3
0°-90°	5269.4	56.3
90°-120°	967.1	10.3
90°-150°	3033.2	32.4
90°-180°	4090.0	43.7
0°-180°	9359.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1870	1870	1870	1870	1870	
5°	1852	1873	1852	1873	1852	176
15°	1779	1802	1779	1802	1779	502
25°	1641	1656	1641	1656	1641	756
35°	1449	1458	1449	1458	1449	907
45°	1218	1218	1218	1218	1218	939
55°	946	947	946	947	946	845
65°	656	653	656	653	656	648
75°	357	349	357	349	357	378
85°	86	72	86	72	86	100
90°	4	31	4	61	4	7
95°	44	32	44	191	44	53
105°	207	331	207	456	207	220
115°	396	549	396	676	396	390
125°	586	870	586	829	586	524
135°	796	1139	796	918	796	616
145°	1017	1313	1017	938	1017	636
155°	1208	1426	1208	973	1208	555
165°	1336	1487	1336	1120	1336	376
175°	1396	1456	1396	1314	1396	132
180°	1401	1401	1401	1401	1401	



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1860.8	1869.7	1878.6	1874.8	1866.9	1863.8	1865.7	1867.3	1868.3	1869.2	1868.3
5°	1851.8	1863.5	1875.2	1871.1	1861.8	1857.7	1858.8	1861.2	1867.0	1872.9	1867.0
7.5°	1836.8	1848.5	1860.2	1856.5	1847.6	1843.8	1845.2	1847.8	1853.9	1860.0	1853.9
10°	1824.2	1835.9	1847.6	1843.5	1834.1	1830.6	1832.9	1835.9	1840.5	1845.2	1840.5
12.5°	1808.4	1820.1	1831.8	1828.4	1819.9	1816.4	1817.8	1820.2	1825.3	1830.5	1825.3
15°	1779.4	1791.1	1802.8	1799.6	1791.4	1788.2	1789.9	1792.4	1797.1	1801.8	1797.1
17.5°	1744.3	1755.3	1766.4	1763.4	1755.8	1753.0	1755.0	1757.5	1761.6	1765.7	1761.6
20°	1720.1	1730.6	1741.2	1738.1	1730.5	1727.0	1727.6	1729.0	1733.1	1737.2	1733.1
22.5°	1690.6	1701.1	1711.7	1709.0	1701.8	1697.6	1696.3	1696.6	1701.6	1706.7	1701.6
25°	1641.1	1651.6	1662.2	1660.0	1653.5	1649.4	1647.7	1647.4	1651.5	1655.6	1651.5
27.5°	1589.5	1598.2	1607.0	1605.2	1599.8	1596.5	1595.3	1595.2	1598.1	1601.0	1598.1
30°	1551.5	1560.3	1569.1	1566.9	1561.0	1557.5	1556.4	1556.2	1559.1	1562.1	1559.1
32.5°	1511.5	1519.8	1528.1	1525.1	1518.3	1514.8	1514.6	1515.2	1518.6	1522.0	1518.6
35°	1448.8	1455.8	1462.8	1459.8	1453.3	1450.4	1451.0	1452.2	1455.1	1458.0	1455.1
37.5°	1385.8	1391.2	1396.6	1393.5	1387.5	1384.5	1384.3	1384.9	1387.3	1389.8	1387.3
40°	1339.5	1345.3	1351.2	1347.8	1341.4	1337.9	1337.3	1337.6	1340.5	1343.4	1340.5
42.5°	1292.1	1296.5	1301.0	1297.9	1292.4	1289.9	1290.2	1290.9	1292.4	1293.9	1292.4
45°	1218.3	1222.4	1226.5	1223.6	1218.3	1215.7	1215.7	1216.0	1217.1	1218.3	1217.1
47.5°	1141.1	1144.3	1147.4	1145.2	1141.1	1138.7	1138.0	1137.9	1139.8	1141.6	1139.8
50°	1085.3	1089.4	1093.5	1091.4	1087.3	1084.7	1083.5	1083.2	1085.6	1087.9	1085.6
52.5°	1030.5	1035.1	1039.6	1037.7	1033.6	1030.7	1029.1	1028.3	1030.2	1032.1	1030.2
55°	945.7	950.9	956.2	954.9	951.4	948.4	946.1	944.6	945.8	947.0	945.8
57.5°	859.0	864.2	869.3	868.3	865.3	862.3	859.5	857.8	859.5	861.1	859.5
60°	802.1	806.8	811.5	810.0	806.5	803.6	801.2	799.8	800.9	802.1	800.9
62.5°	744.2	748.8	753.5	751.7	747.7	744.6	742.2	740.8	741.9	743.1	741.9
65°	655.9	660.0	664.1	662.5	659.0	656.1	653.7	652.1	652.7	653.3	652.7
67.5°	566.9	570.4	573.9	572.2	568.8	565.4	562.0	559.7	560.7	561.6	560.7
70°	505.8	509.3	512.8	511.5	508.5	505.6	502.7	500.5	500.5	500.5	500.5
72.5°	446.8	449.8	452.8	451.1	447.7	444.7	442.3	440.4	440.4	440.4	440.4
75°	356.9	358.7	360.4	359.6	357.8	355.5	352.5	350.2	349.6	349.0	349.6
77.5°	270.3	270.3	270.3	268.6	266.4	264.1	261.9	260.1	259.4	258.7	259.4
80°	213.4	213.4	213.4	212.1	210.3	208.5	206.8	205.2	204.0	202.8	204.0
82.5°	160.7	159.7	158.8	157.3	155.5	153.3	150.6	148.9	150.0	151.2	150.0
85°	85.6	84.4	83.3	81.7	79.9	77.9	75.5	73.6	73.0	72.4	73.0
87.5°	27.2	27.4	27.9	27.7	27.2	25.8	23.9	22.7	22.5	22.0	22.5
90°	4.2	9.9	17.0	22.6	26.9	28.3	28.3	29.7	31.1	31.1	31.1
92.5°	15.6	24.6	24.9	24.9	30.3	32.8	35.1	35.4	36.8	36.8	36.8
95°	43.9	48.1	72.2	70.7	48.1	38.2	32.5	32.5	32.5	32.5	32.5
97.5°	83.8	90.0	93.9	125.9	133.0	128.5	104.7	88.0	78.7	74.4	78.7
100°	118.8	121.7	130.2	131.6	166.9	200.9	183.9	162.7	155.6	151.4	155.6
102.5°	153.9	155.6	168.6	174.6	182.8	202.0	260.9	254.4	249.6	248.7	249.6
105°	206.6	208.0	232.0	243.3	249.0	249.0	247.6	275.9	321.2	331.1	321.2
107.5°	262.9	269.4	297.7	328.0	334.5	336.2	328.8	324.6	322.9	324.0	322.9
110°	301.4	311.3	345.2	383.4	393.3	396.1	393.3	389.1	386.2	386.2	386.2



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	338.7	353.1	391.6	435.5	452.2	460.7	454.4	451.3	448.5	450.8	448.5
115°	396.1	417.4	468.3	513.6	547.5	551.8	550.4	550.4	548.9	548.9	548.9
117.5°	449.3	483.3	540.5	593.1	632.4	643.7	649.4	647.7	646.0	648.8	646.0
120°	486.7	526.3	591.4	650.8	689.0	706.0	711.6	708.8	711.6	708.8	711.6
122.5°	526.3	575.0	638.9	700.6	745.6	764.8	771.6	772.2	772.8	771.1	772.8
125°	585.7	645.2	720.1	783.8	830.5	853.1	858.8	860.2	863.0	870.1	863.0
127.5°	645.7	713.1	795.4	856.8	904.6	932.1	940.8	944.0	949.9	953.0	949.9
130°	687.6	764.0	847.5	905.5	952.2	981.9	997.4	1001.7	1008.8	1007.3	1008.8
132.5°	731.7	811.5	896.1	956.4	999.7	1031.7	1045.0	1057.1	1059.7	1061.7	1059.7
135°	796.5	882.8	967.7	1027.2	1068.2	1099.3	1116.3	1127.6	1134.7	1138.9	1134.7
137.5°	864.7	955.8	1037.3	1090.3	1131.6	1158.4	1177.7	1189.6	1196.9	1200.3	1196.9
140°	911.1	998.9	1078.1	1133.3	1170.0	1196.9	1213.9	1228.1	1236.5	1236.5	1236.5
142.5°	955.3	1041.9	1118.8	1174.0	1206.3	1230.9	1249.0	1259.7	1269.4	1269.4	1269.4
145°	1017.2	1103.6	1174.3	1229.5	1256.4	1279.0	1298.8	1307.3	1312.9	1312.9	1312.9
147.5°	1082.0	1158.4	1223.0	1275.9	1298.5	1325.1	1340.7	1347.5	1354.5	1351.4	1354.5
150°	1120.5	1191.3	1253.5	1303.0	1325.7	1351.1	1366.7	1372.4	1379.4	1375.2	1379.4
152.5°	1157.9	1225.2	1281.8	1327.9	1347.2	1372.6	1390.5	1396.1	1400.9	1397.8	1400.9
155°	1208.2	1267.7	1320.0	1362.5	1379.4	1403.5	1420.5	1427.5	1433.2	1426.1	1433.2
157.5°	1253.2	1304.5	1350.0	1389.1	1407.2	1427.8	1443.7	1452.4	1458.1	1455.0	1458.1
160°	1280.4	1327.1	1368.1	1404.9	1421.9	1440.3	1457.3	1467.2	1472.8	1468.6	1472.8
162.5°	1303.0	1345.2	1384.0	1417.4	1432.1	1448.2	1468.6	1477.3	1483.0	1477.6	1483.0
165°	1335.6	1369.5	1403.5	1431.8	1444.5	1457.3	1478.5	1488.4	1492.6	1487.0	1492.6
167.5°	1360.2	1386.2	1413.7	1438.0	1447.4	1459.8	1481.0	1489.2	1494.6	1487.5	1494.6
170°	1373.8	1396.4	1420.5	1440.3	1447.4	1458.7	1479.9	1487.0	1491.2	1484.1	1491.2
172.5°	1385.1	1402.1	1421.6	1439.1	1442.8	1451.9	1472.0	1479.0	1482.2	1476.2	1482.2
175°	1396.4	1406.3	1420.5	1431.8	1430.4	1436.0	1453.0	1458.7	1464.3	1455.8	1464.3
177.5°	1401.8	1406.3	1410.8	1417.6	1413.1	1413.1	1425.6	1429.0	1430.1	1425.6	1430.1
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1867.3	1865.7	1863.8	1866.9	1874.8	1878.6	1869.7	1860.8	1869.7	1878.6	1874.8
5°	1861.2	1858.8	1857.7	1861.8	1871.1	1875.2	1863.5	1851.8	1863.5	1875.2	1871.1
7.5°	1847.8	1845.2	1843.8	1847.6	1856.5	1860.2	1848.5	1836.8	1848.5	1860.2	1856.5
10°	1835.9	1832.9	1830.6	1834.1	1843.5	1847.6	1835.9	1824.2	1835.9	1847.6	1843.5
12.5°	1820.2	1817.8	1816.4	1819.9	1828.4	1831.8	1820.1	1808.4	1820.1	1831.8	1828.4
15°	1792.4	1789.9	1788.2	1791.4	1799.6	1802.8	1791.1	1779.4	1791.1	1802.8	1799.6
17.5°	1757.5	1755.0	1753.0	1755.8	1763.4	1766.4	1755.3	1744.3	1755.3	1766.4	1763.4
20°	1729.0	1727.6	1727.0	1730.5	1738.1	1741.2	1730.6	1720.1	1730.6	1741.2	1738.1
22.5°	1696.6	1696.3	1697.6	1701.8	1709.0	1711.7	1701.1	1690.6	1701.1	1711.7	1709.0
25°	1647.4	1647.7	1649.4	1653.5	1660.0	1662.2	1651.6	1641.1	1651.6	1662.2	1660.0
27.5°	1595.2	1595.3	1596.5	1599.8	1605.2	1607.0	1598.2	1589.5	1598.2	1607.0	1605.2
30°	1556.2	1556.4	1557.5	1561.0	1566.9	1569.1	1560.3	1551.5	1560.3	1569.1	1566.9
32.5°	1515.2	1514.6	1514.8	1518.3	1525.1	1528.1	1519.8	1511.5	1519.8	1528.1	1525.1
35°	1452.2	1451.0	1450.4	1453.3	1459.8	1462.8	1455.8	1448.8	1455.8	1462.8	1459.8
37.5°	1384.9	1384.3	1384.5	1387.5	1393.5	1396.6	1391.2	1385.8	1391.2	1396.6	1393.5
40°	1337.6	1337.3	1337.9	1341.4	1347.8	1351.2	1345.3	1339.5	1345.3	1351.2	1347.8
42.5°	1290.9	1290.2	1289.9	1292.4	1297.9	1301.0	1296.5	1292.1	1296.5	1301.0	1297.9
45°	1216.0	1215.7	1215.7	1218.3	1223.6	1226.5	1222.4	1218.3	1222.4	1226.5	1223.6
47.5°	1137.9	1138.0	1138.7	1141.1	1145.2	1147.4	1144.3	1141.1	1144.3	1147.4	1145.2
50°	1083.2	1083.5	1084.7	1087.3	1091.4	1093.5	1089.4	1085.3	1089.4	1093.5	1091.4
52.5°	1028.3	1029.1	1030.7	1033.6	1037.7	1039.6	1035.1	1030.5	1035.1	1039.6	1037.7
55°	944.6	946.1	948.4	951.4	954.9	956.2	950.9	945.7	950.9	956.2	954.9
57.5°	857.8	859.5	862.3	865.3	868.3	869.3	864.2	859.0	864.2	869.3	868.3
60°	799.8	801.2	803.6	806.5	810.0	811.5	806.8	802.1	806.8	811.5	810.0
62.5°	740.8	742.2	744.6	747.7	751.7	753.5	748.8	744.2	748.8	753.5	751.7
65°	652.1	653.7	656.1	659.0	662.5	664.1	660.0	655.9	660.0	664.1	662.5
67.5°	559.7	562.0	565.4	568.8	572.2	573.9	570.4	566.9	570.4	573.9	572.2
70°	500.5	502.7	505.6	508.5	511.5	512.8	509.3	505.8	509.3	512.8	511.5
72.5°	440.4	442.3	444.7	447.7	451.1	452.8	449.8	446.8	449.8	452.8	451.1
75°	350.2	352.5	355.5	357.8	359.6	360.4	358.7	356.9	358.7	360.4	359.6
77.5°	260.1	261.9	264.1	266.4	268.6	270.3	270.3	270.3	270.3	270.3	268.6
80°	205.2	206.8	208.5	210.3	212.1	213.4	213.4	213.4	213.4	213.4	212.1
82.5°	148.9	150.6	153.3	155.5	157.3	158.8	159.7	160.7	159.7	158.8	157.3
85°	73.6	75.5	77.9	79.9	81.7	83.3	84.4	85.6	84.4	83.3	81.7
87.5°	22.7	23.9	25.8	27.2	27.7	27.9	27.4	27.2	27.4	27.6	28.3
90°	29.7	28.3	28.3	26.9	22.6	17.0	9.9	4.2	9.9	15.6	25.5
92.5°	35.4	35.1	32.8	30.3	24.9	24.9	24.6	15.6	26.9	38.2	54.9
95°	32.5	32.5	38.2	48.1	70.7	72.2	48.1	43.9	62.3	87.7	110.4
97.5°	88.0	104.7	128.5	133.0	125.9	93.9	90.0	83.8	114.0	139.2	175.7
100°	162.7	183.9	200.9	166.9	131.6	130.2	121.7	118.8	151.4	175.4	210.8
102.5°	254.4	260.9	202.0	182.8	174.6	168.6	155.6	153.9	186.5	219.6	249.3
105°	275.9	247.6	249.0	249.0	243.3	232.0	208.0	206.6	243.3	281.5	318.3
107.5°	324.6	328.8	336.2	334.5	328.0	297.7	269.4	262.9	296.0	341.8	382.3
110°	389.1	393.3	396.1	393.3	383.4	345.2	311.3	301.4	331.1	379.2	423.0



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	451.3	454.4	460.7	452.2	435.5	391.6	353.1	338.7	368.4	417.7	462.6
115°	550.4	550.4	551.8	547.5	513.6	468.3	417.4	396.1	421.6	466.9	516.4
117.5°	647.7	649.4	643.7	632.4	593.1	540.5	483.3	449.3	469.4	517.3	568.2
120°	708.8	711.6	706.0	689.0	650.8	591.4	526.3	486.7	502.3	548.9	599.9
122.5°	772.2	771.6	764.8	745.6	700.6	638.9	575.0	526.3	532.8	576.1	625.9
125°	860.2	858.8	853.1	830.5	783.8	720.1	645.2	585.7	577.2	614.0	665.0
127.5°	944.0	940.8	932.1	904.6	856.8	795.4	713.1	645.7	626.8	650.0	696.7
130°	1001.7	997.4	981.9	952.2	905.5	847.5	764.0	687.6	660.7	674.9	715.9
132.5°	1057.1	1045.0	1031.7	999.7	956.4	896.1	811.5	731.7	694.7	700.9	732.9
135°	1127.6	1116.3	1099.3	1068.2	1027.2	967.7	882.8	796.5	745.6	739.9	758.3
137.5°	1189.6	1177.7	1158.4	1131.6	1090.3	1037.3	955.8	864.7	800.5	781.5	788.6
140°	1228.1	1213.9	1196.9	1170.0	1133.3	1078.1	998.9	911.1	839.0	812.1	807.9
142.5°	1259.7	1249.0	1230.9	1206.3	1174.0	1118.8	1041.9	955.3	878.6	843.8	833.9
145°	1307.3	1298.8	1279.0	1256.4	1229.5	1174.3	1103.6	1017.2	940.8	895.6	874.4
147.5°	1347.5	1340.7	1325.1	1298.5	1275.9	1223.0	1158.4	1082.0	1003.7	947.6	920.2
150°	1372.4	1366.7	1351.1	1325.7	1303.0	1253.5	1191.3	1120.5	1045.5	986.1	950.8
152.5°	1396.1	1390.5	1372.6	1347.2	1327.9	1281.8	1225.2	1157.9	1081.8	1022.3	985.8
155°	1427.5	1420.5	1403.5	1379.4	1362.5	1320.0	1267.7	1208.2	1143.2	1080.9	1039.9
157.5°	1452.4	1443.7	1427.8	1407.2	1389.1	1350.0	1304.5	1253.2	1196.4	1136.9	1095.1
160°	1467.2	1457.3	1440.3	1421.9	1404.9	1368.1	1327.1	1280.4	1228.1	1174.3	1129.0
162.5°	1477.3	1468.6	1448.2	1432.1	1417.4	1384.0	1345.2	1303.0	1256.4	1209.4	1167.5
165°	1488.4	1478.5	1457.3	1444.5	1431.8	1403.5	1369.5	1335.6	1296.0	1257.8	1223.8
167.5°	1489.2	1481.0	1459.8	1447.4	1438.0	1413.7	1386.2	1360.2	1329.4	1299.4	1271.1
170°	1487.0	1479.9	1458.7	1447.4	1440.3	1420.5	1396.4	1373.8	1349.7	1324.3	1301.6
172.5°	1479.0	1472.0	1451.9	1442.8	1439.1	1421.6	1402.1	1385.1	1364.4	1345.8	1327.7
175°	1458.7	1453.0	1436.0	1430.4	1431.8	1420.5	1406.3	1396.4	1383.7	1372.4	1362.5
177.5°	1429.0	1425.6	1413.1	1413.1	1417.6	1410.8	1406.3	1401.8	1396.1	1392.7	1389.3
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3	1870.3
2.5°	1866.9	1863.8	1865.7	1867.3	1868.3	1869.2	1868.3	1867.3	1865.7	1863.8	1866.9
5°	1861.8	1857.7	1858.8	1861.2	1867.0	1872.9	1867.0	1861.2	1858.8	1857.7	1861.8
7.5°	1847.6	1843.8	1845.2	1847.8	1853.9	1860.0	1853.9	1847.8	1845.2	1843.8	1847.6
10°	1834.1	1830.6	1832.9	1835.9	1840.5	1845.2	1840.5	1835.9	1832.9	1830.6	1834.1
12.5°	1819.9	1816.4	1817.8	1820.2	1825.3	1830.5	1825.3	1820.2	1817.8	1816.4	1819.9
15°	1791.4	1788.2	1789.9	1792.4	1797.1	1801.8	1797.1	1792.4	1789.9	1788.2	1791.4
17.5°	1755.8	1753.0	1755.0	1757.5	1761.6	1765.7	1761.6	1757.5	1755.0	1753.0	1755.8
20°	1730.5	1727.0	1727.6	1729.0	1733.1	1737.2	1733.1	1729.0	1727.6	1727.0	1730.5
22.5°	1701.8	1697.6	1696.3	1696.6	1701.6	1706.7	1701.6	1696.6	1696.3	1697.6	1701.8
25°	1653.5	1649.4	1647.7	1647.4	1651.5	1655.6	1651.5	1647.4	1647.7	1649.4	1653.5
27.5°	1599.8	1596.5	1595.3	1595.2	1598.1	1601.0	1598.1	1595.2	1595.3	1596.5	1599.8
30°	1561.0	1557.5	1556.4	1556.2	1559.1	1562.1	1559.1	1556.2	1556.4	1557.5	1561.0
32.5°	1518.3	1514.8	1514.6	1515.2	1518.6	1522.0	1518.6	1515.2	1514.6	1514.8	1518.3
35°	1453.3	1450.4	1451.0	1452.2	1455.1	1458.0	1455.1	1452.2	1451.0	1450.4	1453.3
37.5°	1387.5	1384.5	1384.3	1384.9	1387.3	1389.8	1387.3	1384.9	1384.3	1384.5	1387.5
40°	1341.4	1337.9	1337.3	1337.6	1340.5	1343.4	1340.5	1337.6	1337.3	1337.9	1341.4
42.5°	1292.4	1289.9	1290.2	1290.9	1292.4	1293.9	1292.4	1290.9	1290.2	1289.9	1292.4
45°	1218.3	1215.7	1215.7	1216.0	1217.1	1218.3	1217.1	1216.0	1215.7	1215.7	1218.3
47.5°	1141.1	1138.7	1138.0	1137.9	1139.8	1141.6	1139.8	1137.9	1138.0	1138.7	1141.1
50°	1087.3	1084.7	1083.5	1083.2	1085.6	1087.9	1085.6	1083.2	1083.5	1084.7	1087.3
52.5°	1033.6	1030.7	1029.1	1028.3	1030.2	1032.1	1030.2	1028.3	1029.1	1030.7	1033.6
55°	951.4	948.4	946.1	944.6	945.8	947.0	945.8	944.6	946.1	948.4	951.4
57.5°	865.3	862.3	859.5	857.8	859.5	861.1	859.5	857.8	859.5	862.3	865.3
60°	806.5	803.6	801.2	799.8	800.9	802.1	800.9	799.8	801.2	803.6	806.5
62.5°	747.7	744.6	742.2	740.8	741.9	743.1	741.9	740.8	742.2	744.6	747.7
65°	659.0	656.1	653.7	652.1	652.7	653.3	652.7	652.1	653.7	656.1	659.0
67.5°	568.8	565.4	562.0	559.7	560.7	561.6	560.7	559.7	562.0	565.4	568.8
70°	508.5	505.6	502.7	500.5	500.5	500.5	500.5	500.5	502.7	505.6	508.5
72.5°	447.7	444.7	442.3	440.4	440.4	440.4	440.4	440.4	442.3	444.7	447.7
75°	357.8	355.5	352.5	350.2	349.6	349.0	349.6	350.2	352.5	355.5	357.8
77.5°	266.4	264.1	261.9	260.1	259.4	258.7	259.4	260.1	261.9	264.1	266.4
80°	210.3	208.5	206.8	205.2	204.0	202.8	204.0	205.2	206.8	208.5	210.3
82.5°	155.5	153.3	150.6	148.9	150.0	151.2	150.0	148.9	150.6	153.3	155.5
85°	79.9	77.9	75.5	73.6	73.0	72.4	73.0	73.6	75.5	77.9	79.9
87.5°	28.3	28.6	28.7	28.3	29.0	28.0	29.0	28.3	28.7	28.6	28.3
90°	32.5	42.4	52.3	58.0	63.7	60.8	63.7	58.0	52.3	42.4	32.5
92.5°	65.4	82.1	94.2	104.4	108.9	108.4	108.9	104.4	94.2	82.1	65.4
95°	131.6	151.4	171.2	185.3	193.8	191.0	193.8	185.3	171.2	151.4	131.6
97.5°	202.9	229.5	251.6	264.9	273.3	279.0	273.3	264.9	251.6	229.5	202.9
100°	250.4	275.9	301.4	316.9	331.1	336.7	331.1	316.9	301.4	275.9	250.4
102.5°	288.9	322.3	350.0	366.7	378.6	384.3	378.6	366.7	350.0	322.3	288.9
105°	352.3	387.7	417.4	438.6	451.3	455.6	451.3	438.6	417.4	387.7	352.3
107.5°	415.7	452.2	479.6	503.1	518.7	527.7	518.7	503.1	479.6	452.2	415.7
110°	465.5	495.2	524.9	546.1	561.7	567.3	561.7	546.1	524.9	495.2	465.5



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	507.4	540.5	570.2	591.4	609.2	617.1	609.2	591.4	570.2	540.5	507.4
115°	565.9	609.8	636.7	656.5	669.2	676.3	669.2	656.5	636.7	609.8	565.9
117.5°	614.6	660.4	689.9	705.1	711.1	716.2	711.1	705.1	689.9	660.4	614.6
120°	645.2	687.6	721.6	741.4	748.4	751.3	748.4	741.4	721.6	687.6	645.2
122.5°	673.4	713.6	746.5	770.8	782.4	785.2	782.4	770.8	746.5	713.6	673.4
125°	713.1	751.3	785.2	809.3	822.0	829.1	822.0	809.3	785.2	751.3	713.1
127.5°	747.6	788.9	820.0	841.8	854.3	859.9	854.3	841.8	820.0	788.9	747.6
130°	766.8	809.3	840.4	864.4	875.8	881.4	875.8	864.4	840.4	809.3	766.8
132.5°	781.5	826.2	858.5	880.3	892.7	898.4	892.7	880.3	858.5	826.2	781.5
135°	799.4	846.1	880.0	901.2	912.6	918.2	912.6	901.2	880.0	846.1	799.4
137.5°	814.9	857.4	892.7	915.1	925.3	929.0	925.3	915.1	892.7	857.4	814.9
140°	826.2	863.0	898.4	919.6	930.9	932.4	930.9	919.6	898.4	863.0	826.2
142.5°	841.0	869.8	900.7	921.9	933.2	935.8	933.2	921.9	900.7	869.8	841.0
145°	867.3	884.3	905.5	925.3	935.2	938.0	935.2	925.3	905.5	884.3	867.3
147.5°	900.4	905.8	916.8	929.8	939.4	941.4	939.4	929.8	916.8	905.8	900.4
150°	925.3	923.9	928.1	936.6	945.1	943.7	945.1	936.6	928.1	923.9	925.3
152.5°	953.6	945.4	945.1	949.1	953.0	952.7	953.0	949.1	945.1	945.4	953.6
155°	1001.7	986.1	977.6	974.8	974.8	973.4	974.8	974.8	977.6	986.1	1001.7
157.5°	1054.6	1032.8	1020.1	1013.3	1011.3	1008.2	1011.3	1013.3	1020.1	1032.8	1054.6
160°	1090.8	1066.8	1054.0	1042.7	1038.5	1034.2	1038.5	1042.7	1054.0	1066.8	1090.8
162.5°	1124.8	1101.9	1088.0	1077.8	1073.6	1067.1	1073.6	1077.8	1088.0	1101.9	1124.8
165°	1180.0	1155.9	1140.3	1131.8	1126.2	1120.5	1126.2	1131.8	1140.3	1155.9	1180.0
167.5°	1235.1	1208.8	1198.6	1189.0	1183.6	1173.4	1183.6	1189.0	1198.6	1208.8	1235.1
170°	1269.1	1245.0	1239.4	1230.9	1221.0	1209.7	1221.0	1230.9	1239.4	1245.0	1269.1
172.5°	1298.5	1282.4	1276.7	1268.2	1265.1	1256.1	1265.1	1268.2	1276.7	1282.4	1298.5
175°	1341.2	1328.5	1328.5	1327.1	1322.8	1314.4	1322.8	1327.1	1328.5	1328.5	1341.2
177.5°	1376.9	1370.1	1374.6	1374.6	1373.5	1365.6	1373.5	1374.6	1374.6	1370.1	1376.9
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1870.3	1870.3	1870.3	1870.3
2.5°	1874.8	1878.6	1869.7	1860.8
5°	1871.1	1875.2	1863.5	1851.8
7.5°	1856.5	1860.2	1848.5	1836.8
10°	1843.5	1847.6	1835.9	1824.2
12.5°	1828.4	1831.8	1820.1	1808.4
15°	1799.6	1802.8	1791.1	1779.4
17.5°	1763.4	1766.4	1755.3	1744.3
20°	1738.1	1741.2	1730.6	1720.1
22.5°	1709.0	1711.7	1701.1	1690.6
25°	1660.0	1662.2	1651.6	1641.1
27.5°	1605.2	1607.0	1598.2	1589.5
30°	1566.9	1569.1	1560.3	1551.5
32.5°	1525.1	1528.1	1519.8	1511.5
35°	1459.8	1462.8	1455.8	1448.8
37.5°	1393.5	1396.6	1391.2	1385.8
40°	1347.8	1351.2	1345.3	1339.5
42.5°	1297.9	1301.0	1296.5	1292.1
45°	1223.6	1226.5	1222.4	1218.3
47.5°	1145.2	1147.4	1144.3	1141.1
50°	1091.4	1093.5	1089.4	1085.3
52.5°	1037.7	1039.6	1035.1	1030.5
55°	954.9	956.2	950.9	945.7
57.5°	868.3	869.3	864.2	859.0
60°	810.0	811.5	806.8	802.1
62.5°	751.7	753.5	748.8	744.2
65°	662.5	664.1	660.0	655.9
67.5°	572.2	573.9	570.4	566.9
70°	511.5	512.8	509.3	505.8
72.5°	451.1	452.8	449.8	446.8
75°	359.6	360.4	358.7	356.9
77.5°	268.6	270.3	270.3	270.3
80°	212.1	213.4	213.4	213.4
82.5°	157.3	158.8	159.7	160.7
85°	81.7	83.3	84.4	85.6
87.5°	28.3	27.6	27.4	27.2
90°	25.5	15.6	9.9	4.2
92.5°	54.9	38.2	26.9	15.6
95°	110.4	87.7	62.3	43.9
97.5°	175.7	139.2	114.0	83.8
100°	210.8	175.4	151.4	118.8
102.5°	249.3	219.6	186.5	153.9
105°	318.3	281.5	243.3	206.6
107.5°	382.3	341.8	296.0	262.9
110°	423.0	379.2	331.1	301.4



TEST NUMBER: P1427770

CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	462.6	417.7	368.4	338.7
115°	516.4	466.9	421.6	396.1
117.5°	568.2	517.3	469.4	449.3
120°	599.9	548.9	502.3	486.7
122.5°	625.9	576.1	532.8	526.3
125°	665.0	614.0	577.2	585.7
127.5°	696.7	650.0	626.8	645.7
130°	715.9	674.9	660.7	687.6
132.5°	732.9	700.9	694.7	731.7
135°	758.3	739.9	745.6	796.5
137.5°	788.6	781.5	800.5	864.7
140°	807.9	812.1	839.0	911.1
142.5°	833.9	843.8	878.6	955.3
145°	874.4	895.6	940.8	1017.2
147.5°	920.2	947.6	1003.7	1082.0
150°	950.8	986.1	1045.5	1120.5
152.5°	985.8	1022.3	1081.8	1157.9
155°	1039.9	1080.9	1143.2	1208.2
157.5°	1095.1	1136.9	1196.4	1253.2
160°	1129.0	1174.3	1228.1	1280.4
162.5°	1167.5	1209.4	1256.4	1303.0
165°	1223.8	1257.8	1296.0	1335.6
167.5°	1271.1	1299.4	1329.4	1360.2
170°	1301.6	1324.3	1349.7	1373.8
172.5°	1327.7	1345.8	1364.4	1385.1
175°	1362.5	1372.4	1383.7	1396.4
177.5°	1389.3	1392.7	1396.1	1401.8
180°	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1427770
 CATALOG NUMBER: SQ2W-F-K-100U-125D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.26	21.20	21.16	22.12	23.29	20.18	21.11	21.08	22.03	23.21
	3H	22.06	22.90	22.97	23.83	25.03	21.95	22.79	22.86	23.72	24.93
	4H	22.76	23.55	23.68	24.49	25.70	22.64	23.44	23.57	24.37	25.58
	6H	23.20	23.93	24.13	24.87	26.10	23.06	23.79	23.99	24.73	25.95
	8H	23.36	24.06	24.30	25.02	26.24	23.20	23.90	24.15	24.86	26.08
	12H	23.45	24.11	24.40	25.06	26.31	23.27	23.93	24.22	24.89	26.13
4H	2H	20.85	21.64	21.78	22.58	23.79	20.78	21.58	21.72	22.51	23.72
	3H	22.88	23.54	23.82	24.51	25.73	22.79	23.45	23.73	24.41	25.64
	4H	23.70	24.30	24.65	25.26	26.51	23.58	24.19	24.54	25.15	26.40
	6H	24.25	24.78	25.22	25.76	27.01	24.11	24.64	25.08	25.62	26.87
	8H	24.47	24.96	25.44	25.94	27.20	24.31	24.80	25.28	25.78	27.04
	12H	24.59	25.03	25.57	26.02	27.29	24.40	24.84	25.39	25.84	27.11
8H	4H	23.95	24.44	24.91	25.41	26.68	23.85	24.34	24.82	25.32	26.58
	6H	24.64	25.04	25.63	26.06	27.33	24.51	24.91	25.50	25.93	27.19
	8H	24.94	25.30	25.95	26.31	27.59	24.79	25.15	25.79	26.15	27.43
	12H	25.13	25.45	26.14	26.45	27.77	24.94	25.26	25.94	26.26	27.58
12H	4H	23.94	24.39	24.93	25.38	26.65	23.85	24.29	24.84	25.29	26.56
	6H	24.69	25.05	25.69	26.05	27.34	24.56	24.92	25.57	25.93	27.21
	8H	25.03	25.34	26.03	26.34	27.67	24.88	25.19	25.88	26.19	27.52