

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709399

Luminaire Tested: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

Issue Date: 3/5/2020

Test Information

Test Method: LM-79-2019
Report Number: P709399
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-6, G3-2104-222-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8478.7 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27		
1	94	90	86	83	84	81	78	75	63	61	60	47	46	45	33	32	32	25		
2	86	80	74	70	77	72	67	63	57	54	51	43	41	39	30	29	28	23		
3	79	71	64	59	71	64	59	54	51	47	44	39	37	35	28	26	25	20		
4	73	63	56	51	65	57	51	47	46	42	39	35	33	31	25	24	23	19		
5	67	57	50	44	60	52	45	41	41	37	34	32	29	27	23	22	20	17		
6	62	51	44	39	56	47	40	36	38	33	30	29	26	24	22	20	19	15		
7	58	47	39	34	52	42	36	32	34	30	27	27	24	22	20	18	17	14		
8	54	42	35	30	48	39	33	28	31	27	24	25	22	20	19	17	15	13		
9	50	39	32	27	45	35	29	25	29	25	22	23	20	18	17	15	14	12		
10	47	36	29	25	42	33	27	23	27	22	19	21	18	16	16	14	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	23791	23791	23791	23791	23791
5°	24018	23803	24052	23803	24018
10°	24279	24128	24330	24128	24279
15°	24329	24495	24789	24495	24329
20°	23953	24430	24917	24430	23953
25°	23291	23802	24346	23802	23291
30°	21929	22565	23152	22565	21929
35°	19681	20408	20808	20408	19681
40°	16252	16737	17100	16737	16252
45°	9757	12085	10821	12085	9757
50°	3853	6664	4197	6664	3853
55°	2055	3023	2024	3023	2055
60°	888	1506	956	1506	888
65°	810	917	848	917	810
70°	798	854	850	854	798
75°	724	852	792	852	724
80°	688	790	790	790	688
85°	593	778	778	778	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
 Vertical Angle: 45°
 Luminance: 12166 cd/sqm

TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.1	1.7
10°-20°	414.0	4.9
20°-30°	613.0	7.2
30°-40°	635.0	7.5
40°-50°	381.7	4.5
50°-60°	91.1	1.1
60°-70°	24.9	0.3
70°-80°	13.9	0.2
80°-90°	13.1	0.2
90°-100°	166.8	2.0
100°-110°	487.2	5.7
110°-120°	797.3	9.4
120°-130°	1012.7	11.9
130°-140°	1084.1	12.8
140°-150°	1012.5	11.9
150°-160°	833.2	9.8
160°-170°	558.9	6.6
170°-180°	198.4	2.3
0°-30°	1168.1	13.8
0°-40°	1803.1	21.3
0°-60°	2275.9	26.8
0°-90°	2327.7	27.5
90°-120°	1451.2	17.1
90°-150°	4560.5	53.8
90°-180°	6151.0	72.5
0°-180°	8478.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1474	1474	1474	1474	1474	
5°	1482	1469	1484	1469	1482	141
15°	1456	1465	1483	1465	1456	409
25°	1307	1336	1367	1336	1307	597
35°	998	1035	1056	1035	998	615
45°	427	529	474	529	427	337
55°	73	107	72	107	73	70
65°	21	24	22	24	21	22
75°	12	14	13	14	12	13
85°	3	4	4	4	3	5
90°	44	41	7	57	93	21
95°	49	66	68	216	299	82
105°	497	371	314	555	686	460
115°	820	826	596	882	1010	812
125°	1306	1264	884	1103	1247	1156
135°	1710	1628	1200	1240	1381	1312
145°	1972	1909	1534	1318	1413	1235
155°	2146	2095	1822	1499	1463	991
165°	2237	2183	2011	1759	1687	631
175°	2189	2158	2103	2011	1976	210
180°	2108	2108	2108	2108	2108	

TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5
2.5°	1475.2	1476.7	1478.2	1474.0	1468.0	1467.6	1472.9	1477.4	1479.7	1481.9	1479.7
5°	1481.9	1482.9	1483.8	1477.7	1469.2	1468.1	1474.2	1479.3	1481.7	1484.0	1481.7
7.5°	1481.7	1483.1	1484.5	1479.6	1472.6	1471.6	1476.8	1481.0	1482.5	1484.0	1482.5
10°	1480.9	1482.3	1483.7	1478.8	1471.7	1471.7	1478.8	1484.0	1484.0	1484.0	1484.0
12.5°	1474.1	1476.3	1478.4	1475.1	1469.9	1472.2	1481.9	1488.7	1486.8	1484.9	1486.8
15°	1455.5	1458.8	1462.1	1462.5	1462.1	1468.7	1482.3	1491.5	1487.2	1483.0	1487.2
17.5°	1421.2	1425.7	1430.2	1434.1	1437.8	1449.0	1467.8	1480.3	1473.7	1467.1	1473.7
20°	1394.1	1397.9	1401.7	1407.9	1414.9	1428.8	1449.5	1463.4	1456.8	1450.2	1456.8
22.5°	1362.0	1366.1	1370.3	1376.3	1383.0	1397.4	1419.6	1434.5	1427.5	1420.6	1427.5
25°	1307.4	1311.2	1314.9	1321.5	1329.0	1343.1	1363.8	1377.9	1372.3	1366.6	1372.3
27.5°	1235.5	1239.6	1243.7	1250.1	1257.1	1269.6	1287.4	1300.2	1297.7	1295.1	1297.7
30°	1176.2	1181.9	1187.5	1195.6	1204.6	1216.1	1230.2	1240.9	1241.3	1241.8	1241.3
32.5°	1109.4	1116.9	1124.4	1132.7	1141.3	1152.0	1165.0	1174.6	1173.9	1173.3	1173.9
35°	998.5	1006.5	1014.5	1022.9	1031.3	1039.5	1047.5	1053.8	1054.7	1055.7	1054.7
37.5°	870.1	873.2	876.3	883.9	893.1	901.9	910.5	916.7	916.0	915.4	916.0
40°	771.1	771.6	772.1	779.6	789.4	798.8	807.8	814.1	812.7	811.3	812.7
42.5°	665.3	667.3	669.3	677.5	687.7	696.2	702.9	705.2	694.8	684.4	694.8
45°	427.3	462.1	496.9	514.4	526.2	532.3	532.8	526.5	500.2	473.9	500.2
47.5°	223.6	257.9	292.2	327.0	361.9	370.1	351.5	329.4	296.5	263.6	296.5
50°	153.4	165.1	176.9	214.7	261.3	269.3	238.7	210.4	188.8	167.1	188.8
52.5°	111.9	119.2	126.4	155.8	192.5	195.8	165.6	140.3	129.6	118.9	129.6
55°	73.0	74.9	76.7	89.9	106.8	108.0	93.4	81.3	76.6	71.9	76.6
57.5°	43.6	47.5	51.5	57.5	64.1	64.3	58.0	52.3	48.1	44.0	48.1
60°	27.5	30.3	33.1	39.1	46.2	47.1	42.0	37.1	33.4	29.6	33.4
62.5°	25.0	25.9	26.8	31.0	36.1	36.5	32.1	28.5	27.4	26.2	27.4
65°	21.2	21.6	22.1	22.9	23.9	24.1	23.6	23.2	22.7	22.2	22.7
67.5°	18.6	19.1	19.6	20.0	20.3	20.6	20.7	20.6	20.1	19.7	20.1
70°	16.9	17.4	17.9	18.0	18.0	18.2	18.7	18.9	18.5	18.0	18.5
72.5°	15.2	15.3	15.4	15.7	16.1	16.3	16.4	16.5	16.4	16.3	16.4
75°	11.6	12.1	12.6	13.0	13.5	13.8	13.8	13.6	13.2	12.7	13.2
77.5°	9.1	9.6	10.0	10.2	10.2	10.3	10.7	10.9	10.5	10.2	10.5
80°	7.4	7.9	8.3	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
82.5°	5.7	6.2	6.7	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
85°	3.2	3.6	4.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	9.7	9.9	9.7	9.6	9.7	9.7	8.5	6.8	4.9	3.2	4.9
90°	44.4	45.4	44.4	42.3	41.2	40.2	33.8	25.4	15.9	7.4	15.9
92.5°	54.5	53.9	53.7	51.6	49.7	44.4	36.4	36.4	37.0	23.5	39.5
95°	48.6	48.6	47.6	47.6	56.0	75.0	103.6	102.5	74.0	67.6	95.1
97.5°	112.9	113.1	127.7	158.3	184.1	197.6	184.3	138.4	135.9	130.6	170.6
100°	226.2	223.0	245.2	271.6	299.1	244.1	194.5	193.4	184.9	175.4	227.2
102.5°	359.7	372.6	381.3	381.5	303.3	271.2	261.2	252.6	234.8	228.7	279.6
105°	496.7	475.6	410.0	372.0	366.7	375.2	376.2	344.5	317.0	313.9	364.6
107.5°	487.4	480.0	484.9	494.4	502.8	503.7	490.6	444.7	402.9	396.7	441.1
110°	577.0	573.9	581.3	586.5	595.0	590.8	571.7	520.0	467.1	453.4	497.8

TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	670.0	676.2	675.9	685.5	688.0	682.9	652.1	593.5	532.2	510.9	553.6
115°	820.1	818.0	825.4	827.5	832.8	819.0	772.5	704.9	627.8	596.0	634.1
117.5°	972.5	966.1	966.1	978.0	974.0	945.2	897.9	817.6	730.9	678.5	707.4
120°	1066.3	1064.2	1064.2	1068.4	1065.3	1031.5	980.7	892.0	796.8	733.4	755.6
122.5°	1155.1	1163.1	1156.4	1158.9	1152.4	1119.4	1056.0	966.4	862.8	793.5	802.1
125°	1306.2	1297.8	1292.5	1290.4	1283.0	1246.0	1177.3	1080.1	968.0	883.5	871.9
127.5°	1423.5	1426.7	1420.6	1413.0	1398.6	1361.8	1291.6	1193.6	1076.7	970.2	944.6
130°	1508.1	1511.3	1506.0	1497.5	1476.4	1432.0	1368.6	1271.4	1151.9	1037.8	994.5
132.5°	1597.7	1595.0	1588.0	1569.4	1547.4	1505.5	1437.9	1346.6	1219.6	1098.7	1045.2
135°	1709.9	1711.0	1695.1	1676.1	1650.8	1604.3	1548.2	1458.4	1331.6	1200.5	1123.4
137.5°	1804.0	1802.3	1786.7	1770.8	1739.3	1698.9	1645.0	1559.9	1436.0	1301.6	1205.0
140°	1863.2	1863.2	1848.4	1828.3	1801.9	1760.7	1706.8	1623.3	1507.0	1367.5	1265.0
142.5°	1908.8	1909.7	1894.9	1879.9	1853.4	1817.3	1764.3	1684.1	1567.9	1439.4	1324.2
145°	1972.0	1976.3	1964.6	1951.9	1926.6	1891.7	1849.4	1767.0	1663.4	1534.5	1418.3
147.5°	2032.3	2036.5	2029.5	2016.4	1991.0	1954.7	1916.2	1841.4	1743.5	1628.6	1510.2
150°	2070.3	2074.5	2065.0	2054.5	2033.3	1995.3	1959.3	1885.4	1793.4	1687.7	1573.6
152.5°	2105.8	2110.0	2102.2	2090.0	2065.4	2028.2	1997.4	1925.9	1840.8	1744.4	1633.6
155°	2146.4	2155.9	2148.5	2136.9	2112.6	2077.7	2049.2	1983.6	1906.5	1822.0	1719.4
157.5°	2185.7	2196.1	2185.7	2174.7	2146.2	2116.8	2090.2	2029.9	1963.4	1890.9	1798.1
160°	2207.7	2217.2	2207.7	2195.0	2166.5	2137.9	2114.7	2058.7	1996.3	1929.8	1850.5
162.5°	2221.2	2231.6	2223.8	2209.4	2180.0	2154.0	2132.4	2081.5	2024.2	1963.6	1891.1
165°	2237.3	2248.9	2239.4	2222.5	2194.0	2172.8	2154.9	2109.4	2060.8	2011.1	1953.0
167.5°	2237.1	2250.4	2240.7	2229.5	2197.1	2180.9	2165.4	2128.4	2087.6	2048.1	2001.6
170°	2232.0	2243.6	2237.3	2227.8	2192.9	2179.2	2169.6	2136.9	2102.0	2069.3	2031.2
172.5°	2221.0	2231.8	2224.6	2215.1	2182.8	2171.6	2167.1	2140.3	2110.5	2085.3	2053.2
175°	2188.7	2203.5	2198.2	2189.7	2161.2	2154.9	2155.9	2137.9	2118.9	2103.1	2084.0
177.5°	2145.6	2154.9	2154.0	2146.4	2127.0	2128.6	2135.4	2124.4	2116.8	2110.9	2101.6
180°	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4

TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5
2.5°	1477.4	1472.9	1467.6	1468.0	1474.0	1478.2	1476.7	1475.2
5°	1479.3	1474.2	1468.1	1469.2	1477.7	1483.8	1482.9	1481.9
7.5°	1481.0	1476.8	1471.6	1472.6	1479.6	1484.5	1483.1	1481.7
10°	1484.0	1478.8	1471.7	1471.7	1478.8	1483.7	1482.3	1480.9
12.5°	1488.7	1481.9	1472.2	1469.9	1475.1	1478.4	1476.3	1474.1
15°	1491.5	1482.3	1468.7	1462.1	1462.5	1462.1	1458.8	1455.5
17.5°	1480.3	1467.8	1449.0	1437.8	1434.1	1430.2	1425.7	1421.2
20°	1463.4	1449.5	1428.8	1414.9	1407.9	1401.7	1397.9	1394.1
22.5°	1434.5	1419.6	1397.4	1383.0	1376.3	1370.3	1366.1	1362.0
25°	1377.9	1363.8	1343.1	1329.0	1321.5	1314.9	1311.2	1307.4
27.5°	1300.2	1287.4	1269.6	1257.1	1250.1	1243.7	1239.6	1235.5
30°	1240.9	1230.2	1216.1	1204.6	1195.6	1187.5	1181.9	1176.2
32.5°	1174.6	1165.0	1152.0	1141.3	1132.7	1124.4	1116.9	1109.4
35°	1053.8	1047.5	1039.5	1031.3	1022.9	1014.5	1006.5	998.5
37.5°	916.7	910.5	901.9	893.1	883.9	876.3	873.2	870.1
40°	814.1	807.8	798.8	789.4	779.6	772.1	771.6	771.1
42.5°	705.2	702.9	696.2	687.7	677.5	669.3	667.3	665.3
45°	526.5	532.8	532.3	526.2	514.4	496.9	462.1	427.3
47.5°	329.4	351.5	370.1	361.9	327.0	292.2	257.9	223.6
50°	210.4	238.7	269.3	261.3	214.7	176.9	165.1	153.4
52.5°	140.3	165.6	195.8	192.5	155.8	126.4	119.2	111.9
55°	81.3	93.4	108.0	106.8	89.9	76.7	74.9	73.0
57.5°	52.3	58.0	64.3	64.1	57.5	51.5	47.5	43.6
60°	37.1	42.0	47.1	46.2	39.1	33.1	30.3	27.5
62.5°	28.5	32.1	36.5	36.1	31.0	26.8	25.9	25.0
65°	23.2	23.6	24.1	23.9	22.9	22.1	21.6	21.2
67.5°	20.6	20.7	20.6	20.3	20.0	19.6	19.1	18.6
70°	18.9	18.7	18.2	18.0	18.0	17.9	17.4	16.9
72.5°	16.5	16.4	16.3	16.1	15.7	15.4	15.3	15.2
75°	13.6	13.8	13.8	13.5	13.0	12.6	12.1	11.6
77.5°	10.9	10.7	10.3	10.2	10.2	10.0	9.6	9.1
80°	8.5	8.5	8.5	8.5	8.5	8.3	7.9	7.4
82.5°	6.8	6.8	6.8	6.8	6.8	6.7	6.2	5.7
85°	4.2	4.2	4.2	4.2	4.2	4.1	3.6	3.2
87.5°	6.8	8.9	11.8	14.0	16.6	18.8	19.9	19.4
90°	25.4	35.9	50.7	62.4	77.1	89.8	95.1	93.0
92.5°	57.5	79.1	101.5	122.4	144.8	157.5	162.8	164.0
95°	133.2	163.8	199.7	231.4	258.9	279.0	284.3	299.1
97.5°	209.0	262.7	305.4	342.0	376.4	398.8	411.7	416.8
100°	267.4	320.2	373.1	412.2	453.4	472.4	490.4	503.0
102.5°	329.9	376.9	435.6	484.9	525.2	551.9	563.1	574.1
105°	423.8	477.7	528.4	582.3	624.6	658.4	681.6	685.9
107.5°	511.5	575.1	627.3	681.6	723.3	754.4	777.6	785.6
110°	570.7	635.1	697.5	740.8	788.4	821.1	840.2	855.0

TEST NUMBER: P709399

CATALOG NUMBER: DL2W-WB-M-150U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	624.8	693.5	761.8	816.9	859.4	892.2	913.7	921.8
115°	707.0	775.7	847.6	916.3	961.7	985.0	1000.8	1010.3
117.5°	779.9	854.8	922.4	992.1	1039.1	1063.4	1068.0	1075.6
120°	822.2	900.4	972.3	1033.6	1086.4	1114.9	1125.5	1129.7
122.5°	866.2	941.0	1011.2	1074.2	1125.3	1159.8	1177.1	1182.2
125°	926.8	1000.8	1070.6	1136.1	1183.6	1218.5	1237.5	1247.0
127.5°	979.9	1049.4	1122.8	1187.4	1234.2	1268.0	1288.5	1298.6
130°	1018.8	1079.0	1154.0	1219.6	1267.1	1300.9	1318.9	1327.4
132.5°	1056.0	1104.4	1178.6	1244.1	1294.2	1327.2	1345.1	1351.9
135°	1114.9	1143.5	1204.8	1274.5	1325.3	1357.0	1374.9	1381.3
137.5°	1178.8	1185.3	1227.2	1292.5	1344.5	1377.2	1392.9	1398.2
140°	1222.7	1217.5	1244.9	1300.9	1353.8	1386.5	1401.3	1406.6
142.5°	1270.9	1255.5	1267.8	1310.2	1357.2	1389.9	1405.6	1410.9
145°	1344.3	1315.7	1306.2	1329.5	1364.4	1391.8	1408.7	1413.0
147.5°	1428.0	1386.3	1356.1	1362.9	1380.2	1399.9	1413.8	1416.3
150°	1483.8	1432.0	1395.0	1390.8	1397.1	1410.9	1421.4	1421.4
152.5°	1539.6	1484.4	1437.3	1424.6	1422.5	1427.8	1434.9	1434.1
155°	1628.6	1564.1	1510.2	1486.9	1473.2	1469.0	1466.9	1462.6
157.5°	1714.4	1647.6	1587.1	1555.4	1538.1	1527.5	1522.5	1515.9
160°	1774.4	1702.5	1641.2	1605.3	1590.5	1571.5	1567.3	1555.6
162.5°	1821.7	1760.9	1695.3	1659.4	1639.5	1623.9	1618.0	1604.7
165°	1894.9	1842.0	1776.5	1741.6	1717.3	1703.6	1692.0	1686.7
167.5°	1959.8	1914.5	1857.7	1822.0	1809.5	1788.8	1779.0	1771.2
170°	1995.3	1959.3	1911.8	1876.9	1865.3	1850.5	1839.9	1830.4
172.5°	2025.7	2000.8	1956.6	1932.7	1921.9	1908.8	1900.8	1887.9
175°	2066.1	2050.2	2021.7	2000.6	2005.8	1993.2	1991.0	1976.3
177.5°	2094.8	2089.8	2070.3	2061.9	2072.0	2067.8	2066.9	2057.6
180°	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4

(END OF REPORT)