

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709408

Luminaire Tested: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

Issue Date: 3/5/2020


Test Information

Test Method: LM-79-2019
Report Number: P709408
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-6, G3-2104-222-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11912.9 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 104.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	99	95	92	89	91	88	86	83	75	73	71	62	61	60	51	50	49				44	
2	92	86	80	76	85	79	75	71	68	65	62	57	55	53	47	46	44				40	
3	85	77	71	66	78	72	66	62	61	58	54	52	49	47	43	42	40				36	
4	79	69	62	57	73	65	59	54	56	51	48	48	45	42	40	38	36				33	
5	73	63	56	50	67	59	52	48	51	46	43	44	40	38	37	35	33				30	
6	68	57	50	45	63	53	47	43	47	42	38	40	37	34	34	32	30				27	
7	63	52	45	40	59	49	43	38	43	38	34	37	34	31	32	29	27				25	
8	59	48	41	36	55	45	39	34	40	35	31	34	31	28	30	27	25				23	
9	55	44	37	33	51	41	35	31	37	32	28	32	28	26	28	25	23				21	
10	52	41	34	30	48	38	32	28	34	29	26	30	26	24	26	23	21				19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	59473	59473	59473	59473	59473
5°	60026	59373	59940	59373	60026
10°	60599	60096	60581	60096	60599
15°	60495	60887	61553	60887	60495
20°	59369	60596	61855	60596	59369
25°	57774	58945	60690	58945	57774
30°	54178	55849	57586	55849	54178
35°	48846	50424	51637	50424	48846
40°	39943	41454	42392	41454	39943
45°	24048	29938	26508	29938	24048
50°	9367	16631	10482	16631	9367
55°	5025	7537	5084	7537	5025
60°	2183	3726	2386	3726	2183
65°	2059	2279	2139	2279	2059
70°	1945	2146	2096	2146	1945
75°	1847	2049	2040	2049	1847
80°	1767	1976	1962	1976	1767
85°	1760	1778	1760	1778	1760

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
 Vertical Angle: 45°
 Luminance: 30150 cd/sqm

TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.0	3.0
10°-20°	1028.8	8.6
20°-30°	1520.9	12.8
30°-40°	1571.5	13.2
40°-50°	945.6	7.9
50°-60°	227.0	1.9
60°-70°	62.0	0.5
70°-80°	34.6	0.3
80°-90°	19.6	0.2
90°-100°	166.8	1.4
100°-110°	487.2	4.1
110°-120°	797.3	6.7
120°-130°	1012.7	8.5
130°-140°	1084.1	9.1
140°-150°	1012.5	8.5
150°-160°	833.2	7.0
160°-170°	558.9	4.7
170°-180°	198.4	1.7
0°-30°	2901.6	24.4
0°-40°	4473.1	37.5
0°-60°	5645.7	47.4
0°-90°	5761.9	48.4
90°-120°	1451.2	12.2
90°-150°	4560.5	38.3
90°-180°	6151.0	51.6
0°-180°	11912.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3684	3684	3684	3684	3684	
5°	3704	3663	3698	3663	3704	353
15°	3619	3643	3682	3643	3619	1016
25°	3243	3309	3407	3309	3243	1480
35°	2478	2558	2620	2558	2478	1520
45°	1053	1311	1161	1311	1053	828
55°	178	268	181	268	178	174
65°	54	60	56	60	54	53
75°	30	33	33	33	30	32
85°	10	10	10	10	10	11
90°	44	41	7	57	93	21
95°	49	66	68	216	299	82
105°	497	371	314	555	686	460
115°	820	826	596	882	1010	812
125°	1306	1264	884	1103	1247	1156
135°	1710	1628	1200	1240	1381	1312
145°	1972	1909	1534	1318	1413	1235
155°	2146	2095	1822	1499	1463	991
165°	2237	2183	2011	1759	1687	631
175°	2189	2158	2103	2011	1976	210
180°	2108	2108	2108	2108	2108	

TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5
2.5°	3686.9	3689.5	3692.1	3681.5	3666.5	3665.4	3678.1	3688.8	3692.9	3697.0	3692.9
5°	3703.6	3704.5	3705.4	3688.4	3665.4	3661.2	3675.7	3688.0	3693.1	3698.3	3693.1
7.5°	3695.3	3699.0	3702.7	3690.3	3672.5	3669.8	3682.2	3692.2	3694.9	3697.7	3694.9
10°	3696.2	3697.6	3699.0	3684.9	3665.7	3665.4	3684.2	3697.9	3696.5	3695.1	3696.5
12.5°	3674.2	3677.9	3681.5	3672.2	3658.6	3664.2	3689.0	3706.0	3699.7	3693.4	3699.7
15°	3619.1	3626.1	3633.1	3634.6	3634.1	3651.0	3685.3	3707.8	3695.1	3682.4	3695.1
17.5°	3528.0	3536.9	3545.8	3557.7	3570.6	3599.2	3643.6	3673.1	3657.7	3642.3	3657.7
20°	3455.3	3464.2	3473.2	3489.8	3509.1	3544.3	3595.5	3630.1	3615.1	3600.0	3615.1
22.5°	3376.7	3384.1	3391.6	3408.1	3427.8	3466.0	3522.8	3561.9	3548.0	3534.1	3548.0
25°	3243.0	3247.2	3251.4	3268.0	3288.7	3328.8	3388.4	3430.2	3418.5	3406.7	3418.5
27.5°	3061.5	3068.7	3076.0	3092.9	3113.1	3150.5	3205.2	3244.9	3239.9	3235.0	3239.9
30°	2906.0	2919.6	2933.3	2954.6	2978.6	3012.6	3056.7	3089.7	3089.2	3088.8	3089.2
32.5°	2742.9	2759.9	2776.9	2799.1	2823.1	2852.0	2886.0	2912.3	2915.6	2918.9	2915.6
35°	2478.2	2491.8	2505.4	2525.0	2546.6	2569.9	2594.8	2614.1	2616.9	2619.8	2616.9
37.5°	2141.0	2154.7	2168.4	2185.8	2204.4	2225.6	2249.3	2267.3	2267.7	2268.2	2267.7
40°	1895.1	1903.5	1912.0	1931.7	1955.2	1978.4	2001.4	2017.9	2014.6	2011.3	2014.6
42.5°	1643.3	1648.7	1654.2	1674.8	1700.5	1723.4	1743.4	1752.3	1728.0	1703.7	1728.0
45°	1053.2	1141.0	1228.8	1273.3	1303.3	1319.0	1320.4	1303.7	1232.3	1160.9	1232.3
47.5°	545.3	631.3	717.3	808.8	902.1	924.0	874.4	818.0	741.0	664.0	741.0
50°	372.9	406.7	440.5	535.6	651.1	673.1	601.8	533.7	475.5	417.3	475.5
52.5°	278.2	294.8	311.3	385.1	478.1	488.2	415.3	353.5	325.0	296.4	325.0
55°	178.5	185.6	192.6	225.4	266.7	268.8	231.7	201.3	191.0	180.6	191.0
57.5°	109.9	119.1	128.3	142.5	158.5	158.6	143.0	128.8	119.1	109.4	119.1
60°	67.6	76.1	84.5	98.6	114.6	116.2	103.5	91.8	82.9	73.9	82.9
62.5°	60.8	64.0	67.2	77.5	90.0	91.1	80.7	72.1	68.8	65.5	68.8
65°	53.9	54.8	55.8	57.4	59.3	60.0	59.5	58.8	57.4	56.0	57.4
67.5°	46.3	47.7	49.1	49.8	50.3	50.7	51.2	51.3	50.4	49.4	50.4
70°	41.2	42.6	44.0	44.7	45.2	45.7	46.1	46.2	45.3	44.4	45.3
72.5°	37.0	38.0	39.0	39.6	40.1	40.6	41.1	41.2	40.2	39.3	40.2
75°	29.6	30.5	31.5	32.0	32.5	33.2	34.2	34.6	33.7	32.7	33.7
77.5°	23.2	24.2	25.1	25.6	26.0	26.4	26.9	27.0	26.2	25.4	26.2
80°	19.0	20.0	20.9	21.1	21.1	21.4	21.8	22.1	21.6	21.1	21.6
82.5°	14.8	15.4	15.9	16.1	16.1	16.3	16.8	17.1	17.0	16.9	17.0
85°	9.5	9.5	9.5	9.5	9.5	9.7	10.2	10.4	10.0	9.5	10.0
87.5°	11.4	12.0	12.2	11.8	11.6	11.4	10.1	8.5	6.6	4.9	6.6
90°	44.4	45.4	44.4	42.3	41.2	40.2	33.8	25.4	15.9	7.4	15.9
92.5°	54.5	53.9	53.7	51.6	49.7	44.4	36.4	36.4	37.0	23.5	39.5
95°	48.6	48.6	47.6	47.6	56.0	75.0	103.6	102.5	74.0	67.6	95.1
97.5°	112.9	113.1	127.7	158.3	184.1	197.6	184.3	138.4	135.9	130.6	170.6
100°	226.2	223.0	245.2	271.6	299.1	244.1	194.5	193.4	184.9	175.4	227.2
102.5°	359.7	372.6	381.3	381.5	303.3	271.2	261.2	252.6	234.8	228.7	279.6
105°	496.7	475.6	410.0	372.0	366.7	375.2	376.2	344.5	317.0	313.9	364.6
107.5°	487.4	480.0	484.9	494.4	502.8	503.7	490.6	444.7	402.9	396.7	441.1
110°	577.0	573.9	581.3	586.5	595.0	590.8	571.7	520.0	467.1	453.4	497.8

TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	670.0	676.2	675.9	685.5	688.0	682.9	652.1	593.5	532.2	510.9	553.6
115°	820.1	818.0	825.4	827.5	832.8	819.0	772.5	704.9	627.8	596.0	634.1
117.5°	972.5	966.1	966.1	978.0	974.0	945.2	897.9	817.6	730.9	678.5	707.4
120°	1066.3	1064.2	1064.2	1068.4	1065.3	1031.5	980.7	892.0	796.8	733.4	755.6
122.5°	1155.1	1163.1	1156.4	1158.9	1152.4	1119.4	1056.0	966.4	862.8	793.5	802.1
125°	1306.2	1297.8	1292.5	1290.4	1283.0	1246.0	1177.3	1080.1	968.0	883.5	871.9
127.5°	1423.5	1426.7	1420.6	1413.0	1398.6	1361.8	1291.6	1193.6	1076.7	970.2	944.6
130°	1508.1	1511.3	1506.0	1497.5	1476.4	1432.0	1368.6	1271.4	1151.9	1037.8	994.5
132.5°	1597.7	1595.0	1588.0	1569.4	1547.4	1505.5	1437.9	1346.6	1219.6	1098.7	1045.2
135°	1709.9	1711.0	1695.1	1676.1	1650.8	1604.3	1548.2	1458.4	1331.6	1200.5	1123.4
137.5°	1804.0	1802.3	1786.7	1770.8	1739.3	1698.9	1645.0	1559.9	1436.0	1301.6	1205.0
140°	1863.2	1863.2	1848.4	1828.3	1801.9	1760.7	1706.8	1623.3	1507.0	1367.5	1265.0
142.5°	1908.8	1909.7	1894.9	1879.9	1853.4	1817.3	1764.3	1684.1	1567.9	1439.4	1324.2
145°	1972.0	1976.3	1964.6	1951.9	1926.6	1891.7	1849.4	1767.0	1663.4	1534.5	1418.3
147.5°	2032.3	2036.5	2029.5	2016.4	1991.0	1954.7	1916.2	1841.4	1743.5	1628.6	1510.2
150°	2070.3	2074.5	2065.0	2054.5	2033.3	1995.3	1959.3	1885.4	1793.4	1687.7	1573.6
152.5°	2105.8	2110.0	2102.2	2090.0	2065.4	2028.2	1997.4	1925.9	1840.8	1744.4	1633.6
155°	2146.4	2155.9	2148.5	2136.9	2112.6	2077.7	2049.2	1983.6	1906.5	1822.0	1719.4
157.5°	2185.7	2196.1	2185.7	2174.7	2146.2	2116.8	2090.2	2029.9	1963.4	1890.9	1798.1
160°	2207.7	2217.2	2207.7	2195.0	2166.5	2137.9	2114.7	2058.7	1996.3	1929.8	1850.5
162.5°	2221.2	2231.6	2223.8	2209.4	2180.0	2154.0	2132.4	2081.5	2024.2	1963.6	1891.1
165°	2237.3	2248.9	2239.4	2222.5	2194.0	2172.8	2154.9	2109.4	2060.8	2011.1	1953.0
167.5°	2237.1	2250.4	2240.7	2229.5	2197.1	2180.9	2165.4	2128.4	2087.6	2048.1	2001.6
170°	2232.0	2243.6	2237.3	2227.8	2192.9	2179.2	2169.6	2136.9	2102.0	2069.3	2031.2
172.5°	2221.0	2231.8	2224.6	2215.1	2182.8	2171.6	2167.1	2140.3	2110.5	2085.3	2053.2
175°	2188.7	2203.5	2198.2	2189.7	2161.2	2154.9	2155.9	2137.9	2118.9	2103.1	2084.0
177.5°	2145.6	2154.9	2154.0	2146.4	2127.0	2128.6	2135.4	2124.4	2116.8	2110.9	2101.6
180°	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4

TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5	3683.5
2.5°	3688.8	3678.1	3665.4	3666.5	3681.5	3692.1	3689.5	3686.9
5°	3688.0	3675.7	3661.2	3665.4	3688.4	3705.4	3704.5	3703.6
7.5°	3692.2	3682.2	3669.8	3672.5	3690.3	3702.7	3699.0	3695.3
10°	3697.9	3684.2	3665.4	3665.7	3684.9	3699.0	3697.6	3696.2
12.5°	3706.0	3689.0	3664.2	3658.6	3672.2	3681.5	3677.9	3674.2
15°	3707.8	3685.3	3651.0	3634.1	3634.6	3633.1	3626.1	3619.1
17.5°	3673.1	3643.6	3599.2	3570.6	3557.7	3545.8	3536.9	3528.0
20°	3630.1	3595.5	3544.3	3509.1	3489.8	3473.2	3464.2	3455.3
22.5°	3561.9	3522.8	3466.0	3427.8	3408.1	3391.6	3384.1	3376.7
25°	3430.2	3388.4	3328.8	3288.7	3268.0	3251.4	3247.2	3243.0
27.5°	3244.9	3205.2	3150.5	3113.1	3092.9	3076.0	3068.7	3061.5
30°	3089.7	3056.7	3012.6	2978.6	2954.6	2933.3	2919.6	2906.0
32.5°	2912.3	2886.0	2852.0	2823.1	2799.1	2776.9	2759.9	2742.9
35°	2614.1	2594.8	2569.9	2546.6	2525.0	2505.4	2491.8	2478.2
37.5°	2267.3	2249.3	2225.6	2204.4	2185.8	2168.4	2154.7	2141.0
40°	2017.9	2001.4	1978.4	1955.2	1931.7	1912.0	1903.5	1895.1
42.5°	1752.3	1743.4	1723.4	1700.5	1674.8	1654.2	1648.7	1643.3
45°	1303.7	1320.4	1319.0	1303.3	1273.3	1228.8	1141.0	1053.2
47.5°	818.0	874.4	924.0	902.1	808.8	717.3	631.3	545.3
50°	533.7	601.8	673.1	651.1	535.6	440.5	406.7	372.9
52.5°	353.5	415.3	488.2	478.1	385.1	311.3	294.8	278.2
55°	201.3	231.7	268.8	266.7	225.4	192.6	185.6	178.5
57.5°	128.8	143.0	158.6	158.5	142.5	128.3	119.1	109.9
60°	91.8	103.5	116.2	114.6	98.6	84.5	76.1	67.6
62.5°	72.1	80.7	91.1	90.0	77.5	67.2	64.0	60.8
65°	58.8	59.5	60.0	59.3	57.4	55.8	54.8	53.9
67.5°	51.3	51.2	50.7	50.3	49.8	49.1	47.7	46.3
70°	46.2	46.1	45.7	45.2	44.7	44.0	42.6	41.2
72.5°	41.2	41.1	40.6	40.1	39.6	39.0	38.0	37.0
75°	34.6	34.2	33.2	32.5	32.0	31.5	30.5	29.6
77.5°	27.0	26.9	26.4	26.0	25.6	25.1	24.2	23.2
80°	22.1	21.8	21.4	21.1	21.1	20.9	20.0	19.0
82.5°	17.1	16.8	16.3	16.1	16.1	15.9	15.4	14.8
85°	10.4	10.2	9.7	9.5	9.5	9.5	9.5	9.5
87.5°	8.5	10.6	13.5	15.9	18.8	21.3	21.9	21.1
90°	25.4	35.9	50.7	62.4	77.1	89.8	95.1	93.0
92.5°	57.5	79.1	101.5	122.4	144.8	157.5	162.8	164.0
95°	133.2	163.8	199.7	231.4	258.9	279.0	284.3	299.1
97.5°	209.0	262.7	305.4	342.0	376.4	398.8	411.7	416.8
100°	267.4	320.2	373.1	412.2	453.4	472.4	490.4	503.0
102.5°	329.9	376.9	435.6	484.9	525.2	551.9	563.1	574.1
105°	423.8	477.7	528.4	582.3	624.6	658.4	681.6	685.9
107.5°	511.5	575.1	627.3	681.6	723.3	754.4	777.6	785.6
110°	570.7	635.1	697.5	740.8	788.4	821.1	840.2	855.0

TEST NUMBER: P709408

CATALOG NUMBER: DL2W-WB-M-150U-125D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	624.8	693.5	761.8	816.9	859.4	892.2	913.7	921.8
115°	707.0	775.7	847.6	916.3	961.7	985.0	1000.8	1010.3
117.5°	779.9	854.8	922.4	992.1	1039.1	1063.4	1068.0	1075.6
120°	822.2	900.4	972.3	1033.6	1086.4	1114.9	1125.5	1129.7
122.5°	866.2	941.0	1011.2	1074.2	1125.3	1159.8	1177.1	1182.2
125°	926.8	1000.8	1070.6	1136.1	1183.6	1218.5	1237.5	1247.0
127.5°	979.9	1049.4	1122.8	1187.4	1234.2	1268.0	1288.5	1298.6
130°	1018.8	1079.0	1154.0	1219.6	1267.1	1300.9	1318.9	1327.4
132.5°	1056.0	1104.4	1178.6	1244.1	1294.2	1327.2	1345.1	1351.9
135°	1114.9	1143.5	1204.8	1274.5	1325.3	1357.0	1374.9	1381.3
137.5°	1178.8	1185.3	1227.2	1292.5	1344.5	1377.2	1392.9	1398.2
140°	1222.7	1217.5	1244.9	1300.9	1353.8	1386.5	1401.3	1406.6
142.5°	1270.9	1255.5	1267.8	1310.2	1357.2	1389.9	1405.6	1410.9
145°	1344.3	1315.7	1306.2	1329.5	1364.4	1391.8	1408.7	1413.0
147.5°	1428.0	1386.3	1356.1	1362.9	1380.2	1399.9	1413.8	1416.3
150°	1483.8	1432.0	1395.0	1390.8	1397.1	1410.9	1421.4	1421.4
152.5°	1539.6	1484.4	1437.3	1424.6	1422.5	1427.8	1434.9	1434.1
155°	1628.6	1564.1	1510.2	1486.9	1473.2	1469.0	1466.9	1462.6
157.5°	1714.4	1647.6	1587.1	1555.4	1538.1	1527.5	1522.5	1515.9
160°	1774.4	1702.5	1641.2	1605.3	1590.5	1571.5	1567.3	1555.6
162.5°	1821.7	1760.9	1695.3	1659.4	1639.5	1623.9	1618.0	1604.7
165°	1894.9	1842.0	1776.5	1741.6	1717.3	1703.6	1692.0	1686.7
167.5°	1959.8	1914.5	1857.7	1822.0	1809.5	1788.8	1779.0	1771.2
170°	1995.3	1959.3	1911.8	1876.9	1865.3	1850.5	1839.9	1830.4
172.5°	2025.7	2000.8	1956.6	1932.7	1921.9	1908.8	1900.8	1887.9
175°	2066.1	2050.2	2021.7	2000.6	2005.8	1993.2	1991.0	1976.3
177.5°	2094.8	2089.8	2070.3	2061.9	2072.0	2067.8	2066.9	2057.6
180°	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4	2108.4

(END OF REPORT)