

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435780

Luminaire Tested: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/24/2026

Test Information

Test Method: LM-79-2024
Report Number: P1435780
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/24/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5979.3 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	56	53	51	47
3	85	75	67	61	79	71	64	59	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	41	44	40	37	34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25784	25784	25784	25784
5°	25481	26685	25481	21269
10°	25371	26994	25371	19282
15°	24936	27211	24936	21313
20°	24249	27013	24249	22228
25°	23047	26795	23047	22495
30°	21233	26196	21233	22734
35°	18788	25621	18788	22328
40°	16176	24919	16176	22571
45°	15972	24027	15972	22614
50°	15237	22855	15237	22699
55°	15158	21084	15158	22477
60°	13591	18790	13591	22387
65°	11587	16554	11587	21757
70°	9352	14025	9352	20162
75°	8110	11584	8110	18534
80°	6908	8628	6908	14960
85°	4594	4594	4594	9170

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 24781 cd/sqm



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.7	2.4
10°-20°	401.5	6.7
20°-30°	609.7	10.2
30°-40°	715.9	12.0
40°-50°	726.5	12.1
50°-60°	636.3	10.6
60°-70°	451.3	7.5
70°-80°	232.4	3.9
80°-90°	51.6	0.9
90°-100°	54.8	0.9
100°-110°	159.8	2.7
110°-120°	260.8	4.4
120°-130°	330.9	5.5
130°-140°	354.1	5.9
140°-150°	330.7	5.5
150°-160°	272.1	4.6
160°-170°	182.5	3.1
170°-180°	64.8	1.1
0°-30°	1154.9	19.3
0°-40°	1870.8	31.3
0°-60°	3233.6	54.1
0°-90°	3968.9	66.4
90°-120°	475.4	8.0
90°-150°	1491.1	24.9
90°-180°	2010.0	33.6
0°-180°	5979.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1597	1597	1597	1597	1597	
5°	1572	1646	1572	1312	1572	149
15°	1492	1628	1492	1275	1492	419
25°	1294	1504	1294	1263	1294	591
35°	953	1300	953	1133	953	594
45°	700	1052	700	990	700	535
55°	538	749	538	798	538	466
65°	303	433	303	570	303	303
75°	130	186	130	297	130	141
85°	25	25	25	50	25	31
90°	2	15	2	30	2	2
95°	22	16	22	94	22	26
105°	102	163	102	224	102	108
115°	195	270	195	332	195	192
125°	288	428	288	408	288	258
135°	392	560	392	451	392	303
145°	500	645	500	461	500	313
155°	594	701	594	478	594	273
165°	657	731	657	551	657	185
175°	686	716	686	646	686	65
180°	689	689	689	689	689	



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1587.1	1598.1	1609.1	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9	1611.9
5°	1572.2	1591.5	1610.7	1619.7	1625.2	1629.3	1632.1	1635.5	1641.0	1646.5	1641.0
7.5°	1557.4	1583.2	1609.1	1621.8	1630.0	1636.6	1641.6	1646.0	1648.7	1651.5	1648.7
10°	1547.5	1577.7	1608.0	1621.8	1630.0	1635.5	1638.3	1641.0	1643.8	1646.5	1643.8
12.5°	1532.6	1565.1	1597.5	1613.5	1624.0	1630.6	1633.3	1636.1	1638.8	1641.6	1638.8
15°	1491.8	1535.8	1579.8	1597.0	1605.2	1612.1	1617.6	1622.4	1625.2	1627.9	1625.2
17.5°	1441.0	1494.4	1547.8	1569.3	1580.4	1588.3	1593.3	1597.5	1599.7	1601.9	1599.7
20°	1411.3	1469.1	1526.8	1549.5	1560.5	1567.4	1570.2	1572.2	1572.2	1572.2	1572.2
22.5°	1371.7	1436.1	1500.4	1524.8	1535.8	1541.6	1542.1	1543.1	1545.3	1547.5	1545.3
25°	1293.7	1368.0	1442.2	1473.2	1489.7	1496.6	1493.8	1493.1	1498.6	1504.1	1498.6
27.5°	1198.4	1291.9	1385.4	1417.1	1428.1	1435.0	1437.7	1439.8	1439.8	1439.8	1439.8
30°	1138.9	1243.5	1348.0	1382.4	1393.4	1400.3	1403.0	1405.1	1405.1	1405.1	1405.1
32.5°	1064.7	1189.0	1313.4	1351.0	1359.9	1364.5	1365.1	1365.5	1365.5	1365.5	1365.5
35°	953.2	1104.6	1255.9	1297.8	1303.3	1306.1	1306.1	1305.4	1302.6	1299.9	1302.6
37.5°	841.8	1013.5	1185.2	1234.3	1242.5	1244.7	1240.9	1237.3	1234.5	1231.8	1234.5
40°	767.5	954.6	1141.7	1194.7	1202.9	1202.9	1194.7	1187.8	1185.0	1182.3	1185.0
42.5°	727.9	912.8	1097.7	1150.1	1158.3	1157.2	1146.8	1138.3	1135.5	1132.8	1135.5
45°	699.5	864.5	1029.6	1077.0	1085.3	1083.9	1072.9	1063.3	1057.8	1052.3	1057.8
47.5°	656.1	801.4	946.6	993.3	1007.0	1005.7	989.1	975.4	969.9	964.4	969.9
50°	606.6	749.7	892.7	938.8	952.6	951.2	934.7	920.9	915.4	909.9	915.4
52.5°	571.9	706.2	840.5	882.7	894.2	890.7	872.0	856.5	851.0	845.5	851.0
55°	538.5	651.3	764.1	798.5	806.8	801.2	782.0	765.5	757.2	749.0	757.2
57.5°	460.5	567.8	675.1	708.5	717.3	710.7	688.7	669.9	660.5	651.2	660.5
60°	420.9	517.2	613.5	645.8	656.8	651.3	629.3	609.4	595.6	581.9	595.6
62.5°	376.3	461.6	546.9	579.8	595.2	591.9	569.9	549.9	536.2	522.4	536.2
65°	303.3	377.6	451.9	484.9	504.1	502.8	480.7	460.8	447.0	433.3	447.0
67.5°	237.7	301.5	365.3	397.8	419.8	418.7	394.5	373.6	362.6	351.6	362.6
70°	198.1	253.1	308.1	338.4	360.4	360.4	338.4	319.1	308.1	297.1	308.1
72.5°	173.3	215.1	256.9	285.6	309.8	309.8	285.6	265.2	256.4	247.6	256.4
75°	130.0	154.7	179.5	206.3	233.8	236.6	214.6	196.7	191.2	185.7	191.2
77.5°	94.1	105.6	117.2	138.2	162.5	165.2	146.5	131.9	129.7	127.5	129.7
80°	74.3	77.0	79.8	97.0	119.0	121.7	105.2	92.8	92.8	92.8	92.8
82.5°	49.5	52.3	55.0	67.3	82.7	84.3	72.2	62.6	60.4	58.2	60.4
85°	24.8	24.8	24.8	28.9	34.4	34.4	28.9	24.8	24.8	24.8	24.8
87.5°	5.4	5.9	6.6	8.8	11.4	11.6	9.4	7.9	8.0	8.0	8.0
90°	2.1	4.9	8.3	11.1	13.2	13.9	13.9	14.6	15.3	15.3	15.3
92.5°	7.7	12.1	12.2	12.2	14.9	16.1	17.2	17.4	18.1	18.1	18.1
95°	21.6	23.6	35.5	34.8	23.6	18.8	16.0	16.0	16.0	16.0	16.0
97.5°	41.2	44.2	46.2	61.9	65.4	63.2	51.5	43.3	38.7	36.6	38.7
100°	58.4	59.8	64.0	64.7	82.1	98.8	90.4	80.0	76.5	74.4	76.5
102.5°	75.7	76.5	82.9	85.8	89.9	99.3	128.3	125.1	122.7	122.3	122.7
105°	101.5	102.2	114.1	119.6	122.4	122.4	121.7	135.6	157.9	162.7	157.9
107.5°	129.2	132.4	146.3	161.2	164.4	165.3	161.6	159.5	158.7	159.3	158.7
110°	148.1	153.0	169.7	188.5	193.4	194.7	193.4	191.3	189.9	189.9	189.9



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	166.5	173.6	192.5	214.1	222.3	226.5	223.4	221.9	220.5	221.6	220.5
115°	194.7	205.2	230.2	252.5	269.2	271.2	270.6	270.6	269.9	269.9	269.9
117.5°	220.9	237.6	265.7	291.6	310.9	316.5	319.2	318.4	317.6	319.0	317.6
120°	239.3	258.7	290.7	319.9	338.7	347.1	349.8	348.4	349.8	348.4	349.8
122.5°	258.7	282.7	314.1	344.4	366.5	376.0	379.3	379.6	379.9	379.1	379.9
125°	287.9	317.2	354.0	385.3	408.3	419.4	422.2	422.9	424.3	427.7	424.3
127.5°	317.4	350.5	391.0	421.2	444.7	458.2	462.5	464.0	467.0	468.5	467.0
130°	338.0	375.6	416.6	445.1	468.1	482.7	490.3	492.4	495.9	495.2	495.9
132.5°	359.7	398.9	440.5	470.2	491.4	507.2	513.7	519.7	520.9	521.9	520.9
135°	391.6	434.0	475.7	504.9	525.1	540.4	548.8	554.3	557.8	559.9	557.8
137.5°	425.1	469.9	509.9	536.0	556.3	569.5	578.9	584.8	588.4	590.1	588.4
140°	447.9	491.0	530.0	557.1	575.2	588.4	596.7	603.7	607.9	607.9	607.9
142.5°	469.6	512.2	550.0	577.1	593.0	605.1	614.0	619.3	624.0	624.0	624.0
145°	500.1	542.5	577.3	604.4	617.6	628.7	638.5	642.6	645.4	645.4	645.4
147.5°	531.9	569.5	601.2	627.2	638.3	651.4	659.1	662.4	665.9	664.3	665.9
150°	550.8	585.6	616.2	640.6	651.7	664.2	671.9	674.6	678.1	676.0	678.1
152.5°	569.2	602.3	630.1	652.8	662.3	674.8	683.5	686.3	688.7	687.2	688.7
155°	594.0	623.2	648.9	669.8	678.1	689.9	698.3	701.8	704.5	701.1	704.5
157.5°	616.1	641.3	663.7	682.8	691.8	701.9	709.7	714.0	716.8	715.3	716.8
160°	629.4	652.4	672.6	690.6	699.0	708.0	716.4	721.2	724.0	721.9	724.0
162.5°	640.6	661.3	680.3	696.8	704.0	711.9	721.9	726.2	729.0	726.4	729.0
165°	656.6	673.3	689.9	703.9	710.1	716.4	726.8	731.7	733.8	731.0	733.8
167.5°	668.7	681.5	695.0	706.9	711.5	717.6	728.1	732.1	734.7	731.3	734.7
170°	675.3	686.5	698.3	708.0	711.5	717.1	727.5	731.0	733.1	729.6	733.1
172.5°	680.9	689.2	698.8	707.5	709.3	713.7	723.6	727.1	728.6	725.7	728.6
175°	686.5	691.3	698.3	703.9	703.2	705.9	714.3	717.1	719.9	715.7	719.9
177.5°	689.1	691.3	693.6	696.9	694.7	694.7	700.8	702.5	703.0	700.8	703.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1611.9	1611.9	1611.9	1611.9	1611.9	1609.1	1598.1	1587.1	1587.1	1587.1	1578.8
5°	1635.5	1632.1	1629.3	1625.2	1619.7	1610.7	1591.5	1572.2	1564.0	1555.7	1520.7
7.5°	1646.0	1641.6	1636.6	1630.0	1621.8	1609.1	1583.2	1557.4	1520.5	1483.7	1405.5
10°	1641.0	1638.3	1635.5	1630.0	1621.8	1608.0	1577.7	1547.5	1473.2	1398.9	1324.6
12.5°	1636.1	1633.3	1630.6	1624.0	1613.5	1597.5	1565.1	1532.6	1427.5	1322.4	1255.3
15°	1622.4	1617.6	1612.1	1605.2	1597.0	1579.8	1535.8	1491.8	1373.5	1255.2	1198.8
17.5°	1597.5	1593.3	1588.3	1580.4	1569.3	1547.8	1494.4	1441.0	1317.2	1193.4	1157.1
20°	1572.2	1570.2	1567.4	1560.5	1549.5	1526.8	1469.1	1411.3	1287.5	1163.7	1147.2
22.5°	1543.1	1542.1	1541.6	1535.8	1524.8	1500.4	1436.1	1371.7	1250.1	1128.5	1129.0
25°	1493.1	1493.8	1496.6	1489.7	1473.2	1442.2	1368.0	1293.7	1186.4	1079.1	1097.7
27.5°	1439.8	1437.7	1435.0	1428.1	1417.1	1385.4	1291.9	1198.4	1113.6	1028.9	1059.7
30°	1405.1	1403.0	1400.3	1393.4	1382.4	1348.0	1243.5	1138.9	1067.4	995.9	1031.7
32.5°	1365.5	1365.1	1364.5	1359.9	1351.0	1313.4	1189.0	1064.7	1012.9	961.2	998.6
35°	1305.4	1306.1	1306.1	1303.3	1297.8	1255.9	1104.6	953.2	931.2	909.2	953.2
37.5°	1237.3	1240.9	1244.7	1242.5	1234.3	1185.2	1013.5	841.8	849.0	856.1	909.5
40°	1187.8	1194.7	1202.9	1202.9	1194.7	1141.7	954.6	767.5	792.3	817.1	874.8
42.5°	1138.3	1146.8	1157.2	1158.3	1150.1	1097.7	912.8	727.9	754.9	781.9	841.8
45°	1063.3	1072.9	1083.9	1085.3	1077.0	1029.6	864.5	699.5	716.0	732.5	790.2
47.5°	975.4	989.1	1005.7	1007.0	993.3	946.6	801.4	656.1	668.2	680.3	739.5
50°	920.9	934.7	951.2	952.6	938.8	892.7	749.7	606.6	623.1	639.6	701.5
52.5°	856.5	872.0	890.7	894.2	882.7	840.5	706.2	571.9	581.9	591.8	658.6
55°	765.5	782.0	801.2	806.8	798.5	764.1	651.3	538.5	530.3	522.0	590.1
57.5°	669.9	688.7	710.7	717.3	708.5	675.1	567.8	460.5	453.4	446.2	520.0
60°	609.4	629.3	651.3	656.8	645.8	613.5	517.2	420.9	407.2	393.4	470.4
62.5°	549.9	569.9	591.9	595.2	579.8	546.9	461.6	376.3	367.0	357.6	432.5
65°	460.8	480.7	502.8	504.1	484.9	451.9	377.6	303.3	308.8	314.3	381.7
67.5°	373.6	394.5	418.7	419.8	397.8	365.3	301.5	237.7	255.8	274.0	334.7
70°	319.1	338.4	360.4	360.4	338.4	308.1	253.1	198.1	222.8	247.6	303.3
72.5°	265.2	285.6	309.8	309.8	285.6	256.9	215.1	173.3	198.1	222.8	268.6
75°	196.7	214.6	236.6	233.8	206.3	179.5	154.7	130.0	154.7	179.5	214.6
77.5°	131.9	146.5	165.2	162.5	138.2	117.2	105.6	94.1	114.4	134.8	159.3
80°	92.8	105.2	121.7	119.0	97.0	79.8	77.0	74.3	88.0	101.8	119.7
82.5°	62.6	72.2	84.3	82.7	67.3	55.0	52.3	49.5	61.1	72.6	85.0
85°	24.8	28.9	34.4	34.4	28.9	24.8	24.8	24.8	30.3	35.8	41.3
87.5°	7.9	9.4	11.6	11.4	8.8	6.6	5.9	5.4	8.1	10.9	12.4
90°	14.6	13.9	13.9	13.2	11.1	8.3	4.9	2.1	4.9	7.7	12.5
92.5°	17.4	17.2	16.1	14.9	12.2	12.2	12.1	7.7	13.2	18.8	27.0
95°	16.0	16.0	18.8	23.6	34.8	35.5	23.6	21.6	30.6	43.1	54.2
97.5°	43.3	51.5	63.2	65.4	61.9	46.2	44.2	41.2	56.1	68.4	86.4
100°	80.0	90.4	98.8	82.1	64.7	64.0	59.8	58.4	74.4	86.2	103.6
102.5°	125.1	128.3	99.3	89.9	85.8	82.9	76.5	75.7	91.7	107.9	122.5
105°	135.6	121.7	122.4	122.4	119.6	114.1	102.2	101.5	119.6	138.4	156.5
107.5°	159.5	161.6	165.3	164.4	161.2	146.3	132.4	129.2	145.5	168.0	187.9
110°	191.3	193.4	194.7	193.4	188.5	169.7	153.0	148.1	162.7	186.4	208.0



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	221.9	223.4	226.5	222.3	214.1	192.5	173.6	166.5	181.1	205.3	227.4
115°	270.6	270.6	271.2	269.2	252.5	230.2	205.2	194.7	207.3	229.5	253.9
117.5°	318.4	319.2	316.5	310.9	291.6	265.7	237.6	220.9	230.8	254.3	279.3
120°	348.4	349.8	347.1	338.7	319.9	290.7	258.7	239.3	246.9	269.9	294.9
122.5°	379.6	379.3	376.0	366.5	344.4	314.1	282.7	258.7	261.9	283.2	307.7
125°	422.9	422.2	419.4	408.3	385.3	354.0	317.2	287.9	283.8	301.9	326.9
127.5°	464.0	462.5	458.2	444.7	421.2	391.0	350.5	317.4	308.1	319.5	342.5
130°	492.4	490.3	482.7	468.1	445.1	416.6	375.6	338.0	324.8	331.8	351.9
132.5°	519.7	513.7	507.2	491.4	470.2	440.5	398.9	359.7	341.5	344.6	360.3
135°	554.3	548.8	540.4	525.1	504.9	475.7	434.0	391.6	366.5	363.8	372.8
137.5°	584.8	578.9	569.5	556.3	536.0	509.9	469.9	425.1	393.5	384.2	387.7
140°	603.7	596.7	588.4	575.2	557.1	530.0	491.0	447.9	412.4	399.2	397.1
142.5°	619.3	614.0	605.1	593.0	577.1	550.0	512.2	469.6	431.9	414.8	409.9
145°	642.6	638.5	628.7	617.6	604.4	577.3	542.5	500.1	462.5	440.3	429.8
147.5°	662.4	659.1	651.4	638.3	627.2	601.2	569.5	531.9	493.4	465.9	452.4
150°	674.6	671.9	664.2	651.7	640.6	616.2	585.6	550.8	514.0	484.8	467.4
152.5°	686.3	683.5	674.8	662.3	652.8	630.1	602.3	569.2	531.8	502.6	484.6
155°	701.8	698.3	689.9	678.1	669.8	648.9	623.2	594.0	562.0	531.4	511.2
157.5°	714.0	709.7	701.9	691.8	682.8	663.7	641.3	616.1	588.1	558.9	538.3
160°	721.2	716.4	708.0	699.0	690.6	672.6	652.4	629.4	603.7	577.3	555.0
162.5°	726.2	721.9	711.9	704.0	696.8	680.3	661.3	640.6	617.6	594.5	573.9
165°	731.7	726.8	716.4	710.1	703.9	689.9	673.3	656.6	637.1	618.3	601.6
167.5°	732.1	728.1	717.6	711.5	706.9	695.0	681.5	668.7	653.5	638.8	624.8
170°	731.0	727.5	717.1	711.5	708.0	698.3	686.5	675.3	663.5	651.0	639.9
172.5°	727.1	723.6	713.7	709.3	707.5	698.8	689.2	680.9	670.7	661.6	652.7
175°	717.1	714.3	705.9	703.2	703.9	698.3	691.3	686.5	680.2	674.6	669.8
177.5°	702.5	700.8	694.7	694.7	696.9	693.6	691.3	689.1	686.3	684.7	683.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0	1597.0
2.5°	1567.8	1559.0	1552.4	1546.9	1544.7	1542.5	1544.7	1546.9	1552.4	1559.0	1567.8
5°	1476.6	1429.9	1380.3	1339.8	1326.0	1312.3	1326.0	1339.8	1380.3	1429.9	1476.6
7.5°	1313.6	1257.2	1236.3	1219.5	1215.1	1210.7	1215.1	1219.5	1236.3	1257.2	1313.6
10°	1250.4	1205.0	1188.5	1176.1	1176.1	1176.1	1176.1	1176.1	1188.5	1205.0	1250.4
12.5°	1200.8	1173.1	1172.0	1173.9	1184.9	1195.9	1184.9	1173.9	1172.0	1173.1	1200.8
15°	1163.0	1167.1	1211.2	1247.6	1261.4	1275.1	1261.4	1247.6	1211.2	1167.1	1163.0
17.5°	1149.9	1173.6	1228.1	1271.7	1282.7	1293.7	1282.7	1271.7	1228.1	1173.6	1149.9
20°	1166.5	1196.7	1238.0	1271.7	1282.7	1293.7	1282.7	1271.7	1238.0	1196.7	1166.5
22.5°	1170.3	1207.2	1239.6	1266.7	1277.7	1288.7	1277.7	1266.7	1239.6	1207.2	1170.3
25°	1158.2	1202.2	1229.7	1251.7	1257.2	1262.7	1257.2	1251.7	1229.7	1202.2	1158.2
27.5°	1129.0	1177.5	1205.0	1226.6	1230.4	1234.3	1230.4	1226.6	1205.0	1177.5	1129.0
30°	1103.2	1152.7	1180.2	1202.9	1211.2	1219.4	1211.2	1202.9	1180.2	1152.7	1103.2
32.5°	1065.8	1116.4	1150.5	1176.5	1178.1	1179.8	1178.1	1176.5	1150.5	1116.4	1065.8
35°	1019.3	1071.5	1110.1	1138.3	1135.5	1132.8	1135.5	1138.3	1110.1	1071.5	1019.3
37.5°	978.3	1029.4	1063.0	1089.0	1092.3	1095.6	1092.3	1089.0	1063.0	1029.4	978.3
40°	943.6	995.9	1031.7	1059.8	1065.4	1070.9	1065.4	1059.8	1031.7	995.9	943.6
42.5°	912.8	966.2	1001.9	1030.1	1035.6	1041.1	1035.6	1030.1	1001.9	966.2	912.8
45°	861.8	916.8	955.3	984.9	987.6	990.4	987.6	984.9	955.3	916.8	861.8
47.5°	814.3	869.6	905.4	932.9	935.6	938.4	935.6	932.9	905.4	869.6	814.3
50°	778.6	834.9	870.7	898.2	901.0	903.7	901.0	898.2	870.7	834.9	778.6
52.5°	744.4	803.0	834.4	858.6	861.4	864.1	861.4	858.6	834.4	803.0	744.4
55°	683.6	745.5	775.8	798.5	798.5	798.5	798.5	798.5	775.8	745.5	683.6
57.5°	620.6	684.2	710.6	731.2	734.5	737.8	734.5	731.2	710.6	684.2	620.6
60°	577.7	642.4	664.4	682.3	687.8	693.3	687.8	682.3	664.4	642.4	577.7
62.5°	535.4	597.8	619.8	637.1	640.4	643.7	640.4	637.1	619.8	597.8	535.4
65°	469.7	524.8	546.8	564.0	566.7	569.5	566.7	564.0	546.8	524.8	469.7
67.5°	409.5	454.6	470.0	482.1	484.3	486.5	484.3	482.1	470.0	454.6	409.5
70°	369.3	407.8	418.8	427.1	427.1	427.1	427.1	427.1	418.8	407.8	369.3
72.5°	321.5	353.4	364.4	373.2	375.4	377.6	375.4	373.2	364.4	353.4	321.5
75°	253.1	276.5	284.7	291.6	294.4	297.1	294.4	291.6	284.7	276.5	253.1
77.5°	185.1	200.6	205.5	209.9	212.7	215.4	212.7	209.9	205.5	200.6	185.1
80°	138.9	149.9	152.7	155.4	158.2	160.9	158.2	155.4	152.7	149.9	138.9
82.5°	97.7	105.4	108.1	110.3	110.9	111.4	110.9	110.3	108.1	105.4	97.7
85°	46.8	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5	49.5	46.8
87.5°	13.1	14.1	15.1	15.6	16.2	15.9	16.2	15.6	14.1	13.1	13.1
90°	16.0	20.9	25.7	28.5	31.3	29.9	31.3	28.5	20.9	16.0	16.0
92.5°	32.1	40.3	46.3	51.3	53.6	53.3	53.6	51.3	40.3	32.1	32.1
95°	64.7	74.4	84.2	91.1	95.3	93.9	95.3	91.1	84.2	74.4	64.7
97.5°	99.7	112.8	123.7	130.2	134.4	137.2	134.4	130.2	123.7	112.8	99.7
100°	123.1	135.6	148.1	155.8	162.7	165.5	162.7	155.8	148.1	135.6	123.1
102.5°	142.0	158.4	172.1	180.3	186.1	188.9	186.1	180.3	172.1	158.4	142.0
105°	173.2	190.6	205.2	215.6	221.9	224.0	221.9	215.6	205.2	190.6	173.2
107.5°	204.3	222.3	235.8	247.3	255.0	259.4	255.0	247.3	235.8	222.3	204.3
110°	228.8	243.4	258.0	268.5	276.1	278.9	276.1	268.5	243.4	228.8	228.8



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	249.4	265.7	280.3	290.7	299.5	303.4	299.5	290.7	280.3	265.7	249.4
115°	278.2	299.8	313.0	322.7	329.0	332.5	329.0	322.7	313.0	299.8	278.2
117.5°	302.1	324.7	339.1	346.6	349.6	352.1	349.6	346.6	339.1	324.7	302.1
120°	317.2	338.0	354.7	364.4	367.9	369.3	367.9	364.4	354.7	338.0	317.2
122.5°	331.1	350.8	366.9	378.9	384.6	386.0	384.6	378.9	366.9	350.8	331.1
125°	350.5	369.3	386.0	397.8	404.1	407.6	404.1	397.8	386.0	369.3	350.5
127.5°	367.5	387.8	403.1	413.8	419.9	422.7	419.9	413.8	403.1	387.8	367.5
130°	377.0	397.8	413.1	425.0	430.5	433.3	430.5	425.0	413.1	397.8	377.0
132.5°	384.2	406.2	422.0	432.7	438.9	441.6	438.9	432.7	422.0	406.2	384.2
135°	393.0	415.9	432.6	443.0	448.6	451.4	448.6	443.0	432.6	415.9	393.0
137.5°	400.6	421.5	438.9	449.9	454.9	456.7	454.9	449.9	438.9	421.5	400.6
140°	406.2	424.3	441.6	452.1	457.6	458.3	457.6	452.1	441.6	424.3	406.2
142.5°	413.4	427.6	442.8	453.2	458.8	460.0	458.8	453.2	442.8	427.6	413.4
145°	426.3	434.7	445.1	454.9	459.7	461.1	459.7	454.9	445.1	434.7	426.3
147.5°	442.6	445.3	450.7	457.1	461.8	462.8	461.8	457.1	445.3	442.6	442.6
150°	454.9	454.2	456.3	460.4	464.6	463.9	464.6	460.4	456.3	454.2	454.9
152.5°	468.8	464.7	464.6	466.5	468.5	468.4	468.5	466.5	464.6	464.7	468.8
155°	492.4	484.8	480.6	479.2	479.2	478.5	479.2	479.2	480.6	484.8	492.4
157.5°	518.4	507.7	501.5	498.1	497.1	495.6	497.1	498.1	501.5	507.7	518.4
160°	536.2	524.4	518.2	512.6	510.5	508.4	510.5	512.6	518.2	524.4	536.2
162.5°	552.9	541.7	534.8	529.8	527.8	524.6	527.8	529.8	534.8	541.7	552.9
165°	580.1	568.2	560.6	556.4	553.6	550.8	553.6	556.4	560.6	568.2	580.1
167.5°	607.2	594.2	589.2	584.5	581.9	576.9	581.9	584.5	589.2	594.2	607.2
170°	623.9	612.0	609.3	605.1	600.2	594.7	600.2	605.1	609.3	612.0	623.9
172.5°	638.3	630.4	627.6	623.5	621.9	617.5	621.9	623.5	627.6	630.4	638.3
175°	659.3	653.1	653.1	652.4	650.3	646.1	650.3	652.4	653.1	653.1	659.3
177.5°	676.9	673.5	675.8	675.8	675.2	671.3	675.2	675.8	675.8	673.5	676.9
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1597.0	1597.0	1597.0	1597.0
2.5°	1578.8	1587.1	1587.1	1587.1
5°	1520.7	1555.7	1564.0	1572.2
7.5°	1405.5	1483.7	1520.5	1557.4
10°	1324.6	1398.9	1473.2	1547.5
12.5°	1255.3	1322.4	1427.5	1532.6
15°	1198.8	1255.2	1373.5	1491.8
17.5°	1157.1	1193.4	1317.2	1441.0
20°	1147.2	1163.7	1287.5	1411.3
22.5°	1129.0	1128.5	1250.1	1371.7
25°	1097.7	1079.1	1186.4	1293.7
27.5°	1059.7	1028.9	1113.6	1198.4
30°	1031.7	995.9	1067.4	1138.9
32.5°	998.6	961.2	1012.9	1064.7
35°	953.2	909.2	931.2	953.2
37.5°	909.5	856.1	849.0	841.8
40°	874.8	817.1	792.3	767.5
42.5°	841.8	781.9	754.9	727.9
45°	790.2	732.5	716.0	699.5
47.5°	739.5	680.3	668.2	656.1
50°	701.5	639.6	623.1	606.6
52.5°	658.6	591.8	581.9	571.9
55°	590.1	522.0	530.3	538.5
57.5°	520.0	446.2	453.4	460.5
60°	470.4	393.4	407.2	420.9
62.5°	432.5	357.6	367.0	376.3
65°	381.7	314.3	308.8	303.3
67.5°	334.7	274.0	255.8	237.7
70°	303.3	247.6	222.8	198.1
72.5°	268.6	222.8	198.1	173.3
75°	214.6	179.5	154.7	130.0
77.5°	159.3	134.8	114.4	94.1
80°	119.7	101.8	88.0	74.3
82.5°	85.0	72.6	61.1	49.5
85°	41.3	35.8	30.3	24.8
87.5°	12.4	10.9	8.1	5.4
90°	12.5	7.7	4.9	2.1
92.5°	27.0	18.8	13.2	7.7
95°	54.2	43.1	30.6	21.6
97.5°	86.4	68.4	56.1	41.2
100°	103.6	86.2	74.4	58.4
102.5°	122.5	107.9	91.7	75.7
105°	156.5	138.4	119.6	101.5
107.5°	187.9	168.0	145.5	129.2
110°	208.0	186.4	162.7	148.1



TEST NUMBER: P1435780

CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	227.4	205.3	181.1	166.5
115°	253.9	229.5	207.3	194.7
117.5°	279.3	254.3	230.8	220.9
120°	294.9	269.9	246.9	239.3
122.5°	307.7	283.2	261.9	258.7
125°	326.9	301.9	283.8	287.9
127.5°	342.5	319.5	308.1	317.4
130°	351.9	331.8	324.8	338.0
132.5°	360.3	344.6	341.5	359.7
135°	372.8	363.8	366.5	391.6
137.5°	387.7	384.2	393.5	425.1
140°	397.1	399.2	412.4	447.9
142.5°	409.9	414.8	431.9	469.6
145°	429.8	440.3	462.5	500.1
147.5°	452.4	465.9	493.4	531.9
150°	467.4	484.8	514.0	550.8
152.5°	484.6	502.6	531.8	569.2
155°	511.2	531.4	562.0	594.0
157.5°	538.3	558.9	588.1	616.1
160°	555.0	577.3	603.7	629.4
162.5°	573.9	594.5	617.6	640.6
165°	601.6	618.3	637.1	656.6
167.5°	624.8	638.8	653.5	668.7
170°	639.9	651.0	663.5	675.3
172.5°	652.7	661.6	670.7	680.9
175°	669.8	674.6	680.2	686.5
177.5°	683.0	684.7	686.3	689.1
180°	688.6	688.6	688.6	688.6



TEST NUMBER: P1435780
 CATALOG NUMBER: SQ2W-FA-K-050U-100D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.06	20.09	19.86	20.91	21.93	20.26	21.29	21.06	22.11	23.13
	3H	20.16	21.08	20.98	21.92	22.96	21.51	22.44	22.33	23.27	24.32
	4H	20.52	21.39	21.35	22.23	23.29	21.91	22.78	22.74	23.63	24.68
	6H	20.69	21.49	21.54	22.34	23.41	22.08	22.88	22.93	23.73	24.80
	8H	20.73	21.49	21.58	22.36	23.43	22.11	22.87	22.96	23.74	24.81
	12H	20.73	21.46	21.59	22.32	23.42	22.10	22.83	22.96	23.69	24.79
4H	2H	19.95	20.82	20.78	21.66	22.72	20.86	21.73	21.70	22.57	23.63
	3H	21.35	22.08	22.20	22.95	24.02	22.34	23.07	23.19	23.94	25.01
	4H	21.81	22.47	22.68	23.35	24.44	22.82	23.48	23.69	24.36	25.46
	6H	22.05	22.62	22.93	23.52	24.62	23.06	23.63	23.93	24.52	25.63
	8H	22.11	22.65	22.99	23.54	24.65	23.11	23.64	23.99	24.53	25.65
	12H	22.12	22.60	23.02	23.51	24.63	23.10	23.58	24.01	24.50	25.62
8H	4H	22.21	22.74	23.09	23.63	24.75	23.03	23.56	23.91	24.46	25.57
	6H	22.57	23.01	23.48	23.94	25.06	23.35	23.79	24.26	24.73	25.84
	8H	22.69	23.08	23.61	24.00	25.14	23.45	23.84	24.37	24.77	25.90
	12H	22.73	23.07	23.65	23.99	25.18	23.47	23.82	24.40	24.74	25.92
12H	4H	22.22	22.70	23.12	23.61	24.73	23.01	23.49	23.91	24.40	25.52
	6H	22.64	23.03	23.56	23.96	25.09	23.37	23.76	24.29	24.69	25.82
	8H	22.79	23.14	23.71	24.05	25.24	23.50	23.84	24.42	24.76	25.94