

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1435798

Luminaire Tested: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1435798  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2502-345-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS ASYMMETRIC ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6008.6 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.23 / 1.34  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 50.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47				42	
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40				35	
3	81	72	64	59	75	66	60	55	56	52	48	47	43	41	38	36	34				30	
4	74	63	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22				19	
7	58	46	38	32	53	43	35	30	36	31	27	31	26	23	26	22	20				17	
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16				14	
10	47	35	27	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19178	19178	19178	19178
5°	18953	19847	18953	15818
10°	18870	20077	18870	14340
15°	18545	20239	18545	15853
20°	18036	20092	18036	16532
25°	17141	19929	17141	16732
30°	15793	19484	15793	16909
35°	13974	19056	13974	16606
40°	12033	18533	12033	16787
45°	11878	17872	11878	16819
50°	11333	17000	11333	16884
55°	11274	15682	11274	16718
60°	10110	13976	10110	16649
65°	8619	12313	8619	16183
70°	6954	10433	6954	14997
75°	6032	8615	6032	13786
80°	5132	6425	5132	11130
85°	3409	3409	3409	6817

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 18431 cd/sqm



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.9	1.8
10°-20°	298.6	5.0
20°-30°	453.5	7.5
30°-40°	532.4	8.9
40°-50°	540.3	9.0
50°-60°	473.3	7.9
60°-70°	335.7	5.6
70°-80°	172.8	2.9
80°-90°	40.6	0.7
90°-100°	83.3	1.4
100°-110°	242.8	4.0
110°-120°	396.2	6.6
120°-130°	502.8	8.4
130°-140°	538.0	9.0
140°-150°	502.4	8.4
150°-160°	413.4	6.9
160°-170°	277.2	4.6
170°-180°	98.4	1.6
0°-30°	859.0	14.3
0°-40°	1391.4	23.2
0°-60°	2405.0	40.0
0°-90°	2954.1	49.2
90°-120°	722.3	12.0
90°-150°	2265.4	37.7
90°-180°	3054.0	50.8
0°-180°	6008.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1188	1188	1188	1188	1188	
5°	1169	1225	1169	976	1169	111
15°	1110	1211	1110	948	1110	312
25°	962	1119	962	939	962	439
35°	709	967	709	842	709	442
45°	520	783	520	737	520	398
55°	400	557	400	594	400	346
65°	226	322	226	424	226	225
75°	97	138	97	221	97	105
85°	18	18	18	37	18	23
90°	3	23	3	45	3	3
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8
2.5°	1180.4	1188.6	1196.8	1198.8	1198.8	1198.8	1198.8	1198.8	1198.8	1198.8	1198.8
5°	1169.4	1183.7	1198.0	1204.7	1208.8	1211.8	1213.9	1216.4	1220.5	1224.6	1220.5
7.5°	1158.3	1177.6	1196.8	1206.2	1212.3	1217.3	1220.9	1224.2	1226.3	1228.3	1226.3
10°	1151.0	1173.5	1196.0	1206.2	1212.3	1216.4	1218.5	1220.5	1222.6	1224.6	1222.6
12.5°	1139.9	1164.1	1188.2	1200.1	1207.8	1212.8	1214.8	1216.8	1218.9	1220.9	1218.9
15°	1109.5	1142.3	1175.0	1187.8	1193.9	1199.0	1203.1	1206.7	1208.8	1210.8	1208.8
17.5°	1071.8	1111.5	1151.2	1167.2	1175.4	1181.3	1185.0	1188.2	1189.8	1191.5	1189.8
20°	1049.7	1092.6	1135.6	1152.5	1160.7	1165.8	1167.8	1169.4	1169.4	1169.4	1169.4
22.5°	1020.2	1068.1	1116.0	1134.1	1142.3	1146.6	1147.0	1147.7	1149.3	1151.0	1149.3
25°	962.2	1017.4	1072.7	1095.7	1108.0	1113.1	1111.1	1110.5	1114.6	1118.7	1114.6
27.5°	891.3	960.9	1030.4	1054.0	1062.2	1067.3	1069.3	1070.9	1070.9	1070.9	1070.9
30°	847.1	924.9	1002.6	1028.2	1036.4	1041.5	1043.5	1045.1	1045.1	1045.1	1045.1
32.5°	791.9	884.3	976.8	1004.9	1011.4	1014.9	1015.3	1015.6	1015.6	1015.6	1015.6
35°	709.0	821.5	934.1	965.3	969.4	971.4	971.4	970.9	968.9	966.8	968.9
37.5°	626.1	753.8	881.5	918.0	924.1	925.8	922.9	920.3	918.2	916.2	918.2
40°	570.9	710.0	849.2	888.5	894.7	894.7	888.5	883.4	881.4	879.3	881.4
42.5°	541.4	678.9	816.4	855.4	861.5	860.7	852.9	846.6	844.5	842.5	844.5
45°	520.2	643.0	765.8	801.1	807.2	806.2	798.0	790.8	786.7	782.7	786.7
47.5°	488.0	596.0	704.1	738.8	749.0	748.0	735.7	725.5	721.4	717.3	721.4
50°	451.2	557.6	664.0	698.2	708.5	707.5	695.2	684.9	680.9	676.8	680.9
52.5°	425.4	525.2	625.1	656.5	665.1	662.4	648.5	637.1	633.0	628.9	633.0
55°	400.5	484.4	568.3	593.9	600.0	595.9	581.6	569.3	563.2	557.1	563.2
57.5°	342.5	422.3	502.1	527.0	533.5	528.6	512.3	498.2	491.3	484.3	491.3
60°	313.1	384.7	456.3	480.3	488.5	484.4	468.1	453.2	443.0	432.8	443.0
62.5°	279.9	343.3	406.8	431.2	442.7	440.2	423.9	409.0	398.8	388.6	398.8
65°	225.6	280.8	336.1	360.6	375.0	373.9	357.6	342.7	332.5	322.3	332.5
67.5°	176.8	224.3	271.7	295.9	312.2	311.4	293.4	277.9	269.7	261.5	269.7
70°	147.3	188.2	229.2	251.7	268.0	268.0	251.7	237.4	229.2	221.0	229.2
72.5°	128.9	160.0	191.1	212.4	230.4	230.4	212.4	197.2	190.7	184.2	190.7
75°	96.7	115.1	133.5	153.5	173.9	176.0	159.6	146.3	142.2	138.1	142.2
77.5°	70.0	78.6	87.2	102.8	120.8	122.9	109.0	98.1	96.5	94.8	96.5
80°	55.2	57.3	59.3	72.1	88.5	90.5	78.3	69.1	69.1	69.1	69.1
82.5°	36.8	38.9	40.9	50.0	61.5	62.7	53.7	46.5	44.9	43.3	44.9
85°	18.4	18.4	18.4	21.5	25.6	25.6	21.5	18.4	18.4	18.4	18.4
87.5°	4.3	5.2	6.2	8.3	10.6	10.8	9.1	8.1	8.3	8.3	8.3
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8
2.5°	1198.8	1198.8	1198.8	1198.8	1198.8	1196.8	1188.6	1180.4	1180.4	1180.4	1174.3
5°	1216.4	1213.9	1211.8	1208.8	1204.7	1198.0	1183.7	1169.4	1163.2	1157.1	1131.0
7.5°	1224.2	1220.9	1217.3	1212.3	1206.2	1196.8	1177.6	1158.3	1130.9	1103.5	1045.4
10°	1220.5	1218.5	1216.4	1212.3	1206.2	1196.0	1173.5	1151.0	1095.7	1040.5	985.2
12.5°	1216.8	1214.8	1212.8	1207.8	1200.1	1188.2	1164.1	1139.9	1061.7	983.6	933.7
15°	1206.7	1203.1	1199.0	1193.9	1187.8	1175.0	1142.3	1109.5	1021.5	933.6	891.6
17.5°	1188.2	1185.0	1181.3	1175.4	1167.2	1151.2	1111.5	1071.8	979.7	887.6	860.6
20°	1169.4	1167.8	1165.8	1160.7	1152.5	1135.6	1092.6	1049.7	957.6	865.5	853.2
22.5°	1147.7	1147.0	1146.6	1142.3	1134.1	1116.0	1068.1	1020.2	929.8	839.3	839.7
25°	1110.5	1111.1	1113.1	1108.0	1095.7	1072.7	1017.4	962.2	882.4	802.6	816.4
27.5°	1070.9	1069.3	1067.3	1062.2	1054.0	1030.4	960.9	891.3	828.3	765.3	788.2
30°	1045.1	1043.5	1041.5	1036.4	1028.2	1002.6	924.9	847.1	793.9	740.7	767.3
32.5°	1015.6	1015.3	1014.9	1011.4	1004.9	976.8	884.3	791.9	753.4	714.9	742.8
35°	970.9	971.4	971.4	969.4	965.3	934.1	821.5	709.0	692.6	676.3	709.0
37.5°	920.3	922.9	925.8	924.1	918.0	881.5	753.8	626.1	631.4	636.8	676.5
40°	883.4	888.5	894.7	894.7	888.5	849.2	710.0	570.9	589.3	607.7	650.7
42.5°	846.6	852.9	860.7	861.5	855.4	816.4	678.9	541.4	561.5	581.5	626.1
45°	790.8	798.0	806.2	807.2	801.1	765.8	643.0	520.2	532.5	544.8	587.8
47.5°	725.5	735.7	748.0	749.0	738.8	704.1	596.0	488.0	497.0	506.0	550.0
50°	684.9	695.2	707.5	708.5	698.2	664.0	557.6	451.2	463.5	475.7	521.8
52.5°	637.1	648.5	662.4	665.1	656.5	625.1	525.2	425.4	432.8	440.1	489.8
55°	569.3	581.6	595.9	600.0	593.9	568.3	484.4	400.5	394.4	388.3	438.9
57.5°	498.2	512.3	528.6	533.5	527.0	502.1	422.3	342.5	337.2	331.9	386.7
60°	453.2	468.1	484.4	488.5	480.3	456.3	384.7	313.1	302.8	292.6	349.9
62.5°	409.0	423.9	440.2	442.7	431.2	406.8	343.3	279.9	273.0	266.0	321.7
65°	342.7	357.6	373.9	375.0	360.6	336.1	280.8	225.6	229.7	233.8	283.9
67.5°	277.9	293.4	311.4	312.2	295.9	271.7	224.3	176.8	190.3	203.8	248.9
70°	237.4	251.7	268.0	268.0	251.7	229.2	188.2	147.3	165.7	184.2	225.6
72.5°	197.2	212.4	230.4	230.4	212.4	191.1	160.0	128.9	147.3	165.7	199.8
75°	146.3	159.6	176.0	173.9	153.5	133.5	115.1	96.7	115.1	133.5	159.6
77.5°	98.1	109.0	122.9	120.8	102.8	87.2	78.6	70.0	85.1	100.3	118.5
80°	69.1	78.3	90.5	88.5	72.1	59.3	57.3	55.2	65.5	75.7	89.0
82.5°	46.5	53.7	62.7	61.5	50.0	40.9	38.9	36.8	45.4	54.0	63.2
85°	18.4	21.5	25.6	25.6	21.5	18.4	18.4	18.4	22.5	26.6	30.7
87.5°	8.1	9.1	10.8	10.6	8.3	6.2	5.2	4.3	6.8	9.3	11.2
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8	1187.8
2.5°	1166.1	1159.6	1154.6	1150.5	1148.9	1147.3	1148.9	1150.5	1154.6	1159.6	1166.1
5°	1098.3	1063.5	1026.7	996.5	986.2	976.0	986.2	996.5	1026.7	1063.5	1098.3
7.5°	977.0	935.1	919.5	907.1	903.8	900.5	903.8	907.1	919.5	935.1	977.0
10°	930.0	896.2	883.9	874.7	874.7	874.7	874.7	874.7	883.9	896.2	930.0
12.5°	893.1	872.5	871.7	873.1	881.3	889.5	881.3	873.1	871.7	872.5	893.1
15°	865.0	868.1	900.8	927.9	938.2	948.4	938.2	927.9	900.8	868.1	865.0
17.5°	855.3	872.9	913.4	945.8	954.0	962.2	954.0	945.8	913.4	872.9	855.3
20°	867.6	890.1	920.8	945.8	954.0	962.2	954.0	945.8	920.8	890.1	867.6
22.5°	870.4	897.8	922.0	942.1	950.3	958.5	950.3	942.1	922.0	897.8	870.4
25°	861.4	894.2	914.6	931.0	935.1	939.2	935.1	931.0	914.6	894.2	861.4
27.5°	839.7	875.8	896.2	912.3	915.1	918.0	915.1	912.3	896.2	875.8	839.7
30°	820.5	857.3	877.8	894.7	900.8	907.0	900.8	894.7	877.8	857.3	820.5
32.5°	792.7	830.3	855.7	875.0	876.3	877.5	876.3	875.0	855.7	830.3	792.7
35°	758.1	797.0	825.6	846.6	844.5	842.5	844.5	846.6	825.6	797.0	758.1
37.5°	727.6	765.7	790.6	810.0	812.4	814.9	812.4	810.0	790.6	765.7	727.6
40°	701.8	740.7	767.3	788.3	792.4	796.5	792.4	788.3	767.3	740.7	701.8
42.5°	678.9	718.6	745.2	766.2	770.3	774.4	770.3	766.2	745.2	718.6	678.9
45°	641.0	681.9	710.5	732.5	734.6	736.6	734.6	732.5	710.5	681.9	641.0
47.5°	605.7	646.8	673.4	693.8	695.9	697.9	695.9	693.8	673.4	646.8	605.7
50°	579.1	621.0	647.6	668.1	670.1	672.2	670.1	668.1	647.6	621.0	579.1
52.5°	553.7	597.3	620.6	638.6	640.6	642.7	640.6	638.6	620.6	597.3	553.7
55°	508.5	554.5	577.0	593.9	593.9	593.9	593.9	593.9	577.0	554.5	508.5
57.5°	461.6	508.9	528.5	543.9	546.3	548.8	546.3	543.9	528.5	508.9	461.6
60°	429.7	477.8	494.1	507.4	511.5	515.6	511.5	507.4	494.1	477.8	429.7
62.5°	398.2	444.6	461.0	473.9	476.3	478.8	476.3	473.9	461.0	444.6	398.2
65°	349.4	390.3	406.7	419.5	421.5	423.6	421.5	419.5	406.7	390.3	349.4
67.5°	304.6	338.1	349.6	358.6	360.2	361.9	360.2	358.6	349.6	338.1	304.6
70°	274.7	303.3	311.5	317.7	317.7	317.7	317.7	317.7	311.5	303.3	274.7
72.5°	239.1	262.8	271.0	277.6	279.2	280.8	279.2	277.6	271.0	262.8	239.1
75°	188.2	205.6	211.8	216.9	218.9	221.0	218.9	216.9	211.8	205.6	188.2
77.5°	137.7	149.2	152.8	156.1	158.2	160.2	158.2	156.1	152.8	149.2	137.7
80°	103.3	111.5	113.6	115.6	117.7	119.7	117.7	115.6	113.6	111.5	103.3
82.5°	72.6	78.4	80.4	82.1	82.5	82.9	82.5	82.1	80.4	78.4	72.6
85°	34.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	36.8	34.8
87.5°	12.2	13.7	15.2	16.0	16.9	16.5	16.9	16.0	15.2	13.7	12.2
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	197.8	187.9	171.4	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	1187.8	1187.8	1187.8	1187.8
2.5°	1174.3	1180.4	1180.4	1180.4
5°	1131.0	1157.1	1163.2	1169.4
7.5°	1045.4	1103.5	1130.9	1158.3
10°	985.2	1040.5	1095.7	1151.0
12.5°	933.7	983.6	1061.7	1139.9
15°	891.6	933.6	1021.5	1109.5
17.5°	860.6	887.6	979.7	1071.8
20°	853.2	865.5	957.6	1049.7
22.5°	839.7	839.3	929.8	1020.2
25°	816.4	802.6	882.4	962.2
27.5°	788.2	765.3	828.3	891.3
30°	767.3	740.7	793.9	847.1
32.5°	742.8	714.9	753.4	791.9
35°	709.0	676.3	692.6	709.0
37.5°	676.5	636.8	631.4	626.1
40°	650.7	607.7	589.3	570.9
42.5°	626.1	581.5	561.5	541.4
45°	587.8	544.8	532.5	520.2
47.5°	550.0	506.0	497.0	488.0
50°	521.8	475.7	463.5	451.2
52.5°	489.8	440.1	432.8	425.4
55°	438.9	388.3	394.4	400.5
57.5°	386.7	331.9	337.2	342.5
60°	349.9	292.6	302.8	313.1
62.5°	321.7	266.0	273.0	279.9
65°	283.9	233.8	229.7	225.6
67.5°	248.9	203.8	190.3	176.8
70°	225.6	184.2	165.7	147.3
72.5°	199.8	165.7	147.3	128.9
75°	159.6	133.5	115.1	96.7
77.5°	118.5	100.3	85.1	70.0
80°	89.0	75.7	65.5	55.2
82.5°	63.2	54.0	45.4	36.8
85°	30.7	26.6	22.5	18.4
87.5°	11.2	9.3	6.8	4.3
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1



TEST NUMBER: P1435798

CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1435798  
 CATALOG NUMBER: SQ2W-FA-K-075U-075D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.56	17.41	17.53	18.39	19.68	17.76	18.61	18.72	19.59	20.87
	3H	17.65	18.41	18.62	19.40	20.71	19.00	19.77	19.98	20.76	22.06
	4H	18.00	18.72	18.99	19.72	21.03	19.39	20.12	20.38	21.11	22.42
	6H	18.16	18.83	19.16	19.82	21.15	19.55	20.22	20.55	21.22	22.54
	8H	18.20	18.83	19.20	19.84	21.17	19.58	20.21	20.58	21.22	22.55
	12H	18.19	18.79	19.20	19.80	21.15	19.56	20.16	20.57	21.17	22.52
4H	2H	17.43	18.15	18.42	19.14	20.46	18.34	19.06	19.34	20.06	21.37
	3H	18.82	19.42	19.82	20.44	21.77	19.81	20.41	20.81	21.43	22.76
	4H	19.27	19.82	20.28	20.83	22.19	20.28	20.83	21.29	21.84	23.20
	6H	19.50	19.97	20.52	21.01	22.36	20.50	20.98	21.53	22.01	23.36
	8H	19.56	20.00	20.58	21.03	22.39	20.55	20.99	21.58	22.02	23.39
	12H	19.56	19.96	20.60	21.00	22.37	20.54	20.94	21.58	21.98	23.35
8H	4H	19.65	20.09	20.68	21.12	22.49	20.48	20.92	21.50	21.95	23.31
	6H	20.00	20.37	21.05	21.44	22.80	20.79	21.15	21.84	22.23	23.59
	8H	20.12	20.44	21.18	21.50	22.88	20.89	21.21	21.94	22.26	23.64
	12H	20.16	20.44	21.22	21.49	22.91	20.90	21.18	21.96	22.23	23.66
12H	4H	19.66	20.05	20.70	21.10	22.47	20.44	20.84	21.49	21.89	23.26
	6H	20.07	20.39	21.13	21.45	22.83	20.81	21.13	21.86	22.19	23.57
	8H	20.22	20.50	21.28	21.55	22.97	20.92	21.20	21.98	22.26	23.68