

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1436026

Luminaire Tested: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/24/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1436026  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/24/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - FROSTED CONTINUOUS BATWING ROLL LENS  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10440.3 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.52  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 93.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	50	48	47	42
2	89	81	75	69	81	75	69	65	63	59	56	53	50	47	43	41	39	35
3	81	71	63	57	74	65	59	54	56	51	46	46	43	39	38	35	33	29
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24
5	67	55	47	41	62	51	44	38	43	38	33	36	32	28	30	26	24	21
6	62	49	41	35	56	46	38	33	39	33	29	33	28	25	27	23	21	18
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16	13
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	19	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8578	8578	8578	8578
5°	8363	15194	8363	15194
10°	7832	29568	7832	29568
15°	7089	34032	7089	34032
20°	6276	35640	6276	35640
25°	5553	36224	5553	36224
30°	4905	36671	4905	36671
35°	4380	39424	4380	39424
40°	3983	41890	3983	41890
45°	3674	43863	3674	43863
50°	3464	44660	3464	44660
55°	3381	45016	3381	45016
60°	3465	44791	3465	44791
65°	3610	43525	3610	43525
70°	3739	32922	3739	32922
75°	4142	18166	4142	18166
80°	4277	16866	4277	16866
85°	4261	7095	4261	7095

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 45422 cd/sqm



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.0	0.9
10°-20°	406.2	3.9
20°-30°	714.8	6.8
30°-40°	925.3	8.9
40°-50°	1020.4	9.8
50°-60°	952.4	9.1
60°-70°	735.8	7.0
70°-80°	339.2	3.2
80°-90°	72.2	0.7
90°-100°	141.3	1.4
100°-110°	412.2	3.9
110°-120°	672.6	6.4
120°-130°	853.5	8.2
130°-140°	913.3	8.7
140°-150°	852.8	8.2
150°-160°	701.7	6.7
160°-170°	470.6	4.5
170°-180°	167.1	1.6
0°-30°	1210.0	11.6
0°-40°	2135.3	20.5
0°-60°	4108.1	39.3
0°-90°	5255.2	50.3
90°-120°	1226.1	11.7
90°-150°	3845.7	36.8
90°-180°	5185.0	49.7
0°-180°	10440.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	516	938	516	938	516	48
15°	424	2036	424	2036	424	118
25°	312	2033	312	2033	312	143
35°	222	2000	222	2000	222	140
45°	161	1921	161	1921	161	125
55°	120	1599	120	1599	120	108
65°	94	1139	94	1139	94	93
75°	66	291	66	291	66	68
85°	23	38	23	38	23	24
90°	5	40	5	77	5	5
95°	56	41	56	242	56	67
105°	262	420	262	578	262	279
115°	502	696	502	857	502	495
125°	743	1103	743	1051	743	664
135°	1010	1444	1010	1164	1010	780
145°	1290	1665	1290	1189	1290	807
155°	1532	1808	1532	1234	1532	704
165°	1693	1885	1693	1421	1693	477
175°	1770	1846	1770	1666	1770	168
180°	1776	1776	1776	1776	1776	



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3
2.5°	527.3	537.3	547.2	557.9	568.8	580.6	593.3	604.2	609.7	615.1	609.7
5°	516.0	550.1	584.1	633.5	688.0	749.9	819.2	878.5	908.0	937.5	908.0
7.5°	496.1	565.4	634.6	781.4	953.9	1133.1	1318.8	1472.9	1531.9	1591.0	1531.9
10°	477.7	574.2	670.7	919.6	1219.4	1449.9	1611.1	1739.9	1771.7	1803.5	1771.7
12.5°	457.3	588.3	719.3	1026.6	1392.6	1632.2	1745.3	1838.3	1871.0	1903.7	1871.0
15°	424.1	611.4	798.7	1146.1	1546.9	1793.3	1885.3	1963.3	1999.7	2036.0	1999.7
17.5°	389.8	639.2	888.5	1242.9	1632.3	1872.6	1963.6	2036.8	2056.6	2076.3	2056.6
20°	365.3	658.2	951.1	1306.2	1682.0	1909.1	1987.5	2049.3	2061.8	2074.3	2061.8
22.5°	342.8	670.3	997.7	1353.2	1718.1	1930.2	1989.5	2037.3	2050.7	2064.1	2050.7
25°	311.7	680.6	1049.6	1404.2	1753.9	1947.4	1984.9	2015.3	2024.4	2033.4	2024.4
27.5°	281.5	671.4	1061.3	1411.3	1748.1	1928.7	1953.2	1973.8	1982.7	1991.5	1982.7
30°	263.1	659.4	1055.6	1402.5	1732.8	1907.1	1925.3	1942.0	1954.5	1967.0	1954.5
32.5°	246.8	644.8	1042.9	1385.4	1709.5	1880.1	1897.4	1917.1	1944.1	1971.1	1944.1
35°	222.2	613.9	1005.6	1344.6	1665.9	1840.1	1867.4	1900.3	1950.3	2000.2	1950.3
37.5°	201.3	574.4	947.5	1282.9	1605.8	1795.7	1852.7	1907.5	1955.7	2003.8	1955.7
40°	189.0	546.7	904.3	1237.3	1562.0	1762.4	1838.4	1905.7	1946.6	1987.5	1946.6
42.5°	176.8	515.3	853.9	1184.1	1511.6	1719.7	1808.5	1885.3	1926.1	1967.0	1926.1
45°	160.9	465.2	769.5	1096.8	1431.7	1651.4	1755.8	1843.8	1882.4	1921.0	1882.4
47.5°	146.1	410.4	674.7	1003.4	1353.6	1584.1	1694.9	1785.0	1813.2	1841.3	1813.2
50°	137.9	374.1	610.3	940.1	1301.1	1536.1	1645.1	1732.6	1755.3	1778.0	1755.3
52.5°	129.8	338.7	547.6	878.1	1249.1	1486.0	1588.6	1670.8	1691.7	1712.6	1691.7
55°	120.1	290.4	460.7	787.7	1166.9	1401.3	1491.0	1562.8	1581.0	1599.2	1581.0
57.5°	111.4	248.8	386.1	702.8	1079.3	1305.8	1382.4	1443.4	1458.2	1473.0	1458.2
60°	107.3	226.5	345.7	649.7	1015.3	1232.7	1302.0	1357.6	1372.4	1387.1	1372.4
62.5°	101.2	204.9	308.7	596.6	945.8	1152.3	1216.1	1267.5	1281.3	1295.2	1281.3
65°	94.5	178.5	262.6	522.0	839.9	1025.5	1078.9	1121.2	1130.3	1139.3	1130.3
67.5°	85.3	156.6	227.9	453.7	730.9	886.1	919.3	939.9	922.9	905.8	922.9
70°	79.2	145.0	210.9	412.1	658.5	787.4	798.7	795.0	746.2	697.4	746.2
72.5°	75.1	133.7	192.3	366.5	579.3	673.2	648.2	606.3	513.9	421.5	513.9
75°	66.4	114.1	161.8	292.9	451.9	476.9	367.9	286.7	288.9	291.2	288.9
77.5°	54.2	89.8	125.5	206.1	301.7	320.6	262.9	220.2	222.2	224.3	222.2
80°	46.0	74.4	102.8	134.5	167.5	182.8	180.5	179.1	180.2	181.4	180.2
82.5°	37.8	58.9	80.0	99.1	117.5	127.8	130.1	131.4	129.8	128.2	129.8
85°	23.0	35.5	48.0	55.3	61.0	59.3	50.2	42.9	40.6	38.3	40.6
87.5°	9.3	15.2	21.6	21.4	18.9	17.4	17.4	17.8	18.1	18.1	18.1
90°	5.4	12.6	21.5	28.7	34.1	35.9	35.9	37.7	39.5	39.5	39.5
92.5°	19.7	31.2	31.6	31.6	38.4	41.6	44.5	44.8	46.6	46.6	46.6
95°	55.6	61.0	91.5	89.7	61.0	48.4	41.3	41.3	41.3	41.3	41.3
97.5°	106.2	114.1	119.1	159.6	168.6	162.9	132.7	111.6	99.7	94.4	99.7
100°	150.7	154.3	165.0	166.8	211.7	254.7	233.2	206.3	197.3	191.9	197.3
102.5°	195.2	197.3	213.8	221.4	231.8	256.2	330.8	322.5	316.4	315.3	316.4
105°	261.9	263.7	294.2	308.5	315.7	315.7	313.9	349.8	407.2	419.7	407.2
107.5°	333.3	341.5	377.4	415.8	424.0	426.2	416.9	411.5	409.3	410.8	409.3
110°	382.1	394.6	437.7	486.1	498.7	502.3	498.7	493.3	489.7	489.7	489.7



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	429.4	447.7	496.5	552.1	573.3	584.1	576.2	572.2	568.6	571.5	568.6
115°	502.3	529.2	593.7	651.1	694.2	699.6	697.8	697.8	696.0	696.0	696.0
117.5°	569.7	612.8	685.2	752.0	801.8	816.2	823.3	821.2	819.0	822.6	819.0
120°	617.1	667.3	749.8	825.1	873.6	895.1	902.3	898.7	902.3	898.7	902.3
122.5°	667.3	729.0	810.1	888.3	945.3	969.7	978.3	979.0	979.8	977.6	979.8
125°	742.6	818.0	913.0	993.8	1052.9	1081.6	1088.8	1090.6	1094.2	1103.2	1094.2
127.5°	818.7	904.1	1008.5	1086.3	1146.9	1181.7	1192.9	1196.8	1204.3	1208.3	1204.3
130°	871.8	968.6	1074.5	1148.0	1207.2	1244.9	1264.6	1270.0	1279.0	1277.2	1279.0
132.5°	927.7	1028.9	1136.2	1212.6	1267.5	1308.0	1324.9	1340.3	1343.5	1346.1	1343.5
135°	1009.9	1119.3	1226.9	1302.3	1354.3	1393.8	1415.3	1429.6	1438.6	1444.0	1438.6
137.5°	1096.4	1211.9	1315.2	1382.3	1434.7	1468.7	1493.1	1508.2	1517.5	1521.8	1517.5
140°	1155.2	1266.4	1366.9	1436.8	1483.5	1517.5	1539.1	1557.0	1567.8	1567.8	1567.8
142.5°	1211.2	1320.9	1418.5	1488.5	1529.4	1560.6	1583.5	1597.2	1609.4	1609.4	1609.4
145°	1289.7	1399.1	1488.8	1558.8	1592.9	1621.6	1646.7	1657.5	1664.6	1664.6	1664.6
147.5°	1371.9	1468.7	1550.5	1617.6	1646.3	1680.1	1699.8	1708.4	1717.4	1713.4	1717.4
150°	1420.7	1510.4	1589.3	1652.1	1680.8	1713.1	1732.8	1740.0	1748.9	1743.6	1748.9
152.5°	1468.0	1553.4	1625.2	1683.6	1708.0	1740.3	1762.9	1770.1	1776.2	1772.3	1776.2
155°	1531.9	1607.2	1673.6	1727.4	1748.9	1779.4	1801.0	1809.9	1817.1	1808.1	1817.1
157.5°	1588.9	1653.9	1711.6	1761.1	1784.1	1810.3	1830.4	1841.5	1848.7	1844.7	1848.7
160°	1623.4	1682.6	1734.6	1781.2	1802.7	1826.1	1847.6	1860.1	1867.3	1861.9	1867.3
162.5°	1652.1	1705.5	1754.7	1797.0	1815.7	1836.1	1861.9	1873.1	1880.2	1873.4	1880.2
165°	1693.3	1736.4	1779.4	1815.3	1831.4	1847.6	1874.5	1887.1	1892.4	1885.3	1892.4
167.5°	1724.5	1757.5	1792.3	1823.2	1835.0	1850.8	1877.7	1888.1	1894.9	1886.0	1894.9
170°	1741.8	1770.5	1801.0	1826.1	1835.0	1849.4	1876.3	1885.3	1890.6	1881.7	1890.6
172.5°	1756.1	1777.6	1802.4	1824.6	1829.3	1840.8	1866.2	1875.2	1879.2	1871.6	1879.2
175°	1770.5	1783.0	1801.0	1815.3	1813.5	1820.7	1842.2	1849.4	1856.6	1845.8	1856.6
177.5°	1777.3	1783.0	1788.8	1797.4	1791.6	1791.6	1807.4	1811.7	1813.2	1807.4	1813.2
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3
2.5°	604.2	593.3	580.6	568.8	557.9	547.2	537.3	527.3	537.3	547.2	557.9
5°	878.5	819.2	749.9	688.0	633.5	584.1	550.1	516.0	550.1	584.1	633.5
7.5°	1472.9	1318.8	1133.1	953.9	781.4	634.6	565.4	496.1	565.4	634.6	781.4
10°	1739.9	1611.1	1449.9	1219.4	919.6	670.7	574.2	477.7	574.2	670.7	919.6
12.5°	1838.3	1745.3	1632.2	1392.6	1026.6	719.3	588.3	457.3	588.3	719.3	1026.6
15°	1963.3	1885.3	1793.3	1546.9	1146.1	798.7	611.4	424.1	611.4	798.7	1146.1
17.5°	2036.8	1963.6	1872.6	1632.3	1242.9	888.5	639.2	389.8	639.2	888.5	1242.9
20°	2049.3	1987.5	1909.1	1682.0	1306.2	951.1	658.2	365.3	658.2	951.1	1306.2
22.5°	2037.3	1989.5	1930.2	1718.1	1353.2	997.7	670.3	342.8	670.3	997.7	1353.2
25°	2015.3	1984.9	1947.4	1753.9	1404.2	1049.6	680.6	311.7	680.6	1049.6	1404.2
27.5°	1973.8	1953.2	1928.7	1748.1	1411.3	1061.3	671.4	281.5	671.4	1061.3	1411.3
30°	1942.0	1925.3	1907.1	1732.8	1402.5	1055.6	659.4	263.1	659.4	1055.6	1402.5
32.5°	1917.1	1897.4	1880.1	1709.5	1385.4	1042.9	644.8	246.8	644.8	1042.9	1385.4
35°	1900.3	1867.4	1840.1	1665.9	1344.6	1005.6	613.9	222.2	613.9	1005.6	1344.6
37.5°	1907.5	1852.7	1795.7	1605.8	1282.9	947.5	574.4	201.3	574.4	947.5	1282.9
40°	1905.7	1838.4	1762.4	1562.0	1237.3	904.3	546.7	189.0	546.7	904.3	1237.3
42.5°	1885.3	1808.5	1719.7	1511.6	1184.1	853.9	515.3	176.8	515.3	853.9	1184.1
45°	1843.8	1755.8	1651.4	1431.7	1096.8	769.5	465.2	160.9	465.2	769.5	1096.8
47.5°	1785.0	1694.9	1584.1	1353.6	1003.4	674.7	410.4	146.1	410.4	674.7	1003.4
50°	1732.6	1645.1	1536.1	1301.1	940.1	610.3	374.1	137.9	374.1	610.3	940.1
52.5°	1670.8	1588.6	1486.0	1249.1	878.1	547.6	338.7	129.8	338.7	547.6	878.1
55°	1562.8	1491.0	1401.3	1166.9	787.7	460.7	290.4	120.1	290.4	460.7	787.7
57.5°	1443.4	1382.4	1305.8	1079.3	702.8	386.1	248.8	111.4	248.8	386.1	702.8
60°	1357.6	1302.0	1232.7	1015.3	649.7	345.7	226.5	107.3	226.5	345.7	649.7
62.5°	1267.5	1216.1	1152.3	945.8	596.6	308.7	204.9	101.2	204.9	308.7	596.6
65°	1121.2	1078.9	1025.5	839.9	522.0	262.6	178.5	94.5	178.5	262.6	522.0
67.5°	939.9	919.3	886.1	730.9	453.7	227.9	156.6	85.3	156.6	227.9	453.7
70°	795.0	798.7	787.4	658.5	412.1	210.9	145.0	79.2	145.0	210.9	412.1
72.5°	606.3	648.2	673.2	579.3	366.5	192.3	133.7	75.1	133.7	192.3	366.5
75°	286.7	367.9	476.9	451.9	292.9	161.8	114.1	66.4	114.1	161.8	292.9
77.5°	220.2	262.9	320.6	301.7	206.1	125.5	89.8	54.2	89.8	125.5	206.1
80°	179.1	180.5	182.8	167.5	134.5	102.8	74.4	46.0	74.4	102.8	134.5
82.5°	131.4	130.1	127.8	117.5	99.1	80.0	58.9	37.8	58.9	80.0	99.1
85°	42.9	50.2	59.3	61.0	55.3	48.0	35.5	23.0	35.5	48.0	55.3
87.5°	17.8	17.4	17.4	18.9	21.4	21.6	15.2	9.3	15.2	21.2	22.1
90°	37.7	35.9	35.9	34.1	28.7	21.5	12.6	5.4	12.6	19.7	32.3
92.5°	44.8	44.5	41.6	38.4	31.6	31.6	31.2	19.7	34.1	48.4	69.6
95°	41.3	41.3	48.4	61.0	89.7	91.5	61.0	55.6	78.9	111.2	139.9
97.5°	111.6	132.7	162.9	168.6	159.6	119.1	114.1	106.2	144.6	176.5	222.8
100°	206.3	233.2	254.7	211.7	166.8	165.0	154.3	150.7	191.9	222.4	267.3
102.5°	322.5	330.8	256.2	231.8	221.4	213.8	197.3	195.2	236.4	278.4	316.1
105°	349.8	313.9	315.7	315.7	308.5	294.2	263.7	261.9	308.5	357.0	403.6
107.5°	411.5	416.9	426.2	424.0	415.8	377.4	341.5	333.3	375.3	433.4	484.7
110°	493.3	498.7	502.3	498.7	486.1	437.7	394.6	382.1	419.7	480.7	536.3



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	572.2	576.2	584.1	573.3	552.1	496.5	447.7	429.4	467.1	529.5	586.6
115°	697.8	697.8	699.6	694.2	651.1	593.7	529.2	502.3	534.5	591.9	654.7
117.5°	821.2	823.3	816.2	801.8	752.0	685.2	612.8	569.7	595.2	655.8	720.4
120°	898.7	902.3	895.1	873.6	825.1	749.8	667.3	617.1	636.8	696.0	760.6
122.5°	979.0	978.3	969.7	945.3	888.3	810.1	729.0	667.3	675.5	730.4	793.6
125°	1090.6	1088.8	1081.6	1052.9	993.8	913.0	818.0	742.6	731.9	778.5	843.1
127.5°	1196.8	1192.9	1181.7	1146.9	1086.3	1008.5	904.1	818.7	794.6	824.1	883.3
130°	1270.0	1264.6	1244.9	1207.2	1148.0	1074.5	968.6	871.8	837.7	855.6	907.7
132.5°	1340.3	1324.9	1308.0	1267.5	1212.6	1136.2	1028.9	927.7	880.7	888.6	929.2
135°	1429.6	1415.3	1393.8	1354.3	1302.3	1226.9	1119.3	1009.9	945.3	938.1	961.5
137.5°	1508.2	1493.1	1468.7	1434.7	1382.3	1315.2	1211.9	1096.4	1014.9	990.9	999.9
140°	1557.0	1539.1	1517.5	1483.5	1436.8	1366.9	1266.4	1155.2	1063.7	1029.6	1024.2
142.5°	1597.2	1583.5	1560.6	1529.4	1488.5	1418.5	1320.9	1211.2	1113.9	1069.8	1057.3
145°	1657.5	1646.7	1621.6	1592.9	1558.8	1488.8	1399.1	1289.7	1192.9	1135.5	1108.6
147.5°	1708.4	1699.8	1680.1	1646.3	1617.6	1550.5	1468.7	1371.9	1272.5	1201.5	1166.7
150°	1740.0	1732.8	1713.1	1680.8	1652.1	1589.3	1510.4	1420.7	1325.6	1250.3	1205.4
152.5°	1770.1	1762.9	1740.3	1708.0	1683.6	1625.2	1553.4	1468.0	1371.5	1296.2	1249.9
155°	1809.9	1801.0	1779.4	1748.9	1727.4	1673.6	1607.2	1531.9	1449.4	1370.4	1318.4
157.5°	1841.5	1830.4	1810.3	1784.1	1761.1	1711.6	1653.9	1588.9	1516.8	1441.5	1388.4
160°	1860.1	1847.6	1826.1	1802.7	1781.2	1734.6	1682.6	1623.4	1557.0	1488.8	1431.4
162.5°	1873.1	1861.9	1836.1	1815.7	1797.0	1754.7	1705.5	1652.1	1592.9	1533.3	1480.2
165°	1887.1	1874.5	1847.6	1831.4	1815.3	1779.4	1736.4	1693.3	1643.1	1594.7	1551.6
167.5°	1888.1	1877.7	1850.8	1835.0	1823.2	1792.3	1757.5	1724.5	1685.4	1647.4	1611.5
170°	1885.3	1876.3	1849.4	1835.0	1826.1	1801.0	1770.5	1741.8	1711.3	1679.0	1650.3
172.5°	1875.2	1866.2	1840.8	1829.3	1824.6	1802.4	1777.6	1756.1	1729.9	1706.2	1683.3
175°	1849.4	1842.2	1820.7	1813.5	1815.3	1801.0	1783.0	1770.5	1754.3	1740.0	1727.4
177.5°	1811.7	1807.4	1791.6	1791.6	1797.4	1788.8	1783.0	1777.3	1770.1	1765.8	1761.5
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3	531.3
2.5°	568.8	580.6	593.3	604.2	609.7	615.1	609.7	604.2	593.3	580.6	568.8
5°	688.0	749.9	819.2	878.5	908.0	937.5	908.0	878.5	819.2	749.9	688.0
7.5°	953.9	1133.1	1318.8	1472.9	1531.9	1591.0	1531.9	1472.9	1318.8	1133.1	953.9
10°	1219.4	1449.9	1611.1	1739.9	1771.7	1803.5	1771.7	1739.9	1611.1	1449.9	1219.4
12.5°	1392.6	1632.2	1745.3	1838.3	1871.0	1903.7	1871.0	1838.3	1745.3	1632.2	1392.6
15°	1546.9	1793.3	1885.3	1963.3	1999.7	2036.0	1999.7	1963.3	1885.3	1793.3	1546.9
17.5°	1632.3	1872.6	1963.6	2036.8	2056.6	2076.3	2056.6	2036.8	1963.6	1872.6	1632.3
20°	1682.0	1909.1	1987.5	2049.3	2061.8	2074.3	2061.8	2049.3	1987.5	1909.1	1682.0
22.5°	1718.1	1930.2	1989.5	2037.3	2050.7	2064.1	2050.7	2037.3	1989.5	1930.2	1718.1
25°	1753.9	1947.4	1984.9	2015.3	2024.4	2033.4	2024.4	2015.3	1984.9	1947.4	1753.9
27.5°	1748.1	1928.7	1953.2	1973.8	1982.7	1991.5	1982.7	1973.8	1953.2	1928.7	1748.1
30°	1732.8	1907.1	1925.3	1942.0	1954.5	1967.0	1954.5	1942.0	1925.3	1907.1	1732.8
32.5°	1709.5	1880.1	1897.4	1917.1	1944.1	1971.1	1944.1	1917.1	1897.4	1880.1	1709.5
35°	1665.9	1840.1	1867.4	1900.3	1950.3	2000.2	1950.3	1900.3	1867.4	1840.1	1665.9
37.5°	1605.8	1795.7	1852.7	1907.5	1955.7	2003.8	1955.7	1907.5	1852.7	1795.7	1605.8
40°	1562.0	1762.4	1838.4	1905.7	1946.6	1987.5	1946.6	1905.7	1838.4	1762.4	1562.0
42.5°	1511.6	1719.7	1808.5	1885.3	1926.1	1967.0	1926.1	1885.3	1808.5	1719.7	1511.6
45°	1431.7	1651.4	1755.8	1843.8	1882.4	1921.0	1882.4	1843.8	1755.8	1651.4	1431.7
47.5°	1353.6	1584.1	1694.9	1785.0	1813.2	1841.3	1813.2	1785.0	1694.9	1584.1	1353.6
50°	1301.1	1536.1	1645.1	1732.6	1755.3	1778.0	1755.3	1732.6	1645.1	1536.1	1301.1
52.5°	1249.1	1486.0	1588.6	1670.8	1691.7	1712.6	1691.7	1670.8	1588.6	1486.0	1249.1
55°	1166.9	1401.3	1491.0	1562.8	1581.0	1599.2	1581.0	1562.8	1491.0	1401.3	1166.9
57.5°	1079.3	1305.8	1382.4	1443.4	1458.2	1473.0	1458.2	1443.4	1382.4	1305.8	1079.3
60°	1015.3	1232.7	1302.0	1357.6	1372.4	1387.1	1372.4	1357.6	1302.0	1232.7	1015.3
62.5°	945.8	1152.3	1216.1	1267.5	1281.3	1295.2	1281.3	1267.5	1216.1	1152.3	945.8
65°	839.9	1025.5	1078.9	1121.2	1130.3	1139.3	1130.3	1121.2	1078.9	1025.5	839.9
67.5°	730.9	886.1	919.3	939.9	922.9	905.8	922.9	939.9	919.3	886.1	730.9
70°	658.5	787.4	798.7	795.0	746.2	697.4	746.2	795.0	798.7	787.4	658.5
72.5°	579.3	673.2	648.2	606.3	513.9	421.5	513.9	606.3	648.2	673.2	579.3
75°	451.9	476.9	367.9	286.7	288.9	291.2	288.9	286.7	367.9	476.9	451.9
77.5°	301.7	320.6	262.9	220.2	222.2	224.3	222.2	220.2	262.9	320.6	301.7
80°	167.5	182.8	180.5	179.1	180.2	181.4	180.2	179.1	180.5	182.8	167.5
82.5°	117.5	127.8	130.1	131.4	129.8	128.2	129.8	131.4	130.1	127.8	117.5
85°	61.0	59.3	50.2	42.9	40.6	38.3	40.6	42.9	50.2	59.3	61.0
87.5°	20.3	21.0	23.5	24.9	26.4	25.6	26.4	24.9	23.5	21.0	20.3
90°	41.3	53.8	66.4	73.5	80.7	77.1	80.7	73.5	66.4	53.8	41.3
92.5°	82.9	104.0	119.5	132.4	138.1	137.4	138.1	132.4	119.5	104.0	82.9
95°	166.8	191.9	217.0	235.0	245.7	242.2	245.7	235.0	217.0	191.9	166.8
97.5°	257.2	291.0	318.9	335.8	346.6	353.7	346.6	335.8	318.9	291.0	257.2
100°	317.5	349.8	382.1	401.8	419.7	426.9	419.7	401.8	382.1	349.8	317.5
102.5°	366.3	408.6	443.8	464.9	480.0	487.2	480.0	464.9	443.8	408.6	366.3
105°	446.7	491.5	529.2	556.1	572.2	577.6	572.2	556.1	529.2	491.5	446.7
107.5°	527.0	573.3	608.1	637.9	657.6	669.1	657.6	637.9	608.1	573.3	527.0
110°	590.2	627.8	665.5	692.4	712.1	719.3	712.1	692.4	665.5	627.8	590.2



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	643.2	685.2	722.9	749.8	772.4	782.4	772.4	749.8	722.9	685.2	643.2
115°	717.5	773.1	807.2	832.3	848.5	857.4	848.5	832.3	807.2	773.1	717.5
117.5°	779.2	837.3	874.6	894.0	901.6	908.0	901.6	894.0	874.6	837.3	779.2
120°	818.0	871.8	914.8	939.9	948.9	952.5	948.9	939.9	914.8	871.8	818.0
122.5°	853.8	904.8	946.4	977.3	992.0	995.5	992.0	977.3	946.4	904.8	853.8
125°	904.1	952.5	995.5	1026.0	1042.2	1051.2	1042.2	1026.0	995.5	952.5	904.1
127.5°	947.8	1000.2	1039.7	1067.3	1083.1	1090.3	1083.1	1067.3	1039.7	1000.2	947.8
130°	972.2	1026.0	1065.5	1096.0	1110.3	1117.5	1110.3	1096.0	1065.5	1026.0	972.2
132.5°	990.9	1047.6	1088.5	1116.1	1131.9	1139.0	1131.9	1116.1	1088.5	1047.6	990.9
135°	1013.5	1072.7	1115.7	1142.6	1157.0	1164.2	1157.0	1142.6	1115.7	1072.7	1013.5
137.5°	1033.2	1087.0	1131.9	1160.2	1173.1	1177.8	1173.1	1160.2	1131.9	1087.0	1033.2
140°	1047.6	1094.2	1139.0	1166.0	1180.3	1182.1	1180.3	1166.0	1139.0	1094.2	1047.6
142.5°	1066.2	1102.8	1141.9	1168.8	1183.2	1186.4	1183.2	1168.8	1141.9	1102.8	1066.2
145°	1099.6	1121.1	1148.0	1173.1	1185.7	1189.3	1185.7	1173.1	1148.0	1121.1	1099.6
147.5°	1141.6	1148.4	1162.4	1178.9	1191.1	1193.6	1191.1	1178.9	1162.4	1148.4	1141.6
150°	1173.1	1171.3	1176.7	1187.5	1198.2	1196.5	1198.2	1187.5	1176.7	1171.3	1173.1
152.5°	1209.0	1198.6	1198.2	1203.3	1208.3	1207.9	1208.3	1203.3	1198.2	1198.6	1209.0
155°	1270.0	1250.3	1239.5	1235.9	1235.9	1234.1	1235.9	1235.9	1239.5	1250.3	1270.0
157.5°	1337.1	1309.5	1293.3	1284.7	1282.2	1278.2	1282.2	1284.7	1293.3	1309.5	1337.1
160°	1383.0	1352.5	1336.4	1322.0	1316.6	1311.3	1316.6	1322.0	1336.4	1352.5	1383.0
162.5°	1426.1	1397.0	1379.4	1366.5	1361.1	1352.9	1361.1	1366.5	1379.4	1397.0	1426.1
165°	1496.0	1465.5	1445.8	1435.0	1427.8	1420.7	1427.8	1435.0	1445.8	1465.5	1496.0
167.5°	1566.0	1532.6	1519.7	1507.5	1500.7	1487.8	1500.7	1507.5	1519.7	1532.6	1566.0
170°	1609.0	1578.5	1571.4	1560.6	1548.0	1533.7	1548.0	1560.6	1571.4	1578.5	1609.0
172.5°	1646.3	1625.9	1618.7	1607.9	1604.0	1592.5	1604.0	1607.9	1618.7	1625.9	1646.3
175°	1700.5	1684.4	1684.4	1682.6	1677.2	1666.4	1677.2	1682.6	1684.4	1684.4	1700.5
177.5°	1745.7	1737.1	1742.8	1742.8	1741.4	1731.4	1741.4	1742.8	1742.8	1737.1	1745.7
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	531.3	531.3	531.3	531.3
2.5°	557.9	547.2	537.3	527.3
5°	633.5	584.1	550.1	516.0
7.5°	781.4	634.6	565.4	496.1
10°	919.6	670.7	574.2	477.7
12.5°	1026.6	719.3	588.3	457.3
15°	1146.1	798.7	611.4	424.1
17.5°	1242.9	888.5	639.2	389.8
20°	1306.2	951.1	658.2	365.3
22.5°	1353.2	997.7	670.3	342.8
25°	1404.2	1049.6	680.6	311.7
27.5°	1411.3	1061.3	671.4	281.5
30°	1402.5	1055.6	659.4	263.1
32.5°	1385.4	1042.9	644.8	246.8
35°	1344.6	1005.6	613.9	222.2
37.5°	1282.9	947.5	574.4	201.3
40°	1237.3	904.3	546.7	189.0
42.5°	1184.1	853.9	515.3	176.8
45°	1096.8	769.5	465.2	160.9
47.5°	1003.4	674.7	410.4	146.1
50°	940.1	610.3	374.1	137.9
52.5°	878.1	547.6	338.7	129.8
55°	787.7	460.7	290.4	120.1
57.5°	702.8	386.1	248.8	111.4
60°	649.7	345.7	226.5	107.3
62.5°	596.6	308.7	204.9	101.2
65°	522.0	262.6	178.5	94.5
67.5°	453.7	227.9	156.6	85.3
70°	412.1	210.9	145.0	79.2
72.5°	366.5	192.3	133.7	75.1
75°	292.9	161.8	114.1	66.4
77.5°	206.1	125.5	89.8	54.2
80°	134.5	102.8	74.4	46.0
82.5°	99.1	80.0	58.9	37.8
85°	55.3	48.0	35.5	23.0
87.5°	22.1	21.2	15.2	9.3
90°	32.3	19.7	12.6	5.4
92.5°	69.6	48.4	34.1	19.7
95°	139.9	111.2	78.9	55.6
97.5°	222.8	176.5	144.6	106.2
100°	267.3	222.4	191.9	150.7
102.5°	316.1	278.4	236.4	195.2
105°	403.6	357.0	308.5	261.9
107.5°	484.7	433.4	375.3	333.3
110°	536.3	480.7	419.7	382.1



TEST NUMBER: P1436026

CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	586.6	529.5	467.1	429.4
115°	654.7	591.9	534.5	502.3
117.5°	720.4	655.8	595.2	569.7
120°	760.6	696.0	636.8	617.1
122.5°	793.6	730.4	675.5	667.3
125°	843.1	778.5	731.9	742.6
127.5°	883.3	824.1	794.6	818.7
130°	907.7	855.6	837.7	871.8
132.5°	929.2	888.6	880.7	927.7
135°	961.5	938.1	945.3	1009.9
137.5°	999.9	990.9	1014.9	1096.4
140°	1024.2	1029.6	1063.7	1155.2
142.5°	1057.3	1069.8	1113.9	1211.2
145°	1108.6	1135.5	1192.9	1289.7
147.5°	1166.7	1201.5	1272.5	1371.9
150°	1205.4	1250.3	1325.6	1420.7
152.5°	1249.9	1296.2	1371.5	1468.0
155°	1318.4	1370.4	1449.4	1531.9
157.5°	1388.4	1441.5	1516.8	1588.9
160°	1431.4	1488.8	1557.0	1623.4
162.5°	1480.2	1533.3	1592.9	1652.1
165°	1551.6	1594.7	1643.1	1693.3
167.5°	1611.5	1647.4	1685.4	1724.5
170°	1650.3	1679.0	1711.3	1741.8
172.5°	1683.3	1706.2	1729.9	1756.1
175°	1727.4	1740.0	1754.3	1770.5
177.5°	1761.5	1765.8	1770.1	1777.3
180°	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1436026  
 CATALOG NUMBER: SQ2W-FB-K-125U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.67	14.56	14.62	15.53	16.80	23.27	24.16	24.22	25.13	26.39
	3H	14.61	15.41	15.57	16.39	17.68	24.88	25.68	25.84	26.65	27.94
	4H	15.01	15.77	15.99	16.75	18.05	25.06	25.81	26.03	26.79	28.09
	6H	15.27	15.97	16.25	16.95	18.26	25.13	25.83	26.12	26.82	28.13
	8H	15.36	16.03	16.35	17.03	18.34	25.15	25.82	26.14	26.82	28.12
	12H	15.41	16.04	16.41	17.04	18.37	25.13	25.76	26.13	26.76	28.09
4H	2H	18.40	19.15	19.38	20.13	21.43	23.64	24.40	24.62	25.38	26.67
	3H	19.53	20.16	20.52	21.17	22.48	25.53	26.16	26.52	27.17	28.48
	4H	19.81	20.39	20.81	21.39	22.72	25.75	26.33	26.75	27.33	28.67
	6H	19.95	20.44	20.96	21.47	22.80	25.89	26.38	26.90	27.41	28.74
	8H	19.99	20.45	21.00	21.47	22.82	25.93	26.39	26.94	27.42	28.76
	12H	19.99	20.41	21.02	21.45	22.80	25.91	26.33	26.95	27.37	28.72
8H	4H	21.01	21.47	22.02	22.49	23.84	25.85	26.31	26.86	27.33	28.68
	6H	21.27	21.65	22.30	22.71	24.05	26.04	26.43	27.08	27.49	28.83
	8H	21.36	21.70	22.41	22.75	24.11	26.13	26.47	27.18	27.52	28.88
	12H	21.41	21.70	22.46	22.75	24.15	26.14	26.44	27.19	27.48	28.89
12H	4H	21.03	21.45	22.06	22.49	23.84	25.80	26.22	26.83	27.25	28.60
	6H	21.37	21.71	22.42	22.76	24.12	26.03	26.36	27.07	27.41	28.77
	8H	21.51	21.81	22.56	22.85	24.26	26.13	26.42	27.18	27.47	28.87