

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428382

Luminaire Tested: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428382
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5568.5 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 41.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	102	98	94	90	95	92	89	86	81	79	76	71	69	68	62	61	60	55
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47
3	85	76	69	63	80	72	66	61	64	59	55	57	53	50	50	47	45	41
4	79	68	60	54	74	64	57	52	57	52	48	51	47	43	45	42	39	36
5	72	61	53	47	68	58	51	45	52	46	42	46	42	38	41	37	34	32
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31	28
7	62	50	42	37	58	48	40	35	43	37	33	38	34	30	34	30	27	25
8	58	46	38	33	54	43	36	32	39	33	29	35	31	27	32	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23	21
10	51	39	31	27	48	37	30	26	33	28	24	30	26	22	27	23	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25868	25868	25868	25868
5°	25695	26141	25695	26141
10°	25743	26367	25743	26367
15°	25736	26527	25736	26527
20°	25747	26008	25747	26008
25°	25607	24166	25607	24166
30°	25433	21848	25433	21848
35°	25233	19730	25233	19730
40°	24731	17430	24731	17430
45°	23763	15225	23763	15225
50°	22116	13031	22116	13031
55°	20231	10567	20231	10567
60°	18131	9116	18131	9116
65°	15855	8103	15855	8103
70°	12968	7345	12968	7345
75°	10087	6756	10087	6756
80°	7522	5960	7522	5960
85°	5094	3390	5094	3390

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23763 cd/sqm



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.6	2.7
10°-20°	442.1	7.9
20°-30°	650.5	11.7
30°-40°	711.3	12.8
40°-50°	638.1	11.5
50°-60°	476.0	8.5
60°-70°	300.8	5.4
70°-80°	149.0	2.7
80°-90°	37.7	0.7
90°-100°	54.8	1.0
100°-110°	159.8	2.9
110°-120°	260.8	4.7
120°-130°	330.9	5.9
130°-140°	354.1	6.4
140°-150°	330.7	5.9
150°-160°	272.1	4.9
160°-170°	182.5	3.3
170°-180°	64.8	1.2
0°-30°	1245.2	22.4
0°-40°	1956.4	35.1
0°-60°	3070.5	55.1
0°-90°	3558.1	63.9
90°-120°	475.4	8.5
90°-150°	1491.1	26.8
90°-180°	2010.0	36.1
0°-180°	5568.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1602	1602	1602	1602	1602	
5°	1585	1613	1585	1613	1585	151
15°	1540	1587	1540	1587	1540	435
25°	1437	1356	1437	1356	1437	662
35°	1280	1001	1280	1001	1280	798
45°	1041	667	1041	667	1041	798
55°	719	375	719	375	719	642
65°	415	212	415	212	415	411
75°	162	108	162	108	162	178
85°	28	18	28	18	28	35
90°	2	15	2	30	2	3
95°	22	16	22	94	22	26
105°	102	163	102	224	102	108
115°	195	270	195	332	195	192
125°	288	428	288	408	288	258
135°	392	560	392	451	392	303
145°	500	645	500	461	500	313
155°	594	701	594	478	594	273
165°	657	731	657	551	657	185
175°	686	716	686	646	686	65
180°	689	689	689	689	689	



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2
2.5°	1591.2	1600.5	1609.7	1607.5	1601.5	1598.8	1599.4	1600.2	1601.8	1603.4	1601.8
5°	1585.4	1597.0	1608.5	1606.8	1600.7	1598.0	1598.7	1600.7	1606.8	1612.9	1606.8
7.5°	1577.5	1589.2	1600.8	1600.3	1595.7	1594.5	1596.8	1600.0	1606.0	1612.0	1606.0
10°	1570.2	1582.4	1594.6	1594.6	1590.5	1590.2	1593.6	1597.5	1602.9	1608.3	1602.9
12.5°	1560.4	1573.2	1585.9	1586.9	1583.9	1584.3	1588.3	1592.6	1598.0	1603.4	1598.0
15°	1539.7	1553.2	1566.8	1569.7	1569.0	1571.0	1575.8	1580.2	1583.6	1587.0	1583.6
17.5°	1515.5	1529.1	1542.7	1545.3	1544.4	1544.5	1545.8	1547.1	1548.7	1550.3	1548.7
20°	1498.5	1512.0	1525.6	1527.4	1525.4	1522.0	1517.3	1513.7	1513.7	1513.7	1513.7
22.5°	1474.0	1488.7	1503.3	1503.4	1498.7	1489.9	1477.0	1466.2	1461.9	1457.6	1461.9
25°	1437.4	1451.7	1465.9	1459.3	1445.7	1425.7	1399.3	1376.9	1366.7	1356.5	1366.7
27.5°	1394.7	1406.2	1417.7	1400.5	1373.6	1341.4	1303.8	1272.1	1258.0	1243.9	1258.0
30°	1364.2	1373.0	1381.8	1354.5	1315.2	1274.8	1233.5	1199.0	1185.5	1171.9	1185.5
32.5°	1332.4	1335.8	1339.2	1303.2	1254.1	1208.1	1165.1	1129.2	1114.5	1099.9	1114.5
35°	1280.2	1274.1	1268.0	1220.2	1158.5	1106.0	1062.5	1026.8	1013.9	1001.0	1013.9
37.5°	1218.6	1200.4	1182.2	1128.4	1062.6	1007.0	961.5	923.9	909.7	895.4	909.7
40°	1173.4	1147.7	1121.9	1064.1	995.6	938.6	893.2	855.5	841.3	827.0	841.3
42.5°	1123.4	1091.1	1058.8	999.4	930.9	873.9	828.5	790.7	775.9	761.1	775.9
45°	1040.7	1002.7	964.7	902.8	833.0	776.0	731.9	695.3	681.1	666.8	681.1
47.5°	947.6	909.9	872.2	810.5	740.7	684.5	641.8	606.7	594.5	582.3	594.5
50°	880.5	843.8	807.2	748.2	681.7	627.2	584.4	548.7	533.7	518.8	533.7
52.5°	812.1	779.3	746.4	689.6	624.8	570.5	526.6	488.7	468.4	448.0	468.4
55°	718.7	687.5	656.3	602.7	541.7	486.8	437.9	398.4	386.9	375.4	386.9
57.5°	622.6	595.6	568.6	520.4	465.2	415.5	371.1	335.5	326.0	316.5	326.0
60°	561.5	537.8	514.1	467.9	414.4	368.9	331.6	301.3	291.8	282.3	291.8
62.5°	502.9	481.9	460.9	416.7	364.7	323.9	294.2	270.0	262.1	254.2	262.1
65°	415.0	399.5	383.9	347.4	304.0	270.1	245.7	225.7	218.9	212.1	218.9
67.5°	329.6	320.9	312.2	284.9	251.4	224.0	202.5	185.3	180.9	176.4	180.9
70°	274.7	272.0	269.2	246.7	217.5	194.1	176.5	162.4	159.0	155.6	159.0
72.5°	227.1	228.1	229.2	210.5	185.1	165.5	151.7	140.7	138.4	136.1	138.4
75°	161.7	167.2	172.6	160.2	141.9	128.0	118.5	111.1	109.7	108.3	109.7
77.5°	110.2	118.3	126.4	118.4	105.0	94.7	87.7	82.1	81.0	80.0	81.0
80°	80.9	89.0	97.2	91.6	81.4	73.6	68.2	64.1	64.1	64.1	64.1
82.5°	56.5	63.0	69.5	65.5	58.1	53.0	50.3	48.2	48.2	48.2	48.2
85°	27.5	30.9	34.2	33.1	30.3	27.0	22.9	19.7	19.0	18.3	19.0
87.5°	7.7	9.9	12.2	11.2	8.9	7.4	6.9	6.6	6.7	6.7	6.7
90°	2.1	4.9	8.3	11.1	13.2	13.9	13.9	14.6	15.3	15.3	15.3
92.5°	7.7	12.1	12.2	12.2	14.9	16.1	17.2	17.4	18.1	18.1	18.1
95°	21.6	23.6	35.5	34.8	23.6	18.8	16.0	16.0	16.0	16.0	16.0
97.5°	41.2	44.2	46.2	61.9	65.4	63.2	51.5	43.3	38.7	36.6	38.7
100°	58.4	59.8	64.0	64.7	82.1	98.8	90.4	80.0	76.5	74.4	76.5
102.5°	75.7	76.5	82.9	85.8	89.9	99.3	128.3	125.1	122.7	122.3	122.7
105°	101.5	102.2	114.1	119.6	122.4	122.4	121.7	135.6	157.9	162.7	157.9
107.5°	129.2	132.4	146.3	161.2	164.4	165.3	161.6	159.5	158.7	159.3	158.7
110°	148.1	153.0	169.7	188.5	193.4	194.7	193.4	191.3	189.9	189.9	189.9



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	166.5	173.6	192.5	214.1	222.3	226.5	223.4	221.9	220.5	221.6	220.5
115°	194.7	205.2	230.2	252.5	269.2	271.2	270.6	270.6	269.9	269.9	269.9
117.5°	220.9	237.6	265.7	291.6	310.9	316.5	319.2	318.4	317.6	319.0	317.6
120°	239.3	258.7	290.7	319.9	338.7	347.1	349.8	348.4	349.8	348.4	349.8
122.5°	258.7	282.7	314.1	344.4	366.5	376.0	379.3	379.6	379.9	379.1	379.9
125°	287.9	317.2	354.0	385.3	408.3	419.4	422.2	422.9	424.3	427.7	424.3
127.5°	317.4	350.5	391.0	421.2	444.7	458.2	462.5	464.0	467.0	468.5	467.0
130°	338.0	375.6	416.6	445.1	468.1	482.7	490.3	492.4	495.9	495.2	495.9
132.5°	359.7	398.9	440.5	470.2	491.4	507.2	513.7	519.7	520.9	521.9	520.9
135°	391.6	434.0	475.7	504.9	525.1	540.4	548.8	554.3	557.8	559.9	557.8
137.5°	425.1	469.9	509.9	536.0	556.3	569.5	578.9	584.8	588.4	590.1	588.4
140°	447.9	491.0	530.0	557.1	575.2	588.4	596.7	603.7	607.9	607.9	607.9
142.5°	469.6	512.2	550.0	577.1	593.0	605.1	614.0	619.3	624.0	624.0	624.0
145°	500.1	542.5	577.3	604.4	617.6	628.7	638.5	642.6	645.4	645.4	645.4
147.5°	531.9	569.5	601.2	627.2	638.3	651.4	659.1	662.4	665.9	664.3	665.9
150°	550.8	585.6	616.2	640.6	651.7	664.2	671.9	674.6	678.1	676.0	678.1
152.5°	569.2	602.3	630.1	652.8	662.3	674.8	683.5	686.3	688.7	687.2	688.7
155°	594.0	623.2	648.9	669.8	678.1	689.9	698.3	701.8	704.5	701.1	704.5
157.5°	616.1	641.3	663.7	682.8	691.8	701.9	709.7	714.0	716.8	715.3	716.8
160°	629.4	652.4	672.6	690.6	699.0	708.0	716.4	721.2	724.0	721.9	724.0
162.5°	640.6	661.3	680.3	696.8	704.0	711.9	721.9	726.2	729.0	726.4	729.0
165°	656.6	673.3	689.9	703.9	710.1	716.4	726.8	731.7	733.8	731.0	733.8
167.5°	668.7	681.5	695.0	706.9	711.5	717.6	728.1	732.1	734.7	731.3	734.7
170°	675.3	686.5	698.3	708.0	711.5	717.1	727.5	731.0	733.1	729.6	733.1
172.5°	680.9	689.2	698.8	707.5	709.3	713.7	723.6	727.1	728.6	725.7	728.6
175°	686.5	691.3	698.3	703.9	703.2	705.9	714.3	717.1	719.9	715.7	719.9
177.5°	689.1	691.3	693.6	696.9	694.7	694.7	700.8	702.5	703.0	700.8	703.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2
2.5°	1600.2	1599.4	1598.8	1601.5	1607.5	1609.7	1600.5	1591.2	1600.5	1609.7	1607.5
5°	1600.7	1598.7	1598.0	1600.7	1606.8	1608.5	1597.0	1585.4	1597.0	1608.5	1606.8
7.5°	1600.0	1596.8	1594.5	1595.7	1600.3	1600.8	1589.2	1577.5	1589.2	1600.8	1600.3
10°	1597.5	1593.6	1590.2	1590.5	1594.6	1594.6	1582.4	1570.2	1582.4	1594.6	1594.6
12.5°	1592.6	1588.3	1584.3	1583.9	1586.9	1585.9	1573.2	1560.4	1573.2	1585.9	1586.9
15°	1580.2	1575.8	1571.0	1569.0	1569.7	1566.8	1553.2	1539.7	1553.2	1566.8	1569.7
17.5°	1547.1	1545.8	1544.5	1544.4	1545.3	1542.7	1529.1	1515.5	1529.1	1542.7	1545.3
20°	1513.7	1517.3	1522.0	1525.4	1527.4	1525.6	1512.0	1498.5	1512.0	1525.6	1527.4
22.5°	1466.2	1477.0	1489.9	1498.7	1503.4	1503.3	1488.7	1474.0	1488.7	1503.3	1503.4
25°	1376.9	1399.3	1425.7	1445.7	1459.3	1465.9	1451.7	1437.4	1451.7	1465.9	1459.3
27.5°	1272.1	1303.8	1341.4	1373.6	1400.5	1417.7	1406.2	1394.7	1406.2	1417.7	1400.5
30°	1199.0	1233.5	1274.8	1315.2	1354.5	1381.8	1373.0	1364.2	1373.0	1381.8	1354.5
32.5°	1129.2	1165.1	1208.1	1254.1	1303.2	1339.2	1335.8	1332.4	1335.8	1339.2	1303.2
35°	1026.8	1062.5	1106.0	1158.5	1220.2	1268.0	1274.1	1280.2	1274.1	1268.0	1220.2
37.5°	923.9	961.5	1007.0	1062.6	1128.4	1182.2	1200.4	1218.6	1200.4	1182.2	1128.4
40°	855.5	893.2	938.6	995.6	1064.1	1121.9	1147.7	1173.4	1147.7	1121.9	1064.1
42.5°	790.7	828.5	873.9	930.9	999.4	1058.8	1091.1	1123.4	1091.1	1058.8	999.4
45°	695.3	731.9	776.0	833.0	902.8	964.7	1002.7	1040.7	1002.7	964.7	902.8
47.5°	606.7	641.8	684.5	740.7	810.5	872.2	909.9	947.6	909.9	872.2	810.5
50°	548.7	584.4	627.2	681.7	748.2	807.2	843.8	880.5	843.8	807.2	748.2
52.5°	488.7	526.6	570.5	624.8	689.6	746.4	779.3	812.1	779.3	746.4	689.6
55°	398.4	437.9	486.8	541.7	602.7	656.3	687.5	718.7	687.5	656.3	602.7
57.5°	335.5	371.1	415.5	465.2	520.4	568.6	595.6	622.6	595.6	568.6	520.4
60°	301.3	331.6	368.9	414.4	467.9	514.1	537.8	561.5	537.8	514.1	467.9
62.5°	270.0	294.2	323.9	364.7	416.7	460.9	481.9	502.9	481.9	460.9	416.7
65°	225.7	245.7	270.1	304.0	347.4	383.9	399.5	415.0	399.5	383.9	347.4
67.5°	185.3	202.5	224.0	251.4	284.9	312.2	320.9	329.6	320.9	312.2	284.9
70°	162.4	176.5	194.1	217.5	246.7	269.2	272.0	274.7	272.0	269.2	246.7
72.5°	140.7	151.7	165.5	185.1	210.5	229.2	228.1	227.1	228.1	229.2	210.5
75°	111.1	118.5	128.0	141.9	160.2	172.6	167.2	161.7	167.2	172.6	160.2
77.5°	82.1	87.7	94.7	105.0	118.4	126.4	118.3	110.2	118.3	126.4	118.4
80°	64.1	68.2	73.6	81.4	91.6	97.2	89.0	80.9	89.0	97.2	91.6
82.5°	48.2	50.3	53.0	58.1	65.5	69.5	63.0	56.5	63.0	69.5	65.5
85°	19.7	22.9	27.0	30.3	33.1	34.2	30.9	27.5	30.9	34.2	33.1
87.5°	6.6	6.9	7.4	8.9	11.2	12.2	9.9	7.7	9.9	12.1	11.5
90°	14.6	13.9	13.9	13.2	11.1	8.3	4.9	2.1	4.9	7.7	12.5
92.5°	17.4	17.2	16.1	14.9	12.2	12.2	12.1	7.7	13.2	18.8	27.0
95°	16.0	16.0	18.8	23.6	34.8	35.5	23.6	21.6	30.6	43.1	54.2
97.5°	43.3	51.5	63.2	65.4	61.9	46.2	44.2	41.2	56.1	68.4	86.4
100°	80.0	90.4	98.8	82.1	64.7	64.0	59.8	58.4	74.4	86.2	103.6
102.5°	125.1	128.3	99.3	89.9	85.8	82.9	76.5	75.7	91.7	107.9	122.5
105°	135.6	121.7	122.4	122.4	119.6	114.1	102.2	101.5	119.6	138.4	156.5
107.5°	159.5	161.6	165.3	164.4	161.2	146.3	132.4	129.2	145.5	168.0	187.9
110°	191.3	193.4	194.7	193.4	188.5	169.7	153.0	148.1	162.7	186.4	208.0



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	221.9	223.4	226.5	222.3	214.1	192.5	173.6	166.5	181.1	205.3	227.4
115°	270.6	270.6	271.2	269.2	252.5	230.2	205.2	194.7	207.3	229.5	253.9
117.5°	318.4	319.2	316.5	310.9	291.6	265.7	237.6	220.9	230.8	254.3	279.3
120°	348.4	349.8	347.1	338.7	319.9	290.7	258.7	239.3	246.9	269.9	294.9
122.5°	379.6	379.3	376.0	366.5	344.4	314.1	282.7	258.7	261.9	283.2	307.7
125°	422.9	422.2	419.4	408.3	385.3	354.0	317.2	287.9	283.8	301.9	326.9
127.5°	464.0	462.5	458.2	444.7	421.2	391.0	350.5	317.4	308.1	319.5	342.5
130°	492.4	490.3	482.7	468.1	445.1	416.6	375.6	338.0	324.8	331.8	351.9
132.5°	519.7	513.7	507.2	491.4	470.2	440.5	398.9	359.7	341.5	344.6	360.3
135°	554.3	548.8	540.4	525.1	504.9	475.7	434.0	391.6	366.5	363.8	372.8
137.5°	584.8	578.9	569.5	556.3	536.0	509.9	469.9	425.1	393.5	384.2	387.7
140°	603.7	596.7	588.4	575.2	557.1	530.0	491.0	447.9	412.4	399.2	397.1
142.5°	619.3	614.0	605.1	593.0	577.1	550.0	512.2	469.6	431.9	414.8	409.9
145°	642.6	638.5	628.7	617.6	604.4	577.3	542.5	500.1	462.5	440.3	429.8
147.5°	662.4	659.1	651.4	638.3	627.2	601.2	569.5	531.9	493.4	465.9	452.4
150°	674.6	671.9	664.2	651.7	640.6	616.2	585.6	550.8	514.0	484.8	467.4
152.5°	686.3	683.5	674.8	662.3	652.8	630.1	602.3	569.2	531.8	502.6	484.6
155°	701.8	698.3	689.9	678.1	669.8	648.9	623.2	594.0	562.0	531.4	511.2
157.5°	714.0	709.7	701.9	691.8	682.8	663.7	641.3	616.1	588.1	558.9	538.3
160°	721.2	716.4	708.0	699.0	690.6	672.6	652.4	629.4	603.7	577.3	555.0
162.5°	726.2	721.9	711.9	704.0	696.8	680.3	661.3	640.6	617.6	594.5	573.9
165°	731.7	726.8	716.4	710.1	703.9	689.9	673.3	656.6	637.1	618.3	601.6
167.5°	732.1	728.1	717.6	711.5	706.9	695.0	681.5	668.7	653.5	638.8	624.8
170°	731.0	727.5	717.1	711.5	708.0	698.3	686.5	675.3	663.5	651.0	639.9
172.5°	727.1	723.6	713.7	709.3	707.5	698.8	689.2	680.9	670.7	661.6	652.7
175°	717.1	714.3	705.9	703.2	703.9	698.3	691.3	686.5	680.2	674.6	669.8
177.5°	702.5	700.8	694.7	694.7	696.9	693.6	691.3	689.1	686.3	684.7	683.0
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2	1602.2
2.5°	1601.5	1598.8	1599.4	1600.2	1601.8	1603.4	1601.8	1600.2	1599.4	1598.8	1601.5
5°	1600.7	1598.0	1598.7	1600.7	1606.8	1612.9	1606.8	1600.7	1598.7	1598.0	1600.7
7.5°	1595.7	1594.5	1596.8	1600.0	1606.0	1612.0	1606.0	1600.0	1596.8	1594.5	1595.7
10°	1590.5	1590.2	1593.6	1597.5	1602.9	1608.3	1602.9	1597.5	1593.6	1590.2	1590.5
12.5°	1583.9	1584.3	1588.3	1592.6	1598.0	1603.4	1598.0	1592.6	1588.3	1584.3	1583.9
15°	1569.0	1571.0	1575.8	1580.2	1583.6	1587.0	1583.6	1580.2	1575.8	1571.0	1569.0
17.5°	1544.4	1544.5	1545.8	1547.1	1548.7	1550.3	1548.7	1547.1	1545.8	1544.5	1544.4
20°	1525.4	1522.0	1517.3	1513.7	1513.7	1513.7	1513.7	1513.7	1517.3	1522.0	1525.4
22.5°	1498.7	1489.9	1477.0	1466.2	1461.9	1457.6	1461.9	1466.2	1477.0	1489.9	1498.7
25°	1445.7	1425.7	1399.3	1376.9	1366.7	1356.5	1366.7	1376.9	1399.3	1425.7	1445.7
27.5°	1373.6	1341.4	1303.8	1272.1	1258.0	1243.9	1258.0	1272.1	1303.8	1341.4	1373.6
30°	1315.2	1274.8	1233.5	1199.0	1185.5	1171.9	1185.5	1199.0	1233.5	1274.8	1315.2
32.5°	1254.1	1208.1	1165.1	1129.2	1114.5	1099.9	1114.5	1129.2	1165.1	1208.1	1254.1
35°	1158.5	1106.0	1062.5	1026.8	1013.9	1001.0	1013.9	1026.8	1062.5	1106.0	1158.5
37.5°	1062.6	1007.0	961.5	923.9	909.7	895.4	909.7	923.9	961.5	1007.0	1062.6
40°	995.6	938.6	893.2	855.5	841.3	827.0	841.3	855.5	893.2	938.6	995.6
42.5°	930.9	873.9	828.5	790.7	775.9	761.1	775.9	790.7	828.5	873.9	930.9
45°	833.0	776.0	731.9	695.3	681.1	666.8	681.1	695.3	731.9	776.0	833.0
47.5°	740.7	684.5	641.8	606.7	594.5	582.3	594.5	606.7	641.8	684.5	740.7
50°	681.7	627.2	584.4	548.7	533.7	518.8	533.7	548.7	584.4	627.2	681.7
52.5°	624.8	570.5	526.6	488.7	468.4	448.0	468.4	488.7	526.6	570.5	624.8
55°	541.7	486.8	437.9	398.4	386.9	375.4	386.9	398.4	437.9	486.8	541.7
57.5°	465.2	415.5	371.1	335.5	326.0	316.5	326.0	335.5	371.1	415.5	465.2
60°	414.4	368.9	331.6	301.3	291.8	282.3	291.8	301.3	331.6	368.9	414.4
62.5°	364.7	323.9	294.2	270.0	262.1	254.2	262.1	270.0	294.2	323.9	364.7
65°	304.0	270.1	245.7	225.7	218.9	212.1	218.9	225.7	245.7	270.1	304.0
67.5°	251.4	224.0	202.5	185.3	180.9	176.4	180.9	185.3	202.5	224.0	251.4
70°	217.5	194.1	176.5	162.4	159.0	155.6	159.0	162.4	176.5	194.1	217.5
72.5°	185.1	165.5	151.7	140.7	138.4	136.1	138.4	140.7	151.7	165.5	185.1
75°	141.9	128.0	118.5	111.1	109.7	108.3	109.7	111.1	118.5	128.0	141.9
77.5°	105.0	94.7	87.7	82.1	81.0	80.0	81.0	82.1	87.7	94.7	105.0
80°	81.4	73.6	68.2	64.1	64.1	64.1	64.1	64.1	68.2	73.6	81.4
82.5°	58.1	53.0	50.3	48.2	48.2	48.2	48.2	48.2	50.3	53.0	58.1
85°	30.3	27.0	22.9	19.7	19.0	18.3	19.0	19.7	22.9	27.0	30.3
87.5°	9.4	8.8	9.2	9.4	9.9	9.6	9.9	9.4	9.2	8.8	9.4
90°	16.0	20.9	25.7	28.5	31.3	29.9	31.3	28.5	25.7	20.9	16.0
92.5°	32.1	40.3	46.3	51.3	53.6	53.3	53.6	51.3	46.3	40.3	32.1
95°	64.7	74.4	84.2	91.1	95.3	93.9	95.3	91.1	84.2	74.4	64.7
97.5°	99.7	112.8	123.7	130.2	134.4	137.2	134.4	130.2	123.7	112.8	99.7
100°	123.1	135.6	148.1	155.8	162.7	165.5	162.7	155.8	148.1	135.6	123.1
102.5°	142.0	158.4	172.1	180.3	186.1	188.9	186.1	180.3	172.1	158.4	142.0
105°	173.2	190.6	205.2	215.6	221.9	224.0	221.9	215.6	205.2	190.6	173.2
107.5°	204.3	222.3	235.8	247.3	255.0	259.4	255.0	247.3	235.8	222.3	204.3
110°	228.8	243.4	258.0	268.5	276.1	278.9	276.1	268.5	258.0	243.4	228.8



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	249.4	265.7	280.3	290.7	299.5	303.4	299.5	290.7	280.3	265.7	249.4
115°	278.2	299.8	313.0	322.7	329.0	332.5	329.0	322.7	313.0	299.8	278.2
117.5°	302.1	324.7	339.1	346.6	349.6	352.1	349.6	346.6	339.1	324.7	302.1
120°	317.2	338.0	354.7	364.4	367.9	369.3	367.9	364.4	354.7	338.0	317.2
122.5°	331.1	350.8	366.9	378.9	384.6	386.0	384.6	378.9	366.9	350.8	331.1
125°	350.5	369.3	386.0	397.8	404.1	407.6	404.1	397.8	386.0	369.3	350.5
127.5°	367.5	387.8	403.1	413.8	419.9	422.7	419.9	413.8	403.1	387.8	367.5
130°	377.0	397.8	413.1	425.0	430.5	433.3	430.5	425.0	413.1	397.8	377.0
132.5°	384.2	406.2	422.0	432.7	438.9	441.6	438.9	432.7	422.0	406.2	384.2
135°	393.0	415.9	432.6	443.0	448.6	451.4	448.6	443.0	432.6	415.9	393.0
137.5°	400.6	421.5	438.9	449.9	454.9	456.7	454.9	449.9	438.9	421.5	400.6
140°	406.2	424.3	441.6	452.1	457.6	458.3	457.6	452.1	441.6	424.3	406.2
142.5°	413.4	427.6	442.8	453.2	458.8	460.0	458.8	453.2	442.8	427.6	413.4
145°	426.3	434.7	445.1	454.9	459.7	461.1	459.7	454.9	445.1	434.7	426.3
147.5°	442.6	445.3	450.7	457.1	461.8	462.8	461.8	457.1	445.3	442.6	442.6
150°	454.9	454.2	456.3	460.4	464.6	463.9	464.6	460.4	456.3	454.2	454.9
152.5°	468.8	464.7	464.6	466.5	468.5	468.4	468.5	466.5	464.6	464.7	468.8
155°	492.4	484.8	480.6	479.2	479.2	478.5	479.2	479.2	480.6	484.8	492.4
157.5°	518.4	507.7	501.5	498.1	497.1	495.6	497.1	498.1	501.5	507.7	518.4
160°	536.2	524.4	518.2	512.6	510.5	508.4	510.5	512.6	518.2	524.4	536.2
162.5°	552.9	541.7	534.8	529.8	527.8	524.6	527.8	529.8	534.8	541.7	552.9
165°	580.1	568.2	560.6	556.4	553.6	550.8	553.6	556.4	560.6	568.2	580.1
167.5°	607.2	594.2	589.2	584.5	581.9	576.9	581.9	584.5	589.2	594.2	607.2
170°	623.9	612.0	609.3	605.1	600.2	594.7	600.2	605.1	609.3	612.0	623.9
172.5°	638.3	630.4	627.6	623.5	621.9	617.5	621.9	623.5	627.6	630.4	638.3
175°	659.3	653.1	653.1	652.4	650.3	646.1	650.3	652.4	653.1	653.1	659.3
177.5°	676.9	673.5	675.8	675.8	675.2	671.3	675.2	675.8	675.8	673.5	676.9
180°	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6	688.6



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1602.2	1602.2	1602.2	1602.2
2.5°	1607.5	1609.7	1600.5	1591.2
5°	1606.8	1608.5	1597.0	1585.4
7.5°	1600.3	1600.8	1589.2	1577.5
10°	1594.6	1594.6	1582.4	1570.2
12.5°	1586.9	1585.9	1573.2	1560.4
15°	1569.7	1566.8	1553.2	1539.7
17.5°	1545.3	1542.7	1529.1	1515.5
20°	1527.4	1525.6	1512.0	1498.5
22.5°	1503.4	1503.3	1488.7	1474.0
25°	1459.3	1465.9	1451.7	1437.4
27.5°	1400.5	1417.7	1406.2	1394.7
30°	1354.5	1381.8	1373.0	1364.2
32.5°	1303.2	1339.2	1335.8	1332.4
35°	1220.2	1268.0	1274.1	1280.2
37.5°	1128.4	1182.2	1200.4	1218.6
40°	1064.1	1121.9	1147.7	1173.4
42.5°	999.4	1058.8	1091.1	1123.4
45°	902.8	964.7	1002.7	1040.7
47.5°	810.5	872.2	909.9	947.6
50°	748.2	807.2	843.8	880.5
52.5°	689.6	746.4	779.3	812.1
55°	602.7	656.3	687.5	718.7
57.5°	520.4	568.6	595.6	622.6
60°	467.9	514.1	537.8	561.5
62.5°	416.7	460.9	481.9	502.9
65°	347.4	383.9	399.5	415.0
67.5°	284.9	312.2	320.9	329.6
70°	246.7	269.2	272.0	274.7
72.5°	210.5	229.2	228.1	227.1
75°	160.2	172.6	167.2	161.7
77.5°	118.4	126.4	118.3	110.2
80°	91.6	97.2	89.0	80.9
82.5°	65.5	69.5	63.0	56.5
85°	33.1	34.2	30.9	27.5
87.5°	11.5	12.1	9.9	7.7
90°	12.5	7.7	4.9	2.1
92.5°	27.0	18.8	13.2	7.7
95°	54.2	43.1	30.6	21.6
97.5°	86.4	68.4	56.1	41.2
100°	103.6	86.2	74.4	58.4
102.5°	122.5	107.9	91.7	75.7
105°	156.5	138.4	119.6	101.5
107.5°	187.9	168.0	145.5	129.2
110°	208.0	186.4	162.7	148.1



TEST NUMBER: P1428382

CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	227.4	205.3	181.1	166.5
115°	253.9	229.5	207.3	194.7
117.5°	279.3	254.3	230.8	220.9
120°	294.9	269.9	246.9	239.3
122.5°	307.7	283.2	261.9	258.7
125°	326.9	301.9	283.8	287.9
127.5°	342.5	319.5	308.1	317.4
130°	351.9	331.8	324.8	338.0
132.5°	360.3	344.6	341.5	359.7
135°	372.8	363.8	366.5	391.6
137.5°	387.7	384.2	393.5	425.1
140°	397.1	399.2	412.4	447.9
142.5°	409.9	414.8	431.9	469.6
145°	429.8	440.3	462.5	500.1
147.5°	452.4	465.9	493.4	531.9
150°	467.4	484.8	514.0	550.8
152.5°	484.6	502.6	531.8	569.2
155°	511.2	531.4	562.0	594.0
157.5°	538.3	558.9	588.1	616.1
160°	555.0	577.3	603.7	629.4
162.5°	573.9	594.5	617.6	640.6
165°	601.6	618.3	637.1	656.6
167.5°	624.8	638.8	653.5	668.7
170°	639.9	651.0	663.5	675.3
172.5°	652.7	661.6	670.7	680.9
175°	669.8	674.6	680.2	686.5
177.5°	683.0	684.7	686.3	689.1
180°	688.6	688.6	688.6	688.6



TEST NUMBER: P1428382
 CATALOG NUMBER: SQ2W-PW1-K-050U-075D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.43	20.38	20.27	21.23	22.29	15.68	16.63	16.51	17.48	18.54
	3H	20.74	21.58	21.59	22.45	23.54	16.95	17.80	17.80	18.66	19.75
	4H	21.15	21.95	22.02	22.82	23.92	17.46	18.26	18.33	19.13	20.23
	6H	21.33	22.07	22.21	22.95	24.06	17.78	18.51	18.65	19.39	20.50
	8H	21.38	22.08	22.27	22.97	24.08	17.89	18.59	18.78	19.49	20.60
	12H	21.38	22.05	22.27	22.94	24.07	17.93	18.59	18.82	19.48	20.62
4H	2H	19.57	20.37	20.44	21.24	22.34	16.50	17.30	17.37	18.17	19.27
	3H	21.12	21.78	22.00	22.68	23.80	17.95	18.61	18.83	19.52	20.63
	4H	21.67	22.27	22.56	23.17	24.31	18.53	19.14	19.43	20.03	21.18
	6H	21.98	22.50	22.89	23.42	24.57	18.92	19.44	19.83	20.36	21.51
	8H	22.08	22.56	22.99	23.48	24.63	19.07	19.56	19.99	20.48	21.63
	12H	22.10	22.54	23.03	23.47	24.63	19.12	19.56	20.05	20.49	21.65
8H	4H	21.71	22.20	22.62	23.11	24.27	18.88	19.37	19.79	20.28	21.44
	6H	22.14	22.54	23.07	23.50	24.65	19.38	19.78	20.32	20.74	21.89
	8H	22.31	22.66	23.26	23.61	24.79	19.60	19.95	20.55	20.90	22.08
	12H	22.39	22.70	23.34	23.64	24.87	19.69	20.00	20.63	20.94	22.16
12H	4H	21.68	22.11	22.61	23.05	24.21	18.91	19.34	19.84	20.28	21.44
	6H	22.13	22.49	23.08	23.44	24.61	19.45	19.81	20.40	20.76	21.93
	8H	22.33	22.64	23.27	23.58	24.80	19.70	20.01	20.65	20.96	22.18