

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428424

Luminaire Tested: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428424
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - PERCEIVE WAVES LENS
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6560.0 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	64	53	52	51	40	39	39	33
2	87	80	74	70	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19
6	62	50	43	37	56	46	39	35	38	33	29	31	27	24	24	22	20	16
7	57	46	38	33	52	42	35	30	35	30	26	28	24	22	22	19	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17933	17933	17933	17933
5°	17812	18121	17812	18121
10°	17846	18278	17846	18278
15°	17840	18388	17840	18388
20°	17847	18029	17847	18029
25°	17751	16753	17751	16753
30°	17631	15146	17631	15146
35°	17493	13677	17493	13677
40°	17144	12083	17144	12083
45°	16472	10554	16472	10554
50°	15330	9032	15330	9032
55°	14024	7324	14024	7324
60°	12571	6319	12571	6319
65°	10991	5616	10991	5616
70°	8988	5094	8988	5094
75°	6993	4685	6993	4685
80°	5216	4128	5216	4128
85°	3520	2353	3520	2353

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16472 cd/sqm



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.6
10°-20°	306.4	4.7
20°-30°	451.0	6.9
30°-40°	493.1	7.5
40°-50°	442.3	6.7
50°-60°	329.9	5.0
60°-70°	208.5	3.2
70°-80°	103.3	1.6
80°-90°	30.0	0.5
90°-100°	111.5	1.7
100°-110°	325.1	5.0
110°-120°	530.5	8.1
120°-130°	673.2	10.3
130°-140°	720.3	11.0
140°-150°	672.6	10.3
150°-160°	553.5	8.4
160°-170°	371.2	5.7
170°-180°	131.8	2.0
0°-30°	863.2	13.2
0°-40°	1356.2	20.7
0°-60°	2128.5	32.4
0°-90°	2470.3	37.7
90°-120°	967.1	14.7
90°-150°	3033.2	46.2
90°-180°	4090.0	62.3
0°-180°	6560.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1111	1111	1111	1111	1111	
5°	1099	1118	1099	1118	1099	105
15°	1067	1100	1067	1100	1067	301
25°	996	940	996	940	996	459
35°	888	694	888	694	888	553
45°	721	462	721	462	721	553
55°	498	260	498	260	498	445
65°	288	147	288	147	288	285
75°	112	75	112	75	112	124
85°	19	13	19	13	19	24
90°	4	31	4	61	4	4
95°	44	32	44	191	44	53
105°	207	331	207	456	207	220
115°	396	549	396	676	396	390
125°	586	870	586	829	586	524
135°	796	1139	796	918	796	616
145°	1017	1313	1017	938	1017	636
155°	1208	1426	1208	973	1208	555
165°	1336	1487	1336	1120	1336	376
175°	1396	1456	1396	1314	1396	132
180°	1401	1401	1401	1401	1401	



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7
2.5°	1103.1	1109.4	1115.8	1114.3	1110.2	1108.3	1108.7	1109.3	1110.4	1111.5	1110.4
5°	1099.0	1107.0	1115.0	1113.8	1109.6	1107.7	1108.2	1109.6	1113.8	1118.1	1113.8
7.5°	1093.5	1101.6	1109.7	1109.3	1106.1	1105.3	1106.9	1109.2	1113.3	1117.4	1113.3
10°	1088.5	1096.9	1105.4	1105.4	1102.6	1102.3	1104.7	1107.4	1111.1	1114.9	1111.1
12.5°	1081.7	1090.5	1099.4	1100.0	1098.0	1098.3	1101.0	1104.0	1107.8	1111.5	1107.8
15°	1067.3	1076.7	1086.1	1088.1	1087.6	1089.0	1092.3	1095.4	1097.7	1100.1	1097.7
17.5°	1050.6	1060.0	1069.4	1071.2	1070.6	1070.7	1071.5	1072.4	1073.6	1074.7	1073.6
20°	1038.7	1048.1	1057.5	1058.8	1057.4	1055.1	1051.8	1049.3	1049.3	1049.3	1049.3
22.5°	1021.8	1032.0	1042.1	1042.2	1038.9	1032.8	1023.9	1016.4	1013.4	1010.4	1013.4
25°	996.4	1006.3	1016.2	1011.6	1002.2	988.3	970.0	954.5	947.4	940.4	947.4
27.5°	966.8	974.8	982.8	970.8	952.2	929.9	903.8	881.9	872.1	862.3	872.1
30°	945.7	951.8	957.9	939.0	911.7	883.7	855.0	831.2	821.8	812.4	821.8
32.5°	923.7	926.0	928.4	903.4	869.4	837.5	807.6	782.8	772.6	762.4	772.6
35°	887.5	883.2	879.0	845.9	803.1	766.7	736.6	711.8	702.8	693.9	702.8
37.5°	844.7	832.1	819.5	782.2	736.6	698.0	666.5	640.4	630.6	620.7	630.6
40°	813.4	795.6	777.7	737.6	690.1	650.7	619.2	593.1	583.2	573.3	583.2
42.5°	778.7	756.4	734.0	692.8	645.3	605.8	574.3	548.1	537.9	527.6	537.9
45°	721.4	695.1	668.8	625.9	577.4	537.9	507.4	482.0	472.1	462.2	472.1
47.5°	656.9	630.7	604.6	561.8	513.5	474.5	444.9	420.6	412.1	403.6	412.1
50°	610.3	585.0	559.6	518.7	472.6	434.7	405.1	380.3	370.0	359.6	370.0
52.5°	562.9	540.2	517.4	478.0	433.1	395.4	365.1	338.8	324.7	310.6	324.7
55°	498.2	476.6	455.0	417.8	375.5	337.4	303.6	276.2	268.2	260.2	268.2
57.5°	431.6	412.9	394.2	360.8	322.5	288.0	257.3	232.5	226.0	219.4	226.0
60°	389.3	372.8	356.4	324.4	287.2	255.7	229.9	208.9	202.3	195.7	202.3
62.5°	348.6	334.1	319.5	288.8	252.8	224.5	203.9	187.1	181.7	176.2	181.7
65°	287.7	276.9	266.1	240.8	210.7	187.2	170.3	156.4	151.7	147.0	151.7
67.5°	228.5	222.5	216.4	197.5	174.3	155.3	140.4	128.5	125.4	122.3	125.4
70°	190.4	188.5	186.6	171.0	150.8	134.6	122.3	112.6	110.2	107.9	110.2
72.5°	157.4	158.1	158.9	145.9	128.3	114.7	105.1	97.6	96.0	94.4	96.0
75°	112.1	115.9	119.6	111.1	98.4	88.7	82.2	77.0	76.0	75.1	76.0
77.5°	76.4	82.0	87.7	82.1	72.8	65.7	60.8	56.9	56.2	55.4	56.2
80°	56.1	61.7	67.3	63.5	56.4	51.0	47.2	44.4	44.4	44.4	44.4
82.5°	39.1	43.7	48.2	45.4	40.2	36.7	34.8	33.4	33.4	33.4	33.4
85°	19.0	21.4	23.7	22.9	21.0	18.7	15.9	13.6	13.2	12.7	13.2
87.5°	5.9	8.2	10.7	10.7	9.7	8.9	8.5	8.5	8.8	8.8	8.8
90°	4.2	9.9	17.0	22.6	26.9	28.3	28.3	29.7	31.1	31.1	31.1
92.5°	15.6	24.6	24.9	24.9	30.3	32.8	35.1	35.4	36.8	36.8	36.8
95°	43.9	48.1	72.2	70.7	48.1	38.2	32.5	32.5	32.5	32.5	32.5
97.5°	83.8	90.0	93.9	125.9	133.0	128.5	104.7	88.0	78.7	74.4	78.7
100°	118.8	121.7	130.2	131.6	166.9	200.9	183.9	162.7	155.6	151.4	155.6
102.5°	153.9	155.6	168.6	174.6	182.8	202.0	260.9	254.4	249.6	248.7	249.6
105°	206.6	208.0	232.0	243.3	249.0	249.0	247.6	275.9	321.2	331.1	321.2
107.5°	262.9	269.4	297.7	328.0	334.5	336.2	328.8	324.6	322.9	324.0	322.9
110°	301.4	311.3	345.2	383.4	393.3	396.1	393.3	389.1	386.2	386.2	386.2



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	338.7	353.1	391.6	435.5	452.2	460.7	454.4	451.3	448.5	450.8	448.5
115°	396.1	417.4	468.3	513.6	547.5	551.8	550.4	550.4	548.9	548.9	548.9
117.5°	449.3	483.3	540.5	593.1	632.4	643.7	649.4	647.7	646.0	648.8	646.0
120°	486.7	526.3	591.4	650.8	689.0	706.0	711.6	708.8	711.6	708.8	711.6
122.5°	526.3	575.0	638.9	700.6	745.6	764.8	771.6	772.2	772.8	771.1	772.8
125°	585.7	645.2	720.1	783.8	830.5	853.1	858.8	860.2	863.0	870.1	863.0
127.5°	645.7	713.1	795.4	856.8	904.6	932.1	940.8	944.0	949.9	953.0	949.9
130°	687.6	764.0	847.5	905.5	952.2	981.9	997.4	1001.7	1008.8	1007.3	1008.8
132.5°	731.7	811.5	896.1	956.4	999.7	1031.7	1045.0	1057.1	1059.7	1061.7	1059.7
135°	796.5	882.8	967.7	1027.2	1068.2	1099.3	1116.3	1127.6	1134.7	1138.9	1134.7
137.5°	864.7	955.8	1037.3	1090.3	1131.6	1158.4	1177.7	1189.6	1196.9	1200.3	1196.9
140°	911.1	998.9	1078.1	1133.3	1170.0	1196.9	1213.9	1228.1	1236.5	1236.5	1236.5
142.5°	955.3	1041.9	1118.8	1174.0	1206.3	1230.9	1249.0	1259.7	1269.4	1269.4	1269.4
145°	1017.2	1103.6	1174.3	1229.5	1256.4	1279.0	1298.8	1307.3	1312.9	1312.9	1312.9
147.5°	1082.0	1158.4	1223.0	1275.9	1298.5	1325.1	1340.7	1347.5	1354.5	1351.4	1354.5
150°	1120.5	1191.3	1253.5	1303.0	1325.7	1351.1	1366.7	1372.4	1379.4	1375.2	1379.4
152.5°	1157.9	1225.2	1281.8	1327.9	1347.2	1372.6	1390.5	1396.1	1400.9	1397.8	1400.9
155°	1208.2	1267.7	1320.0	1362.5	1379.4	1403.5	1420.5	1427.5	1433.2	1426.1	1433.2
157.5°	1253.2	1304.5	1350.0	1389.1	1407.2	1427.8	1443.7	1452.4	1458.1	1455.0	1458.1
160°	1280.4	1327.1	1368.1	1404.9	1421.9	1440.3	1457.3	1467.2	1472.8	1468.6	1472.8
162.5°	1303.0	1345.2	1384.0	1417.4	1432.1	1448.2	1468.6	1477.3	1483.0	1477.6	1483.0
165°	1335.6	1369.5	1403.5	1431.8	1444.5	1457.3	1478.5	1488.4	1492.6	1487.0	1492.6
167.5°	1360.2	1386.2	1413.7	1438.0	1447.4	1459.8	1481.0	1489.2	1494.6	1487.5	1494.6
170°	1373.8	1396.4	1420.5	1440.3	1447.4	1458.7	1479.9	1487.0	1491.2	1484.1	1491.2
172.5°	1385.1	1402.1	1421.6	1439.1	1442.8	1451.9	1472.0	1479.0	1482.2	1476.2	1482.2
175°	1396.4	1406.3	1420.5	1431.8	1430.4	1436.0	1453.0	1458.7	1464.3	1455.8	1464.3
177.5°	1401.8	1406.3	1410.8	1417.6	1413.1	1413.1	1425.6	1429.0	1430.1	1425.6	1430.1
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7
2.5°	1109.3	1108.7	1108.3	1110.2	1114.3	1115.8	1109.4	1103.1	1109.4	1115.8	1114.3
5°	1109.6	1108.2	1107.7	1109.6	1113.8	1115.0	1107.0	1099.0	1107.0	1115.0	1113.8
7.5°	1109.2	1106.9	1105.3	1106.1	1109.3	1109.7	1101.6	1093.5	1101.6	1109.7	1109.3
10°	1107.4	1104.7	1102.3	1102.6	1105.4	1105.4	1096.9	1088.5	1096.9	1105.4	1105.4
12.5°	1104.0	1101.0	1098.3	1098.0	1100.0	1099.4	1090.5	1081.7	1090.5	1099.4	1100.0
15°	1095.4	1092.3	1089.0	1087.6	1088.1	1086.1	1076.7	1067.3	1076.7	1086.1	1088.1
17.5°	1072.4	1071.5	1070.7	1070.6	1071.2	1069.4	1060.0	1050.6	1060.0	1069.4	1071.2
20°	1049.3	1051.8	1055.1	1057.4	1058.8	1057.5	1048.1	1038.7	1048.1	1057.5	1058.8
22.5°	1016.4	1023.9	1032.8	1038.9	1042.2	1042.1	1032.0	1021.8	1032.0	1042.1	1042.2
25°	954.5	970.0	988.3	1002.2	1011.6	1016.2	1006.3	996.4	1006.3	1016.2	1011.6
27.5°	881.9	903.8	929.9	952.2	970.8	982.8	974.8	966.8	974.8	982.8	970.8
30°	831.2	855.0	883.7	911.7	939.0	957.9	951.8	945.7	951.8	957.9	939.0
32.5°	782.8	807.6	837.5	869.4	903.4	928.4	926.0	923.7	926.0	928.4	903.4
35°	711.8	736.6	766.7	803.1	845.9	879.0	883.2	887.5	883.2	879.0	845.9
37.5°	640.4	666.5	698.0	736.6	782.2	819.5	832.1	844.7	832.1	819.5	782.2
40°	593.1	619.2	650.7	690.1	737.6	777.7	795.6	813.4	795.6	777.7	737.6
42.5°	548.1	574.3	605.8	645.3	692.8	734.0	756.4	778.7	756.4	734.0	692.8
45°	482.0	507.4	537.9	577.4	625.9	668.8	695.1	721.4	695.1	668.8	625.9
47.5°	420.6	444.9	474.5	513.5	561.8	604.6	630.7	656.9	630.7	604.6	561.8
50°	380.3	405.1	434.7	472.6	518.7	559.6	585.0	610.3	585.0	559.6	518.7
52.5°	338.8	365.1	395.4	433.1	478.0	517.4	540.2	562.9	540.2	517.4	478.0
55°	276.2	303.6	337.4	375.5	417.8	455.0	476.6	498.2	476.6	455.0	417.8
57.5°	232.5	257.3	288.0	322.5	360.8	394.2	412.9	431.6	412.9	394.2	360.8
60°	208.9	229.9	255.7	287.2	324.4	356.4	372.8	389.3	372.8	356.4	324.4
62.5°	187.1	203.9	224.5	252.8	288.8	319.5	334.1	348.6	334.1	319.5	288.8
65°	156.4	170.3	187.2	210.7	240.8	266.1	276.9	287.7	276.9	266.1	240.8
67.5°	128.5	140.4	155.3	174.3	197.5	216.4	222.5	228.5	222.5	216.4	197.5
70°	112.6	122.3	134.6	150.8	171.0	186.6	188.5	190.4	188.5	186.6	171.0
72.5°	97.6	105.1	114.7	128.3	145.9	158.9	158.1	157.4	158.1	158.9	145.9
75°	77.0	82.2	88.7	98.4	111.1	119.6	115.9	112.1	115.9	119.6	111.1
77.5°	56.9	60.8	65.7	72.8	82.1	87.7	82.0	76.4	82.0	87.7	82.1
80°	44.4	47.2	51.0	56.4	63.5	67.3	61.7	56.1	61.7	67.3	63.5
82.5°	33.4	34.8	36.7	40.2	45.4	48.2	43.7	39.1	43.7	48.2	45.4
85°	13.6	15.9	18.7	21.0	22.9	23.7	21.4	19.0	21.4	23.7	22.9
87.5°	8.5	8.5	8.9	9.7	10.7	10.7	8.2	5.9	8.2	10.4	11.3
90°	29.7	28.3	28.3	26.9	22.6	17.0	9.9	4.2	9.9	15.6	25.5
92.5°	35.4	35.1	32.8	30.3	24.9	24.9	24.6	15.6	26.9	38.2	54.9
95°	32.5	32.5	38.2	48.1	70.7	72.2	48.1	43.9	62.3	87.7	110.4
97.5°	88.0	104.7	128.5	133.0	125.9	93.9	90.0	83.8	114.0	139.2	175.7
100°	162.7	183.9	200.9	166.9	131.6	130.2	121.7	118.8	151.4	175.4	210.8
102.5°	254.4	260.9	202.0	182.8	174.6	168.6	155.6	153.9	186.5	219.6	249.3
105°	275.9	247.6	249.0	249.0	243.3	232.0	208.0	206.6	243.3	281.5	318.3
107.5°	324.6	328.8	336.2	334.5	328.0	297.7	269.4	262.9	296.0	341.8	382.3
110°	389.1	393.3	396.1	393.3	383.4	345.2	311.3	301.4	331.1	379.2	423.0

TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	451.3	454.4	460.7	452.2	435.5	391.6	353.1	338.7	368.4	417.7	462.6
115°	550.4	550.4	551.8	547.5	513.6	468.3	417.4	396.1	421.6	466.9	516.4
117.5°	647.7	649.4	643.7	632.4	593.1	540.5	483.3	449.3	469.4	517.3	568.2
120°	708.8	711.6	706.0	689.0	650.8	591.4	526.3	486.7	502.3	548.9	599.9
122.5°	772.2	771.6	764.8	745.6	700.6	638.9	575.0	526.3	532.8	576.1	625.9
125°	860.2	858.8	853.1	830.5	783.8	720.1	645.2	585.7	577.2	614.0	665.0
127.5°	944.0	940.8	932.1	904.6	856.8	795.4	713.1	645.7	626.8	650.0	696.7
130°	1001.7	997.4	981.9	952.2	905.5	847.5	764.0	687.6	660.7	674.9	715.9
132.5°	1057.1	1045.0	1031.7	999.7	956.4	896.1	811.5	731.7	694.7	700.9	732.9
135°	1127.6	1116.3	1099.3	1068.2	1027.2	967.7	882.8	796.5	745.6	739.9	758.3
137.5°	1189.6	1177.7	1158.4	1131.6	1090.3	1037.3	955.8	864.7	800.5	781.5	788.6
140°	1228.1	1213.9	1196.9	1170.0	1133.3	1078.1	998.9	911.1	839.0	812.1	807.9
142.5°	1259.7	1249.0	1230.9	1206.3	1174.0	1118.8	1041.9	955.3	878.6	843.8	833.9
145°	1307.3	1298.8	1279.0	1256.4	1229.5	1174.3	1103.6	1017.2	940.8	895.6	874.4
147.5°	1347.5	1340.7	1325.1	1298.5	1275.9	1223.0	1158.4	1082.0	1003.7	947.6	920.2
150°	1372.4	1366.7	1351.1	1325.7	1303.0	1253.5	1191.3	1120.5	1045.5	986.1	950.8
152.5°	1396.1	1390.5	1372.6	1347.2	1327.9	1281.8	1225.2	1157.9	1081.8	1022.3	985.8
155°	1427.5	1420.5	1403.5	1379.4	1362.5	1320.0	1267.7	1208.2	1143.2	1080.9	1039.9
157.5°	1452.4	1443.7	1427.8	1407.2	1389.1	1350.0	1304.5	1253.2	1196.4	1136.9	1095.1
160°	1467.2	1457.3	1440.3	1421.9	1404.9	1368.1	1327.1	1280.4	1228.1	1174.3	1129.0
162.5°	1477.3	1468.6	1448.2	1432.1	1417.4	1384.0	1345.2	1303.0	1256.4	1209.4	1167.5
165°	1488.4	1478.5	1457.3	1444.5	1431.8	1403.5	1369.5	1335.6	1296.0	1257.8	1223.8
167.5°	1489.2	1481.0	1459.8	1447.4	1438.0	1413.7	1386.2	1360.2	1329.4	1299.4	1271.1
170°	1487.0	1479.9	1458.7	1447.4	1440.3	1420.5	1396.4	1373.8	1349.7	1324.3	1301.6
172.5°	1479.0	1472.0	1451.9	1442.8	1439.1	1421.6	1402.1	1385.1	1364.4	1345.8	1327.7
175°	1458.7	1453.0	1436.0	1430.4	1431.8	1420.5	1406.3	1396.4	1383.7	1372.4	1362.5
177.5°	1429.0	1425.6	1413.1	1413.1	1417.6	1410.8	1406.3	1401.8	1396.1	1392.7	1389.3
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7	1110.7
2.5°	1110.2	1108.3	1108.7	1109.3	1110.4	1111.5	1110.4	1109.3	1108.7	1108.3	1110.2
5°	1109.6	1107.7	1108.2	1109.6	1113.8	1118.1	1113.8	1109.6	1108.2	1107.7	1109.6
7.5°	1106.1	1105.3	1106.9	1109.2	1113.3	1117.4	1113.3	1109.2	1106.9	1105.3	1106.1
10°	1102.6	1102.3	1104.7	1107.4	1111.1	1114.9	1111.1	1107.4	1104.7	1102.3	1102.6
12.5°	1098.0	1098.3	1101.0	1104.0	1107.8	1111.5	1107.8	1104.0	1101.0	1098.3	1098.0
15°	1087.6	1089.0	1092.3	1095.4	1097.7	1100.1	1097.7	1095.4	1092.3	1089.0	1087.6
17.5°	1070.6	1070.7	1071.5	1072.4	1073.6	1074.7	1073.6	1072.4	1071.5	1070.7	1070.6
20°	1057.4	1055.1	1051.8	1049.3	1049.3	1049.3	1049.3	1049.3	1051.8	1055.1	1057.4
22.5°	1038.9	1032.8	1023.9	1016.4	1013.4	1010.4	1013.4	1016.4	1023.9	1032.8	1038.9
25°	1002.2	988.3	970.0	954.5	947.4	940.4	947.4	954.5	970.0	988.3	1002.2
27.5°	952.2	929.9	903.8	881.9	872.1	862.3	872.1	881.9	903.8	929.9	952.2
30°	911.7	883.7	855.0	831.2	821.8	812.4	821.8	831.2	855.0	883.7	911.7
32.5°	869.4	837.5	807.6	782.8	772.6	762.4	772.6	782.8	807.6	837.5	869.4
35°	803.1	766.7	736.6	711.8	702.8	693.9	702.8	711.8	736.6	766.7	803.1
37.5°	736.6	698.0	666.5	640.4	630.6	620.7	630.6	640.4	666.5	698.0	736.6
40°	690.1	650.7	619.2	593.1	583.2	573.3	583.2	593.1	619.2	650.7	690.1
42.5°	645.3	605.8	574.3	548.1	537.9	527.6	537.9	548.1	574.3	605.8	645.3
45°	577.4	537.9	507.4	482.0	472.1	462.2	472.1	482.0	507.4	537.9	577.4
47.5°	513.5	474.5	444.9	420.6	412.1	403.6	412.1	420.6	444.9	474.5	513.5
50°	472.6	434.7	405.1	380.3	370.0	359.6	370.0	380.3	405.1	434.7	472.6
52.5°	433.1	395.4	365.1	338.8	324.7	310.6	324.7	338.8	365.1	395.4	433.1
55°	375.5	337.4	303.6	276.2	268.2	260.2	268.2	276.2	303.6	337.4	375.5
57.5°	322.5	288.0	257.3	232.5	226.0	219.4	226.0	232.5	257.3	288.0	322.5
60°	287.2	255.7	229.9	208.9	202.3	195.7	202.3	208.9	229.9	255.7	287.2
62.5°	252.8	224.5	203.9	187.1	181.7	176.2	181.7	187.1	203.9	224.5	252.8
65°	210.7	187.2	170.3	156.4	151.7	147.0	151.7	156.4	170.3	187.2	210.7
67.5°	174.3	155.3	140.4	128.5	125.4	122.3	125.4	128.5	140.4	155.3	174.3
70°	150.8	134.6	122.3	112.6	110.2	107.9	110.2	112.6	122.3	134.6	150.8
72.5°	128.3	114.7	105.1	97.6	96.0	94.4	96.0	97.6	105.1	114.7	128.3
75°	98.4	88.7	82.2	77.0	76.0	75.1	76.0	77.0	82.2	88.7	98.4
77.5°	72.8	65.7	60.8	56.9	56.2	55.4	56.2	56.9	60.8	65.7	72.8
80°	56.4	51.0	47.2	44.4	44.4	44.4	44.4	44.4	47.2	51.0	56.4
82.5°	40.2	36.7	34.8	33.4	33.4	33.4	33.4	33.4	34.8	36.7	40.2
85°	21.0	18.7	15.9	13.6	13.2	12.7	13.2	13.6	15.9	18.7	21.0
87.5°	10.8	11.7	13.3	14.1	15.3	14.7	15.3	14.1	13.3	11.7	10.8
90°	32.5	42.4	52.3	58.0	63.7	60.8	63.7	58.0	52.3	42.4	32.5
92.5°	65.4	82.1	94.2	104.4	108.9	108.4	108.9	104.4	94.2	82.1	65.4
95°	131.6	151.4	171.2	185.3	193.8	191.0	193.8	185.3	171.2	151.4	131.6
97.5°	202.9	229.5	251.6	264.9	273.3	279.0	273.3	264.9	251.6	229.5	202.9
100°	250.4	275.9	301.4	316.9	331.1	336.7	331.1	316.9	301.4	275.9	250.4
102.5°	288.9	322.3	350.0	366.7	378.6	384.3	378.6	366.7	350.0	322.3	288.9
105°	352.3	387.7	417.4	438.6	451.3	455.6	451.3	438.6	417.4	387.7	352.3
107.5°	415.7	452.2	479.6	503.1	518.7	527.7	518.7	503.1	479.6	452.2	415.7
110°	465.5	495.2	524.9	546.1	561.7	567.3	561.7	546.1	524.9	495.2	465.5



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	507.4	540.5	570.2	591.4	609.2	617.1	609.2	591.4	570.2	540.5	507.4
115°	565.9	609.8	636.7	656.5	669.2	676.3	669.2	656.5	636.7	609.8	565.9
117.5°	614.6	660.4	689.9	705.1	711.1	716.2	711.1	705.1	689.9	660.4	614.6
120°	645.2	687.6	721.6	741.4	748.4	751.3	748.4	741.4	721.6	687.6	645.2
122.5°	673.4	713.6	746.5	770.8	782.4	785.2	782.4	770.8	746.5	713.6	673.4
125°	713.1	751.3	785.2	809.3	822.0	829.1	822.0	809.3	785.2	751.3	713.1
127.5°	747.6	788.9	820.0	841.8	854.3	859.9	854.3	841.8	820.0	788.9	747.6
130°	766.8	809.3	840.4	864.4	875.8	881.4	875.8	864.4	840.4	809.3	766.8
132.5°	781.5	826.2	858.5	880.3	892.7	898.4	892.7	880.3	858.5	826.2	781.5
135°	799.4	846.1	880.0	901.2	912.6	918.2	912.6	901.2	880.0	846.1	799.4
137.5°	814.9	857.4	892.7	915.1	925.3	929.0	925.3	915.1	892.7	857.4	814.9
140°	826.2	863.0	898.4	919.6	930.9	932.4	930.9	919.6	898.4	863.0	826.2
142.5°	841.0	869.8	900.7	921.9	933.2	935.8	933.2	921.9	900.7	869.8	841.0
145°	867.3	884.3	905.5	925.3	935.2	938.0	935.2	925.3	905.5	884.3	867.3
147.5°	900.4	905.8	916.8	929.8	939.4	941.4	939.4	929.8	916.8	905.8	900.4
150°	925.3	923.9	928.1	936.6	945.1	943.7	945.1	936.6	928.1	923.9	925.3
152.5°	953.6	945.4	945.1	949.1	953.0	952.7	953.0	949.1	945.1	945.4	953.6
155°	1001.7	986.1	977.6	974.8	974.8	973.4	974.8	974.8	977.6	986.1	1001.7
157.5°	1054.6	1032.8	1020.1	1013.3	1011.3	1008.2	1011.3	1013.3	1020.1	1032.8	1054.6
160°	1090.8	1066.8	1054.0	1042.7	1038.5	1034.2	1038.5	1042.7	1054.0	1066.8	1090.8
162.5°	1124.8	1101.9	1088.0	1077.8	1073.6	1067.1	1073.6	1077.8	1088.0	1101.9	1124.8
165°	1180.0	1155.9	1140.3	1131.8	1126.2	1120.5	1126.2	1131.8	1140.3	1155.9	1180.0
167.5°	1235.1	1208.8	1198.6	1189.0	1183.6	1173.4	1183.6	1189.0	1198.6	1208.8	1235.1
170°	1269.1	1245.0	1239.4	1230.9	1221.0	1209.7	1221.0	1230.9	1239.4	1245.0	1269.1
172.5°	1298.5	1282.4	1276.7	1268.2	1265.1	1256.1	1265.1	1268.2	1276.7	1282.4	1298.5
175°	1341.2	1328.5	1328.5	1327.1	1322.8	1314.4	1322.8	1327.1	1328.5	1328.5	1341.2
177.5°	1376.9	1370.1	1374.6	1374.6	1373.5	1365.6	1373.5	1374.6	1374.6	1370.1	1376.9
180°	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	1110.7	1110.7	1110.7	1110.7
2.5°	1114.3	1115.8	1109.4	1103.1
5°	1113.8	1115.0	1107.0	1099.0
7.5°	1109.3	1109.7	1101.6	1093.5
10°	1105.4	1105.4	1096.9	1088.5
12.5°	1100.0	1099.4	1090.5	1081.7
15°	1088.1	1086.1	1076.7	1067.3
17.5°	1071.2	1069.4	1060.0	1050.6
20°	1058.8	1057.5	1048.1	1038.7
22.5°	1042.2	1042.1	1032.0	1021.8
25°	1011.6	1016.2	1006.3	996.4
27.5°	970.8	982.8	974.8	966.8
30°	939.0	957.9	951.8	945.7
32.5°	903.4	928.4	926.0	923.7
35°	845.9	879.0	883.2	887.5
37.5°	782.2	819.5	832.1	844.7
40°	737.6	777.7	795.6	813.4
42.5°	692.8	734.0	756.4	778.7
45°	625.9	668.8	695.1	721.4
47.5°	561.8	604.6	630.7	656.9
50°	518.7	559.6	585.0	610.3
52.5°	478.0	517.4	540.2	562.9
55°	417.8	455.0	476.6	498.2
57.5°	360.8	394.2	412.9	431.6
60°	324.4	356.4	372.8	389.3
62.5°	288.8	319.5	334.1	348.6
65°	240.8	266.1	276.9	287.7
67.5°	197.5	216.4	222.5	228.5
70°	171.0	186.6	188.5	190.4
72.5°	145.9	158.9	158.1	157.4
75°	111.1	119.6	115.9	112.1
77.5°	82.1	87.7	82.0	76.4
80°	63.5	67.3	61.7	56.1
82.5°	45.4	48.2	43.7	39.1
85°	22.9	23.7	21.4	19.0
87.5°	11.3	10.4	8.2	5.9
90°	25.5	15.6	9.9	4.2
92.5°	54.9	38.2	26.9	15.6
95°	110.4	87.7	62.3	43.9
97.5°	175.7	139.2	114.0	83.8
100°	210.8	175.4	151.4	118.8
102.5°	249.3	219.6	186.5	153.9
105°	318.3	281.5	243.3	206.6
107.5°	382.3	341.8	296.0	262.9
110°	423.0	379.2	331.1	301.4



TEST NUMBER: P1428424

CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	462.6	417.7	368.4	338.7
115°	516.4	466.9	421.6	396.1
117.5°	568.2	517.3	469.4	449.3
120°	599.9	548.9	502.3	486.7
122.5°	625.9	576.1	532.8	526.3
125°	665.0	614.0	577.2	585.7
127.5°	696.7	650.0	626.8	645.7
130°	715.9	674.9	660.7	687.6
132.5°	732.9	700.9	694.7	731.7
135°	758.3	739.9	745.6	796.5
137.5°	788.6	781.5	800.5	864.7
140°	807.9	812.1	839.0	911.1
142.5°	833.9	843.8	878.6	955.3
145°	874.4	895.6	940.8	1017.2
147.5°	920.2	947.6	1003.7	1082.0
150°	950.8	986.1	1045.5	1120.5
152.5°	985.8	1022.3	1081.8	1157.9
155°	1039.9	1080.9	1143.2	1208.2
157.5°	1095.1	1136.9	1196.4	1253.2
160°	1129.0	1174.3	1228.1	1280.4
162.5°	1167.5	1209.4	1256.4	1303.0
165°	1223.8	1257.8	1296.0	1335.6
167.5°	1271.1	1299.4	1329.4	1360.2
170°	1301.6	1324.3	1349.7	1373.8
172.5°	1327.7	1345.8	1364.4	1385.1
175°	1362.5	1372.4	1383.7	1396.4
177.5°	1389.3	1392.7	1396.1	1401.8
180°	1400.7	1400.7	1400.7	1400.7



TEST NUMBER: P1428424
 CATALOG NUMBER: SQ2W-PW1-K-100U-050D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.67	16.40	16.73	17.46	18.90	11.91	12.65	12.98	13.71	15.15
	3H	16.96	17.61	18.03	18.68	20.14	13.17	13.83	14.24	14.90	16.36
	4H	17.36	17.98	18.44	19.05	20.52	13.67	14.29	14.76	15.37	16.83
	6H	17.53	18.11	18.63	19.18	20.66	13.97	14.55	15.07	15.62	17.10
	8H	17.57	18.12	18.67	19.21	20.68	14.08	14.63	15.18	15.72	17.19
	12H	17.57	18.09	18.67	19.17	20.66	14.11	14.63	15.21	15.71	17.20
4H	2H	15.78	16.40	16.87	17.47	18.94	12.71	13.33	13.80	14.40	15.86
	3H	17.31	17.83	18.41	18.92	20.40	14.14	14.66	15.24	15.76	17.23
	4H	17.85	18.32	18.95	19.41	20.91	14.71	15.19	15.82	16.28	17.78
	6H	18.15	18.56	19.26	19.67	21.16	15.09	15.50	16.20	16.61	18.10
	8H	18.24	18.62	19.35	19.73	21.23	15.24	15.62	16.35	16.72	18.23
	12H	18.26	18.60	19.39	19.72	21.23	15.28	15.62	16.40	16.74	18.25
8H	4H	17.88	18.26	18.99	19.36	20.87	15.05	15.43	16.16	16.53	18.04
	6H	18.30	18.61	19.43	19.76	21.26	15.54	15.85	16.67	17.00	18.50
	8H	18.47	18.74	19.60	19.87	21.39	15.76	16.03	16.89	17.16	18.68
	12H	18.54	18.78	19.68	19.90	21.46	15.83	16.07	16.97	17.20	18.76
12H	4H	17.83	18.18	18.96	19.29	20.80	15.06	15.40	16.19	16.52	18.03
	6H	18.29	18.56	19.43	19.69	21.22	15.61	15.89	16.75	17.01	18.54
	8H	18.47	18.71	19.61	19.84	21.40	15.85	16.09	16.99	17.21	18.78