

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428508

Luminaire Tested: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428508
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, MEDIUM 80-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4476.8 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	107	103	100	97	102	99	96	94	90	88	87	83	81	80	76	75	74
2	100	94	89	85	95	90	85	82	83	79	77	76	74	72	70	69	67
3	93	85	79	74	89	82	77	72	76	72	68	70	67	64	65	63	60
4	87	78	71	66	83	75	69	64	70	65	61	65	61	58	60	57	55
5	81	71	64	59	77	69	62	57	64	59	55	60	56	52	56	53	50
6	76	65	58	53	72	63	56	52	59	54	50	55	51	48	52	48	45
7	71	60	53	48	68	58	52	47	55	49	45	51	47	43	48	44	42
8	66	55	48	43	64	54	47	43	51	45	41	48	43	40	45	41	38
9	62	51	44	40	60	50	43	39	47	42	38	44	40	36	42	38	35
10	59	48	41	36	56	46	40	36	44	38	35	42	37	34	39	35	32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35625	35625	35625	35625
5°	35949	35933	35949	35933
10°	36314	36296	36314	36296
15°	36917	36263	36917	36263
20°	37094	35676	37094	35676
25°	36331	34673	36331	34673
30°	34471	32421	34471	32421
35°	31002	29250	31002	29250
40°	25416	24078	25416	24078
45°	15892	14926	15892	14926
50°	6217	5687	6217	5687
55°	3068	3037	3068	3037
60°	1434	1298	1434	1298
65°	1291	1211	1291	1211
70°	1246	1199	1246	1199
75°	1254	1123	1254	1123
80°	1181	1079	1181	1079
85°	1167	982	1167	982

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 18091 cd/sqm

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.0	4.7
10°-20°	616.9	13.8
20°-30°	912.1	20.4
30°-40°	943.7	21.1
40°-50°	567.7	12.7
50°-60°	135.7	3.0
60°-70°	37.1	0.8
70°-80°	20.8	0.5
80°-90°	8.0	0.2
90°-100°	27.9	0.6
100°-110°	81.4	1.8
110°-120°	132.8	3.0
120°-130°	168.5	3.8
130°-140°	180.3	4.0
140°-150°	168.4	3.8
150°-160°	138.6	3.1
160°-170°	92.9	2.1
170°-180°	33.0	0.7
0°-30°	1739.9	38.9
0°-40°	2683.7	59.9
0°-60°	3387.0	75.7
0°-90°	3452.9	77.1
90°-120°	242.1	5.4
90°-150°	759.4	17.0
90°-180°	1024.0	22.9
0°-180°	4476.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2206	2206	2206	2206	2206	
5°	2218	2217	2218	2217	2218	212
15°	2209	2170	2209	2170	2209	622
25°	2039	1946	2039	1946	2039	932
35°	1573	1484	1573	1484	1573	966
45°	696	654	696	654	696	538
55°	109	108	109	108	109	109
65°	34	32	34	32	34	34
75°	20	18	20	18	20	21
85°	6	5	6	5	6	6
90°	1	8	1	15	1	1
95°	11	8	11	48	11	13
105°	52	83	52	114	52	55
115°	99	137	99	169	99	98
125°	147	218	147	208	147	131
135°	199	285	199	230	199	154
145°	255	329	255	235	255	159
155°	302	357	302	244	302	139
165°	334	372	334	280	334	94
175°	350	364	350	329	350	33
180°	351	351	351	351	351	

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5
2.5°	2217.5	2214.9	2212.2	2205.7	2197.8	2197.9	2206.2	2212.0	2210.1	2208.2	2210.1
5°	2218.1	2214.8	2211.6	2204.0	2195.1	2197.2	2210.4	2219.9	2218.5	2217.1	2218.5
7.5°	2215.8	2214.4	2213.0	2207.5	2200.6	2202.2	2212.1	2219.1	2216.9	2214.8	2216.9
10°	2215.0	2215.4	2215.9	2208.6	2198.7	2199.0	2209.3	2216.7	2215.3	2213.9	2215.3
12.5°	2214.1	2218.0	2221.8	2212.0	2197.6	2194.5	2202.6	2207.8	2204.5	2201.2	2204.5
15°	2208.6	2216.1	2223.7	2210.4	2190.2	2180.1	2180.1	2178.9	2174.2	2169.5	2174.2
17.5°	2185.1	2194.1	2203.0	2185.0	2158.0	2140.9	2133.7	2126.8	2121.1	2115.3	2121.1
20°	2158.9	2167.8	2176.8	2155.4	2123.9	2102.3	2090.5	2081.1	2078.7	2076.4	2078.7
22.5°	2117.4	2127.1	2136.8	2113.9	2080.2	2056.8	2044.0	2033.3	2029.5	2025.6	2029.5
25°	2039.4	2046.9	2054.4	2030.6	1996.2	1974.4	1965.0	1956.6	1951.5	1946.3	1951.5
27.5°	1935.3	1939.4	1943.6	1920.5	1888.3	1866.9	1856.2	1846.3	1839.2	1832.1	1839.2
30°	1849.0	1850.9	1852.7	1834.2	1808.8	1789.0	1774.9	1761.5	1750.3	1739.0	1750.3
32.5°	1746.6	1748.5	1750.3	1734.0	1711.7	1693.8	1680.4	1668.2	1659.1	1650.1	1659.1
35°	1572.9	1572.0	1571.0	1560.6	1546.9	1532.4	1516.8	1502.9	1493.5	1484.0	1493.5
37.5°	1355.6	1357.0	1358.3	1350.5	1339.7	1328.2	1315.9	1304.4	1294.9	1285.4	1294.9
40°	1205.9	1206.8	1207.7	1201.3	1192.3	1178.9	1161.1	1147.1	1144.7	1142.4	1144.7
42.5°	1023.1	1037.2	1051.3	1045.6	1033.3	1020.2	1006.5	993.5	982.5	971.5	982.5
45°	696.0	738.8	781.6	792.3	792.3	784.0	767.6	744.0	698.8	653.7	698.8
47.5°	393.1	441.8	490.5	522.5	548.9	537.7	488.8	438.4	383.6	328.8	383.6
50°	247.5	280.4	313.3	354.4	398.1	386.1	318.4	263.0	244.7	226.4	244.7
52.5°	175.6	192.3	209.1	247.7	293.7	288.1	230.9	185.6	176.0	166.3	176.0
55°	109.0	115.1	121.2	140.0	163.0	161.6	135.7	115.4	111.7	107.9	111.7
57.5°	64.7	71.0	77.3	85.7	94.7	94.7	85.7	77.4	71.5	65.6	71.5
60°	44.4	49.6	54.8	61.7	69.2	68.3	58.9	50.5	45.4	40.2	45.4
62.5°	38.5	40.7	42.8	48.2	54.6	54.0	46.5	40.4	38.6	36.8	38.6
65°	33.8	34.3	34.8	35.3	35.7	35.5	34.6	33.6	32.7	31.7	32.7
67.5°	29.8	30.3	30.8	30.6	30.2	30.0	29.9	29.6	28.8	27.9	28.8
70°	26.4	26.9	27.4	27.5	27.5	27.3	26.8	26.3	25.9	25.4	25.9
72.5°	23.9	24.4	24.8	24.7	24.3	24.1	24.0	23.7	22.8	22.0	22.8
75°	20.1	20.1	20.1	20.1	20.1	19.9	19.4	18.9	18.5	18.0	18.5
77.5°	15.2	15.7	16.2	15.9	15.5	15.2	15.2	15.1	14.6	14.2	14.6
80°	12.7	13.2	13.6	13.4	12.9	12.7	12.7	12.6	12.1	11.6	12.1
82.5°	10.2	10.2	10.3	10.3	10.2	10.2	10.2	10.0	9.6	9.1	9.6
85°	6.3	6.3	6.3	6.0	5.5	5.3	5.3	5.3	5.3	5.3	5.3
87.5°	1.9	2.6	3.3	3.4	3.2	3.1	3.1	3.2	3.3	3.3	3.3
90°	1.1	2.5	4.3	5.7	6.7	7.1	7.1	7.4	7.8	7.8	7.8
92.5°	3.9	6.2	6.2	6.2	7.6	8.2	8.8	8.9	9.2	9.2	9.2
95°	11.0	12.0	18.1	17.7	12.0	9.6	8.1	8.1	8.1	8.1	8.1
97.5°	21.0	22.5	23.5	31.5	33.3	32.2	26.2	22.0	19.7	18.6	19.7
100°	29.8	30.5	32.6	32.9	41.8	50.3	46.0	40.7	39.0	37.9	39.0
102.5°	38.5	39.0	42.2	43.7	45.8	50.6	65.3	63.7	62.5	62.3	62.5
105°	51.7	52.1	58.1	60.9	62.3	62.3	62.0	69.1	80.4	82.9	80.4
107.5°	65.8	67.4	74.5	82.1	83.7	84.2	82.3	81.3	80.8	81.1	80.8
110°	75.4	77.9	86.4	96.0	98.5	99.2	98.5	97.4	96.7	96.7	96.7

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	84.8	88.4	98.0	109.0	113.2	115.3	113.8	113.0	112.3	112.9	112.3
115°	99.2	104.5	117.2	128.6	137.1	138.1	137.8	137.8	137.4	137.4	137.4
117.5°	112.5	121.0	135.3	148.5	158.3	161.2	162.6	162.2	161.7	162.4	161.7
120°	121.9	131.8	148.1	162.9	172.5	176.8	178.2	177.5	178.2	177.5	178.2
122.5°	131.8	144.0	160.0	175.4	186.7	191.5	193.2	193.3	193.5	193.1	193.5
125°	146.6	161.5	180.3	196.2	207.9	213.6	215.0	215.4	216.1	217.8	216.1
127.5°	161.7	178.5	199.1	214.5	226.5	233.4	235.6	236.3	237.8	238.6	237.8
130°	172.2	191.3	212.2	226.7	238.4	245.8	249.7	250.8	252.6	252.2	252.6
132.5°	183.2	203.2	224.4	239.5	250.3	258.3	261.6	264.7	265.3	265.8	265.3
135°	199.4	221.0	242.3	257.2	267.4	275.2	279.5	282.3	284.1	285.1	284.1
137.5°	216.5	239.3	259.7	273.0	283.3	290.0	294.9	297.8	299.7	300.5	299.7
140°	228.1	250.1	269.9	283.7	292.9	299.7	303.9	307.5	309.6	309.6	309.6
142.5°	239.2	260.9	280.1	293.9	302.0	308.2	312.7	315.4	317.8	317.8	317.8
145°	254.7	276.3	294.0	307.8	314.6	320.2	325.2	327.3	328.7	328.7	328.7
147.5°	270.9	290.0	306.2	319.4	325.1	331.8	335.7	337.4	339.1	338.4	339.1
150°	280.5	298.3	313.8	326.2	331.9	338.3	342.2	343.6	345.4	344.3	345.4
152.5°	289.9	306.8	320.9	332.5	337.3	343.7	348.1	349.5	350.8	350.0	350.8
155°	302.5	317.4	330.5	341.1	345.4	351.4	355.6	357.4	358.8	357.1	358.8
157.5°	313.8	326.6	338.0	347.8	352.3	357.5	361.4	363.6	365.1	364.3	365.1
160°	320.6	332.3	342.5	351.7	356.0	360.6	364.9	367.3	368.7	367.7	368.7
162.5°	326.2	336.8	346.5	354.9	358.5	362.6	367.7	369.9	371.3	370.0	371.3
165°	334.4	342.9	351.4	358.5	361.7	364.9	370.2	372.6	373.7	372.3	373.7
167.5°	340.6	347.1	353.9	360.0	362.4	365.5	370.8	372.9	374.2	372.4	374.2
170°	344.0	349.6	355.6	360.6	362.4	365.2	370.5	372.3	373.4	371.6	373.4
172.5°	346.8	351.0	355.9	360.3	361.2	363.5	368.5	370.3	371.1	369.6	371.1
175°	349.6	352.1	355.6	358.5	358.1	359.5	363.8	365.2	366.6	364.5	366.6
177.5°	351.0	352.1	353.2	354.9	353.8	353.8	356.9	357.8	358.0	356.9	358.0
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5
2.5°	2212.0	2206.2	2197.9	2197.8	2205.7	2212.2	2214.9	2217.5	2214.9	2212.2	2205.7
5°	2219.9	2210.4	2197.2	2195.1	2204.0	2211.6	2214.8	2218.1	2214.8	2211.6	2204.0
7.5°	2219.1	2212.1	2202.2	2200.6	2207.5	2213.0	2214.4	2215.8	2214.4	2213.0	2207.5
10°	2216.7	2209.3	2199.0	2198.7	2208.6	2215.9	2215.4	2215.0	2215.4	2215.9	2208.6
12.5°	2207.8	2202.6	2194.5	2197.6	2212.0	2221.8	2218.0	2214.1	2218.0	2221.8	2212.0
15°	2178.9	2180.1	2180.1	2190.2	2210.4	2223.7	2216.1	2208.6	2216.1	2223.7	2210.4
17.5°	2126.8	2133.7	2140.9	2158.0	2185.0	2203.0	2194.1	2185.1	2194.1	2203.0	2185.0
20°	2081.1	2090.5	2102.3	2123.9	2155.4	2176.8	2167.8	2158.9	2167.8	2176.8	2155.4
22.5°	2033.3	2044.0	2056.8	2080.2	2113.9	2136.8	2127.1	2117.4	2127.1	2136.8	2113.9
25°	1956.6	1965.0	1974.4	1996.2	2030.6	2054.4	2046.9	2039.4	2046.9	2054.4	2030.6
27.5°	1846.3	1856.2	1866.9	1888.3	1920.5	1943.6	1939.4	1935.3	1939.4	1943.6	1920.5
30°	1761.5	1774.9	1789.0	1808.8	1834.2	1852.7	1850.9	1849.0	1850.9	1852.7	1834.2
32.5°	1668.2	1680.4	1693.8	1711.7	1734.0	1750.3	1748.5	1746.6	1748.5	1750.3	1734.0
35°	1502.9	1516.8	1532.4	1546.9	1560.6	1571.0	1572.0	1572.9	1572.0	1571.0	1560.6
37.5°	1304.4	1315.9	1328.2	1339.7	1350.5	1358.3	1357.0	1355.6	1357.0	1358.3	1350.5
40°	1147.1	1161.1	1178.9	1192.3	1201.3	1207.7	1206.8	1205.9	1206.8	1207.7	1201.3
42.5°	993.5	1006.5	1020.2	1033.3	1045.6	1051.3	1037.2	1023.1	1037.2	1051.3	1045.6
45°	744.0	767.6	784.0	792.3	792.3	781.6	738.8	696.0	738.8	781.6	792.3
47.5°	438.4	488.8	537.7	548.9	522.5	490.5	441.8	393.1	441.8	490.5	522.5
50°	263.0	318.4	386.1	398.1	354.4	313.3	280.4	247.5	280.4	313.3	354.4
52.5°	185.6	230.9	288.1	293.7	247.7	209.1	192.3	175.6	192.3	209.1	247.7
55°	115.4	135.7	161.6	163.0	140.0	121.2	115.1	109.0	115.1	121.2	140.0
57.5°	77.4	85.7	94.7	94.7	85.7	77.3	71.0	64.7	71.0	77.3	85.7
60°	50.5	58.9	68.3	69.2	61.7	54.8	49.6	44.4	49.6	54.8	61.7
62.5°	40.4	46.5	54.0	54.6	48.2	42.8	40.7	38.5	40.7	42.8	48.2
65°	33.6	34.6	35.5	35.7	35.3	34.8	34.3	33.8	34.3	34.8	35.3
67.5°	29.6	29.9	30.0	30.2	30.6	30.8	30.3	29.8	30.3	30.8	30.6
70°	26.3	26.8	27.3	27.5	27.5	27.4	26.9	26.4	26.9	27.4	27.5
72.5°	23.7	24.0	24.1	24.3	24.7	24.8	24.4	23.9	24.4	24.8	24.7
75°	18.9	19.4	19.9	20.1	20.1	20.1	20.1	20.1	20.1	20.1	20.1
77.5°	15.1	15.2	15.2	15.5	15.9	16.2	15.7	15.2	15.7	16.2	15.9
80°	12.6	12.7	12.7	12.9	13.4	13.6	13.2	12.7	13.2	13.6	13.4
82.5°	10.0	10.2	10.2	10.2	10.3	10.3	10.2	10.2	10.2	10.3	10.3
85°	5.3	5.3	5.3	5.5	6.0	6.3	6.3	6.3	6.3	6.3	6.0
87.5°	3.2	3.1	3.1	3.2	3.4	3.3	2.6	1.9	2.6	3.2	3.5
90°	7.4	7.1	7.1	6.7	5.7	4.3	2.5	1.1	2.5	3.9	6.4
92.5°	8.9	8.8	8.2	7.6	6.2	6.2	6.2	3.9	6.7	9.6	13.7
95°	8.1	8.1	9.6	12.0	17.7	18.1	12.0	11.0	15.6	22.0	27.6
97.5°	22.0	26.2	32.2	33.3	31.5	23.5	22.5	21.0	28.6	34.9	44.0
100°	40.7	46.0	50.3	41.8	32.9	32.6	30.5	29.8	37.9	43.9	52.8
102.5°	63.7	65.3	50.6	45.8	43.7	42.2	39.0	38.5	46.7	55.0	62.4
105°	69.1	62.0	62.3	62.3	60.9	58.1	52.1	51.7	60.9	70.5	79.7
107.5°	81.3	82.3	84.2	83.7	82.1	74.5	67.4	65.8	74.1	85.6	95.7
110°	97.4	98.5	99.2	98.5	96.0	86.4	77.9	75.4	82.9	94.9	105.9

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	113.0	113.8	115.3	113.2	109.0	98.0	88.4	84.8	92.2	104.6	115.8
115°	137.8	137.8	138.1	137.1	128.6	117.2	104.5	99.2	105.6	116.9	129.3
117.5°	162.2	162.6	161.2	158.3	148.5	135.3	121.0	112.5	117.5	129.5	142.3
120°	177.5	178.2	176.8	172.5	162.9	148.1	131.8	121.9	125.7	137.4	150.2
122.5°	193.3	193.2	191.5	186.7	175.4	160.0	144.0	131.8	133.4	144.2	156.7
125°	215.4	215.0	213.6	207.9	196.2	180.3	161.5	146.6	144.5	153.7	166.5
127.5°	236.3	235.6	233.4	226.5	214.5	199.1	178.5	161.7	156.9	162.7	174.4
130°	250.8	249.7	245.8	238.4	226.7	212.2	191.3	172.2	165.4	169.0	179.2
132.5°	264.7	261.6	258.3	250.3	239.5	224.4	203.2	183.2	173.9	175.5	183.5
135°	282.3	279.5	275.2	267.4	257.2	242.3	221.0	199.4	186.7	185.3	189.9
137.5°	297.8	294.9	290.0	283.3	273.0	259.7	239.3	216.5	200.4	195.7	197.4
140°	307.5	303.9	299.7	292.9	283.7	269.9	250.1	228.1	210.1	203.3	202.3
142.5°	315.4	312.7	308.2	302.0	293.9	280.1	260.9	239.2	220.0	211.3	208.8
145°	327.3	325.2	320.2	314.6	307.8	294.0	276.3	254.7	235.6	224.2	218.9
147.5°	337.4	335.7	331.8	325.1	319.4	306.2	290.0	270.9	251.3	237.3	230.4
150°	343.6	342.2	338.3	331.9	326.2	313.8	298.3	280.5	261.8	246.9	238.0
152.5°	349.5	348.1	343.7	337.3	332.5	320.9	306.8	289.9	270.8	256.0	246.8
155°	357.4	355.6	351.4	345.4	341.1	330.5	317.4	302.5	286.2	270.6	260.4
157.5°	363.6	361.4	357.5	352.3	347.8	338.0	326.6	313.8	299.5	284.7	274.2
160°	367.3	364.9	360.6	356.0	351.7	342.5	332.3	320.6	307.5	294.0	282.7
162.5°	369.9	367.7	362.6	358.5	354.9	346.5	336.8	326.2	314.6	302.8	292.3
165°	372.6	370.2	364.9	361.7	358.5	351.4	342.9	334.4	324.5	314.9	306.4
167.5°	372.9	370.8	365.5	362.4	360.0	353.9	347.1	340.6	332.8	325.3	318.2
170°	372.3	370.5	365.2	362.4	360.6	355.6	349.6	344.0	337.9	331.6	325.9
172.5°	370.3	368.5	363.5	361.2	360.3	355.9	351.0	346.8	341.6	336.9	332.4
175°	365.2	363.8	359.5	358.1	358.5	355.6	352.1	349.6	346.4	343.6	341.1
177.5°	357.8	356.9	353.8	353.8	354.9	353.2	352.1	351.0	349.5	348.7	347.8
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5	2206.5
2.5°	2197.8	2197.9	2206.2	2212.0	2210.1	2208.2	2210.1	2212.0	2206.2	2197.9	2197.8
5°	2195.1	2197.2	2210.4	2219.9	2218.5	2217.1	2218.5	2219.9	2210.4	2197.2	2195.1
7.5°	2200.6	2202.2	2212.1	2219.1	2216.9	2214.8	2216.9	2219.1	2212.1	2202.2	2200.6
10°	2198.7	2199.0	2209.3	2216.7	2215.3	2213.9	2215.3	2216.7	2209.3	2199.0	2198.7
12.5°	2197.6	2194.5	2202.6	2207.8	2204.5	2201.2	2204.5	2207.8	2202.6	2194.5	2197.6
15°	2190.2	2180.1	2180.1	2178.9	2174.2	2169.5	2174.2	2178.9	2180.1	2180.1	2190.2
17.5°	2158.0	2140.9	2133.7	2126.8	2121.1	2115.3	2121.1	2126.8	2133.7	2140.9	2158.0
20°	2123.9	2102.3	2090.5	2081.1	2078.7	2076.4	2078.7	2081.1	2090.5	2102.3	2123.9
22.5°	2080.2	2056.8	2044.0	2033.3	2029.5	2025.6	2029.5	2033.3	2044.0	2056.8	2080.2
25°	1996.2	1974.4	1965.0	1956.6	1951.5	1946.3	1951.5	1956.6	1965.0	1974.4	1996.2
27.5°	1888.3	1866.9	1856.2	1846.3	1839.2	1832.1	1839.2	1846.3	1856.2	1866.9	1888.3
30°	1808.8	1789.0	1774.9	1761.5	1750.3	1739.0	1750.3	1761.5	1774.9	1789.0	1808.8
32.5°	1711.7	1693.8	1680.4	1668.2	1659.1	1650.1	1659.1	1668.2	1680.4	1693.8	1711.7
35°	1546.9	1532.4	1516.8	1502.9	1493.5	1484.0	1493.5	1502.9	1516.8	1532.4	1546.9
37.5°	1339.7	1328.2	1315.9	1304.4	1294.9	1285.4	1294.9	1304.4	1315.9	1328.2	1339.7
40°	1192.3	1178.9	1161.1	1147.1	1144.7	1142.4	1144.7	1147.1	1161.1	1178.9	1192.3
42.5°	1033.3	1020.2	1006.5	993.5	982.5	971.5	982.5	993.5	1006.5	1020.2	1033.3
45°	792.3	784.0	767.6	744.0	698.8	653.7	698.8	744.0	767.6	784.0	792.3
47.5°	548.9	537.7	488.8	438.4	383.6	328.8	383.6	438.4	488.8	537.7	548.9
50°	398.1	386.1	318.4	263.0	244.7	226.4	244.7	263.0	318.4	386.1	398.1
52.5°	293.7	288.1	230.9	185.6	176.0	166.3	176.0	185.6	230.9	288.1	293.7
55°	163.0	161.6	135.7	115.4	111.7	107.9	111.7	115.4	135.7	161.6	163.0
57.5°	94.7	94.7	85.7	77.4	71.5	65.6	71.5	77.4	85.7	94.7	94.7
60°	69.2	68.3	58.9	50.5	45.4	40.2	45.4	50.5	58.9	68.3	69.2
62.5°	54.6	54.0	46.5	40.4	38.6	36.8	38.6	40.4	46.5	54.0	54.6
65°	35.7	35.5	34.6	33.6	32.7	31.7	32.7	33.6	34.6	35.5	35.7
67.5°	30.2	30.0	29.9	29.6	28.8	27.9	28.8	29.6	29.9	30.0	30.2
70°	27.5	27.3	26.8	26.3	25.9	25.4	25.9	26.3	26.8	27.3	27.5
72.5°	24.3	24.1	24.0	23.7	22.8	22.0	22.8	23.7	24.0	24.1	24.3
75°	20.1	19.9	19.4	18.9	18.5	18.0	18.5	18.9	19.4	19.9	20.1
77.5°	15.5	15.2	15.2	15.1	14.6	14.2	14.6	15.1	15.2	15.2	15.5
80°	12.9	12.7	12.7	12.6	12.1	11.6	12.1	12.6	12.7	12.7	12.9
82.5°	10.2	10.2	10.2	10.0	9.6	9.1	9.6	10.0	10.2	10.2	10.2
85°	5.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.5
87.5°	3.5	3.8	4.3	4.6	4.9	4.7	4.9	4.6	4.3	3.8	3.5
90°	8.1	10.6	13.1	14.5	15.9	15.2	15.9	14.5	13.1	10.6	8.1
92.5°	16.4	20.5	23.6	26.1	27.3	27.1	27.3	26.1	23.6	20.5	16.4
95°	32.9	37.9	42.9	46.4	48.5	47.8	48.5	46.4	42.9	37.9	32.9
97.5°	50.8	57.5	63.0	66.3	68.4	69.9	68.4	66.3	63.0	57.5	50.8
100°	62.7	69.1	75.4	79.3	82.9	84.3	82.9	79.3	75.4	69.1	62.7
102.5°	72.3	80.7	87.6	91.8	94.8	96.2	94.8	91.8	87.6	80.7	72.3
105°	88.2	97.1	104.5	109.8	113.0	114.1	113.0	109.8	104.5	97.1	88.2
107.5°	104.1	113.2	120.1	126.0	129.9	132.1	129.9	126.0	120.1	113.2	104.1
110°	116.5	124.0	131.4	136.7	140.6	142.0	140.6	136.7	131.4	124.0	116.5

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	127.0	135.3	142.8	148.1	152.5	154.5	152.5	148.1	142.8	135.3	127.0
115°	141.7	152.7	159.4	164.4	167.5	169.3	167.5	164.4	159.4	152.7	141.7
117.5°	153.9	165.4	172.7	176.5	178.0	179.3	178.0	176.5	172.7	165.4	153.9
120°	161.5	172.2	180.7	185.6	187.4	188.1	187.4	185.6	180.7	172.2	161.5
122.5°	168.6	178.7	186.9	193.0	195.9	196.6	195.9	193.0	186.9	178.7	168.6
125°	178.5	188.1	196.6	202.6	205.8	207.6	205.8	202.6	196.6	188.1	178.5
127.5°	187.2	197.5	205.3	210.8	213.9	215.3	213.9	210.8	205.3	197.5	187.2
130°	192.0	202.6	210.4	216.4	219.3	220.7	219.3	216.4	210.4	202.6	192.0
132.5°	195.7	206.9	214.9	220.4	223.5	224.9	223.5	220.4	214.9	206.9	195.7
135°	200.1	211.8	220.3	225.6	228.5	229.9	228.5	225.6	220.3	211.8	200.1
137.5°	204.0	214.7	223.5	229.1	231.7	232.6	231.7	229.1	223.5	214.7	204.0
140°	206.9	216.1	224.9	230.2	233.1	233.4	233.1	230.2	224.9	216.1	206.9
142.5°	210.6	217.8	225.5	230.8	233.6	234.3	233.6	230.8	225.5	217.8	210.6
145°	217.1	221.4	226.7	231.7	234.1	234.9	234.1	231.7	226.7	221.4	217.1
147.5°	225.4	226.8	229.5	232.8	235.2	235.7	235.2	232.8	229.5	226.8	225.4
150°	231.7	231.3	232.4	234.5	236.6	236.3	236.6	234.5	232.4	231.3	231.7
152.5°	238.7	236.7	236.6	237.6	238.6	238.5	238.6	237.6	236.6	236.7	238.7
155°	250.8	246.9	244.8	244.1	244.1	243.7	244.1	244.1	244.8	246.9	250.8
157.5°	264.0	258.6	255.4	253.7	253.2	252.4	253.2	253.7	255.4	258.6	264.0
160°	273.1	267.1	263.9	261.1	260.0	258.9	260.0	261.1	263.9	267.1	273.1
162.5°	281.6	275.9	272.4	269.8	268.8	267.2	268.8	269.8	272.4	275.9	281.6
165°	295.4	289.4	285.5	283.4	282.0	280.5	282.0	283.4	285.5	289.4	295.4
167.5°	309.2	302.6	300.1	297.7	296.3	293.8	296.3	297.7	300.1	302.6	309.2
170°	317.7	311.7	310.3	308.2	305.7	302.9	305.7	308.2	310.3	311.7	317.7
172.5°	325.1	321.1	319.7	317.5	316.7	314.5	316.7	317.5	319.7	321.1	325.1
175°	335.8	332.6	332.6	332.3	331.2	329.1	331.2	332.3	332.6	332.6	335.8
177.5°	344.7	343.0	344.2	344.2	343.9	341.9	343.9	344.2	344.2	343.0	344.7
180°	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7	350.7

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	2206.5	2206.5	2206.5	2206.5
2.5°	2205.7	2212.2	2214.9	2217.5
5°	2204.0	2211.6	2214.8	2218.1
7.5°	2207.5	2213.0	2214.4	2215.8
10°	2208.6	2215.9	2215.4	2215.0
12.5°	2212.0	2221.8	2218.0	2214.1
15°	2210.4	2223.7	2216.1	2208.6
17.5°	2185.0	2203.0	2194.1	2185.1
20°	2155.4	2176.8	2167.8	2158.9
22.5°	2113.9	2136.8	2127.1	2117.4
25°	2030.6	2054.4	2046.9	2039.4
27.5°	1920.5	1943.6	1939.4	1935.3
30°	1834.2	1852.7	1850.9	1849.0
32.5°	1734.0	1750.3	1748.5	1746.6
35°	1560.6	1571.0	1572.0	1572.9
37.5°	1350.5	1358.3	1357.0	1355.6
40°	1201.3	1207.7	1206.8	1205.9
42.5°	1045.6	1051.3	1037.2	1023.1
45°	792.3	781.6	738.8	696.0
47.5°	522.5	490.5	441.8	393.1
50°	354.4	313.3	280.4	247.5
52.5°	247.7	209.1	192.3	175.6
55°	140.0	121.2	115.1	109.0
57.5°	85.7	77.3	71.0	64.7
60°	61.7	54.8	49.6	44.4
62.5°	48.2	42.8	40.7	38.5
65°	35.3	34.8	34.3	33.8
67.5°	30.6	30.8	30.3	29.8
70°	27.5	27.4	26.9	26.4
72.5°	24.7	24.8	24.4	23.9
75°	20.1	20.1	20.1	20.1
77.5°	15.9	16.2	15.7	15.2
80°	13.4	13.6	13.2	12.7
82.5°	10.3	10.3	10.2	10.2
85°	6.0	6.3	6.3	6.3
87.5°	3.5	3.2	2.6	1.9
90°	6.4	3.9	2.5	1.1
92.5°	13.7	9.6	6.7	3.9
95°	27.6	22.0	15.6	11.0
97.5°	44.0	34.9	28.6	21.0
100°	52.8	43.9	37.9	29.8
102.5°	62.4	55.0	46.7	38.5
105°	79.7	70.5	60.9	51.7
107.5°	95.7	85.6	74.1	65.8
110°	105.9	94.9	82.9	75.4

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	115.8	104.6	92.2	84.8
115°	129.3	116.9	105.6	99.2
117.5°	142.3	129.5	117.5	112.5
120°	150.2	137.4	125.7	121.9
122.5°	156.7	144.2	133.4	131.8
125°	166.5	153.7	144.5	146.6
127.5°	174.4	162.7	156.9	161.7
130°	179.2	169.0	165.4	172.2
132.5°	183.5	175.5	173.9	183.2
135°	189.9	185.3	186.7	199.4
137.5°	197.4	195.7	200.4	216.5
140°	202.3	203.3	210.1	228.1
142.5°	208.8	211.3	220.0	239.2
145°	218.9	224.2	235.6	254.7
147.5°	230.4	237.3	251.3	270.9
150°	238.0	246.9	261.8	280.5
152.5°	246.8	256.0	270.8	289.9
155°	260.4	270.6	286.2	302.5
157.5°	274.2	284.7	299.5	313.8
160°	282.7	294.0	307.5	320.6
162.5°	292.3	302.8	314.6	326.2
165°	306.4	314.9	324.5	334.4
167.5°	318.2	325.3	332.8	340.6
170°	325.9	331.6	337.9	344.0
172.5°	332.4	336.9	341.6	346.8
175°	341.1	343.6	346.4	349.6
177.5°	347.8	348.7	349.5	351.0
180°	350.7	350.7	350.7	350.7

TEST NUMBER: P1428508

CATALOG NUMBER: SQ2W-WBM-K-025U-075D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.70	7.60	7.42	8.31	9.15	6.68	7.59	7.40	8.29	9.13
	3H	7.40	8.20	8.13	8.92	9.79	7.32	8.12	8.05	8.84	9.71
	4H	7.77	8.51	8.52	9.24	10.13	7.63	8.38	8.38	9.11	9.99
	6H	8.05	8.73	8.81	9.47	10.36	7.87	8.55	8.63	9.29	10.19
	8H	8.17	8.81	8.94	9.57	10.47	7.97	8.61	8.74	9.37	10.27
	12H	8.25	8.86	9.02	9.61	10.53	8.03	8.64	8.80	9.39	10.31
4H	2H	6.81	7.55	7.56	8.28	9.17	6.80	7.54	7.55	8.27	9.15
	3H	7.76	8.37	8.52	9.14	10.04	7.68	8.29	8.44	9.06	9.95
	4H	8.27	8.82	9.05	9.59	10.52	8.13	8.67	8.90	9.44	10.37
	6H	8.70	9.17	9.50	9.96	10.90	8.50	8.97	9.30	9.77	10.71
	8H	8.89	9.33	9.69	10.12	11.06	8.67	9.11	9.47	9.89	10.84
	12H	9.02	9.41	9.83	10.22	11.17	8.77	9.15	9.58	9.97	10.91
8H	4H	8.39	8.83	9.19	9.62	10.56	8.26	8.70	9.06	9.48	10.43
	6H	8.97	9.32	9.79	10.16	11.11	8.78	9.13	9.60	9.97	10.91
	8H	9.25	9.57	10.09	10.40	11.37	9.04	9.36	9.88	10.19	11.15
	12H	9.47	9.75	10.31	10.57	11.60	9.21	9.49	10.05	10.31	11.34
12H	4H	8.38	8.76	9.19	9.58	10.53	8.25	8.64	9.06	9.45	10.40
	6H	9.00	9.32	9.84	10.15	11.11	8.82	9.14	9.66	9.97	10.93
	8H	9.33	9.61	10.16	10.43	11.45	9.12	9.40	9.96	10.22	11.25

END OF REPORT