

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428586

Luminaire Tested: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428586  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT N/A - DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5793.9 lumens  
Efficiency: N/A  
Efficacy: 116.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	71	65	61	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	161097	161097	161097	161097
5°	155544	155716	155544	155716
10°	134446	134765	134446	134765
15°	106985	104026	106985	104026
20°	76002	75545	76002	75545
25°	54678	53227	54678	53227
30°	41778	40557	41778	40557
35°	32794	31398	32794	31398
40°	24847	23317	24847	23317
45°	13903	12408	13903	12408
50°	4890	4313	4890	4313
55°	2989	2840	2989	2840
60°	2286	2115	2286	2115
65°	2097	1960	2097	1960
70°	2006	1836	2006	1836
75°	1878	1765	1878	1765
80°	1646	1646	1646	1646
85°	1649	1315	1649	1315

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 16486 cd/sqm



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	866.1	14.9
10°-20°	1721.4	29.7
20°-30°	1425.6	24.6
30°-40°	1025.5	17.7
40°-50°	522.4	9.0
50°-60°	135.8	2.3
60°-70°	56.4	1.0
70°-80°	31.3	0.5
80°-90°	9.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4013.1	69.3
0°-40°	5038.6	87.0
0°-60°	5696.9	98.3
0°-90°	5793.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5793.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	9978	9978	9978	9978	9978	
5°	9597	9608	9597	9608	9597	866
15°	6400	6224	6400	6224	6400	1737
25°	3069	2988	3069	2988	3069	1444
35°	1664	1593	1664	1593	1664	1044
45°	609	543	609	543	609	487
55°	106	101	106	101	106	104
65°	55	51	55	51	55	55
75°	30	28	30	28	30	32
85°	9	7	9	7	9	10
90°	0	0	0	0	0	



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8
2.5°	9962.2	9954.6	9947.1	9913.6	9871.4	9868.0	9903.2	9927.4	9918.6	9909.8	9918.6
5°	9597.2	9590.9	9584.6	9555.9	9519.7	9532.3	9593.7	9636.2	9622.0	9607.8	9622.0
7.5°	8843.5	8848.9	8854.2	8839.5	8818.1	8834.6	8888.8	8925.8	8910.7	8895.6	8910.7
10°	8200.6	8214.8	8229.0	8208.9	8177.4	8201.4	8280.9	8327.1	8273.6	8220.1	8273.6
12.5°	7491.2	7482.1	7473.0	7454.6	7433.2	7428.9	7441.6	7443.8	7414.2	7384.7	7414.2
15°	6400.5	6367.5	6334.4	6283.7	6227.0	6208.6	6228.2	6240.8	6232.2	6223.5	6232.2
17.5°	5155.5	5168.2	5180.9	5146.6	5096.6	5070.6	5068.7	5064.9	5055.1	5045.4	5055.1
20°	4423.4	4427.3	4431.2	4409.8	4379.9	4372.8	4388.5	4400.0	4398.4	4396.8	4398.4
22.5°	3834.3	3835.1	3835.9	3807.5	3769.4	3762.0	3785.3	3799.2	3785.1	3770.9	3785.1
25°	3069.3	3066.9	3064.5	3045.7	3021.3	3003.2	2991.4	2983.1	2985.5	2987.8	2985.5
27.5°	2517.0	2507.3	2497.5	2481.4	2463.1	2457.9	2465.8	2470.2	2464.4	2458.6	2464.4
30°	2240.9	2233.0	2225.2	2209.0	2190.1	2183.1	2187.8	2189.6	2182.5	2175.4	2182.5
32.5°	1993.1	1993.4	1993.7	1979.2	1959.6	1948.8	1946.6	1943.6	1938.4	1933.2	1938.4
35°	1663.8	1668.6	1673.3	1661.5	1644.2	1629.6	1617.8	1607.2	1600.1	1593.0	1600.1
37.5°	1370.0	1374.4	1378.8	1369.0	1354.3	1338.4	1321.0	1306.6	1300.6	1294.6	1300.6
40°	1178.9	1182.0	1185.1	1178.3	1168.0	1152.7	1132.2	1115.7	1111.0	1106.3	1111.0
42.5°	970.7	983.9	997.1	992.8	982.5	967.8	948.6	931.6	921.3	910.9	921.3
45°	608.9	650.6	692.3	711.0	722.0	716.9	695.6	664.6	604.0	543.4	604.0
47.5°	308.0	365.7	423.5	464.9	501.0	489.5	430.5	371.4	311.9	252.4	311.9
50°	194.7	234.8	274.9	325.7	380.0	368.2	290.3	225.2	198.4	171.7	198.4
52.5°	149.4	170.0	190.6	238.8	296.3	290.8	222.3	167.3	152.5	137.7	152.5
55°	106.2	114.1	121.9	148.7	181.7	179.8	142.8	113.5	107.2	100.9	107.2
57.5°	82.1	86.5	90.9	100.9	112.7	111.6	97.6	86.1	82.2	78.2	82.2
60°	70.8	73.9	77.1	82.0	87.5	86.7	79.7	73.4	69.4	65.5	69.4
62.5°	63.7	65.6	67.5	69.7	72.1	71.0	66.4	62.7	61.2	59.8	61.2
65°	54.9	55.7	56.4	56.6	56.6	55.9	54.3	52.9	52.1	51.3	52.1
67.5°	46.7	47.5	48.3	48.4	48.2	47.8	47.0	46.2	45.4	44.6	45.4
70°	42.5	43.3	44.1	43.7	42.9	42.1	41.3	40.5	39.7	38.9	39.7
72.5°	36.8	37.6	38.4	38.0	37.2	36.7	36.6	36.3	35.5	34.7	35.5
75°	30.1	30.1	30.1	30.1	30.1	29.7	28.9	28.3	28.3	28.3	28.3
77.5°	23.4	23.5	23.7	23.1	22.3	21.9	21.9	21.8	21.2	20.5	21.2
80°	17.7	18.5	19.3	18.9	18.1	17.7	17.7	17.7	17.7	17.7	17.7
82.5°	14.9	15.0	15.2	14.6	13.8	13.5	13.5	13.5	13.5	13.5	13.5
85°	8.9	8.9	8.9	8.3	7.5	7.5	8.3	8.7	7.9	7.1	7.9
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8
2.5°	9927.4	9903.2	9868.0	9871.4	9913.6	9947.1	9954.6	9962.2	9954.6	9947.1	9913.6
5°	9636.2	9593.7	9532.3	9519.7	9555.9	9584.6	9590.9	9597.2	9590.9	9584.6	9555.9
7.5°	8925.8	8888.8	8834.6	8818.1	8839.5	8854.2	8848.9	8843.5	8848.9	8854.2	8839.5
10°	8327.1	8280.9	8201.4	8177.4	8208.9	8229.0	8214.8	8200.6	8214.8	8229.0	8208.9
12.5°	7443.8	7441.6	7428.9	7433.2	7454.6	7473.0	7482.1	7491.2	7482.1	7473.0	7454.6
15°	6240.8	6228.2	6208.6	6227.0	6283.7	6334.4	6367.5	6400.5	6367.5	6334.4	6283.7
17.5°	5064.9	5068.7	5070.6	5096.6	5146.6	5180.9	5168.2	5155.5	5168.2	5180.9	5146.6
20°	4400.0	4388.5	4372.8	4379.9	4409.8	4431.2	4427.3	4423.4	4427.3	4431.2	4409.8
22.5°	3799.2	3785.3	3762.0	3769.4	3807.5	3835.9	3835.1	3834.3	3835.1	3835.9	3807.5
25°	2983.1	2991.4	3003.2	3021.3	3045.7	3064.5	3066.9	3069.3	3066.9	3064.5	3045.7
27.5°	2470.2	2465.8	2457.9	2463.1	2481.4	2497.5	2507.3	2517.0	2507.3	2497.5	2481.4
30°	2189.6	2187.8	2183.1	2190.1	2209.0	2225.2	2233.0	2240.9	2233.0	2225.2	2209.0
32.5°	1943.6	1946.6	1948.8	1959.6	1979.2	1993.7	1993.4	1993.1	1993.4	1993.7	1979.2
35°	1607.2	1617.8	1629.6	1644.2	1661.5	1673.3	1668.6	1663.8	1668.6	1673.3	1661.5
37.5°	1306.6	1321.0	1338.4	1354.3	1369.0	1378.8	1374.4	1370.0	1374.4	1378.8	1369.0
40°	1115.7	1132.2	1152.7	1168.0	1178.3	1185.1	1182.0	1178.9	1182.0	1185.1	1178.3
42.5°	931.6	948.6	967.8	982.5	992.8	997.1	983.9	970.7	983.9	997.1	992.8
45°	664.6	695.6	716.9	722.0	711.0	692.3	650.6	608.9	650.6	692.3	711.0
47.5°	371.4	430.5	489.5	501.0	464.9	423.5	365.7	308.0	365.7	423.5	464.9
50°	225.2	290.3	368.2	380.0	325.7	274.9	234.8	194.7	234.8	274.9	325.7
52.5°	167.3	222.3	290.8	296.3	238.8	190.6	170.0	149.4	170.0	190.6	238.8
55°	113.5	142.8	179.8	181.7	148.7	121.9	114.1	106.2	114.1	121.9	148.7
57.5°	86.1	97.6	111.6	112.7	100.9	90.9	86.5	82.1	86.5	90.9	100.9
60°	73.4	79.7	86.7	87.5	82.0	77.1	73.9	70.8	73.9	77.1	82.0
62.5°	62.7	66.4	71.0	72.1	69.7	67.5	65.6	63.7	65.6	67.5	69.7
65°	52.9	54.3	55.9	56.6	56.6	56.4	55.7	54.9	55.7	56.4	56.6
67.5°	46.2	47.0	47.8	48.2	48.4	48.3	47.5	46.7	47.5	48.3	48.4
70°	40.5	41.3	42.1	42.9	43.7	44.1	43.3	42.5	43.3	44.1	43.7
72.5°	36.3	36.6	36.7	37.2	38.0	38.4	37.6	36.8	37.6	38.4	38.0
75°	28.3	28.9	29.7	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.1
77.5°	21.8	21.9	21.9	22.3	23.1	23.7	23.5	23.4	23.5	23.7	23.1
80°	17.7	17.7	17.7	18.1	18.9	19.3	18.5	17.7	18.5	19.3	18.9
82.5°	13.5	13.5	13.5	13.8	14.6	15.2	15.0	14.9	15.0	15.2	14.6
85°	8.7	8.3	7.5	7.5	8.3	8.9	8.9	8.9	8.9	8.9	8.3
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8	9977.8
2.5°	9871.4	9868.0	9903.2	9927.4	9918.6	9909.8	9918.6	9927.4	9903.2	9868.0	9871.4
5°	9519.7	9532.3	9593.7	9636.2	9622.0	9607.8	9622.0	9636.2	9593.7	9532.3	9519.7
7.5°	8818.1	8834.6	8888.8	8925.8	8910.7	8895.6	8910.7	8925.8	8888.8	8834.6	8818.1
10°	8177.4	8201.4	8280.9	8327.1	8273.6	8220.1	8273.6	8327.1	8280.9	8201.4	8177.4
12.5°	7433.2	7428.9	7441.6	7443.8	7414.2	7384.7	7414.2	7443.8	7441.6	7428.9	7433.2
15°	6227.0	6208.6	6228.2	6240.8	6232.2	6223.5	6232.2	6240.8	6228.2	6208.6	6227.0
17.5°	5096.6	5070.6	5068.7	5064.9	5055.1	5045.4	5055.1	5064.9	5068.7	5070.6	5096.6
20°	4379.9	4372.8	4388.5	4400.0	4398.4	4396.8	4398.4	4400.0	4388.5	4372.8	4379.9
22.5°	3769.4	3762.0	3785.3	3799.2	3785.1	3770.9	3785.1	3799.2	3785.3	3762.0	3769.4
25°	3021.3	3003.2	2991.4	2983.1	2985.5	2987.8	2985.5	2983.1	2991.4	3003.2	3021.3
27.5°	2463.1	2457.9	2465.8	2470.2	2464.4	2458.6	2464.4	2470.2	2465.8	2457.9	2463.1
30°	2190.1	2183.1	2187.8	2189.6	2182.5	2175.4	2182.5	2189.6	2187.8	2183.1	2190.1
32.5°	1959.6	1948.8	1946.6	1943.6	1938.4	1933.2	1938.4	1943.6	1946.6	1948.8	1959.6
35°	1644.2	1629.6	1617.8	1607.2	1600.1	1593.0	1600.1	1607.2	1617.8	1629.6	1644.2
37.5°	1354.3	1338.4	1321.0	1306.6	1300.6	1294.6	1300.6	1306.6	1321.0	1338.4	1354.3
40°	1168.0	1152.7	1132.2	1115.7	1111.0	1106.3	1111.0	1115.7	1132.2	1152.7	1168.0
42.5°	982.5	967.8	948.6	931.6	921.3	910.9	921.3	931.6	948.6	967.8	982.5
45°	722.0	716.9	695.6	664.6	604.0	543.4	604.0	664.6	695.6	716.9	722.0
47.5°	501.0	489.5	430.5	371.4	311.9	252.4	311.9	371.4	430.5	489.5	501.0
50°	380.0	368.2	290.3	225.2	198.4	171.7	198.4	225.2	290.3	368.2	380.0
52.5°	296.3	290.8	222.3	167.3	152.5	137.7	152.5	167.3	222.3	290.8	296.3
55°	181.7	179.8	142.8	113.5	107.2	100.9	107.2	113.5	142.8	179.8	181.7
57.5°	112.7	111.6	97.6	86.1	82.2	78.2	82.2	86.1	97.6	111.6	112.7
60°	87.5	86.7	79.7	73.4	69.4	65.5	69.4	73.4	79.7	86.7	87.5
62.5°	72.1	71.0	66.4	62.7	61.2	59.8	61.2	62.7	66.4	71.0	72.1
65°	56.6	55.9	54.3	52.9	52.1	51.3	52.1	52.9	54.3	55.9	56.6
67.5°	48.2	47.8	47.0	46.2	45.4	44.6	45.4	46.2	47.0	47.8	48.2
70°	42.9	42.1	41.3	40.5	39.7	38.9	39.7	40.5	41.3	42.1	42.9
72.5°	37.2	36.7	36.6	36.3	35.5	34.7	35.5	36.3	36.6	36.7	37.2
75°	30.1	29.7	28.9	28.3	28.3	28.3	28.3	28.3	28.9	29.7	30.1
77.5°	22.3	21.9	21.9	21.8	21.2	20.5	21.2	21.8	21.9	21.9	22.3
80°	18.1	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	18.1
82.5°	13.8	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.8
85°	7.5	7.5	8.3	8.7	7.9	7.1	7.9	8.7	8.3	7.5	7.5
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1428586

CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	9977.8	9977.8	9977.8	9977.8
2.5°	9913.6	9947.1	9954.6	9962.2
5°	9555.9	9584.6	9590.9	9597.2
7.5°	8839.5	8854.2	8848.9	8843.5
10°	8208.9	8229.0	8214.8	8200.6
12.5°	7454.6	7473.0	7482.1	7491.2
15°	6283.7	6334.4	6367.5	6400.5
17.5°	5146.6	5180.9	5168.2	5155.5
20°	4409.8	4431.2	4427.3	4423.4
22.5°	3807.5	3835.9	3835.1	3834.3
25°	3045.7	3064.5	3066.9	3069.3
27.5°	2481.4	2497.5	2507.3	2517.0
30°	2209.0	2225.2	2233.0	2240.9
32.5°	1979.2	1993.7	1993.4	1993.1
35°	1661.5	1673.3	1668.6	1663.8
37.5°	1369.0	1378.8	1374.4	1370.0
40°	1178.3	1185.1	1182.0	1178.9
42.5°	992.8	997.1	983.9	970.7
45°	711.0	692.3	650.6	608.9
47.5°	464.9	423.5	365.7	308.0
50°	325.7	274.9	234.8	194.7
52.5°	238.8	190.6	170.0	149.4
55°	148.7	121.9	114.1	106.2
57.5°	100.9	90.9	86.5	82.1
60°	82.0	77.1	73.9	70.8
62.5°	69.7	67.5	65.6	63.7
65°	56.6	56.4	55.7	54.9
67.5°	48.4	48.3	47.5	46.7
70°	43.7	44.1	43.3	42.5
72.5°	38.0	38.4	37.6	36.8
75°	30.1	30.1	30.1	30.1
77.5°	23.1	23.7	23.5	23.4
80°	18.9	19.3	18.5	17.7
82.5°	14.6	15.2	15.0	14.9
85°	8.3	8.9	8.9	8.9
87.5°	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P1428586  
 CATALOG NUMBER: SQ2W-WBN-0U-125D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.12	9.19	8.49	9.50	9.81	7.75	8.81	8.12	9.12	9.44
	3H	9.36	10.30	9.75	10.63	11.00	8.97	9.90	9.35	10.24	10.60
	4H	9.89	10.76	10.30	11.11	11.50	9.50	10.36	9.90	10.71	11.10
	6H	10.25	11.04	10.67	11.42	11.81	9.84	10.62	10.25	11.00	11.40
	8H	10.40	11.15	10.84	11.54	11.95	9.98	10.72	10.42	11.12	11.52
	12H	10.50	11.21	10.94	11.60	12.03	10.06	10.77	10.49	11.15	11.58
4H	2H	8.47	9.33	8.87	9.68	10.07	8.16	9.02	8.57	9.38	9.76
	3H	9.97	10.68	10.39	11.08	11.49	9.63	10.33	10.05	10.74	11.15
	4H	10.62	11.24	11.06	11.67	12.12	10.27	10.89	10.70	11.31	11.76
	6H	11.12	11.65	11.58	12.10	12.57	10.73	11.26	11.20	11.71	12.19
	8H	11.32	11.82	11.80	12.27	12.74	10.92	11.42	11.40	11.87	12.34
	12H	11.47	11.90	11.96	12.39	12.86	11.04	11.47	11.53	11.96	12.44
8H	4H	10.78	11.28	11.26	11.73	12.20	10.47	10.96	10.94	11.41	11.89
	6H	11.41	11.81	11.92	12.31	12.80	11.06	11.46	11.57	11.96	12.44
	8H	11.72	12.07	12.25	12.59	13.09	11.34	11.69	11.87	12.21	12.71
	12H	11.96	12.27	12.48	12.77	13.35	11.55	11.86	12.07	12.36	12.93
12H	4H	10.77	11.20	11.26	11.69	12.17	10.46	10.90	10.96	11.38	11.86
	6H	11.43	11.79	11.97	12.31	12.81	11.09	11.45	11.63	11.97	12.47
	8H	11.80	12.11	12.32	12.60	13.18	11.43	11.74	11.95	12.24	12.82