

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428616

Luminaire Tested: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

Test Information

Test Method: LM-79-2019
Report Number: P1428616
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/10/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC
UPLIGHT - ASYMMETRIC ROLL LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6523.6 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot





TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	101	97	94	92	94	91	88	86	78	76	75	67	65	64	56	55	54	50				50
2	94	88	84	79	87	83	78	75	72	69	66	62	60	58	53	51	50	46				46
3	88	80	75	70	82	76	71	67	66	63	60	58	55	53	50	48	46	43				43
4	82	74	67	63	77	69	64	60	61	57	54	54	51	48	47	45	43	40				40
5	77	68	61	56	72	64	58	54	57	53	49	50	47	45	44	42	40	37				37
6	72	63	56	51	68	59	53	49	53	49	45	47	44	41	42	39	37	35				35
7	68	58	51	47	64	55	49	45	50	45	42	44	41	38	39	37	35	33				33
8	64	54	48	43	60	51	46	42	46	42	39	42	38	36	37	35	33	31				31
9	61	50	44	40	57	48	43	39	44	39	36	40	36	34	36	33	31	29				29
10	58	47	41	37	54	45	40	36	41	37	34	37	34	32	34	31	30	28				28

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	96337	96337	96337	96337
5°	93018	93120	93018	93120
10°	80401	80591	80401	80591
15°	63979	62209	63979	62209
20°	45449	45176	45449	45176
25°	32699	31831	32699	31831
30°	24984	24253	24984	24253
35°	19612	18778	19612	18778
40°	14859	13944	14859	13944
45°	8314	7421	8314	7421
50°	2924	2580	2924	2580
55°	1787	1697	1787	1697
60°	1366	1266	1366	1266
65°	1253	1173	1253	1173
70°	1199	1100	1199	1100
75°	1123	1054	1123	1054
80°	986	986	986	986
85°	982	778	982	778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 40°
 Vertical Angle: 45°
 Luminance: 9859 cd/sqm



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	518.0	7.9
10°-20°	1029.4	15.8
20°-30°	852.5	13.1
30°-40°	613.3	9.4
40°-50°	312.4	4.8
50°-60°	81.2	1.2
60°-70°	33.7	0.5
70°-80°	18.7	0.3
80°-90°	9.9	0.2
90°-100°	83.3	1.3
100°-110°	242.8	3.7
110°-120°	396.2	6.1
120°-130°	502.8	7.7
130°-140°	538.0	8.2
140°-150°	502.4	7.7
150°-160°	413.4	6.3
160°-170°	277.2	4.2
170°-180°	98.4	1.5
0°-30°	2399.9	36.8
0°-40°	3013.2	46.2
0°-60°	3406.8	52.2
0°-90°	3469.2	53.2
90°-120°	722.3	11.1
90°-150°	2265.4	34.7
90°-180°	3054.0	46.8
0°-180°	6523.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5967	5967	5967	5967	5967	
5°	5739	5746	5739	5746	5739	518
15°	3828	3722	3828	3722	3828	1039
25°	1836	1787	1836	1787	1836	863
35°	995	953	995	953	995	624
45°	364	325	364	325	364	291
55°	64	60	64	60	64	62
65°	33	31	33	31	33	33
75°	18	17	18	17	18	19
85°	5	4	5	4	5	6
90°	3	23	3	45	3	3
95°	33	24	33	143	33	40
105°	154	247	154	340	154	164
115°	296	410	296	505	296	292
125°	438	650	438	619	438	391
135°	595	851	595	686	595	460
145°	760	981	760	701	760	475
155°	902	1065	902	727	902	415
165°	998	1111	998	837	998	281
175°	1043	1087	1043	982	1043	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5957.5	5953.0	5948.5	5928.4	5903.2	5901.2	5922.2	5936.7	5931.5	5926.2	5931.5
5°	5739.3	5735.5	5731.7	5714.6	5692.9	5700.4	5737.1	5762.5	5754.1	5745.6	5754.1
7.5°	5288.5	5291.7	5294.9	5286.1	5273.3	5283.2	5315.6	5337.7	5328.7	5319.7	5328.7
10°	4904.1	4912.6	4921.0	4909.0	4890.2	4904.6	4952.1	4979.7	4947.7	4915.7	4947.7
12.5°	4479.8	4474.4	4468.9	4458.0	4445.2	4442.6	4450.2	4451.5	4433.8	4416.1	4433.8
15°	3827.6	3807.8	3788.1	3757.7	3723.8	3712.8	3724.6	3732.1	3726.9	3721.7	3726.9
17.5°	3083.0	3090.6	3098.3	3077.7	3047.8	3032.3	3031.2	3028.9	3023.0	3017.2	3023.0
20°	2645.2	2647.6	2649.9	2637.1	2619.2	2615.0	2624.4	2631.2	2630.3	2629.3	2630.3
22.5°	2292.9	2293.4	2293.9	2276.9	2254.2	2249.7	2263.7	2272.0	2263.5	2255.1	2263.5
25°	1835.5	1834.0	1832.6	1821.3	1806.8	1795.9	1788.9	1783.9	1785.4	1786.8	1785.4
27.5°	1505.2	1499.4	1493.5	1483.9	1473.0	1469.9	1474.6	1477.2	1473.8	1470.3	1473.8
30°	1340.1	1335.4	1330.7	1321.0	1309.7	1305.5	1308.3	1309.4	1305.1	1300.9	1305.1
32.5°	1191.9	1192.1	1192.3	1183.6	1171.9	1165.4	1164.1	1162.3	1159.2	1156.1	1159.2
35°	995.0	997.8	1000.6	993.6	983.2	974.5	967.5	961.1	956.9	952.7	956.9
37.5°	819.3	821.9	824.6	818.7	809.9	800.4	790.0	781.3	777.8	774.2	777.8
40°	705.0	706.9	708.7	704.6	698.5	689.3	677.1	667.2	664.4	661.6	664.4
42.5°	580.5	588.4	596.3	593.7	587.6	578.8	567.3	557.1	550.9	544.7	550.9
45°	364.1	389.1	414.0	425.2	431.8	428.7	416.0	397.4	361.2	325.0	361.2
47.5°	184.2	218.7	253.2	278.0	299.6	292.7	257.4	222.1	186.5	150.9	186.5
50°	116.4	140.4	164.4	194.8	227.2	220.2	173.6	134.7	118.7	102.7	118.7
52.5°	89.3	101.7	114.0	142.8	177.2	173.9	132.9	100.0	91.2	82.4	91.2
55°	63.5	68.2	72.9	88.9	108.7	107.5	85.4	67.9	64.1	60.3	64.1
57.5°	49.1	51.7	54.4	60.3	67.4	66.7	58.4	51.5	49.1	46.8	49.1
60°	42.3	44.2	46.1	49.0	52.3	51.9	47.6	43.9	41.5	39.2	41.5
62.5°	38.1	39.2	40.4	41.7	43.1	42.5	39.7	37.5	36.6	35.8	36.6
65°	32.8	33.3	33.8	33.9	33.9	33.4	32.5	31.6	31.2	30.7	31.2
67.5°	27.9	28.4	28.9	28.9	28.8	28.6	28.1	27.6	27.1	26.7	27.1
70°	25.4	25.9	26.3	26.1	25.6	25.2	24.7	24.2	23.8	23.3	23.8
72.5°	22.0	22.5	23.0	22.7	22.3	22.0	21.9	21.7	21.2	20.7	21.2
75°	18.0	18.0	18.0	18.0	18.0	17.8	17.3	16.9	16.9	16.9	16.9
77.5°	14.0	14.1	14.2	13.8	13.4	13.1	13.1	13.0	12.7	12.3	12.7
80°	10.6	11.1	11.5	11.3	10.8	10.6	10.6	10.6	10.6	10.6	10.6
82.5°	8.9	9.0	9.1	8.8	8.3	8.0	8.0	8.0	8.0	8.0	8.0
85°	5.3	5.3	5.3	4.9	4.5	4.5	4.9	5.2	4.7	4.2	4.7
87.5°	2.3	3.2	4.2	5.1	5.7	5.9	5.9	6.1	6.3	6.3	6.3
90°	3.2	7.4	12.7	16.9	20.1	21.1	21.1	22.2	23.2	23.2	23.2
92.5°	11.6	18.4	18.6	18.6	22.6	24.5	26.2	26.4	27.5	27.5	27.5
95°	32.8	35.9	53.9	52.8	35.9	28.5	24.3	24.3	24.3	24.3	24.3
97.5°	62.6	67.2	70.2	94.0	99.3	95.9	78.2	65.7	58.8	55.6	58.8
100°	88.8	90.9	97.2	98.3	124.7	150.0	137.4	121.5	116.2	113.1	116.2
102.5°	115.0	116.2	126.0	130.4	136.5	150.9	194.9	190.0	186.4	185.8	186.4
105°	154.3	155.3	173.3	181.7	186.0	186.0	184.9	206.1	239.9	247.3	239.9
107.5°	196.3	201.2	222.3	244.9	249.8	251.1	245.6	242.4	241.1	242.0	241.1
110°	225.1	232.5	257.8	286.4	293.8	295.9	293.8	290.6	288.5	288.5	288.5



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	253.0	263.7	292.5	325.2	337.7	344.1	339.4	337.1	335.0	336.7	335.0
115°	295.9	311.7	349.8	383.6	408.9	412.1	411.0	411.0	410.0	410.0	410.0
117.5°	335.6	361.0	403.7	443.0	472.3	480.8	485.0	483.7	482.5	484.6	482.5
120°	363.5	393.1	441.7	486.1	514.6	527.3	531.5	529.4	531.5	529.4	531.5
122.5°	393.1	429.4	477.2	523.3	556.9	571.2	576.3	576.7	577.2	575.9	577.2
125°	437.5	481.8	537.8	585.4	620.3	637.2	641.4	642.5	644.6	649.9	644.6
127.5°	482.3	532.6	594.1	639.9	675.6	696.1	702.7	705.0	709.5	711.8	709.5
130°	513.5	570.6	632.9	676.3	711.1	733.3	745.0	748.1	753.4	752.4	753.4
132.5°	546.5	606.1	669.3	714.3	746.6	770.5	780.5	789.5	791.5	792.9	791.5
135°	594.9	659.4	722.8	767.1	797.8	821.0	833.7	842.2	847.5	850.6	847.5
137.5°	645.8	713.9	774.8	814.3	845.1	865.2	879.6	888.5	893.9	896.5	893.9
140°	680.5	746.0	805.2	846.4	873.9	893.9	906.6	917.2	923.5	923.5	923.5
142.5°	713.5	778.1	835.6	876.8	900.9	919.3	932.8	940.9	948.0	948.0	948.0
145°	759.7	824.2	877.0	918.3	938.3	955.2	970.0	976.4	980.6	980.6	980.6
147.5°	808.1	865.2	913.4	952.9	969.8	989.7	1001.3	1006.4	1011.7	1009.3	1011.7
150°	836.9	889.7	936.2	973.2	990.1	1009.1	1020.7	1025.0	1030.3	1027.1	1030.3
152.5°	864.8	915.1	957.3	991.8	1006.2	1025.2	1038.5	1042.7	1046.3	1044.0	1046.3
155°	902.4	946.8	985.9	1017.6	1030.3	1048.2	1060.9	1066.2	1070.4	1065.1	1070.4
157.5°	936.0	974.3	1008.3	1037.4	1051.0	1066.4	1078.2	1084.8	1089.0	1086.7	1089.0
160°	956.3	991.2	1021.8	1049.3	1062.0	1075.7	1088.4	1095.8	1100.0	1096.8	1100.0
162.5°	973.2	1004.7	1033.6	1058.6	1069.6	1081.6	1096.8	1103.4	1107.6	1103.6	1107.6
165°	997.5	1022.9	1048.2	1069.4	1078.9	1088.4	1104.2	1111.6	1114.8	1110.6	1114.8
167.5°	1015.9	1035.3	1055.8	1074.0	1081.0	1090.3	1106.1	1112.3	1116.3	1111.0	1116.3
170°	1026.0	1042.9	1060.9	1075.7	1081.0	1089.4	1105.3	1110.6	1113.7	1108.5	1113.7
172.5°	1034.5	1047.2	1061.7	1074.9	1077.6	1084.4	1099.4	1104.6	1107.0	1102.5	1107.0
175°	1042.9	1050.3	1060.9	1069.4	1068.3	1072.5	1085.2	1089.4	1093.7	1087.3	1093.7
177.5°	1047.0	1050.3	1053.7	1058.8	1055.4	1055.4	1064.7	1067.2	1068.1	1064.7	1068.1
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5936.7	5922.2	5901.2	5903.2	5928.4	5948.5	5953.0	5957.5	5953.0	5948.5	5928.4
5°	5762.5	5737.1	5700.4	5692.9	5714.6	5731.7	5735.5	5739.3	5735.5	5731.7	5714.6
7.5°	5337.7	5315.6	5283.2	5273.3	5286.1	5294.9	5291.7	5288.5	5291.7	5294.9	5286.1
10°	4979.7	4952.1	4904.6	4890.2	4909.0	4921.0	4912.6	4904.1	4912.6	4921.0	4909.0
12.5°	4451.5	4450.2	4442.6	4445.2	4458.0	4468.9	4474.4	4479.8	4474.4	4468.9	4458.0
15°	3732.1	3724.6	3712.8	3723.8	3757.7	3788.1	3807.8	3827.6	3807.8	3788.1	3757.7
17.5°	3028.9	3031.2	3032.3	3047.8	3077.7	3098.3	3090.6	3083.0	3090.6	3098.3	3077.7
20°	2631.2	2624.4	2615.0	2619.2	2637.1	2649.9	2647.6	2645.2	2647.6	2649.9	2637.1
22.5°	2272.0	2263.7	2249.7	2254.2	2276.9	2293.9	2293.4	2292.9	2293.4	2293.9	2276.9
25°	1783.9	1788.9	1795.9	1806.8	1821.3	1832.6	1834.0	1835.5	1834.0	1832.6	1821.3
27.5°	1477.2	1474.6	1469.9	1473.0	1483.9	1493.5	1499.4	1505.2	1499.4	1493.5	1483.9
30°	1309.4	1308.3	1305.5	1309.7	1321.0	1330.7	1335.4	1340.1	1335.4	1330.7	1321.0
32.5°	1162.3	1164.1	1165.4	1171.9	1183.6	1192.3	1192.1	1191.9	1192.1	1192.3	1183.6
35°	961.1	967.5	974.5	983.2	993.6	1000.6	997.8	995.0	997.8	1000.6	993.6
37.5°	781.3	790.0	800.4	809.9	818.7	824.6	821.9	819.3	821.9	824.6	818.7
40°	667.2	677.1	689.3	698.5	704.6	708.7	706.9	705.0	706.9	708.7	704.6
42.5°	557.1	567.3	578.8	587.6	593.7	596.3	588.4	580.5	588.4	596.3	593.7
45°	397.4	416.0	428.7	431.8	425.2	414.0	389.1	364.1	389.1	414.0	425.2
47.5°	222.1	257.4	292.7	299.6	278.0	253.2	218.7	184.2	218.7	253.2	278.0
50°	134.7	173.6	220.2	227.2	194.8	164.4	140.4	116.4	140.4	164.4	194.8
52.5°	100.0	132.9	173.9	177.2	142.8	114.0	101.7	89.3	101.7	114.0	142.8
55°	67.9	85.4	107.5	108.7	88.9	72.9	68.2	63.5	68.2	72.9	88.9
57.5°	51.5	58.4	66.7	67.4	60.3	54.4	51.7	49.1	51.7	54.4	60.3
60°	43.9	47.6	51.9	52.3	49.0	46.1	44.2	42.3	44.2	46.1	49.0
62.5°	37.5	39.7	42.5	43.1	41.7	40.4	39.2	38.1	39.2	40.4	41.7
65°	31.6	32.5	33.4	33.9	33.9	33.8	33.3	32.8	33.3	33.8	33.9
67.5°	27.6	28.1	28.6	28.8	28.9	28.9	28.4	27.9	28.4	28.9	28.9
70°	24.2	24.7	25.2	25.6	26.1	26.3	25.9	25.4	25.9	26.3	26.1
72.5°	21.7	21.9	22.0	22.3	22.7	23.0	22.5	22.0	22.5	23.0	22.7
75°	16.9	17.3	17.8	18.0	18.0	18.0	18.0	18.0	18.0	18.0	18.0
77.5°	13.0	13.1	13.1	13.4	13.8	14.2	14.1	14.0	14.1	14.2	13.8
80°	10.6	10.6	10.6	10.8	11.3	11.5	11.1	10.6	11.1	11.5	11.3
82.5°	8.0	8.0	8.0	8.3	8.8	9.1	9.0	8.9	9.0	9.1	8.8
85°	5.2	4.9	4.5	4.5	4.9	5.3	5.3	5.3	5.3	5.3	4.9
87.5°	6.1	5.9	5.9	5.7	5.1	4.2	3.2	2.3	3.2	4.0	5.5
90°	22.2	21.1	21.1	20.1	16.9	12.7	7.4	3.2	7.4	11.6	19.0
92.5°	26.4	26.2	24.5	22.6	18.6	18.6	18.4	11.6	20.1	28.5	41.0
95°	24.3	24.3	28.5	35.9	52.8	53.9	35.9	32.8	46.5	65.5	82.4
97.5°	65.7	78.2	95.9	99.3	94.0	70.2	67.2	62.6	85.2	104.0	131.2
100°	121.5	137.4	150.0	124.7	98.3	97.2	90.9	88.8	113.1	131.0	157.4
102.5°	190.0	194.9	150.9	136.5	130.4	126.0	116.2	115.0	139.3	164.0	186.2
105°	206.1	184.9	186.0	186.0	181.7	173.3	155.3	154.3	181.7	210.3	237.8
107.5°	242.4	245.6	251.1	249.8	244.9	222.3	201.2	196.3	221.1	255.3	285.5
110°	290.6	293.8	295.9	293.8	286.4	257.8	232.5	225.1	247.3	283.2	315.9



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	337.1	339.4	344.1	337.7	325.2	292.5	263.7	253.0	275.2	311.9	345.5
115°	411.0	411.0	412.1	408.9	383.6	349.8	311.7	295.9	314.9	348.7	385.7
117.5°	483.7	485.0	480.8	472.3	443.0	403.7	361.0	335.6	350.6	386.3	424.4
120°	529.4	531.5	527.3	514.6	486.1	441.7	393.1	363.5	375.1	410.0	448.0
122.5°	576.7	576.3	571.2	556.9	523.3	477.2	429.4	393.1	397.9	430.3	467.5
125°	642.5	641.4	637.2	620.3	585.4	537.8	481.8	437.5	431.1	458.6	496.6
127.5°	705.0	702.7	696.1	675.6	639.9	594.1	532.6	482.3	468.1	485.4	520.3
130°	748.1	745.0	733.3	711.1	676.3	632.9	570.6	513.5	493.5	504.0	534.7
132.5°	789.5	780.5	770.5	746.6	714.3	669.3	606.1	546.5	518.8	523.5	547.4
135°	842.2	833.7	821.0	797.8	767.1	722.8	659.4	594.9	556.9	552.6	566.4
137.5°	888.5	879.6	865.2	845.1	814.3	774.8	713.9	645.8	597.9	583.7	589.0
140°	917.2	906.6	893.9	873.9	846.4	805.2	746.0	680.5	626.6	606.5	603.4
142.5°	940.9	932.8	919.3	900.9	876.8	835.6	778.1	713.5	656.2	630.2	622.8
145°	976.4	970.0	955.2	938.3	918.3	877.0	824.2	759.7	702.7	668.9	653.0
147.5°	1006.4	1001.3	989.7	969.8	952.9	913.4	865.2	808.1	749.6	707.8	687.3
150°	1025.0	1020.7	1009.1	990.1	973.2	936.2	889.7	836.9	780.9	736.5	710.1
152.5°	1042.7	1038.5	1025.2	1006.2	991.8	957.3	915.1	864.8	807.9	763.6	736.3
155°	1066.2	1060.9	1048.2	1030.3	1017.6	985.9	946.8	902.4	853.8	807.3	776.7
157.5°	1084.8	1078.2	1066.4	1051.0	1037.4	1008.3	974.3	936.0	893.5	849.1	817.9
160°	1095.8	1088.4	1075.7	1062.0	1049.3	1021.8	991.2	956.3	917.2	877.0	843.2
162.5°	1103.4	1096.8	1081.6	1069.6	1058.6	1033.6	1004.7	973.2	938.3	903.2	872.0
165°	1111.6	1104.2	1088.4	1078.9	1069.4	1048.2	1022.9	997.5	967.9	939.4	914.0
167.5°	1112.3	1106.1	1090.3	1081.0	1074.0	1055.8	1035.3	1015.9	992.9	970.5	949.3
170°	1110.6	1105.3	1089.4	1081.0	1075.7	1060.9	1042.9	1026.0	1008.1	989.0	972.1
172.5°	1104.6	1099.4	1084.4	1077.6	1074.9	1061.7	1047.2	1034.5	1019.1	1005.1	991.6
175°	1089.4	1085.2	1072.5	1068.3	1069.4	1060.9	1050.3	1042.9	1033.4	1025.0	1017.6
177.5°	1067.2	1064.7	1055.4	1055.4	1058.8	1053.7	1050.3	1047.0	1042.7	1040.2	1037.7
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8	5966.8
2.5°	5903.2	5901.2	5922.2	5936.7	5931.5	5926.2	5931.5	5936.7	5922.2	5901.2	5903.2
5°	5692.9	5700.4	5737.1	5762.5	5754.1	5745.6	5754.1	5762.5	5737.1	5700.4	5692.9
7.5°	5273.3	5283.2	5315.6	5337.7	5328.7	5319.7	5328.7	5337.7	5315.6	5283.2	5273.3
10°	4890.2	4904.6	4952.1	4979.7	4947.7	4915.7	4947.7	4979.7	4952.1	4904.6	4890.2
12.5°	4445.2	4442.6	4450.2	4451.5	4433.8	4416.1	4433.8	4451.5	4450.2	4442.6	4445.2
15°	3723.8	3712.8	3724.6	3732.1	3726.9	3721.7	3726.9	3732.1	3724.6	3712.8	3723.8
17.5°	3047.8	3032.3	3031.2	3028.9	3023.0	3017.2	3023.0	3028.9	3031.2	3032.3	3047.8
20°	2619.2	2615.0	2624.4	2631.2	2630.3	2629.3	2630.3	2631.2	2624.4	2615.0	2619.2
22.5°	2254.2	2249.7	2263.7	2272.0	2263.5	2255.1	2263.5	2272.0	2263.7	2249.7	2254.2
25°	1806.8	1795.9	1788.9	1783.9	1785.4	1786.8	1785.4	1783.9	1788.9	1795.9	1806.8
27.5°	1473.0	1469.9	1474.6	1477.2	1473.8	1470.3	1473.8	1477.2	1474.6	1469.9	1473.0
30°	1309.7	1305.5	1308.3	1309.4	1305.1	1300.9	1305.1	1309.4	1308.3	1305.5	1309.7
32.5°	1171.9	1165.4	1164.1	1162.3	1159.2	1156.1	1159.2	1162.3	1164.1	1165.4	1171.9
35°	983.2	974.5	967.5	961.1	956.9	952.7	956.9	961.1	967.5	974.5	983.2
37.5°	809.9	800.4	790.0	781.3	777.8	774.2	777.8	781.3	790.0	800.4	809.9
40°	698.5	689.3	677.1	667.2	664.4	661.6	664.4	667.2	677.1	689.3	698.5
42.5°	587.6	578.8	567.3	557.1	550.9	544.7	550.9	557.1	567.3	578.8	587.6
45°	431.8	428.7	416.0	397.4	361.2	325.0	361.2	397.4	416.0	428.7	431.8
47.5°	299.6	292.7	257.4	222.1	186.5	150.9	186.5	222.1	257.4	292.7	299.6
50°	227.2	220.2	173.6	134.7	118.7	102.7	118.7	134.7	173.6	220.2	227.2
52.5°	177.2	173.9	132.9	100.0	91.2	82.4	91.2	100.0	132.9	173.9	177.2
55°	108.7	107.5	85.4	67.9	64.1	60.3	64.1	67.9	85.4	107.5	108.7
57.5°	67.4	66.7	58.4	51.5	49.1	46.8	49.1	51.5	58.4	66.7	67.4
60°	52.3	51.9	47.6	43.9	41.5	39.2	41.5	43.9	47.6	51.9	52.3
62.5°	43.1	42.5	39.7	37.5	36.6	35.8	36.6	37.5	39.7	42.5	43.1
65°	33.9	33.4	32.5	31.6	31.2	30.7	31.2	31.6	32.5	33.4	33.9
67.5°	28.8	28.6	28.1	27.6	27.1	26.7	27.1	27.6	28.1	28.6	28.8
70°	25.6	25.2	24.7	24.2	23.8	23.3	23.8	24.2	24.7	25.2	25.6
72.5°	22.3	22.0	21.9	21.7	21.2	20.7	21.2	21.7	21.9	22.0	22.3
75°	18.0	17.8	17.3	16.9	16.9	16.9	16.9	16.9	17.3	17.8	18.0
77.5°	13.4	13.1	13.1	13.0	12.7	12.3	12.7	13.0	13.1	13.1	13.4
80°	10.8	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.8
82.5°	8.3	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.3
85°	4.5	4.5	4.9	5.2	4.7	4.2	4.7	5.2	4.9	4.5	4.5
87.5°	6.6	8.0	9.5	10.4	11.2	10.8	11.2	10.4	9.5	8.0	6.6
90°	24.3	31.7	39.1	43.3	47.6	45.4	47.6	43.3	39.1	31.7	24.3
92.5°	48.8	61.3	70.4	78.0	81.4	80.9	81.4	78.0	70.4	61.3	48.8
95°	98.3	113.1	127.9	138.4	144.8	142.7	144.8	138.4	127.9	113.1	98.3
97.5°	151.5	171.4	187.9	197.8	204.1	208.4	204.1	187.9	171.4	151.5	151.5
100°	187.0	206.1	225.1	236.7	247.3	251.5	247.3	236.7	225.1	206.1	187.0
102.5°	215.8	240.7	261.4	273.9	282.8	287.0	282.8	273.9	261.4	240.7	215.8
105°	263.1	289.5	311.7	327.6	337.1	340.2	337.1	327.6	311.7	289.5	263.1
107.5°	310.5	337.7	358.2	375.8	387.4	394.1	387.4	375.8	358.2	337.7	310.5
110°	347.6	369.8	392.0	407.9	419.5	423.7	419.5	407.9	392.0	369.8	347.6



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	378.9	403.7	425.8	441.7	455.0	460.9	455.0	441.7	425.8	403.7	378.9
115°	422.7	455.4	475.5	490.3	499.8	505.1	499.8	490.3	475.5	455.4	422.7
117.5°	459.0	493.3	515.2	526.6	531.1	534.9	531.1	526.6	515.2	493.3	459.0
120°	481.8	513.5	538.9	553.7	559.0	561.1	559.0	553.7	538.9	513.5	481.8
122.5°	503.0	533.0	557.5	575.7	584.3	586.5	584.3	575.7	557.5	533.0	503.0
125°	532.6	561.1	586.5	604.4	613.9	619.2	613.9	604.4	586.5	561.1	532.6
127.5°	558.3	589.2	612.4	628.7	638.0	642.2	638.0	628.7	612.4	589.2	558.3
130°	572.7	604.4	627.7	645.6	654.1	658.3	654.1	645.6	627.7	604.4	572.7
132.5°	583.7	617.1	641.2	657.5	666.8	671.0	666.8	657.5	641.2	617.1	583.7
135°	597.0	631.9	657.3	673.1	681.6	685.8	681.6	673.1	657.3	631.9	597.0
137.5°	608.6	640.3	666.8	683.5	691.1	693.8	691.1	683.5	666.8	640.3	608.6
140°	617.1	644.6	671.0	686.8	695.3	696.3	695.3	686.8	671.0	644.6	617.1
142.5°	628.1	649.6	672.7	688.5	697.0	698.9	697.0	688.5	672.7	649.6	628.1
145°	647.7	660.4	676.3	691.1	698.5	700.6	698.5	691.1	676.3	660.4	647.7
147.5°	672.5	676.5	684.7	694.4	701.6	703.1	701.6	694.4	684.7	676.5	672.5
150°	691.1	690.0	693.2	699.5	705.9	704.8	705.9	699.5	693.2	690.0	691.1
152.5°	712.2	706.1	705.9	708.8	711.8	711.6	711.8	708.8	705.9	706.1	712.2
155°	748.1	736.5	730.2	728.0	728.0	727.0	728.0	728.0	730.2	736.5	748.1
157.5°	787.6	771.4	761.9	756.8	755.3	753.0	755.3	756.8	761.9	771.4	787.6
160°	814.7	796.7	787.2	778.8	775.6	772.4	775.6	778.8	787.2	796.7	814.7
162.5°	840.1	822.9	812.6	805.0	801.8	796.9	801.8	805.0	812.6	822.9	840.1
165°	881.3	863.3	851.7	845.3	841.1	836.9	841.1	845.3	851.7	863.3	881.3
167.5°	922.5	902.8	895.2	888.0	884.0	876.4	884.0	888.0	895.2	902.8	922.5
170°	947.8	929.9	925.6	919.3	911.9	903.5	911.9	919.3	925.6	929.9	947.8
172.5°	969.8	957.8	953.5	947.2	944.9	938.1	944.9	947.2	953.5	957.8	969.8
175°	1001.7	992.2	992.2	991.2	988.0	981.7	988.0	991.2	992.2	992.2	1001.7
177.5°	1028.4	1023.3	1026.7	1026.7	1025.8	1019.9	1025.8	1026.7	1026.7	1023.3	1028.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
0°	5966.8	5966.8	5966.8	5966.8
2.5°	5928.4	5948.5	5953.0	5957.5
5°	5714.6	5731.7	5735.5	5739.3
7.5°	5286.1	5294.9	5291.7	5288.5
10°	4909.0	4921.0	4912.6	4904.1
12.5°	4458.0	4468.9	4474.4	4479.8
15°	3757.7	3788.1	3807.8	3827.6
17.5°	3077.7	3098.3	3090.6	3083.0
20°	2637.1	2649.9	2647.6	2645.2
22.5°	2276.9	2293.9	2293.4	2292.9
25°	1821.3	1832.6	1834.0	1835.5
27.5°	1483.9	1493.5	1499.4	1505.2
30°	1321.0	1330.7	1335.4	1340.1
32.5°	1183.6	1192.3	1192.1	1191.9
35°	993.6	1000.6	997.8	995.0
37.5°	818.7	824.6	821.9	819.3
40°	704.6	708.7	706.9	705.0
42.5°	593.7	596.3	588.4	580.5
45°	425.2	414.0	389.1	364.1
47.5°	278.0	253.2	218.7	184.2
50°	194.8	164.4	140.4	116.4
52.5°	142.8	114.0	101.7	89.3
55°	88.9	72.9	68.2	63.5
57.5°	60.3	54.4	51.7	49.1
60°	49.0	46.1	44.2	42.3
62.5°	41.7	40.4	39.2	38.1
65°	33.9	33.8	33.3	32.8
67.5°	28.9	28.9	28.4	27.9
70°	26.1	26.3	25.9	25.4
72.5°	22.7	23.0	22.5	22.0
75°	18.0	18.0	18.0	18.0
77.5°	13.8	14.2	14.1	14.0
80°	11.3	11.5	11.1	10.6
82.5°	8.8	9.1	9.0	8.9
85°	4.9	5.3	5.3	5.3
87.5°	5.5	4.0	3.2	2.3
90°	19.0	11.6	7.4	3.2
92.5°	41.0	28.5	20.1	11.6
95°	82.4	65.5	46.5	32.8
97.5°	131.2	104.0	85.2	62.6
100°	157.4	131.0	113.1	88.8
102.5°	186.2	164.0	139.3	115.0
105°	237.8	210.3	181.7	154.3
107.5°	285.5	255.3	221.1	196.3
110°	315.9	283.2	247.3	225.1



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	330°	340°	350°	360°
112.5°	345.5	311.9	275.2	253.0
115°	385.7	348.7	314.9	295.9
117.5°	424.4	386.3	350.6	335.6
120°	448.0	410.0	375.1	363.5
122.5°	467.5	430.3	397.9	393.1
125°	496.6	458.6	431.1	437.5
127.5°	520.3	485.4	468.1	482.3
130°	534.7	504.0	493.5	513.5
132.5°	547.4	523.5	518.8	546.5
135°	566.4	552.6	556.9	594.9
137.5°	589.0	583.7	597.9	645.8
140°	603.4	606.5	626.6	680.5
142.5°	622.8	630.2	656.2	713.5
145°	653.0	668.9	702.7	759.7
147.5°	687.3	707.8	749.6	808.1
150°	710.1	736.5	780.9	836.9
152.5°	736.3	763.6	807.9	864.8
155°	776.7	807.3	853.8	902.4
157.5°	817.9	849.1	893.5	936.0
160°	843.2	877.0	917.2	956.3
162.5°	872.0	903.2	938.3	973.2
165°	914.0	939.4	967.9	997.5
167.5°	949.3	970.5	992.9	1015.9
170°	972.1	989.0	1008.1	1026.0
172.5°	991.6	1005.1	1019.1	1034.5
175°	1017.6	1025.0	1033.4	1042.9
177.5°	1037.7	1040.2	1042.7	1047.0
180°	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P1428616

CATALOG NUMBER: SQ2W-WBN-K-075U-075D-L940-UNV-STD-W-WM-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.34	3.04	3.32	3.99	5.24	1.97	2.66	2.94	3.62	4.86
	3H	3.57	4.19	4.55	5.15	6.42	3.17	3.79	4.15	4.76	6.02
	4H	4.08	4.67	5.08	5.64	6.91	3.68	4.27	4.68	5.24	6.51
	6H	4.44	4.97	5.44	5.95	7.23	4.02	4.55	5.02	5.53	6.81
	8H	4.58	5.09	5.59	6.08	7.36	4.15	4.66	5.16	5.65	6.93
	12H	4.68	5.16	5.69	6.14	7.44	4.22	4.70	5.23	5.69	6.99
4H	2H	2.66	3.24	3.66	4.21	5.49	2.35	2.93	3.35	3.90	5.18
	3H	4.15	4.64	5.16	5.64	6.92	3.81	4.29	4.82	5.29	6.58
	4H	4.80	5.24	5.81	6.23	7.54	4.45	4.88	5.46	5.88	7.19
	6H	5.29	5.67	6.31	6.68	7.99	4.90	5.28	5.93	6.29	7.60
	8H	5.50	5.85	6.52	6.86	8.18	5.10	5.45	6.12	6.45	7.77
	12H	5.64	5.95	6.67	6.97	8.30	5.20	5.51	6.24	6.54	7.86
8H	4H	4.96	5.31	5.98	6.32	7.64	4.64	4.99	5.66	6.00	7.32
	6H	5.60	5.88	6.64	6.93	8.25	5.24	5.52	6.28	6.58	7.89
	8H	5.92	6.16	6.97	7.20	8.54	5.53	5.78	6.58	6.81	8.15
	12H	6.14	6.36	7.20	7.39	8.77	5.73	5.94	6.78	6.97	8.36
12H	4H	4.94	5.25	5.98	6.28	7.60	4.63	4.94	5.67	5.97	7.29
	6H	5.63	5.88	6.68	6.92	8.25	5.29	5.54	6.34	6.58	7.91
	8H	5.98	6.20	7.03	7.23	8.61	5.61	5.83	6.66	6.85	8.24