

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1428643

Luminaire Tested: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

Issue Date: 3/10/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1428643  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2303-941-3, G3-2308-130-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/10/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4  
Description: CORELITE SQ2W WALL MOUNTED LED LUMINAIRE  
DOWNLIGHT - WHITE DISCREET BAFFLE, NARROW 35-DEGREE OPTIC  
UPLIGHT - ASYMMETRIC ROLL LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9821.8 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 82.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot





TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	99	96	93	90	91	88	86	84	75	73	71	62	61	60	51	50	49	44				44
2	92	86	82	77	85	80	76	73	68	66	63	58	56	54	48	46	45	41				41
3	86	79	73	68	80	73	68	64	63	59	56	53	51	49	45	43	42	38				38
4	80	72	65	60	74	67	61	57	58	54	51	50	47	45	42	40	39	35				35
5	75	66	59	54	70	62	56	51	54	49	46	46	43	41	40	38	36	33				33
6	70	60	54	49	65	57	51	47	50	46	42	44	40	38	37	35	34	31				31
7	66	56	49	45	62	53	47	43	47	42	39	41	38	35	35	33	32	29				29
8	62	52	45	41	58	49	43	39	44	39	36	38	35	33	34	31	30	28				28
9	59	48	42	38	55	46	40	36	41	37	33	36	33	31	32	30	28	26				26
10	56	45	39	35	52	43	37	34	39	34	31	34	31	29	30	28	26	25				25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	128719	128719	128719	128719
5°	124282	124420	124282	124420
10°	107424	107680	107424	107680
15°	85483	83119	85483	83119
20°	60725	60361	60725	60361
25°	43689	42529	43689	42529
30°	33381	32406	33381	32406
35°	26203	25089	26203	25089
40°	19852	18630	19852	18630
45°	11108	9914	11108	9914
50°	3908	3446	3908	3446
55°	2390	2269	2390	2269
60°	1828	1689	1828	1689
65°	1673	1566	1673	1566
70°	1600	1468	1600	1468
75°	1497	1410	1497	1410
80°	1311	1311	1311	1311
85°	1315	1056	1315	1056

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 45°  
 Luminance: 13173 cd/sqm



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	692.0	7.0
10°-20°	1375.4	14.0
20°-30°	1139.0	11.6
30°-40°	819.4	8.3
40°-50°	417.4	4.2
50°-60°	108.5	1.1
60°-70°	45.1	0.5
70°-80°	25.0	0.3
80°-90°	14.8	0.2
90°-100°	141.3	1.4
100°-110°	412.2	4.2
110°-120°	672.6	6.8
120°-130°	853.5	8.7
130°-140°	913.3	9.3
140°-150°	852.8	8.7
150°-160°	701.7	7.1
160°-170°	470.6	4.8
170°-180°	167.1	1.7
0°-30°	3206.5	32.6
0°-40°	4025.9	41.0
0°-60°	4551.9	46.3
0°-90°	4636.7	47.2
90°-120°	1226.1	12.5
90°-150°	3845.7	39.2
90°-180°	5185.0	52.8
0°-180°	9821.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	7972	7972	7972	7972	7972	
5°	7668	7677	7668	7677	7668	692
15°	5114	4973	5114	4973	5114	1388
25°	2452	2387	2452	2387	2452	1153
35°	1329	1273	1329	1273	1329	834
45°	486	434	486	434	486	389
55°	85	81	85	81	85	83
65°	44	41	44	41	44	44
75°	24	23	24	23	24	25
85°	7	6	7	6	7	8
90°	5	40	5	77	5	5
95°	56	41	56	242	56	67
105°	262	420	262	578	262	279
115°	502	696	502	857	502	495
125°	743	1103	743	1051	743	664
135°	1010	1444	1010	1164	1010	780
145°	1290	1665	1290	1189	1290	807
155°	1532	1808	1532	1234	1532	704
165°	1693	1885	1693	1421	1693	477
175°	1770	1846	1770	1666	1770	168
180°	1776	1776	1776	1776	1776	



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4
2.5°	7959.9	7953.9	7947.9	7921.1	7887.4	7884.6	7912.8	7932.1	7925.1	7918.1	7925.1
5°	7668.3	7663.3	7658.2	7635.3	7606.4	7616.4	7665.5	7699.4	7688.1	7676.8	7688.1
7.5°	7066.1	7070.4	7074.6	7062.9	7045.8	7058.9	7102.3	7131.8	7119.7	7107.7	7119.7
10°	6552.4	6563.7	6575.0	6559.0	6533.9	6553.0	6616.5	6653.5	6610.7	6568.0	6610.7
12.5°	5985.6	5978.3	5971.0	5956.3	5939.2	5935.8	5946.0	5947.7	5924.1	5900.4	5924.1
15°	5114.1	5087.7	5061.3	5020.7	4975.5	4960.7	4976.4	4986.5	4979.6	4972.7	4979.6
17.5°	4119.3	4129.5	4139.6	4112.2	4072.2	4051.5	4050.0	4046.9	4039.1	4031.3	4039.1
20°	3534.3	3537.5	3540.6	3523.5	3499.6	3493.9	3506.5	3515.6	3514.4	3513.1	3514.4
22.5°	3063.6	3064.3	3064.9	3042.2	3011.8	3005.9	3024.5	3035.6	3024.3	3013.0	3024.3
25°	2452.4	2450.5	2448.6	2433.5	2414.0	2399.6	2390.2	2383.6	2385.4	2387.3	2385.4
27.5°	2011.1	2003.3	1995.5	1982.6	1968.1	1963.9	1970.2	1973.8	1969.1	1964.5	1969.1
30°	1790.5	1784.2	1777.9	1765.0	1750.0	1744.3	1748.1	1749.5	1743.8	1738.2	1743.8
32.5°	1592.5	1592.7	1593.0	1581.4	1565.8	1557.1	1555.3	1553.0	1548.8	1544.7	1548.8
35°	1329.4	1333.2	1337.0	1327.5	1313.7	1302.1	1292.7	1284.2	1278.5	1272.9	1278.5
37.5°	1094.7	1098.2	1101.7	1093.8	1082.1	1069.4	1055.5	1044.0	1039.2	1034.4	1039.2
40°	941.9	944.4	946.9	941.4	933.3	921.0	904.7	891.5	887.7	883.9	887.7
42.5°	775.6	786.2	796.7	793.2	785.1	773.3	758.0	744.4	736.1	727.8	736.1
45°	486.5	519.8	553.1	568.1	576.9	572.8	555.8	531.0	482.6	434.2	482.6
47.5°	246.1	292.2	338.4	371.5	400.3	391.1	344.0	296.7	249.2	201.7	249.2
50°	155.6	187.6	219.7	260.2	303.6	294.2	231.9	179.9	158.6	137.2	158.6
52.5°	119.4	135.8	152.3	190.8	236.7	232.3	177.6	133.7	121.8	110.0	121.8
55°	84.9	91.1	97.4	118.8	145.2	143.6	114.1	90.7	85.6	80.6	85.6
57.5°	65.6	69.1	72.7	80.6	90.0	89.2	78.0	68.8	65.7	62.5	65.7
60°	56.6	59.1	61.6	65.5	69.9	69.3	63.6	58.6	55.5	52.3	55.5
62.5°	50.9	52.4	53.9	55.7	57.6	56.7	53.1	50.1	48.9	47.8	48.9
65°	43.8	44.5	45.1	45.3	45.3	44.6	43.4	42.3	41.6	41.0	41.6
67.5°	37.3	38.0	38.6	38.7	38.5	38.2	37.5	36.9	36.3	35.6	36.3
70°	33.9	34.6	35.2	34.9	34.3	33.6	33.0	32.4	31.7	31.1	31.7
72.5°	29.4	30.0	30.7	30.4	29.7	29.4	29.2	29.0	28.3	27.7	28.3
75°	24.0	24.0	24.0	24.0	24.0	23.7	23.1	22.6	22.6	22.6	22.6
77.5°	18.7	18.8	18.9	18.5	17.9	17.5	17.5	17.4	16.9	16.4	16.9
80°	14.1	14.8	15.4	15.1	14.5	14.1	14.1	14.1	14.1	14.1	14.1
82.5°	11.9	12.0	12.1	11.7	11.1	10.7	10.7	10.7	10.7	10.7	10.7
85°	7.1	7.1	7.1	6.6	6.0	6.0	6.6	6.9	6.3	5.7	6.3
87.5°	3.3	4.8	6.6	8.0	9.1	9.4	9.4	9.8	10.2	10.2	10.2
90°	5.4	12.6	21.5	28.7	34.1	35.9	35.9	37.7	39.5	39.5	39.5
92.5°	19.7	31.2	31.6	31.6	38.4	41.6	44.5	44.8	46.6	46.6	46.6
95°	55.6	61.0	91.5	89.7	61.0	48.4	41.3	41.3	41.3	41.3	41.3
97.5°	106.2	114.1	119.1	159.6	168.6	162.9	132.7	111.6	99.7	94.4	99.7
100°	150.7	154.3	165.0	166.8	211.7	254.7	233.2	206.3	197.3	191.9	197.3
102.5°	195.2	197.3	213.8	221.4	231.8	256.2	330.8	322.5	316.4	315.3	316.4
105°	261.9	263.7	294.2	308.5	315.7	315.7	313.9	349.8	407.2	419.7	407.2
107.5°	333.3	341.5	377.4	415.8	424.0	426.2	416.9	411.5	409.3	410.8	409.3
110°	382.1	394.6	437.7	486.1	498.7	502.3	498.7	493.3	489.7	489.7	489.7



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	429.4	447.7	496.5	552.1	573.3	584.1	576.2	572.2	568.6	571.5	568.6
115°	502.3	529.2	593.7	651.1	694.2	699.6	697.8	697.8	696.0	696.0	696.0
117.5°	569.7	612.8	685.2	752.0	801.8	816.2	823.3	821.2	819.0	822.6	819.0
120°	617.1	667.3	749.8	825.1	873.6	895.1	902.3	898.7	902.3	898.7	902.3
122.5°	667.3	729.0	810.1	888.3	945.3	969.7	978.3	979.0	979.8	977.6	979.8
125°	742.6	818.0	913.0	993.8	1052.9	1081.6	1088.8	1090.6	1094.2	1103.2	1094.2
127.5°	818.7	904.1	1008.5	1086.3	1146.9	1181.7	1192.9	1196.8	1204.3	1208.3	1204.3
130°	871.8	968.6	1074.5	1148.0	1207.2	1244.9	1264.6	1270.0	1279.0	1277.2	1279.0
132.5°	927.7	1028.9	1136.2	1212.6	1267.5	1308.0	1324.9	1340.3	1343.5	1346.1	1343.5
135°	1009.9	1119.3	1226.9	1302.3	1354.3	1393.8	1415.3	1429.6	1438.6	1444.0	1438.6
137.5°	1096.4	1211.9	1315.2	1382.3	1434.7	1468.7	1493.1	1508.2	1517.5	1521.8	1517.5
140°	1155.2	1266.4	1366.9	1436.8	1483.5	1517.5	1539.1	1557.0	1567.8	1567.8	1567.8
142.5°	1211.2	1320.9	1418.5	1488.5	1529.4	1560.6	1583.5	1597.2	1609.4	1609.4	1609.4
145°	1289.7	1399.1	1488.8	1558.8	1592.9	1621.6	1646.7	1657.5	1664.6	1664.6	1664.6
147.5°	1371.9	1468.7	1550.5	1617.6	1646.3	1680.1	1699.8	1708.4	1717.4	1713.4	1717.4
150°	1420.7	1510.4	1589.3	1652.1	1680.8	1713.1	1732.8	1740.0	1748.9	1743.6	1748.9
152.5°	1468.0	1553.4	1625.2	1683.6	1708.0	1740.3	1762.9	1770.1	1776.2	1772.3	1776.2
155°	1531.9	1607.2	1673.6	1727.4	1748.9	1779.4	1801.0	1809.9	1817.1	1808.1	1817.1
157.5°	1588.9	1653.9	1711.6	1761.1	1784.1	1810.3	1830.4	1841.5	1848.7	1844.7	1848.7
160°	1623.4	1682.6	1734.6	1781.2	1802.7	1826.1	1847.6	1860.1	1867.3	1861.9	1867.3
162.5°	1652.1	1705.5	1754.7	1797.0	1815.7	1836.1	1861.9	1873.1	1880.2	1873.4	1880.2
165°	1693.3	1736.4	1779.4	1815.3	1831.4	1847.6	1874.5	1887.1	1892.4	1885.3	1892.4
167.5°	1724.5	1757.5	1792.3	1823.2	1835.0	1850.8	1877.7	1888.1	1894.9	1886.0	1894.9
170°	1741.8	1770.5	1801.0	1826.1	1835.0	1849.4	1876.3	1885.3	1890.6	1881.7	1890.6
172.5°	1756.1	1777.6	1802.4	1824.6	1829.3	1840.8	1866.2	1875.2	1879.2	1871.6	1879.2
175°	1770.5	1783.0	1801.0	1815.3	1813.5	1820.7	1842.2	1849.4	1856.6	1845.8	1856.6
177.5°	1777.3	1783.0	1788.8	1797.4	1791.6	1791.6	1807.4	1811.7	1813.2	1807.4	1813.2
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
0°	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4
2.5°	7932.1	7912.8	7884.6	7887.4	7921.1	7947.9	7953.9	7959.9	7953.9	7947.9	7921.1
5°	7699.4	7665.5	7616.4	7606.4	7635.3	7658.2	7663.3	7668.3	7663.3	7658.2	7635.3
7.5°	7131.8	7102.3	7058.9	7045.8	7062.9	7074.6	7070.4	7066.1	7070.4	7074.6	7062.9
10°	6653.5	6616.5	6553.0	6533.9	6559.0	6575.0	6563.7	6552.4	6563.7	6575.0	6559.0
12.5°	5947.7	5946.0	5935.8	5939.2	5956.3	5971.0	5978.3	5985.6	5978.3	5971.0	5956.3
15°	4986.5	4976.4	4960.7	4975.5	5020.7	5061.3	5087.7	5114.1	5087.7	5061.3	5020.7
17.5°	4046.9	4050.0	4051.5	4072.2	4112.2	4139.6	4129.5	4119.3	4129.5	4139.6	4112.2
20°	3515.6	3506.5	3493.9	3499.6	3523.5	3540.6	3537.5	3534.3	3537.5	3540.6	3523.5
22.5°	3035.6	3024.5	3005.9	3011.8	3042.2	3064.9	3064.3	3063.6	3064.3	3064.9	3042.2
25°	2383.6	2390.2	2399.6	2414.0	2433.5	2448.6	2450.5	2452.4	2450.5	2448.6	2433.5
27.5°	1973.8	1970.2	1963.9	1968.1	1982.6	1995.5	2003.3	2011.1	2003.3	1995.5	1982.6
30°	1749.5	1748.1	1744.3	1750.0	1765.0	1777.9	1784.2	1790.5	1784.2	1777.9	1765.0
32.5°	1553.0	1555.3	1557.1	1565.8	1581.4	1593.0	1592.7	1592.5	1592.7	1593.0	1581.4
35°	1284.2	1292.7	1302.1	1313.7	1327.5	1337.0	1333.2	1329.4	1333.2	1337.0	1327.5
37.5°	1044.0	1055.5	1069.4	1082.1	1093.8	1101.7	1098.2	1094.7	1098.2	1101.7	1093.8
40°	891.5	904.7	921.0	933.3	941.4	946.9	944.4	941.9	944.4	946.9	941.4
42.5°	744.4	758.0	773.3	785.1	793.2	796.7	786.2	775.6	786.2	796.7	793.2
45°	531.0	555.8	572.8	576.9	568.1	553.1	519.8	486.5	519.8	553.1	568.1
47.5°	296.7	344.0	391.1	400.3	371.5	338.4	292.2	246.1	292.2	338.4	371.5
50°	179.9	231.9	294.2	303.6	260.2	219.7	187.6	155.6	187.6	219.7	260.2
52.5°	133.7	177.6	232.3	236.7	190.8	152.3	135.8	119.4	135.8	152.3	190.8
55°	90.7	114.1	143.6	145.2	118.8	97.4	91.1	84.9	91.1	97.4	118.8
57.5°	68.8	78.0	89.2	90.0	80.6	72.7	69.1	65.6	69.1	72.7	80.6
60°	58.6	63.6	69.3	69.9	65.5	61.6	59.1	56.6	59.1	61.6	65.5
62.5°	50.1	53.1	56.7	57.6	55.7	53.9	52.4	50.9	52.4	53.9	55.7
65°	42.3	43.4	44.6	45.3	45.3	45.1	44.5	43.8	44.5	45.1	45.3
67.5°	36.9	37.5	38.2	38.5	38.7	38.6	38.0	37.3	38.0	38.6	38.7
70°	32.4	33.0	33.6	34.3	34.9	35.2	34.6	33.9	34.6	35.2	34.9
72.5°	29.0	29.2	29.4	29.7	30.4	30.7	30.0	29.4	30.0	30.7	30.4
75°	22.6	23.1	23.7	24.0	24.0	24.0	24.0	24.0	24.0	24.0	24.0
77.5°	17.4	17.5	17.5	17.9	18.5	18.9	18.8	18.7	18.8	18.9	18.5
80°	14.1	14.1	14.1	14.5	15.1	15.4	14.8	14.1	14.8	15.4	15.1
82.5°	10.7	10.7	10.7	11.1	11.7	12.1	12.0	11.9	12.0	12.1	11.7
85°	6.9	6.6	6.0	6.0	6.6	7.1	7.1	7.1	7.1	7.1	6.6
87.5°	9.8	9.4	9.4	9.1	8.0	6.6	4.8	3.3	4.8	6.2	8.7
90°	37.7	35.9	35.9	34.1	28.7	21.5	12.6	5.4	12.6	19.7	32.3
92.5°	44.8	44.5	41.6	38.4	31.6	31.6	31.2	19.7	34.1	48.4	69.6
95°	41.3	41.3	48.4	61.0	89.7	91.5	61.0	55.6	78.9	111.2	139.9
97.5°	111.6	132.7	162.9	168.6	159.6	119.1	114.1	106.2	144.6	176.5	222.8
100°	206.3	233.2	254.7	211.7	166.8	165.0	154.3	150.7	191.9	222.4	267.3
102.5°	322.5	330.8	256.2	231.8	221.4	213.8	197.3	195.2	236.4	278.4	316.1
105°	349.8	313.9	315.7	315.7	308.5	294.2	263.7	261.9	308.5	357.0	403.6
107.5°	411.5	416.9	426.2	424.0	415.8	377.4	341.5	333.3	375.3	433.4	484.7
110°	493.3	498.7	502.3	498.7	486.1	437.7	394.6	382.1	419.7	480.7	536.3



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°	190°	200°	210°
112.5°	572.2	576.2	584.1	573.3	552.1	496.5	447.7	429.4	467.1	529.5	586.6
115°	697.8	697.8	699.6	694.2	651.1	593.7	529.2	502.3	534.5	591.9	654.7
117.5°	821.2	823.3	816.2	801.8	752.0	685.2	612.8	569.7	595.2	655.8	720.4
120°	898.7	902.3	895.1	873.6	825.1	749.8	667.3	617.1	636.8	696.0	760.6
122.5°	979.0	978.3	969.7	945.3	888.3	810.1	729.0	667.3	675.5	730.4	793.6
125°	1090.6	1088.8	1081.6	1052.9	993.8	913.0	818.0	742.6	731.9	778.5	843.1
127.5°	1196.8	1192.9	1181.7	1146.9	1086.3	1008.5	904.1	818.7	794.6	824.1	883.3
130°	1270.0	1264.6	1244.9	1207.2	1148.0	1074.5	968.6	871.8	837.7	855.6	907.7
132.5°	1340.3	1324.9	1308.0	1267.5	1212.6	1136.2	1028.9	927.7	880.7	888.6	929.2
135°	1429.6	1415.3	1393.8	1354.3	1302.3	1226.9	1119.3	1009.9	945.3	938.1	961.5
137.5°	1508.2	1493.1	1468.7	1434.7	1382.3	1315.2	1211.9	1096.4	1014.9	990.9	999.9
140°	1557.0	1539.1	1517.5	1483.5	1436.8	1366.9	1266.4	1155.2	1063.7	1029.6	1024.2
142.5°	1597.2	1583.5	1560.6	1529.4	1488.5	1418.5	1320.9	1211.2	1113.9	1069.8	1057.3
145°	1657.5	1646.7	1621.6	1592.9	1558.8	1488.8	1399.1	1289.7	1192.9	1135.5	1108.6
147.5°	1708.4	1699.8	1680.1	1646.3	1617.6	1550.5	1468.7	1371.9	1272.5	1201.5	1166.7
150°	1740.0	1732.8	1713.1	1680.8	1652.1	1589.3	1510.4	1420.7	1325.6	1250.3	1205.4
152.5°	1770.1	1762.9	1740.3	1708.0	1683.6	1625.2	1553.4	1468.0	1371.5	1296.2	1249.9
155°	1809.9	1801.0	1779.4	1748.9	1727.4	1673.6	1607.2	1531.9	1449.4	1370.4	1318.4
157.5°	1841.5	1830.4	1810.3	1784.1	1761.1	1711.6	1653.9	1588.9	1516.8	1441.5	1388.4
160°	1860.1	1847.6	1826.1	1802.7	1781.2	1734.6	1682.6	1623.4	1557.0	1488.8	1431.4
162.5°	1873.1	1861.9	1836.1	1815.7	1797.0	1754.7	1705.5	1652.1	1592.9	1533.3	1480.2
165°	1887.1	1874.5	1847.6	1831.4	1815.3	1779.4	1736.4	1693.3	1643.1	1594.7	1551.6
167.5°	1888.1	1877.7	1850.8	1835.0	1823.2	1792.3	1757.5	1724.5	1685.4	1647.4	1611.5
170°	1885.3	1876.3	1849.4	1835.0	1826.1	1801.0	1770.5	1741.8	1711.3	1679.0	1650.3
172.5°	1875.2	1866.2	1840.8	1829.3	1824.6	1802.4	1777.6	1756.1	1729.9	1706.2	1683.3
175°	1849.4	1842.2	1820.7	1813.5	1815.3	1801.0	1783.0	1770.5	1754.3	1740.0	1727.4
177.5°	1811.7	1807.4	1791.6	1791.6	1797.4	1788.8	1783.0	1777.3	1770.1	1765.8	1761.5
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
0°	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4	7972.4
2.5°	7887.4	7884.6	7912.8	7932.1	7925.1	7918.1	7925.1	7932.1	7912.8	7884.6	7887.4
5°	7606.4	7616.4	7665.5	7699.4	7688.1	7676.8	7688.1	7699.4	7665.5	7616.4	7606.4
7.5°	7045.8	7058.9	7102.3	7131.8	7119.7	7107.7	7119.7	7131.8	7102.3	7058.9	7045.8
10°	6533.9	6553.0	6616.5	6653.5	6610.7	6568.0	6610.7	6653.5	6616.5	6553.0	6533.9
12.5°	5939.2	5935.8	5946.0	5947.7	5924.1	5900.4	5924.1	5947.7	5946.0	5935.8	5939.2
15°	4975.5	4960.7	4976.4	4986.5	4979.6	4972.7	4979.6	4986.5	4976.4	4960.7	4975.5
17.5°	4072.2	4051.5	4050.0	4046.9	4039.1	4031.3	4039.1	4046.9	4050.0	4051.5	4072.2
20°	3499.6	3493.9	3506.5	3515.6	3514.4	3513.1	3514.4	3515.6	3506.5	3493.9	3499.6
22.5°	3011.8	3005.9	3024.5	3035.6	3024.3	3013.0	3024.3	3035.6	3024.5	3005.9	3011.8
25°	2414.0	2399.6	2390.2	2383.6	2385.4	2387.3	2385.4	2383.6	2390.2	2399.6	2414.0
27.5°	1968.1	1963.9	1970.2	1973.8	1969.1	1964.5	1969.1	1973.8	1970.2	1963.9	1968.1
30°	1750.0	1744.3	1748.1	1749.5	1743.8	1738.2	1743.8	1749.5	1748.1	1744.3	1750.0
32.5°	1565.8	1557.1	1555.3	1553.0	1548.8	1544.7	1548.8	1553.0	1555.3	1557.1	1565.8
35°	1313.7	1302.1	1292.7	1284.2	1278.5	1272.9	1278.5	1284.2	1292.7	1302.1	1313.7
37.5°	1082.1	1069.4	1055.5	1044.0	1039.2	1034.4	1039.2	1044.0	1055.5	1069.4	1082.1
40°	933.3	921.0	904.7	891.5	887.7	883.9	887.7	891.5	904.7	921.0	933.3
42.5°	785.1	773.3	758.0	744.4	736.1	727.8	736.1	744.4	758.0	773.3	785.1
45°	576.9	572.8	555.8	531.0	482.6	434.2	482.6	531.0	555.8	572.8	576.9
47.5°	400.3	391.1	344.0	296.7	249.2	201.7	249.2	296.7	344.0	391.1	400.3
50°	303.6	294.2	231.9	179.9	158.6	137.2	158.6	179.9	231.9	294.2	303.6
52.5°	236.7	232.3	177.6	133.7	121.8	110.0	121.8	133.7	177.6	232.3	236.7
55°	145.2	143.6	114.1	90.7	85.6	80.6	85.6	90.7	114.1	143.6	145.2
57.5°	90.0	89.2	78.0	68.8	65.7	62.5	65.7	78.0	89.2	90.0	
60°	69.9	69.3	63.6	58.6	55.5	52.3	55.5	63.6	69.3	69.9	
62.5°	57.6	56.7	53.1	50.1	48.9	47.8	48.9	50.1	53.1	56.7	57.6
65°	45.3	44.6	43.4	42.3	41.6	41.0	41.6	42.3	43.4	44.6	45.3
67.5°	38.5	38.2	37.5	36.9	36.3	35.6	36.3	36.9	37.5	38.2	38.5
70°	34.3	33.6	33.0	32.4	31.7	31.1	31.7	32.4	33.0	33.6	34.3
72.5°	29.7	29.4	29.2	29.0	28.3	27.7	28.3	29.0	29.2	29.4	29.7
75°	24.0	23.7	23.1	22.6	22.6	22.6	22.6	22.6	23.1	23.7	24.0
77.5°	17.9	17.5	17.5	17.4	16.9	16.4	16.9	17.4	17.5	17.5	17.9
80°	14.5	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.5
82.5°	11.1	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	11.1
85°	6.0	6.0	6.6	6.9	6.3	5.7	6.3	6.9	6.6	6.0	6.0
87.5°	10.5	13.0	15.5	17.0	18.4	17.7	18.4	17.0	15.5	13.0	10.5
90°	41.3	53.8	66.4	73.5	80.7	77.1	80.7	73.5	66.4	53.8	41.3
92.5°	82.9	104.0	119.5	132.4	138.1	137.4	138.1	132.4	119.5	104.0	82.9
95°	166.8	191.9	217.0	235.0	245.7	242.2	245.7	235.0	217.0	191.9	166.8
97.5°	257.2	291.0	318.9	335.8	346.6	353.7	346.6	335.8	318.9	291.0	257.2
100°	317.5	349.8	382.1	401.8	419.7	426.9	419.7	401.8	382.1	349.8	317.5
102.5°	366.3	408.6	443.8	464.9	480.0	487.2	480.0	464.9	443.8	408.6	366.3
105°	446.7	491.5	529.2	556.1	572.2	577.6	572.2	556.1	529.2	491.5	446.7
107.5°	527.0	573.3	608.1	637.9	657.6	669.1	657.6	608.1	573.3	527.0	
110°	590.2	627.8	665.5	692.4	712.1	719.3	712.1	692.4	665.5	627.8	590.2



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	220°	230°	240°	250°	260°	270°	280°	290°	300°	310°	320°
112.5°	643.2	685.2	722.9	749.8	772.4	782.4	772.4	749.8	722.9	685.2	643.2
115°	717.5	773.1	807.2	832.3	848.5	857.4	848.5	832.3	807.2	773.1	717.5
117.5°	779.2	837.3	874.6	894.0	901.6	908.0	901.6	894.0	874.6	837.3	779.2
120°	818.0	871.8	914.8	939.9	948.9	952.5	948.9	939.9	914.8	871.8	818.0
122.5°	853.8	904.8	946.4	977.3	992.0	995.5	992.0	977.3	946.4	904.8	853.8
125°	904.1	952.5	995.5	1026.0	1042.2	1051.2	1042.2	1026.0	995.5	952.5	904.1
127.5°	947.8	1000.2	1039.7	1067.3	1083.1	1090.3	1083.1	1067.3	1039.7	1000.2	947.8
130°	972.2	1026.0	1065.5	1096.0	1110.3	1117.5	1110.3	1096.0	1065.5	1026.0	972.2
132.5°	990.9	1047.6	1088.5	1116.1	1131.9	1139.0	1131.9	1116.1	1088.5	1047.6	990.9
135°	1013.5	1072.7	1115.7	1142.6	1157.0	1164.2	1157.0	1142.6	1115.7	1072.7	1013.5
137.5°	1033.2	1087.0	1131.9	1160.2	1173.1	1177.8	1173.1	1160.2	1131.9	1087.0	1033.2
140°	1047.6	1094.2	1139.0	1166.0	1180.3	1182.1	1180.3	1166.0	1139.0	1094.2	1047.6
142.5°	1066.2	1102.8	1141.9	1168.8	1183.2	1186.4	1183.2	1168.8	1141.9	1102.8	1066.2
145°	1099.6	1121.1	1148.0	1173.1	1185.7	1189.3	1185.7	1173.1	1148.0	1121.1	1099.6
147.5°	1141.6	1148.4	1162.4	1178.9	1191.1	1193.6	1191.1	1178.9	1162.4	1148.4	1141.6
150°	1173.1	1171.3	1176.7	1187.5	1198.2	1196.5	1198.2	1187.5	1176.7	1171.3	1173.1
152.5°	1209.0	1198.6	1198.2	1203.3	1208.3	1207.9	1208.3	1203.3	1198.2	1198.6	1209.0
155°	1270.0	1250.3	1239.5	1235.9	1235.9	1234.1	1235.9	1235.9	1239.5	1250.3	1270.0
157.5°	1337.1	1309.5	1293.3	1284.7	1282.2	1278.2	1282.2	1284.7	1293.3	1309.5	1337.1
160°	1383.0	1352.5	1336.4	1322.0	1316.6	1311.3	1316.6	1322.0	1336.4	1352.5	1383.0
162.5°	1426.1	1397.0	1379.4	1366.5	1361.1	1352.9	1361.1	1366.5	1379.4	1397.0	1426.1
165°	1496.0	1465.5	1445.8	1435.0	1427.8	1420.7	1427.8	1435.0	1445.8	1465.5	1496.0
167.5°	1566.0	1532.6	1519.7	1507.5	1500.7	1487.8	1500.7	1507.5	1519.7	1532.6	1566.0
170°	1609.0	1578.5	1571.4	1560.6	1548.0	1533.7	1548.0	1560.6	1571.4	1578.5	1609.0
172.5°	1646.3	1625.9	1618.7	1607.9	1604.0	1592.5	1604.0	1607.9	1618.7	1625.9	1646.3
175°	1700.5	1684.4	1684.4	1682.6	1677.2	1666.4	1677.2	1682.6	1684.4	1684.4	1700.5
177.5°	1745.7	1737.1	1742.8	1742.8	1741.4	1731.4	1741.4	1742.8	1742.8	1737.1	1745.7
180°	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8	1775.8



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
0°	7972.4	7972.4	7972.4	7972.4
2.5°	7921.1	7947.9	7953.9	7959.9
5°	7635.3	7658.2	7663.3	7668.3
7.5°	7062.9	7074.6	7070.4	7066.1
10°	6559.0	6575.0	6563.7	6552.4
12.5°	5956.3	5971.0	5978.3	5985.6
15°	5020.7	5061.3	5087.7	5114.1
17.5°	4112.2	4139.6	4129.5	4119.3
20°	3523.5	3540.6	3537.5	3534.3
22.5°	3042.2	3064.9	3064.3	3063.6
25°	2433.5	2448.6	2450.5	2452.4
27.5°	1982.6	1995.5	2003.3	2011.1
30°	1765.0	1777.9	1784.2	1790.5
32.5°	1581.4	1593.0	1592.7	1592.5
35°	1327.5	1337.0	1333.2	1329.4
37.5°	1093.8	1101.7	1098.2	1094.7
40°	941.4	946.9	944.4	941.9
42.5°	793.2	796.7	786.2	775.6
45°	568.1	553.1	519.8	486.5
47.5°	371.5	338.4	292.2	246.1
50°	260.2	219.7	187.6	155.6
52.5°	190.8	152.3	135.8	119.4
55°	118.8	97.4	91.1	84.9
57.5°	80.6	72.7	69.1	65.6
60°	65.5	61.6	59.1	56.6
62.5°	55.7	53.9	52.4	50.9
65°	45.3	45.1	44.5	43.8
67.5°	38.7	38.6	38.0	37.3
70°	34.9	35.2	34.6	33.9
72.5°	30.4	30.7	30.0	29.4
75°	24.0	24.0	24.0	24.0
77.5°	18.5	18.9	18.8	18.7
80°	15.1	15.4	14.8	14.1
82.5°	11.7	12.1	12.0	11.9
85°	6.6	7.1	7.1	7.1
87.5°	8.7	6.2	4.8	3.3
90°	32.3	19.7	12.6	5.4
92.5°	69.6	48.4	34.1	19.7
95°	139.9	111.2	78.9	55.6
97.5°	222.8	176.5	144.6	106.2
100°	267.3	222.4	191.9	150.7
102.5°	316.1	278.4	236.4	195.2
105°	403.6	357.0	308.5	261.9
107.5°	484.7	433.4	375.3	333.3
110°	536.3	480.7	419.7	382.1



TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	330°	340°	350°	360°
112.5°	586.6	529.5	467.1	429.4
115°	654.7	591.9	534.5	502.3
117.5°	720.4	655.8	595.2	569.7
120°	760.6	696.0	636.8	617.1
122.5°	793.6	730.4	675.5	667.3
125°	843.1	778.5	731.9	742.6
127.5°	883.3	824.1	794.6	818.7
130°	907.7	855.6	837.7	871.8
132.5°	929.2	888.6	880.7	927.7
135°	961.5	938.1	945.3	1009.9
137.5°	999.9	990.9	1014.9	1096.4
140°	1024.2	1029.6	1063.7	1155.2
142.5°	1057.3	1069.8	1113.9	1211.2
145°	1108.6	1135.5	1192.9	1289.7
147.5°	1166.7	1201.5	1272.5	1371.9
150°	1205.4	1250.3	1325.6	1420.7
152.5°	1249.9	1296.2	1371.5	1468.0
155°	1318.4	1370.4	1449.4	1531.9
157.5°	1388.4	1441.5	1516.8	1588.9
160°	1431.4	1488.8	1557.0	1623.4
162.5°	1480.2	1533.3	1592.9	1652.1
165°	1551.6	1594.7	1643.1	1693.3
167.5°	1611.5	1647.4	1685.4	1724.5
170°	1650.3	1679.0	1711.3	1741.8
172.5°	1683.3	1706.2	1729.9	1756.1
175°	1727.4	1740.0	1754.3	1770.5
177.5°	1761.5	1765.8	1770.1	1777.3
180°	1775.8	1775.8	1775.8	1775.8

TEST NUMBER: P1428643

CATALOG NUMBER: SQ2W-WBN-K-125U-100D-L940-UNV-STD-W-WM-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.76	3.43	3.78	4.43	5.76	2.38	3.06	3.40	4.06	5.38
	3H	3.99	4.58	5.01	5.59	6.94	3.59	4.19	4.62	5.20	6.54
	4H	4.50	5.06	5.54	6.08	7.43	4.10	4.67	5.14	5.68	7.03
	6H	4.85	5.37	5.90	6.39	7.75	4.43	4.95	5.48	5.97	7.33
	8H	5.00	5.49	6.05	6.52	7.88	4.57	5.06	5.62	6.09	7.45
	12H	5.09	5.55	6.14	6.58	7.96	4.64	5.10	5.69	6.13	7.51
4H	2H	3.08	3.64	4.12	4.65	6.01	2.77	3.33	3.81	4.34	5.70
	3H	4.57	5.04	5.62	6.08	7.45	4.23	4.69	5.28	5.74	7.10
	4H	5.22	5.64	6.27	6.68	8.06	4.86	5.29	5.92	6.32	7.71
	6H	5.70	6.07	6.77	7.12	8.51	5.32	5.68	6.38	6.74	8.12
	8H	5.91	6.25	6.98	7.30	8.70	5.51	5.85	6.57	6.90	8.29
	12H	6.05	6.35	7.13	7.42	8.82	5.62	5.92	6.69	6.98	8.38
8H	4H	5.38	5.72	6.44	6.76	8.16	5.06	5.40	6.12	6.45	7.84
	6H	6.01	6.29	7.10	7.38	8.77	5.65	5.93	6.74	7.02	8.41
	8H	6.33	6.57	7.42	7.65	9.06	5.94	6.18	7.03	7.26	8.67
	12H	6.56	6.77	7.65	7.84	9.29	6.14	6.35	7.23	7.42	8.88
12H	4H	5.35	5.66	6.43	6.72	8.12	5.05	5.35	6.12	6.41	7.81
	6H	6.05	6.29	7.14	7.36	8.78	5.70	5.94	6.79	7.02	8.43
	8H	6.39	6.60	7.49	7.67	9.13	6.02	6.23	7.11	7.30	8.76