

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709376

Luminaire Tested: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

Issue Date: 3/5/2020

Test Information

Test Method: LM-79-2019
Report Number: P709376
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-4, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6868.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709376
CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				
1	98	95	92	89	90	87	85	82	73	71	70	60	59	58	49	48	47	42				
2	91	85	80	75	84	78	74	70	66	63	61	55	53	51	45	44	43	38				
3	84	76	70	65	77	71	65	61	60	56	53	50	48	46	42	40	38	34				
4	78	69	62	56	72	64	58	53	55	50	47	46	43	41	38	36	35	31				
5	72	62	55	50	67	58	52	47	50	45	42	42	39	36	35	33	31	28				
6	67	56	49	44	62	53	46	42	46	41	37	39	35	33	33	30	28	26				
7	62	51	44	39	58	48	42	37	42	37	33	36	32	30	30	28	26	23				
8	58	47	40	35	54	44	38	34	39	34	30	33	30	27	28	26	24	22				
9	54	43	36	32	50	41	35	30	36	31	28	31	27	25	26	24	22	20				
10	51	40	33	29	47	38	32	28	33	28	25	29	25	23	25	22	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	32411	32411	32411	32411	32411
5°	32692	32383	32707	32383	32692
10°	33023	32798	33037	32798	33023
15°	32991	33230	33588	33230	32991
20°	32459	33032	33747	33032	32459
25°	31545	32177	33054	32177	31545
30°	29496	30512	31362	30512	29496
35°	26613	27609	28206	27609	26613
40°	21905	22736	23123	22736	21905
45°	13579	16373	14458	16373	13579
50°	5172	8961	5657	8961	5172
55°	2764	4156	2790	4156	2764
60°	1182	2020	1305	2020	1182
65°	1104	1238	1177	1238	1104
70°	1090	1175	1138	1175	1090
75°	1023	1135	1142	1135	1023
80°	986	1083	1069	1083	986
85°	889	908	1074	908	889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 50°
 Vertical Angle: 45°
 Luminance: 16459 cd/sqm

TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	2.8
10°-20°	561.2	8.2
20°-30°	829.8	12.1
30°-40°	858.6	12.5
40°-50°	516.4	7.5
50°-60°	123.5	1.8
60°-70°	33.8	0.5
70°-80°	18.9	0.3
80°-90°	11.3	0.2
90°-100°	101.4	1.5
100°-110°	296.2	4.3
110°-120°	483.0	7.0
120°-130°	612.9	8.9
130°-140°	655.7	9.5
140°-150°	612.2	8.9
150°-160°	503.7	7.3
160°-170°	337.8	4.9
170°-180°	120.0	1.7
0°-30°	1583.0	23.0
0°-40°	2441.5	35.5
0°-60°	3081.4	44.9
0°-90°	3145.4	45.8
90°-120°	880.5	12.8
90°-150°	2761.2	40.2
90°-180°	3723.0	54.2
0°-180°	6868.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2007	2007	2007	2007	2007	
5°	2017	1998	2018	1998	2017	192
15°	1974	1988	2009	1988	1974	554
25°	1771	1806	1855	1806	1771	807
35°	1350	1401	1431	1401	1350	830
45°	595	717	633	717	595	454
55°	98	148	99	148	98	95
65°	29	32	31	32	29	29
75°	16	18	18	18	16	17
85°	5	5	6	5	5	6
90°	27	24	4	35	61	13
95°	30	38	39	131	174	49
105°	309	225	188	337	417	283
115°	502	499	359	534	614	495
125°	787	765	532	668	755	701
135°	1038	984	723	749	836	794
145°	1196	1154	927	796	854	748
155°	1301	1267	1100	905	884	599
165°	1354	1321	1216	1062	1020	382
175°	1323	1306	1272	1215	1197	127
180°	1274	1274	1274	1274	1274	

TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4
2.5°	2009.0	2010.7	2012.4	2007.2	1999.6	1999.5	2006.7	2012.6	2015.0	2017.4	2015.0
5°	2017.1	2018.3	2019.6	2011.0	1999.0	1997.1	2005.2	2012.0	2015.0	2018.0	2015.0
7.5°	2014.9	2016.9	2018.9	2012.6	2003.5	2002.1	2008.3	2013.3	2014.6	2015.9	2014.6
10°	2014.2	2015.5	2016.7	2010.0	2000.6	2000.4	2009.4	2016.0	2015.6	2015.1	2015.6
12.5°	2002.6	2005.6	2008.6	2003.8	1996.5	1999.3	2012.4	2021.4	2017.9	2014.4	2017.9
15°	1973.7	1978.0	1982.3	1983.4	1983.4	1992.6	2011.0	2023.0	2016.2	2009.4	2016.2
17.5°	1924.5	1929.7	1934.9	1941.2	1947.7	1963.3	1987.9	2004.2	1996.1	1988.0	1996.1
20°	1889.1	1891.2	1893.3	1901.9	1912.6	1932.3	1960.9	1980.4	1972.3	1964.1	1972.3
22.5°	1842.9	1846.4	1849.9	1859.6	1871.3	1892.5	1923.2	1944.0	1935.2	1926.4	1935.2
25°	1770.7	1775.4	1780.1	1787.7	1796.3	1816.1	1847.4	1869.1	1862.2	1855.4	1862.2
27.5°	1666.8	1673.3	1679.8	1688.7	1698.5	1718.0	1747.2	1768.2	1764.5	1760.7	1764.5
30°	1582.1	1592.3	1602.6	1614.8	1627.6	1645.6	1668.7	1685.6	1683.9	1682.2	1683.9
32.5°	1501.2	1509.5	1517.7	1528.8	1541.0	1557.2	1577.6	1592.4	1590.7	1589.0	1590.7
35°	1350.2	1358.7	1367.3	1380.0	1394.1	1407.4	1419.8	1429.3	1430.1	1431.0	1430.1
37.5°	1169.4	1178.1	1186.7	1197.2	1208.3	1218.8	1228.6	1235.7	1234.5	1233.3	1234.5
40°	1039.3	1041.5	1043.6	1056.3	1072.6	1084.8	1092.9	1098.8	1097.9	1097.1	1097.9
42.5°	883.8	893.8	903.8	915.7	928.2	940.0	951.2	956.4	943.6	930.8	943.6
45°	594.7	635.8	676.8	698.3	713.3	720.8	720.8	711.1	672.1	633.2	672.1
47.5°	299.1	349.0	398.8	444.7	489.1	499.4	475.3	446.2	401.9	357.6	401.9
50°	205.9	222.6	239.3	289.7	351.3	362.2	322.4	285.1	255.1	225.2	255.1
52.5°	151.3	160.1	168.9	210.1	262.1	267.2	225.4	190.2	175.0	159.7	175.0
55°	98.2	101.6	105.0	123.5	147.0	148.3	127.3	110.2	104.7	99.1	104.7
57.5°	59.7	65.1	70.4	77.9	86.2	86.2	77.9	70.4	64.6	58.9	64.6
60°	36.6	41.3	46.0	53.6	62.1	63.0	56.1	49.8	45.1	40.4	45.1
62.5°	33.5	35.1	36.7	42.3	49.1	49.6	43.8	39.0	37.0	35.0	37.0
65°	28.9	29.7	30.6	31.4	32.3	32.5	32.1	31.7	31.2	30.8	31.2
67.5°	25.4	26.2	26.9	27.2	27.3	27.5	27.8	28.0	27.6	27.1	27.6
70°	23.1	23.5	24.0	24.4	24.8	25.0	25.0	24.9	24.5	24.1	24.5
72.5°	20.0	20.8	21.6	21.8	21.9	22.1	22.5	22.6	22.2	21.7	22.2
75°	16.4	16.8	17.2	17.6	18.1	18.3	18.3	18.3	18.3	18.3	18.3
77.5°	12.9	13.3	13.8	13.9	13.9	14.1	14.5	14.7	14.3	13.9	14.3
80°	10.6	11.0	11.4	11.5	11.5	11.8	12.2	12.4	12.0	11.5	12.0
82.5°	8.3	8.7	9.1	9.2	9.2	9.3	9.4	9.4	9.3	9.2	9.3
85°	4.8	4.8	4.8	4.8	4.8	5.0	5.5	5.8	5.8	5.8	5.8
87.5°	6.9	7.1	7.1	6.5	6.5	6.5	6.1	5.5	3.8	2.3	3.6
90°	26.9	27.9	27.9	25.0	25.0	24.0	20.2	16.4	9.6	3.8	8.7
92.5°	33.1	32.5	32.5	31.2	29.6	27.1	22.5	21.7	23.5	14.6	24.8
95°	29.8	29.8	28.9	28.9	33.7	42.3	62.5	68.3	44.2	39.4	56.7
97.5°	68.3	72.7	81.0	93.5	114.8	122.5	113.3	85.4	80.8	77.9	103.7
100°	129.8	140.4	151.0	163.5	189.5	154.8	120.2	115.4	107.7	108.7	137.5
102.5°	226.8	227.4	231.8	236.6	186.4	164.9	159.5	153.1	140.8	141.0	170.6
105°	308.7	288.5	252.0	227.0	223.1	227.0	227.0	212.6	187.6	188.5	219.3
107.5°	298.0	295.7	297.2	298.2	304.3	305.7	297.4	271.4	245.6	240.3	271.4
110°	351.1	351.1	354.9	355.9	363.6	358.8	348.2	314.5	281.8	274.1	303.0

TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	408.8	409.5	411.1	415.9	419.7	412.6	395.9	359.1	321.8	306.4	334.5
115°	502.1	501.1	501.1	504.9	503.0	495.3	470.3	428.0	379.9	358.8	382.8
117.5°	590.7	585.9	587.1	585.5	588.4	573.0	543.6	491.9	440.3	410.9	428.6
120°	649.2	644.4	646.3	646.3	645.4	626.1	590.5	539.6	481.9	446.3	457.8
122.5°	706.2	702.9	703.3	701.0	698.5	680.0	638.2	585.0	521.9	477.8	484.7
125°	786.8	788.7	782.9	782.9	774.2	756.0	711.7	655.0	586.7	531.9	528.0
127.5°	862.9	865.6	859.8	856.4	849.7	822.1	781.7	724.8	651.5	587.1	571.7
130°	913.7	915.6	913.7	904.1	893.5	867.5	827.1	773.3	695.4	627.1	600.2
132.5°	964.5	968.7	959.1	951.8	935.8	909.1	869.5	817.1	739.2	664.8	630.9
135°	1037.8	1034.9	1025.3	1013.7	997.4	971.4	934.9	880.0	806.0	723.3	680.0
137.5°	1092.0	1092.4	1083.0	1070.3	1053.6	1029.3	994.7	943.1	867.7	786.8	731.2
140°	1128.2	1126.3	1117.6	1104.1	1089.7	1064.7	1033.9	983.9	907.0	829.1	766.6
142.5°	1153.6	1155.5	1148.4	1137.2	1120.5	1098.6	1067.0	1017.0	949.3	868.3	802.7
145°	1196.5	1196.5	1189.7	1182.1	1166.7	1141.7	1117.6	1068.6	1004.1	927.2	855.0
147.5°	1231.5	1232.1	1227.8	1218.8	1203.8	1182.2	1158.0	1114.1	1054.3	983.2	913.1
150°	1252.3	1255.1	1249.4	1242.6	1229.2	1206.1	1184.9	1142.6	1085.9	1022.4	949.3
152.5°	1272.3	1275.9	1270.9	1262.6	1249.2	1226.1	1208.0	1166.5	1113.6	1054.7	984.7
155°	1301.3	1304.2	1300.4	1292.7	1277.3	1256.1	1239.8	1201.3	1154.2	1100.3	1037.8
157.5°	1322.9	1327.5	1321.9	1315.0	1298.4	1279.8	1264.4	1228.6	1186.5	1141.5	1085.7
160°	1335.9	1339.8	1335.0	1327.3	1310.0	1293.6	1278.2	1245.5	1208.0	1163.8	1115.7
162.5°	1344.4	1350.6	1345.0	1336.5	1318.4	1302.9	1289.8	1258.6	1224.2	1186.9	1142.6
165°	1354.2	1359.0	1354.2	1345.6	1327.3	1313.8	1303.2	1276.3	1246.5	1215.7	1178.2
167.5°	1354.2	1360.2	1355.6	1348.1	1328.8	1318.4	1310.4	1287.8	1263.0	1237.4	1209.6
170°	1350.4	1357.1	1353.3	1346.5	1327.3	1317.7	1311.9	1291.7	1271.5	1251.3	1227.3
172.5°	1343.4	1350.2	1345.6	1339.6	1320.4	1313.8	1310.4	1294.0	1276.9	1260.5	1241.1
175°	1323.4	1332.1	1329.2	1322.5	1308.0	1303.2	1304.2	1292.7	1281.1	1271.5	1259.0
177.5°	1296.7	1302.9	1299.8	1298.2	1286.7	1285.2	1290.5	1285.2	1279.8	1275.9	1270.5
180°	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4

TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4	2007.4
2.5°	2012.6	2006.7	1999.5	1999.6	2007.2	2012.4	2010.7	2009.0
5°	2012.0	2005.2	1997.1	1999.0	2011.0	2019.6	2018.3	2017.1
7.5°	2013.3	2008.3	2002.1	2003.5	2012.6	2018.9	2016.9	2014.9
10°	2016.0	2009.4	2000.4	2000.6	2010.0	2016.7	2015.5	2014.2
12.5°	2021.4	2012.4	1999.3	1996.5	2003.8	2008.6	2005.6	2002.6
15°	2023.0	2011.0	1992.6	1983.4	1983.4	1982.3	1978.0	1973.7
17.5°	2004.2	1987.9	1963.3	1947.7	1941.2	1934.9	1929.7	1924.5
20°	1980.4	1960.9	1932.3	1912.6	1901.9	1893.3	1891.2	1889.1
22.5°	1944.0	1923.2	1892.5	1871.3	1859.6	1849.9	1846.4	1842.9
25°	1869.1	1847.4	1816.1	1796.3	1787.7	1780.1	1775.4	1770.7
27.5°	1768.2	1747.2	1718.0	1698.5	1688.7	1679.8	1673.3	1666.8
30°	1685.6	1668.7	1645.6	1627.6	1614.8	1602.6	1592.3	1582.1
32.5°	1592.4	1577.6	1557.2	1541.0	1528.8	1517.7	1509.5	1501.2
35°	1429.3	1419.8	1407.4	1394.1	1380.0	1367.3	1358.7	1350.2
37.5°	1235.7	1228.6	1218.8	1208.3	1197.2	1186.7	1178.1	1169.4
40°	1098.8	1092.9	1084.8	1072.6	1056.3	1043.6	1041.5	1039.3
42.5°	956.4	951.2	940.0	928.2	915.7	903.8	893.8	883.8
45°	711.1	720.8	720.8	713.3	698.3	676.8	635.8	594.7
47.5°	446.2	475.3	499.4	489.1	444.7	398.8	349.0	299.1
50°	285.1	322.4	362.2	351.3	289.7	239.3	222.6	205.9
52.5°	190.2	225.4	267.2	262.1	210.1	168.9	160.1	151.3
55°	110.2	127.3	148.3	147.0	123.5	105.0	101.6	98.2
57.5°	70.4	77.9	86.2	86.2	77.9	70.4	65.1	59.7
60°	49.8	56.1	63.0	62.1	53.6	46.0	41.3	36.6
62.5°	39.0	43.8	49.6	49.1	42.3	36.7	35.1	33.5
65°	31.7	32.1	32.5	32.3	31.4	30.6	29.7	28.9
67.5°	28.0	27.8	27.5	27.3	27.2	26.9	26.2	25.4
70°	24.9	25.0	25.0	24.8	24.4	24.0	23.5	23.1
72.5°	22.6	22.5	22.1	21.9	21.8	21.6	20.8	20.0
75°	18.3	18.3	18.3	18.1	17.6	17.2	16.8	16.4
77.5°	14.7	14.5	14.1	13.9	13.9	13.8	13.3	12.9
80°	12.4	12.2	11.8	11.5	11.5	11.4	11.0	10.6
82.5°	9.4	9.4	9.3	9.2	9.2	9.1	8.7	8.3
85°	5.8	5.5	5.0	4.8	4.8	4.8	4.8	4.8
87.5°	5.3	6.5	7.7	9.6	11.2	12.3	12.9	13.7
90°	15.4	22.1	29.8	40.4	48.1	53.9	56.7	60.6
92.5°	35.4	49.1	59.8	72.7	86.6	93.9	98.3	99.8
95°	81.8	99.1	121.2	140.4	157.7	169.3	176.0	174.1
97.5°	126.8	159.1	184.3	206.6	226.8	240.6	251.6	250.6
100°	164.5	191.4	225.1	252.0	272.2	287.6	300.1	303.0
102.5°	202.2	227.6	264.3	294.3	317.6	334.5	343.9	353.0
105°	254.9	290.5	318.4	354.9	378.9	401.1	407.8	417.4
107.5°	310.1	349.1	380.1	410.5	439.0	457.4	471.9	479.6
110°	346.2	383.8	423.2	452.0	479.0	498.2	512.6	520.3

TEST NUMBER: P709376

CATALOG NUMBER: DL2W-WB-M-100U-075D-930-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	378.6	419.9	462.4	494.4	519.0	541.3	553.4	561.9
115°	426.1	471.3	513.6	555.0	579.0	596.3	606.9	613.6
117.5°	469.5	516.7	557.8	599.6	629.6	642.3	646.3	651.3
120°	497.2	544.4	584.8	624.2	658.8	672.3	681.0	686.7
122.5°	521.9	569.0	611.7	648.8	681.9	700.8	711.0	718.3
125°	559.8	604.0	648.3	687.7	714.6	734.8	748.3	755.0
127.5°	591.7	634.2	679.6	717.5	746.5	767.9	779.1	784.3
130°	615.6	651.1	697.3	736.7	766.6	788.7	798.3	801.2
132.5°	638.6	667.3	711.2	752.9	782.7	802.5	812.9	815.8
135°	674.2	690.6	729.0	769.4	800.2	820.4	830.0	835.8
137.5°	713.5	717.7	741.5	781.2	812.9	832.3	842.0	845.4
140°	739.6	737.7	753.1	785.8	817.5	837.7	847.3	849.3
142.5°	767.3	759.2	764.6	791.2	819.8	839.3	849.7	852.3
145°	813.7	796.4	789.6	803.1	824.3	840.6	852.2	854.1
147.5°	863.5	835.6	820.4	822.9	834.5	846.0	855.0	855.2
150°	897.4	865.6	843.5	840.6	844.5	852.2	858.9	859.8
152.5°	929.7	895.6	868.9	861.4	859.1	863.7	866.6	866.8
155°	983.9	947.4	912.7	896.4	889.7	887.7	886.8	883.9
157.5°	1035.3	996.4	958.1	940.4	929.7	923.7	919.3	916.2
160°	1067.6	1027.2	989.7	970.5	958.9	952.2	945.4	941.6
162.5°	1100.7	1062.6	1024.3	1002.0	990.5	983.0	975.5	969.3
165°	1144.5	1112.8	1074.3	1050.3	1035.9	1031.0	1024.3	1019.5
167.5°	1183.0	1158.4	1124.0	1101.3	1090.3	1081.4	1074.7	1066.1
170°	1206.1	1186.9	1153.2	1132.0	1127.2	1117.6	1110.9	1102.2
172.5°	1224.6	1209.2	1182.4	1165.1	1161.1	1155.3	1150.1	1143.0
175°	1249.4	1241.7	1221.5	1209.0	1209.0	1207.1	1206.1	1197.4
177.5°	1266.7	1262.8	1251.3	1245.1	1250.5	1252.1	1248.2	1241.3
180°	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4	1274.4

(END OF REPORT)