

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709329

Luminaire Tested: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

Issue Date: 3/5/2020


Test Information

Test Method: LM-79-2019
Report Number: P709329
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-1, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4235.1 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77		
1	107	103	100	97	102	99	96	94	90	88	87	83	81	80	76	75	74	70		
2	100	94	89	85	95	90	85	82	83	79	77	76	74	72	70	69	67	64		
3	93	85	79	74	89	82	77	72	76	72	68	70	67	64	65	63	60	58		
4	87	78	71	66	83	75	69	64	70	65	61	65	61	58	60	57	55	52		
5	81	71	64	59	77	69	62	57	64	59	55	60	56	52	56	53	50	48		
6	76	65	58	53	72	63	56	52	59	54	50	55	51	48	52	48	45	43		
7	71	60	53	48	68	58	52	47	55	49	45	51	47	43	48	44	42	40		
8	66	55	48	43	64	54	47	43	51	45	41	48	43	40	45	41	38	36		
9	62	51	44	40	60	50	43	39	47	42	38	44	40	36	42	38	35	33		
10	59	48	41	36	56	46	40	36	44	38	35	42	37	34	39	35	32	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	33700	33700	33700	33700	33700
5°	33990	33669	34007	33669	33990
10°	34334	34101	34351	34101	34334
15°	34302	34550	34922	34550	34302
20°	33747	34343	35087	34343	33747
25°	32797	33456	34367	33456	32797
30°	30667	31725	32608	31725	30667
35°	27670	28706	29325	28706	27670
40°	22776	23639	24040	23639	22776
45°	14118	17022	15034	17022	14118
50°	5378	9315	5880	9315	5378
55°	2874	4322	2902	4322	2874
60°	1227	2101	1356	2101	1227
65°	1146	1287	1223	1287	1146
70°	1133	1223	1180	1223	1133
75°	1061	1179	1185	1179	1061
80°	1023	1125	1116	1125	1023
85°	926	945	1112	945	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 50°
 Vertical Angle: 45°
 Luminance: 17112 cd/sqm

TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.6	4.7
10°-20°	583.5	13.8
20°-30°	862.8	20.4
30°-40°	892.7	21.1
40°-50°	536.9	12.7
50°-60°	128.4	3.0
60°-70°	35.1	0.8
70°-80°	19.6	0.5
80°-90°	7.6	0.2
90°-100°	26.5	0.6
100°-110°	77.1	1.8
110°-120°	125.7	3.0
120°-130°	159.4	3.8
130°-140°	170.6	4.0
140°-150°	159.3	3.8
150°-160°	131.1	3.1
160°-170°	88.0	2.1
170°-180°	31.2	0.7
0°-30°	1645.8	38.9
0°-40°	2538.5	59.9
0°-60°	3203.8	75.6
0°-90°	3266.2	77.1
90°-120°	229.2	5.4
90°-150°	718.6	17.0
90°-180°	969.0	22.9
0°-180°	4235.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2087	2087	2087	2087	2087	
5°	2097	2077	2098	2077	2097	200
15°	2052	2067	2089	2067	2052	577
25°	1841	1878	1929	1878	1841	840
35°	1404	1456	1488	1456	1404	863
45°	618	746	658	746	618	473
55°	102	154	103	154	102	99
65°	30	34	32	34	30	30
75°	17	19	19	19	17	18
85°	5	5	6	5	5	6
90°	7	6	1	9	16	4
95°	8	10	11	34	46	13
105°	80	59	49	88	109	73
115°	130	130	94	139	161	128
125°	205	200	139	174	196	182
135°	270	256	188	194	217	207
145°	311	300	241	207	222	194
155°	339	330	286	236	230	156
165°	353	344	316	276	265	100
175°	345	340	331	316	312	33
180°	332	332	332	332	332	

TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2
2.5°	2088.8	2090.5	2092.3	2086.9	2079.1	2078.9	2086.4	2092.6	2095.1	2097.6	2095.1
5°	2097.2	2098.5	2099.8	2090.8	2078.4	2076.4	2084.8	2091.9	2095.1	2098.2	2095.1
7.5°	2095.0	2097.0	2099.1	2092.5	2083.1	2081.6	2088.1	2093.3	2094.6	2096.0	2094.6
10°	2094.2	2095.5	2096.8	2089.8	2080.1	2079.8	2089.2	2096.1	2095.6	2095.2	2095.6
12.5°	2082.2	2085.3	2088.4	2083.4	2075.8	2078.8	2092.4	2101.7	2098.0	2094.4	2098.0
15°	2052.1	2056.6	2061.0	2062.2	2062.2	2071.7	2090.8	2103.4	2096.3	2089.2	2096.3
17.5°	2000.9	2006.3	2011.8	2018.3	2025.1	2041.3	2066.8	2083.9	2075.4	2067.0	2075.4
20°	1964.1	1966.3	1968.5	1977.4	1988.6	2009.0	2038.8	2059.0	2050.6	2042.1	2050.6
22.5°	1916.1	1919.7	1923.4	1933.4	1945.6	1967.7	1999.6	2021.2	2012.1	2002.9	2012.1
25°	1841.0	1845.9	1850.8	1858.7	1867.6	1888.3	1920.7	1943.3	1936.2	1929.1	1936.2
27.5°	1733.0	1739.7	1746.5	1755.8	1765.9	1786.2	1816.6	1838.4	1834.5	1830.6	1834.5
30°	1644.9	1655.6	1666.3	1678.9	1692.3	1711.0	1735.0	1752.5	1750.8	1749.0	1750.8
32.5°	1560.9	1569.4	1577.9	1589.6	1602.2	1619.1	1640.2	1655.7	1653.9	1652.1	1653.9
35°	1403.8	1412.7	1421.6	1434.8	1449.5	1463.3	1476.2	1486.1	1486.9	1487.8	1486.9
37.5°	1215.9	1224.9	1233.8	1244.8	1256.3	1267.2	1277.4	1284.8	1283.6	1282.3	1283.6
40°	1080.6	1082.8	1085.1	1098.3	1115.2	1127.9	1136.3	1142.4	1141.5	1140.6	1141.5
42.5°	918.9	929.3	939.7	952.1	965.0	977.4	989.0	994.4	981.1	967.7	981.1
45°	618.3	661.0	703.7	726.1	741.6	749.4	749.4	739.3	698.8	658.4	698.8
47.5°	311.0	362.8	414.7	462.3	508.6	519.2	494.2	463.9	417.9	371.8	417.9
50°	214.1	231.5	248.8	301.2	365.2	376.5	335.2	296.4	265.3	234.1	265.3
52.5°	157.3	166.4	175.6	218.5	272.5	277.8	234.3	197.8	181.9	166.1	181.9
55°	102.1	105.6	109.2	128.4	152.9	154.2	132.4	114.6	108.8	103.1	108.8
57.5°	62.0	67.6	73.2	81.0	89.6	89.6	81.0	73.2	67.2	61.2	67.2
60°	38.0	42.9	47.8	55.7	64.6	65.5	58.4	51.8	46.9	42.0	46.9
62.5°	34.8	36.5	38.2	44.0	51.1	51.6	45.6	40.5	38.5	36.4	38.5
65°	30.0	30.9	31.8	32.7	33.6	33.8	33.4	32.9	32.5	32.0	32.5
67.5°	26.4	27.2	28.0	28.3	28.4	28.6	28.9	29.1	28.7	28.2	28.7
70°	24.0	24.5	24.9	25.3	25.8	26.0	26.0	25.9	25.5	25.0	25.5
72.5°	20.8	21.6	22.4	22.7	22.8	23.0	23.3	23.5	23.1	22.6	23.1
75°	17.0	17.5	17.9	18.3	18.8	19.0	19.0	19.0	19.0	19.0	19.0
77.5°	13.4	13.9	14.3	14.4	14.4	14.6	15.1	15.3	14.9	14.4	14.9
80°	11.0	11.5	11.9	12.0	12.0	12.2	12.7	12.9	12.5	12.0	12.5
82.5°	8.6	9.0	9.5	9.6	9.6	9.6	9.7	9.8	9.7	9.6	9.7
85°	5.0	5.0	5.0	5.0	5.0	5.2	5.7	6.0	6.0	6.0	6.0
87.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.3	3.1	2.6	1.8	2.4
90°	7.0	7.0	7.0	7.0	7.0	6.0	6.0	4.0	3.0	1.0	2.0
92.5°	8.6	8.6	8.6	8.6	7.8	6.8	6.0	5.6	6.2	3.4	6.8
95°	8.0	8.0	8.0	8.0	9.0	12.0	16.0	17.0	12.0	11.0	15.0
97.5°	18.2	19.4	20.6	24.4	30.6	31.8	30.2	21.2	21.0	20.0	27.0
100°	35.0	37.0	39.0	42.0	49.0	39.0	31.0	30.0	29.0	28.0	35.0
102.5°	58.2	59.4	62.2	62.0	48.2	43.0	41.4	39.6	37.0	36.0	43.8
105°	80.0	75.0	66.0	58.0	59.0	59.0	59.0	54.0	50.0	49.0	57.0
107.5°	76.8	75.8	76.8	78.6	79.6	79.4	77.0	70.6	63.6	62.2	70.2
110°	92.0	91.0	92.0	93.0	94.0	93.0	89.0	81.0	74.0	71.0	79.0

TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	105.6	106.2	107.2	108.2	108.4	107.4	102.6	93.0	83.6	79.8	87.0
115°	130.0	130.0	130.0	131.0	131.0	129.0	122.0	111.0	99.0	94.0	99.0
117.5°	153.6	152.8	152.8	152.8	152.8	149.4	141.2	128.0	114.6	107.2	111.8
120°	168.0	168.0	168.0	168.0	168.0	163.0	154.0	140.0	125.0	116.0	119.0
122.5°	183.2	182.4	183.2	182.4	181.6	176.6	166.0	152.0	136.2	124.8	126.2
125°	205.0	205.0	203.0	203.0	202.0	197.0	185.0	170.0	153.0	139.0	138.0
127.5°	225.2	226.0	223.4	222.4	220.8	213.8	203.0	189.0	169.0	152.6	148.0
130°	238.0	238.0	237.0	236.0	232.0	225.0	215.0	201.0	181.0	163.0	156.0
132.5°	251.6	251.6	250.6	248.0	243.2	237.0	227.0	213.0	192.2	173.4	164.0
135°	270.0	269.0	267.0	265.0	260.0	253.0	244.0	230.0	209.0	188.0	177.0
137.5°	285.0	284.0	282.2	278.4	274.4	267.6	258.6	245.4	225.8	204.6	189.4
140°	293.0	292.0	291.0	288.0	284.0	278.0	269.0	255.0	237.0	215.0	199.0
142.5°	300.2	300.0	298.2	296.0	292.0	285.2	277.8	264.6	246.6	226.2	208.6
145°	311.0	311.0	310.0	308.0	304.0	297.0	291.0	279.0	261.0	241.0	223.0
147.5°	320.4	320.6	319.4	317.4	313.6	307.6	301.8	289.8	274.2	256.2	237.4
150°	326.0	327.0	325.0	323.0	320.0	314.0	309.0	297.0	283.0	265.0	247.0
152.5°	330.8	332.6	330.6	329.4	325.6	319.6	314.6	303.4	290.2	274.6	256.6
155°	339.0	340.0	338.0	337.0	332.0	327.0	323.0	312.0	300.0	286.0	271.0
157.5°	344.8	345.8	344.8	342.8	337.8	333.0	329.0	320.0	309.2	297.6	283.0
160°	348.0	349.0	348.0	346.0	341.0	337.0	333.0	324.0	314.0	304.0	291.0
162.5°	350.4	351.4	350.4	348.4	343.4	339.4	336.2	328.0	318.8	308.8	297.4
165°	353.0	354.0	353.0	350.0	346.0	342.0	339.0	332.0	324.0	316.0	308.0
167.5°	352.8	354.8	353.0	351.8	346.0	344.0	341.2	335.2	328.6	322.0	314.4
170°	352.0	354.0	353.0	351.0	346.0	344.0	342.0	336.0	331.0	326.0	320.0
172.5°	350.4	351.6	350.6	349.4	344.4	342.4	341.2	336.8	332.6	328.4	323.2
175°	345.0	347.0	346.0	345.0	340.0	339.0	340.0	336.0	333.0	331.0	328.0
177.5°	337.6	339.2	338.4	337.6	335.2	334.4	336.0	334.4	332.8	332.0	330.4
180°	332.0	332.0	332.0	332.0	332.0	332.0	332.0	332.0	332.0	332.0	332.0

TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2	2087.2
2.5°	2092.6	2086.4	2078.9	2079.1	2086.9	2092.3	2090.5	2088.8
5°	2091.9	2084.8	2076.4	2078.4	2090.8	2099.8	2098.5	2097.2
7.5°	2093.3	2088.1	2081.6	2083.1	2092.5	2099.1	2097.0	2095.0
10°	2096.1	2089.2	2079.8	2080.1	2089.8	2096.8	2095.5	2094.2
12.5°	2101.7	2092.4	2078.8	2075.8	2083.4	2088.4	2085.3	2082.2
15°	2103.4	2090.8	2071.7	2062.2	2062.2	2061.0	2056.6	2052.1
17.5°	2083.9	2066.8	2041.3	2025.1	2018.3	2011.8	2006.3	2000.9
20°	2059.0	2038.8	2009.0	1988.6	1977.4	1968.5	1966.3	1964.1
22.5°	2021.2	1999.6	1967.7	1945.6	1933.4	1923.4	1919.7	1916.1
25°	1943.3	1920.7	1888.3	1867.6	1858.7	1850.8	1845.9	1841.0
27.5°	1838.4	1816.6	1786.2	1765.9	1755.8	1746.5	1739.7	1733.0
30°	1752.5	1735.0	1711.0	1692.3	1678.9	1666.3	1655.6	1644.9
32.5°	1655.7	1640.2	1619.1	1602.2	1589.6	1577.9	1569.4	1560.9
35°	1486.1	1476.2	1463.3	1449.5	1434.8	1421.6	1412.7	1403.8
37.5°	1284.8	1277.4	1267.2	1256.3	1244.8	1233.8	1224.9	1215.9
40°	1142.4	1136.3	1127.9	1115.2	1098.3	1085.1	1082.8	1080.6
42.5°	994.4	989.0	977.4	965.0	952.1	939.7	929.3	918.9
45°	739.3	749.4	749.4	741.6	726.1	703.7	661.0	618.3
47.5°	463.9	494.2	519.2	508.6	462.3	414.7	362.8	311.0
50°	296.4	335.2	376.5	365.2	301.2	248.8	231.5	214.1
52.5°	197.8	234.3	277.8	272.5	218.5	175.6	166.4	157.3
55°	114.6	132.4	154.2	152.9	128.4	109.2	105.6	102.1
57.5°	73.2	81.0	89.6	89.6	81.0	73.2	67.6	62.0
60°	51.8	58.4	65.5	64.6	55.7	47.8	42.9	38.0
62.5°	40.5	45.6	51.6	51.1	44.0	38.2	36.5	34.8
65°	32.9	33.4	33.8	33.6	32.7	31.8	30.9	30.0
67.5°	29.1	28.9	28.6	28.4	28.3	28.0	27.2	26.4
70°	25.9	26.0	26.0	25.8	25.3	24.9	24.5	24.0
72.5°	23.5	23.3	23.0	22.8	22.7	22.4	21.6	20.8
75°	19.0	19.0	19.0	18.8	18.3	17.9	17.5	17.0
77.5°	15.3	15.1	14.6	14.4	14.4	14.3	13.9	13.4
80°	12.9	12.7	12.2	12.0	12.0	11.9	11.5	11.0
82.5°	9.8	9.7	9.6	9.6	9.6	9.5	9.0	8.6
85°	6.0	5.7	5.2	5.0	5.0	5.0	5.0	5.0
87.5°	3.1	3.3	3.4	3.6	4.2	4.4	4.6	4.8
90°	4.0	6.0	8.0	10.0	13.0	14.0	15.0	16.0
92.5°	8.8	12.4	16.0	18.8	22.6	25.2	25.4	26.4
95°	21.0	26.0	31.0	36.0	41.0	45.0	46.0	46.0
97.5°	33.4	41.2	47.8	53.8	59.6	63.0	65.2	67.2
100°	43.0	50.0	59.0	65.0	70.0	75.0	78.0	80.0
102.5°	52.6	59.6	68.6	76.2	83.6	87.0	90.8	92.0
105°	67.0	75.0	84.0	93.0	99.0	104.0	107.0	109.0
107.5°	80.4	90.4	99.0	107.4	113.6	119.6	123.4	124.6
110°	90.0	100.0	111.0	117.0	124.0	130.0	133.0	135.0

TEST NUMBER: P709329

CATALOG NUMBER: DL2W-WB-M-025U-075D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	98.8	109.6	120.6	128.2	135.2	141.2	144.2	146.2
115°	111.0	122.0	133.0	145.0	152.0	156.0	159.0	161.0
117.5°	122.0	134.0	145.0	155.8	163.8	167.0	169.0	170.2
120°	130.0	142.0	153.0	163.0	171.0	175.0	177.0	179.0
122.5°	136.4	148.4	159.4	169.4	177.4	182.2	185.0	186.2
125°	146.0	157.0	169.0	178.0	186.0	192.0	195.0	196.0
127.5°	153.6	165.0	177.0	186.4	194.4	199.2	202.2	204.0
130°	160.0	169.0	181.0	192.0	200.0	204.0	207.0	208.0
132.5°	166.4	173.8	185.0	196.0	204.0	208.8	211.8	212.8
135°	175.0	179.0	189.0	200.0	208.0	213.0	216.0	217.0
137.5°	185.8	187.2	192.8	203.2	211.4	216.4	219.2	220.2
140°	193.0	192.0	196.0	204.0	213.0	218.0	220.0	221.0
142.5°	199.4	197.6	199.2	205.6	213.0	218.0	220.8	221.0
145°	212.0	207.0	205.0	209.0	214.0	219.0	222.0	222.0
147.5°	224.2	218.0	213.4	214.2	216.8	220.4	222.2	222.4
150°	233.0	226.0	219.0	219.0	220.0	222.0	223.0	224.0
152.5°	242.6	234.0	226.2	224.6	224.0	224.4	226.2	225.6
155°	256.0	246.0	237.0	234.0	232.0	231.0	231.0	230.0
157.5°	269.2	260.0	249.2	245.0	241.8	240.0	238.8	237.8
160°	278.0	268.0	258.0	253.0	249.0	248.0	246.0	245.0
162.5°	286.8	276.0	266.8	261.0	257.0	256.0	254.8	253.0
165°	298.0	290.0	279.0	273.0	271.0	268.0	267.0	265.0
167.5°	308.4	301.8	293.0	287.2	283.4	281.4	280.4	278.4
170°	314.0	309.0	301.0	296.0	293.0	291.0	290.0	288.0
172.5°	318.8	314.6	308.2	304.0	301.8	300.6	298.8	297.6
175°	325.0	323.0	317.0	314.0	315.0	314.0	314.0	312.0
177.5°	329.6	328.8	325.6	324.0	326.4	325.6	325.6	323.2
180°	332.0	332.0	332.0	332.0	332.0	332.0	332.0	332.0

(END OF REPORT)