

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709350

Luminaire Tested: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

Issue Date: 3/5/2020

Test Information

Test Method: LM-79-2019
Report Number: P709350
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-3, G3-2104-222-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5087.1 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 41.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	98	94	91	88	89	86	84	81	72	70	68	59	57	56	46	46	45	39
2	90	84	79	74	83	77	73	69	65	62	59	53	51	50	43	42	40	36
3	84	75	69	64	77	70	64	60	59	55	52	49	46	44	40	38	36	32
4	77	68	61	56	71	63	57	52	53	49	46	45	42	39	36	35	33	29
5	72	61	54	49	66	57	51	46	49	44	40	41	38	35	34	32	30	27
6	66	56	48	43	61	52	45	41	44	40	36	38	34	32	31	29	27	24
7	62	51	44	39	57	47	41	37	41	36	33	35	31	29	29	27	25	22
8	58	46	39	35	53	43	37	33	38	33	29	32	29	26	27	24	23	20
9	54	43	36	31	50	40	34	30	35	30	27	30	26	24	25	23	21	19
10	50	39	33	28	47	37	31	27	32	28	24	28	24	22	23	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	22491	22491	22491	22491	22491
5°	22707	22503	22739	22503	22707
10°	22953	22810	23002	22810	22953
15°	23000	23156	23435	23156	23000
20°	22646	23097	23557	23097	22646
25°	22019	22502	23017	22502	22019
30°	20732	21333	21888	21333	20732
35°	18607	19295	19671	19295	18607
40°	15365	15823	16166	15823	15365
45°	9225	11424	10229	11424	9225
50°	3642	6300	3969	6300	3642
55°	1942	2859	1914	2859	1942
60°	840	1426	904	1426	840
65°	764	867	802	867	764
70°	755	807	803	807	755
75°	686	805	749	805	686
80°	651	744	744	744	651
85°	556	741	741	741	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
 Vertical Angle: 45°
 Luminance: 11501 cd/sqm

TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	2.6
10°-20°	391.4	7.7
20°-30°	579.5	11.4
30°-40°	600.3	11.8
40°-50°	360.8	7.1
50°-60°	86.2	1.7
60°-70°	23.5	0.5
70°-80°	13.1	0.3
80°-90°	8.3	0.2
90°-100°	78.8	1.5
100°-110°	229.8	4.5
110°-120°	375.0	7.4
120°-130°	475.8	9.4
130°-140°	509.1	10.0
140°-150°	475.4	9.3
150°-160°	391.2	7.7
160°-170°	262.4	5.2
170°-180°	93.2	1.8
0°-30°	1104.3	21.7
0°-40°	1704.6	33.5
0°-60°	2151.6	42.3
0°-90°	2196.5	43.2
90°-120°	683.5	13.4
90°-150°	2143.9	42.1
90°-180°	2891.0	56.8
0°-180°	5087.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1393	1393	1393	1393	1393	
5°	1401	1388	1403	1388	1401	134
15°	1376	1385	1402	1385	1376	387
25°	1236	1263	1292	1263	1236	565
35°	944	979	998	979	944	582
45°	404	500	448	500	404	318
55°	69	102	68	102	69	67
65°	20	23	21	23	20	20
75°	11	13	12	13	11	12
85°	3	4	4	4	3	4
90°	22	20	3	26	43	10
95°	23	30	31	100	135	39
105°	234	176	146	262	322	219
115°	388	388	280	416	478	384
125°	615	595	414	518	586	545
135°	805	766	563	582	649	617
145°	928	896	719	619	663	580
155°	1008	984	854	702	688	465
165°	1051	1026	944	826	792	297
175°	1029	1013	987	944	929	99
180°	990	990	990	990	990	

TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0
2.5°	1394.6	1396.0	1397.4	1393.5	1387.8	1387.5	1392.5	1396.7	1398.9	1401.0	1398.9
5°	1401.0	1401.9	1402.8	1397.0	1389.0	1387.9	1393.7	1398.6	1400.8	1403.0	1400.8
7.5°	1400.8	1402.1	1403.5	1398.8	1392.1	1391.2	1396.1	1400.2	1401.6	1403.0	1401.6
10°	1400.0	1401.3	1402.7	1398.0	1391.3	1391.3	1398.0	1403.0	1403.0	1403.0	1403.0
12.5°	1393.6	1395.6	1397.7	1394.5	1389.6	1391.8	1400.9	1407.4	1405.6	1403.8	1405.6
15°	1376.0	1379.1	1382.2	1382.7	1382.2	1388.4	1401.3	1410.0	1406.0	1402.0	1406.0
17.5°	1343.6	1347.9	1352.1	1355.8	1359.3	1369.9	1387.7	1399.4	1393.2	1387.0	1393.2
20°	1318.0	1321.6	1325.1	1331.0	1337.7	1350.8	1370.3	1383.4	1377.2	1371.0	1377.2
22.5°	1287.6	1291.5	1295.4	1301.1	1307.4	1321.1	1342.1	1356.2	1349.6	1343.0	1349.6
25°	1236.0	1239.6	1243.1	1249.3	1256.4	1269.8	1289.3	1302.7	1297.3	1292.0	1297.3
27.5°	1168.0	1171.9	1175.8	1181.8	1188.5	1200.2	1217.1	1229.2	1226.8	1224.4	1226.8
30°	1112.0	1117.3	1122.7	1130.3	1138.8	1149.7	1163.0	1173.1	1173.6	1174.0	1173.6
32.5°	1048.8	1055.9	1063.0	1070.9	1079.0	1089.1	1101.4	1110.4	1109.8	1109.2	1109.8
35°	944.0	951.6	959.1	967.0	975.0	982.8	990.3	996.2	997.1	998.0	997.1
37.5°	822.6	825.5	828.5	835.7	844.3	852.6	860.7	866.6	866.0	865.4	866.0
40°	729.0	729.4	729.9	737.0	746.3	755.2	763.7	769.7	768.3	767.0	768.3
42.5°	629.0	630.9	632.7	640.5	650.2	658.2	664.5	666.7	656.9	647.0	656.9
45°	404.0	436.9	469.8	486.3	497.4	503.2	503.7	497.8	472.9	448.0	472.9
47.5°	211.4	243.8	276.3	309.1	342.1	349.8	332.3	311.4	280.3	249.2	280.3
50°	145.0	156.1	167.2	203.0	247.0	254.6	225.7	198.9	178.4	158.0	178.4
52.5°	105.8	112.6	119.5	147.3	182.0	185.1	156.6	132.7	122.5	112.4	122.5
55°	69.0	70.8	72.6	85.0	101.0	102.1	88.3	76.9	72.4	68.0	72.4
57.5°	41.2	44.9	48.7	54.3	60.6	60.8	54.9	49.4	45.5	41.6	45.5
60°	26.0	28.7	31.3	37.0	43.7	44.6	39.7	35.1	31.6	28.0	31.6
62.5°	23.6	24.5	25.4	29.3	34.2	34.5	30.3	26.9	25.9	24.8	25.9
65°	20.0	20.4	20.9	21.7	22.6	22.8	22.3	21.9	21.4	21.0	21.4
67.5°	17.6	18.0	18.5	18.9	19.2	19.4	19.5	19.5	19.0	18.6	19.0
70°	16.0	16.4	16.9	17.0	17.0	17.2	17.7	17.9	17.4	17.0	17.4
72.5°	14.4	14.5	14.6	14.9	15.2	15.4	15.5	15.6	15.5	15.4	15.5
75°	11.0	11.4	11.9	12.3	12.8	13.0	13.0	12.9	12.4	12.0	12.4
77.5°	8.6	9.0	9.5	9.6	9.6	9.8	10.1	10.3	10.0	9.6	10.0
80°	7.0	7.4	7.9	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
82.5°	5.4	5.8	6.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
85°	3.0	3.4	3.9	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	5.2	5.2	5.0	5.1	5.4	5.4	4.8	4.0	3.0	2.2	3.0
90°	22.0	22.0	21.0	20.0	20.0	19.0	16.0	12.0	7.0	3.0	7.0
92.5°	26.0	26.0	25.0	24.8	23.2	21.4	17.6	17.6	17.4	11.0	19.0
95°	23.0	23.0	23.0	23.0	27.0	34.0	50.0	51.0	34.0	31.0	44.0
97.5°	52.6	55.6	62.2	74.0	90.8	94.0	89.0	66.4	63.6	59.2	80.6
100°	107.0	110.0	115.0	130.0	142.0	118.0	93.0	92.0	86.0	84.0	107.0
102.5°	175.8	176.4	179.8	184.4	142.8	129.2	123.4	119.2	110.0	108.8	131.8
105°	234.0	227.0	195.0	175.0	176.0	176.0	172.0	164.0	147.0	146.0	172.0
107.5°	229.0	228.2	229.4	232.4	237.6	236.4	231.8	210.4	190.4	185.8	209.2
110°	273.0	273.0	275.0	278.0	280.0	278.0	271.0	244.0	220.0	213.0	234.0

TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	318.6	317.0	319.0	321.2	325.6	319.6	307.8	276.8	249.6	239.4	260.4
115°	388.0	388.0	389.0	389.0	390.0	387.0	363.0	331.0	295.0	280.0	298.0
117.5°	458.6	456.6	457.8	459.0	455.0	447.0	419.2	382.0	341.6	317.6	331.8
120°	501.0	503.0	501.0	503.0	499.0	487.0	460.0	418.0	372.0	344.0	355.0
122.5°	545.0	546.2	545.8	545.4	540.6	527.0	495.2	451.6	406.4	372.0	376.6
125°	615.0	610.0	608.0	607.0	603.0	587.0	554.0	509.0	456.0	414.0	408.0
127.5°	673.6	671.4	667.2	665.0	658.8	639.4	605.6	562.2	504.0	456.4	443.0
130°	712.0	713.0	708.0	705.0	694.0	673.0	640.0	599.0	540.0	486.0	467.0
132.5°	750.4	749.0	747.2	738.6	729.2	706.6	676.0	633.4	573.6	517.2	491.0
135°	805.0	802.0	797.0	789.0	777.0	755.0	726.0	684.0	624.0	563.0	527.0
137.5°	848.4	846.0	840.8	832.4	818.8	799.8	770.6	733.2	675.6	611.2	565.8
140°	874.0	874.0	868.0	858.0	846.0	827.0	801.0	762.0	706.0	644.0	593.0
142.5°	897.2	897.2	890.4	882.8	870.0	852.6	829.8	790.8	736.4	675.2	621.0
145°	928.0	928.0	924.0	918.0	904.0	888.0	869.0	830.0	780.0	719.0	665.0
147.5°	955.2	957.4	952.4	947.6	936.6	917.8	901.8	864.4	818.8	764.8	709.4
150°	972.0	975.0	970.0	966.0	955.0	937.0	921.0	886.0	842.0	792.0	739.0
152.5°	988.0	990.2	986.8	982.8	970.2	952.2	938.6	906.0	866.0	818.4	764.6
155°	1008.0	1013.0	1009.0	1004.0	992.0	975.0	963.0	933.0	896.0	854.0	808.0
157.5°	1028.4	1030.6	1026.6	1020.4	1009.2	994.6	981.8	954.2	922.0	885.8	845.6
160°	1038.0	1041.0	1037.0	1030.0	1018.0	1005.0	993.0	967.0	938.0	905.0	868.0
162.5°	1044.4	1048.2	1044.2	1038.0	1023.6	1012.2	1001.8	978.2	950.8	921.0	888.0
165°	1051.0	1055.0	1052.0	1045.0	1030.0	1021.0	1012.0	992.0	968.0	944.0	916.0
167.5°	1051.4	1056.4	1052.6	1046.8	1031.8	1023.0	1016.4	999.2	979.8	961.4	939.6
170°	1049.0	1054.0	1051.0	1046.0	1031.0	1023.0	1018.0	1004.0	987.0	971.0	954.0
172.5°	1043.4	1047.6	1045.4	1040.4	1026.2	1019.8	1017.2	1004.8	991.0	979.0	964.4
175°	1029.0	1035.0	1031.0	1027.0	1015.0	1011.0	1012.0	1004.0	994.0	987.0	978.0
177.5°	1007.6	1010.8	1010.0	1007.6	998.8	998.8	1002.0	997.2	994.0	990.8	986.8
180°	990.0	990.0	990.0	990.0	990.0	990.0	990.0	990.0	990.0	990.0	990.0

TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0	1393.0
2.5°	1396.7	1392.5	1387.5	1387.8	1393.5	1397.4	1396.0	1394.6
5°	1398.6	1393.7	1387.9	1389.0	1397.0	1402.8	1401.9	1401.0
7.5°	1400.2	1396.1	1391.2	1392.1	1398.8	1403.5	1402.1	1400.8
10°	1403.0	1398.0	1391.3	1391.3	1398.0	1402.7	1401.3	1400.0
12.5°	1407.4	1400.9	1391.8	1389.6	1394.5	1397.7	1395.6	1393.6
15°	1410.0	1401.3	1388.4	1382.2	1382.7	1382.2	1379.1	1376.0
17.5°	1399.4	1387.7	1369.9	1359.3	1355.8	1352.1	1347.9	1343.6
20°	1383.4	1370.3	1350.8	1337.7	1331.0	1325.1	1321.6	1318.0
22.5°	1356.2	1342.1	1321.1	1307.4	1301.1	1295.4	1291.5	1287.6
25°	1302.7	1289.3	1269.8	1256.4	1249.3	1243.1	1239.6	1236.0
27.5°	1229.2	1217.1	1200.2	1188.5	1181.8	1175.8	1171.9	1168.0
30°	1173.1	1163.0	1149.7	1138.8	1130.3	1122.7	1117.3	1112.0
32.5°	1110.4	1101.4	1089.1	1079.0	1070.9	1063.0	1055.9	1048.8
35°	996.2	990.3	982.8	975.0	967.0	959.1	951.6	944.0
37.5°	866.6	860.7	852.6	844.3	835.7	828.5	825.5	822.6
40°	769.7	763.7	755.2	746.3	737.0	729.9	729.4	729.0
42.5°	666.7	664.5	658.2	650.2	640.5	632.7	630.9	629.0
45°	497.8	503.7	503.2	497.4	486.3	469.8	436.9	404.0
47.5°	311.4	332.3	349.8	342.1	309.1	276.3	243.8	211.4
50°	198.9	225.7	254.6	247.0	203.0	167.2	156.1	145.0
52.5°	132.7	156.6	185.1	182.0	147.3	119.5	112.6	105.8
55°	76.9	88.3	102.1	101.0	85.0	72.6	70.8	69.0
57.5°	49.4	54.9	60.8	60.6	54.3	48.7	44.9	41.2
60°	35.1	39.7	44.6	43.7	37.0	31.3	28.7	26.0
62.5°	26.9	30.3	34.5	34.2	29.3	25.4	24.5	23.6
65°	21.9	22.3	22.8	22.6	21.7	20.9	20.4	20.0
67.5°	19.5	19.5	19.4	19.2	18.9	18.5	18.0	17.6
70°	17.9	17.7	17.2	17.0	17.0	16.9	16.4	16.0
72.5°	15.6	15.5	15.4	15.2	14.9	14.6	14.5	14.4
75°	12.9	13.0	13.0	12.8	12.3	11.9	11.4	11.0
77.5°	10.3	10.1	9.8	9.6	9.6	9.5	9.0	8.6
80°	8.0	8.0	8.0	8.0	8.0	7.9	7.4	7.0
82.5°	6.4	6.4	6.4	6.4	6.4	6.3	5.8	5.4
85°	4.0	4.0	4.0	4.0	4.0	3.9	3.4	3.0
87.5°	3.8	5.2	6.2	7.4	8.5	9.0	9.8	9.4
90°	11.0	18.0	23.0	30.0	37.0	41.0	45.0	43.0
92.5°	27.0	38.8	46.2	58.0	66.6	73.8	77.0	76.6
95°	62.0	78.0	93.0	107.0	121.0	131.0	137.0	135.0
97.5°	98.4	124.2	143.4	162.2	177.8	187.2	193.2	197.2
100°	124.0	149.0	177.0	195.0	213.0	224.0	234.0	238.0
102.5°	155.2	176.2	204.2	227.8	247.4	259.2	267.6	271.6
105°	199.0	225.0	249.0	274.0	295.0	310.0	319.0	322.0
107.5°	241.6	270.2	293.8	319.6	339.0	355.6	366.6	373.0
110°	268.0	299.0	329.0	350.0	371.0	386.0	397.0	401.0

TEST NUMBER: P709350

CATALOG NUMBER: DL2W-WB-M-075U-050D-935-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	295.2	327.0	358.6	382.0	403.0	418.0	430.6	436.2
115°	330.0	365.0	400.0	431.0	450.0	464.0	473.0	478.0
117.5°	365.6	401.6	434.4	466.8	487.6	498.4	502.6	506.2
120°	388.0	424.0	456.0	486.0	510.0	524.0	529.0	531.0
122.5°	407.2	442.4	476.0	504.4	527.6	544.8	553.0	555.0
125°	434.0	470.0	504.0	531.0	555.0	572.0	581.0	586.0
127.5°	459.4	492.4	528.4	557.6	579.6	595.0	603.8	607.8
130°	477.0	506.0	542.0	572.0	594.0	611.0	619.0	623.0
132.5°	495.4	518.0	552.4	584.0	606.8	622.2	631.0	635.0
135°	523.0	536.0	565.0	598.0	622.0	637.0	645.0	649.0
137.5°	552.4	557.4	576.0	606.0	631.0	646.8	654.0	656.6
140°	574.0	571.0	584.0	610.0	635.0	650.0	658.0	659.0
142.5°	596.4	589.4	594.4	614.8	636.6	651.6	659.6	661.4
145°	633.0	618.0	613.0	625.0	640.0	654.0	661.0	663.0
147.5°	669.8	650.4	636.4	640.2	648.0	657.2	664.0	665.4
150°	697.0	672.0	654.0	653.0	656.0	662.0	668.0	667.0
152.5°	722.6	696.8	674.0	668.2	668.0	670.8	673.6	673.4
155°	764.0	735.0	708.0	697.0	691.0	689.0	689.0	688.0
157.5°	803.6	774.0	745.4	730.0	721.0	716.2	714.8	712.6
160°	830.0	798.0	771.0	754.0	745.0	737.0	734.0	731.0
162.5°	854.8	825.2	795.0	778.8	769.0	761.8	758.8	754.2
165°	889.0	865.0	834.0	817.0	806.0	800.0	796.0	792.0
167.5°	918.4	898.4	873.0	854.4	847.2	840.4	836.6	829.4
170°	936.0	920.0	897.0	880.0	876.0	870.0	863.0	855.0
172.5°	951.2	938.4	917.8	906.4	902.4	896.4	894.2	887.8
175°	970.0	963.0	948.0	939.0	939.0	938.0	935.0	929.0
177.5°	984.4	982.0	973.2	968.4	971.6	971.6	970.8	965.2
180°	990.0	990.0	990.0	990.0	990.0	990.0	990.0	990.0

(END OF REPORT)