

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709339

Luminaire Tested: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

Issue Date: 3/5/2020


Test Information

Test Method: LM-79-2019
Report Number: P709339
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-2, G3-2104-222-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/5/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4332.5 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.23 / 1.17
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

Luminous Intensity Polar Plot



TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54		
1	100	97	94	91	93	90	87	85	78	76	74	66	65	64	55	55	54	49		
2	93	87	82	78	86	81	77	73	70	67	65	61	58	56	51	50	49	44		
3	86	78	72	67	80	73	68	64	64	60	57	55	53	50	47	45	44	40		
4	80	71	64	59	75	67	61	56	58	54	50	51	48	45	44	42	40	36		
5	74	64	57	52	69	60	54	50	53	49	45	47	43	40	41	38	36	33		
6	69	59	51	46	65	55	49	44	49	44	40	43	39	36	38	35	33	30		
7	65	54	46	41	60	51	44	40	45	40	36	40	36	33	35	32	30	27		
8	60	49	42	37	56	47	40	36	42	37	33	37	33	30	32	30	27	25		
9	56	45	38	34	53	43	37	33	38	34	30	34	30	28	30	27	25	23		
10	53	42	35	31	50	40	34	30	36	31	28	32	28	25	28	25	23	21		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	23791	23791	23791	23791	23791
5°	24018	23803	24052	23803	24018
10°	24279	24128	24330	24128	24279
15°	24329	24495	24789	24495	24329
20°	23953	24430	24917	24430	23953
25°	23291	23802	24346	23802	23291
30°	21929	22565	23152	22565	21929
35°	19681	20408	20808	20408	19681
40°	16252	16737	17100	16737	16252
45°	9757	12085	10821	12085	9757
50°	3853	6664	4197	6664	3853
55°	2055	3023	2024	3023	2055
60°	888	1506	956	1506	888
65°	810	917	848	917	810
70°	798	854	850	854	798
75°	724	852	792	852	724
80°	688	790	790	790	688
85°	593	778	778	778	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
 Vertical Angle: 45°
 Luminance: 12166 cd/sqm

TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.1	3.3
10°-20°	414.0	9.6
20°-30°	613.0	14.1
30°-40°	635.0	14.7
40°-50°	381.7	8.8
50°-60°	91.1	2.1
60°-70°	24.9	0.6
70°-80°	13.9	0.3
80°-90°	7.3	0.2
90°-100°	54.9	1.3
100°-110°	159.9	3.7
110°-120°	260.7	6.0
120°-130°	331.0	7.6
130°-140°	354.0	8.2
140°-150°	330.6	7.6
150°-160°	272.2	6.3
160°-170°	182.5	4.2
170°-180°	64.8	1.5
0°-30°	1168.1	27.0
0°-40°	1803.1	41.6
0°-60°	2275.9	52.5
0°-90°	2321.9	53.6
90°-120°	475.5	11.0
90°-150°	1491.1	34.4
90°-180°	2011.0	46.4
0°-180°	4332.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1474	1474	1474	1474	1474	
5°	1482	1469	1484	1469	1482	141
15°	1456	1465	1483	1465	1456	409
25°	1307	1336	1367	1336	1307	597
35°	998	1035	1056	1035	998	615
45°	427	529	474	529	427	337
55°	73	107	72	107	73	70
65°	21	24	22	24	21	22
75°	12	14	13	14	12	13
85°	3	4	4	4	3	4
90°	15	14	2	20	32	7
95°	16	21	21	71	96	27
105°	164	123	100	182	225	153
115°	267	269	193	289	333	267
125°	425	412	288	360	407	379
135°	559	532	392	405	451	429
145°	644	624	500	430	461	403
155°	702	684	594	489	478	324
165°	732	713	656	573	550	207
175°	714	705	687	657	647	69
180°	688	688	688	688	688	

TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5
2.5°	1475.2	1476.7	1478.2	1474.0	1468.0	1467.6	1472.9	1477.4	1479.7	1481.9	1479.7
5°	1481.9	1482.9	1483.8	1477.7	1469.2	1468.1	1474.2	1479.3	1481.7	1484.0	1481.7
7.5°	1481.7	1483.1	1484.5	1479.6	1472.6	1471.6	1476.8	1481.0	1482.5	1484.0	1482.5
10°	1480.9	1482.3	1483.7	1478.8	1471.7	1471.7	1478.8	1484.0	1484.0	1484.0	1484.0
12.5°	1474.1	1476.3	1478.4	1475.1	1469.9	1472.2	1481.9	1488.7	1486.8	1484.9	1486.8
15°	1455.5	1458.8	1462.1	1462.5	1462.1	1468.7	1482.3	1491.5	1487.2	1483.0	1487.2
17.5°	1421.2	1425.7	1430.2	1434.1	1437.8	1449.0	1467.8	1480.3	1473.7	1467.1	1473.7
20°	1394.1	1397.9	1401.7	1407.9	1414.9	1428.8	1449.5	1463.4	1456.8	1450.2	1456.8
22.5°	1362.0	1366.1	1370.3	1376.3	1383.0	1397.4	1419.6	1434.5	1427.5	1420.6	1427.5
25°	1307.4	1311.2	1314.9	1321.5	1329.0	1343.1	1363.8	1377.9	1372.3	1366.6	1372.3
27.5°	1235.5	1239.6	1243.7	1250.1	1257.1	1269.6	1287.4	1300.2	1297.7	1295.1	1297.7
30°	1176.2	1181.9	1187.5	1195.6	1204.6	1216.1	1230.2	1240.9	1241.3	1241.8	1241.3
32.5°	1109.4	1116.9	1124.4	1132.7	1141.3	1152.0	1165.0	1174.6	1173.9	1173.3	1173.9
35°	998.5	1006.5	1014.5	1022.9	1031.3	1039.5	1047.5	1053.8	1054.7	1055.7	1054.7
37.5°	870.1	873.2	876.3	883.9	893.1	901.9	910.5	916.7	916.0	915.4	916.0
40°	771.1	771.6	772.1	779.6	789.4	798.8	807.8	814.1	812.7	811.3	812.7
42.5°	665.3	667.3	669.3	677.5	687.7	696.2	702.9	705.2	694.8	684.4	694.8
45°	427.3	462.1	496.9	514.4	526.2	532.3	532.8	526.5	500.2	473.9	500.2
47.5°	223.6	257.9	292.2	327.0	361.9	370.1	351.5	329.4	296.5	263.6	296.5
50°	153.4	165.1	176.9	214.7	261.3	269.3	238.7	210.4	188.8	167.1	188.8
52.5°	111.9	119.2	126.4	155.8	192.5	195.8	165.6	140.3	129.6	118.9	129.6
55°	73.0	74.9	76.7	89.9	106.8	108.0	93.4	81.3	76.6	71.9	76.6
57.5°	43.6	47.5	51.5	57.5	64.1	64.3	58.0	52.3	48.1	44.0	48.1
60°	27.5	30.3	33.1	39.1	46.2	47.1	42.0	37.1	33.4	29.6	33.4
62.5°	25.0	25.9	26.8	31.0	36.1	36.5	32.1	28.5	27.4	26.2	27.4
65°	21.2	21.6	22.1	22.9	23.9	24.1	23.6	23.2	22.7	22.2	22.7
67.5°	18.6	19.1	19.6	20.0	20.3	20.6	20.7	20.6	20.1	19.7	20.1
70°	16.9	17.4	17.9	18.0	18.0	18.2	18.7	18.9	18.5	18.0	18.5
72.5°	15.2	15.3	15.4	15.7	16.1	16.3	16.4	16.5	16.4	16.3	16.4
75°	11.6	12.1	12.6	13.0	13.5	13.8	13.8	13.6	13.2	12.7	13.2
77.5°	9.1	9.6	10.0	10.2	10.2	10.3	10.7	10.9	10.5	10.2	10.5
80°	7.4	7.9	8.3	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
82.5°	5.7	6.2	6.7	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
85°	3.2	3.6	4.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	3.8	3.8	3.8	4.1	4.3	4.4	4.0	3.4	2.7	2.1	2.7
90°	14.8	14.8	14.8	14.8	13.7	13.7	11.6	8.5	5.3	2.1	5.3
92.5°	18.2	18.2	17.3	17.3	16.3	14.6	12.5	11.8	12.9	7.2	13.7
95°	15.9	15.9	15.9	15.9	18.0	24.3	33.8	35.9	24.3	21.1	29.6
97.5°	37.4	39.9	43.5	52.4	61.7	66.6	62.6	45.4	44.0	42.1	56.2
100°	77.1	77.1	82.4	88.8	101.5	83.5	63.4	62.4	59.2	58.1	74.0
102.5°	122.0	124.5	127.2	128.5	99.8	90.3	87.1	81.0	76.1	75.0	91.7
105°	163.8	156.4	134.2	121.5	121.5	123.6	121.5	114.1	103.6	100.4	118.4
107.5°	160.2	157.0	159.8	161.1	166.1	164.7	160.2	146.7	131.9	129.1	145.0
110°	188.1	189.2	190.2	192.3	196.6	193.4	188.1	171.2	152.2	146.9	162.8

TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	221.1	220.5	223.2	224.5	224.5	223.0	214.3	193.2	172.5	166.3	180.5
115°	267.4	269.5	270.5	271.6	270.5	268.4	252.6	229.3	204.0	193.4	206.1
117.5°	320.6	315.8	317.3	318.1	318.7	311.1	293.8	266.3	236.9	221.3	231.0
120°	351.9	348.8	347.7	347.7	346.6	338.2	319.2	291.7	258.9	239.9	246.2
122.5°	379.8	379.2	379.0	378.1	377.9	366.1	345.4	316.2	282.6	259.3	261.5
125°	424.8	425.9	422.7	418.5	417.4	406.9	384.7	354.0	318.1	288.5	285.3
127.5°	467.5	469.7	466.3	463.9	458.2	443.7	422.5	391.9	351.7	318.5	308.2
130°	494.6	496.7	492.5	489.3	481.9	468.2	447.0	416.4	376.2	337.1	323.4
132.5°	521.6	522.1	517.8	513.8	505.6	491.8	470.7	440.9	398.2	359.1	341.1
135°	559.1	560.1	554.8	549.5	536.9	526.3	506.2	476.6	433.3	392.1	367.8
137.5°	589.9	590.1	585.5	577.7	569.2	555.7	537.1	509.2	469.2	424.8	394.0
140°	607.7	608.7	602.4	597.1	588.6	576.0	559.1	529.5	490.4	446.0	414.3
142.5°	622.9	623.9	619.3	614.0	605.6	592.9	577.7	549.8	511.5	468.0	433.7
145°	643.6	646.8	642.5	637.3	629.9	618.2	602.4	577.0	542.1	499.9	461.8
147.5°	665.6	665.8	662.6	659.5	651.0	638.5	627.1	601.8	568.6	531.4	491.6
150°	677.4	678.5	675.3	672.1	663.7	652.1	641.5	616.1	585.5	551.7	513.6
152.5°	687.6	689.5	687.1	683.1	675.5	663.1	653.3	629.7	601.5	569.4	533.1
155°	701.7	704.9	702.8	698.6	690.1	678.5	669.0	648.9	622.5	593.9	561.2
157.5°	715.3	718.2	715.9	710.8	702.2	691.8	682.7	663.7	641.3	616.3	586.3
160°	722.9	725.0	721.8	717.6	708.1	698.6	691.2	672.1	653.1	629.9	602.4
162.5°	727.1	730.1	726.9	721.8	712.3	703.6	697.1	679.7	661.6	640.9	616.8
165°	732.4	733.4	731.3	727.1	716.5	709.1	703.8	690.1	673.2	656.3	637.3
167.5°	732.0	736.2	733.0	729.0	717.6	712.3	707.4	695.2	682.7	668.5	654.4
170°	730.3	734.5	731.3	728.2	717.6	712.3	709.1	698.6	686.9	675.3	663.7
172.5°	726.0	729.4	727.1	723.9	714.2	709.8	708.3	699.4	689.5	680.4	670.4
175°	714.4	718.6	717.6	714.4	706.0	703.8	704.9	698.6	692.2	686.9	679.5
177.5°	699.8	704.1	702.4	700.7	694.8	693.9	697.3	693.9	690.5	688.8	685.5
180°	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0

TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
0°	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5	1473.5
2.5°	1477.4	1472.9	1467.6	1468.0	1474.0	1478.2	1476.7	1475.2
5°	1479.3	1474.2	1468.1	1469.2	1477.7	1483.8	1482.9	1481.9
7.5°	1481.0	1476.8	1471.6	1472.6	1479.6	1484.5	1483.1	1481.7
10°	1484.0	1478.8	1471.7	1471.7	1478.8	1483.7	1482.3	1480.9
12.5°	1488.7	1481.9	1472.2	1469.9	1475.1	1478.4	1476.3	1474.1
15°	1491.5	1482.3	1468.7	1462.1	1462.5	1462.1	1458.8	1455.5
17.5°	1480.3	1467.8	1449.0	1437.8	1434.1	1430.2	1425.7	1421.2
20°	1463.4	1449.5	1428.8	1414.9	1407.9	1401.7	1397.9	1394.1
22.5°	1434.5	1419.6	1397.4	1383.0	1376.3	1370.3	1366.1	1362.0
25°	1377.9	1363.8	1343.1	1329.0	1321.5	1314.9	1311.2	1307.4
27.5°	1300.2	1287.4	1269.6	1257.1	1250.1	1243.7	1239.6	1235.5
30°	1240.9	1230.2	1216.1	1204.6	1195.6	1187.5	1181.9	1176.2
32.5°	1174.6	1165.0	1152.0	1141.3	1132.7	1124.4	1116.9	1109.4
35°	1053.8	1047.5	1039.5	1031.3	1022.9	1014.5	1006.5	998.5
37.5°	916.7	910.5	901.9	893.1	883.9	876.3	873.2	870.1
40°	814.1	807.8	798.8	789.4	779.6	772.1	771.6	771.1
42.5°	705.2	702.9	696.2	687.7	677.5	669.3	667.3	665.3
45°	526.5	532.8	532.3	526.2	514.4	496.9	462.1	427.3
47.5°	329.4	351.5	370.1	361.9	327.0	292.2	257.9	223.6
50°	210.4	238.7	269.3	261.3	214.7	176.9	165.1	153.4
52.5°	140.3	165.6	195.8	192.5	155.8	126.4	119.2	111.9
55°	81.3	93.4	108.0	106.8	89.9	76.7	74.9	73.0
57.5°	52.3	58.0	64.3	64.1	57.5	51.5	47.5	43.6
60°	37.1	42.0	47.1	46.2	39.1	33.1	30.3	27.5
62.5°	28.5	32.1	36.5	36.1	31.0	26.8	25.9	25.0
65°	23.2	23.6	24.1	23.9	22.9	22.1	21.6	21.2
67.5°	20.6	20.7	20.6	20.3	20.0	19.6	19.1	18.6
70°	18.9	18.7	18.2	18.0	18.0	17.9	17.4	16.9
72.5°	16.5	16.4	16.3	16.1	15.7	15.4	15.3	15.2
75°	13.6	13.8	13.8	13.5	13.0	12.6	12.1	11.6
77.5°	10.9	10.7	10.3	10.2	10.2	10.0	9.6	9.1
80°	8.5	8.5	8.5	8.5	8.5	8.3	7.9	7.4
82.5°	6.8	6.8	6.8	6.8	6.8	6.7	6.2	5.7
85°	4.2	4.2	4.2	4.2	4.2	4.1	3.6	3.2
87.5°	3.2	4.0	5.1	5.9	6.4	6.6	7.0	7.2
90°	7.4	11.6	16.9	22.2	26.4	28.5	30.6	31.7
92.5°	19.2	26.0	33.8	39.9	46.7	51.4	53.5	53.7
95°	44.4	53.9	65.5	76.1	84.5	90.9	95.1	96.2
97.5°	68.3	86.0	98.9	111.2	123.4	131.0	135.9	136.5
100°	87.7	104.6	122.6	133.2	148.0	156.4	159.6	162.8
102.5°	108.9	123.2	142.9	158.5	172.5	180.1	186.6	189.8
105°	138.4	156.4	173.3	191.3	207.1	215.6	221.9	225.1
107.5°	166.6	188.5	205.4	223.0	236.9	247.3	254.9	258.1
110°	186.0	207.1	228.3	244.1	258.9	268.4	276.9	280.1

TEST NUMBER: P709339

CATALOG NUMBER: DL2W-WB-M-050U-050D-940-UNV-STD-W-WM-4

CANDELA DISTRIBUTION (continued):

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	204.6	226.6	249.4	267.0	280.9	293.0	298.9	304.6
115°	230.4	254.7	277.9	300.1	314.9	323.4	328.7	332.9
117.5°	253.2	277.7	301.6	323.8	339.0	346.0	349.2	353.2
120°	268.4	293.8	316.0	338.2	355.1	364.6	367.8	370.9
122.5°	282.8	307.3	330.4	351.7	368.6	379.0	383.8	386.2
125°	302.3	326.6	349.8	370.9	385.7	398.4	404.8	406.9
127.5°	318.3	342.6	367.1	387.4	403.1	413.6	420.0	422.9
130°	331.8	351.9	377.3	398.4	413.2	423.8	430.1	432.2
132.5°	343.7	360.4	384.0	406.0	421.7	433.1	437.7	440.7
135°	364.6	373.1	393.1	416.4	433.3	442.8	448.1	451.3
137.5°	384.9	387.2	399.9	421.2	438.2	448.7	454.0	456.1
140°	398.4	397.4	405.8	423.8	440.7	451.3	456.5	458.7
142.5°	413.6	410.0	414.3	427.2	442.4	453.0	459.1	460.4
145°	438.6	429.1	425.9	433.3	444.9	454.4	459.7	460.8
147.5°	466.5	451.9	442.8	444.1	450.6	457.4	461.4	462.3
150°	485.1	467.1	455.5	453.4	456.5	460.8	463.9	463.9
152.5°	502.0	484.9	469.0	465.2	464.2	466.7	469.0	468.2
155°	531.6	510.4	492.5	486.1	480.9	479.8	478.7	477.7
157.5°	561.2	538.1	517.8	508.3	502.6	499.2	496.9	494.2
160°	578.1	555.9	534.8	525.2	517.8	513.6	510.4	509.4
162.5°	594.1	574.5	554.2	541.3	534.8	528.8	527.4	523.8
165°	617.2	601.3	579.1	566.5	561.2	556.9	553.8	549.5
167.5°	640.0	625.2	606.6	594.4	588.4	584.2	580.6	578.3
170°	651.0	640.4	623.5	613.0	608.7	604.5	599.2	596.0
172.5°	662.0	653.1	639.6	629.9	628.2	623.1	621.2	617.2
175°	675.3	670.0	659.5	654.2	654.2	652.1	652.1	646.8
177.5°	684.6	682.9	676.2	672.8	675.3	675.3	674.5	671.9
180°	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0

(END OF REPORT)