

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P709342

Luminaire Tested: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

Issue Date: 3/5/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P709342  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2303-941-2, G3-2104-222-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/5/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4  
Description: CORELITE DISCREET DL2W WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5466.9 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.23 / 1.17  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 42.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

### Luminous Intensity Polar Plot



TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	103	99	96	93	97	94	91	89	83	81	79	73	72	70	64	63	62	58
2	96	90	85	80	90	85	80	77	76	72	69	67	65	63	59	57	56	52
3	89	81	75	70	84	77	71	67	69	65	61	62	58	56	55	53	51	47
4	83	74	67	62	78	70	64	59	63	58	55	57	53	50	51	48	46	43
5	77	67	60	55	73	64	57	53	58	53	49	52	48	45	47	44	42	39
6	72	61	54	49	68	58	52	47	53	48	44	48	44	41	43	40	38	35
7	67	56	49	44	63	54	47	43	49	44	40	45	40	37	40	37	35	32
8	63	52	45	40	59	49	43	39	45	40	36	41	37	34	38	34	32	30
9	59	48	41	36	56	46	39	35	42	37	33	38	34	31	35	32	29	27
10	55	44	38	33	52	42	36	32	39	34	30	36	32	29	33	29	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	35645	35645	35645	35645	35645
5°	35953	35614	35971	35614	35953
10°	36316	36070	36334	36070	36316
15°	36284	36546	36939	36546	36284
20°	35697	36327	37115	36327	35697
25°	34693	35389	36351	35389	34693
30°	32438	33557	34491	33557	32438
35°	29268	30364	31020	30364	29268
40°	24091	25004	25429	25004	24091
45°	14936	18007	15901	18007	14936
50°	5689	9854	6222	9854	5689
55°	3040	4571	3068	4571	3040
60°	1298	2222	1437	2222	1298
65°	1215	1360	1295	1360	1215
70°	1199	1293	1251	1293	1199
75°	1123	1248	1254	1248	1123
80°	1079	1190	1181	1190	1079
85°	982	1000	1186	1000	982

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 50°  
 Vertical Angle: 45°  
 Luminance: 18100 cd/sqm

TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.1	3.9
10°-20°	617.2	11.3
20°-30°	912.6	16.7
30°-40°	944.2	17.3
40°-50°	568.0	10.4
50°-60°	135.8	2.5
60°-70°	37.1	0.7
70°-80°	20.8	0.4
80°-90°	9.4	0.2
90°-100°	54.9	1.0
100°-110°	159.9	2.9
110°-120°	260.7	4.8
120°-130°	331.0	6.1
130°-140°	354.0	6.5
140°-150°	330.6	6.0
150°-160°	272.2	5.0
160°-170°	182.5	3.3
170°-180°	64.8	1.2
0°-30°	1740.9	31.8
0°-40°	2685.2	49.1
0°-60°	3388.9	62.0
0°-90°	3456.3	63.2
90°-120°	475.5	8.7
90°-150°	1491.1	27.3
90°-180°	2011.0	36.8
0°-180°	5466.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2208	2208	2208	2208	2208	
5°	2218	2197	2219	2197	2218	211
15°	2171	2186	2210	2186	2171	610
25°	1947	1986	2040	1986	1947	888
35°	1485	1540	1574	1540	1485	913
45°	654	789	696	789	654	500
55°	108	162	109	162	108	105
65°	32	36	34	36	32	32
75°	18	20	20	20	18	19
85°	5	5	6	5	5	6
90°	15	14	2	20	32	7
95°	16	21	21	71	96	27
105°	164	123	100	182	225	153
115°	267	269	193	289	333	267
125°	425	412	288	360	407	379
135°	559	532	392	405	451	429
145°	644	624	500	430	461	403
155°	702	684	594	489	478	324
165°	732	713	656	573	550	207
175°	714	705	687	657	647	69
180°	688	688	688	688	688	

TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
0°	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7
2.5°	2209.4	2211.3	2213.2	2207.5	2199.2	2199.0	2206.9	2213.5	2216.1	2218.7	2216.1
5°	2218.3	2219.7	2221.1	2211.6	2198.4	2196.3	2205.3	2212.8	2216.1	2219.4	2216.1
7.5°	2216.0	2218.2	2220.3	2213.4	2203.4	2201.9	2208.7	2214.2	2215.6	2217.0	2215.6
10°	2215.1	2216.6	2218.0	2210.6	2200.2	2200.0	2209.9	2217.1	2216.7	2216.2	2216.7
12.5°	2202.4	2205.7	2209.0	2203.8	2195.7	2198.8	2213.2	2223.1	2219.2	2215.4	2219.2
15°	2170.7	2175.4	2180.1	2181.3	2181.3	2191.4	2211.6	2224.9	2217.4	2209.9	2217.4
17.5°	2116.5	2122.2	2128.0	2134.8	2142.1	2159.2	2186.2	2204.2	2195.3	2186.4	2195.3
20°	2077.6	2079.9	2082.3	2091.7	2103.4	2125.1	2156.6	2178.0	2169.0	2160.1	2169.0
22.5°	2026.8	2030.6	2034.5	2045.1	2058.0	2081.3	2115.1	2138.0	2128.3	2118.6	2128.3
25°	1947.4	1952.6	1957.7	1966.1	1975.5	1997.4	2031.7	2055.6	2048.0	2040.5	2048.0
27.5°	1833.1	1840.2	1847.4	1857.2	1867.9	1889.4	1921.6	1944.6	1940.5	1936.4	1940.5
30°	1739.9	1751.2	1762.5	1775.9	1790.0	1809.8	1835.2	1853.8	1851.9	1850.0	1851.9
32.5°	1651.0	1660.1	1669.1	1681.4	1694.7	1712.6	1735.0	1751.3	1749.4	1747.6	1749.4
35°	1484.9	1494.3	1503.7	1517.7	1533.2	1547.8	1561.4	1571.9	1572.8	1573.8	1572.8
37.5°	1286.1	1295.6	1305.1	1316.7	1328.9	1340.4	1351.2	1359.0	1357.7	1356.4	1357.7
40°	1143.0	1145.4	1147.7	1161.7	1179.6	1193.0	1201.9	1208.4	1207.5	1206.5	1207.5
42.5°	972.0	983.0	994.0	1007.1	1020.8	1033.8	1046.2	1051.9	1037.8	1023.6	1037.8
45°	654.1	699.2	744.4	768.0	784.5	792.7	792.7	782.0	739.2	696.4	739.2
47.5°	328.9	383.8	438.6	489.0	538.0	549.2	522.8	490.7	442.0	393.3	442.0
50°	226.5	244.8	263.2	318.6	386.3	398.3	354.5	313.5	280.6	247.7	280.6
52.5°	166.4	176.1	185.8	231.1	288.3	293.9	247.9	209.2	192.4	175.7	192.4
55°	108.0	111.7	115.5	135.8	161.7	163.1	140.1	121.2	115.1	109.0	115.1
57.5°	65.6	71.5	77.5	85.7	94.8	94.8	85.7	77.4	71.1	64.8	71.1
60°	40.2	45.4	50.6	58.9	68.3	69.3	61.7	54.8	49.6	44.5	49.6
62.5°	36.8	38.6	40.4	46.5	54.0	54.6	48.2	42.9	40.7	38.5	40.7
65°	31.8	32.7	33.6	34.6	35.5	35.7	35.3	34.8	34.3	33.9	34.3
67.5°	27.9	28.8	29.6	29.9	30.0	30.2	30.6	30.8	30.3	29.8	30.3
70°	25.4	25.9	26.3	26.8	27.3	27.5	27.5	27.4	26.9	26.5	26.9
72.5°	22.0	22.9	23.7	24.0	24.1	24.3	24.7	24.9	24.4	23.9	24.4
75°	18.0	18.5	18.9	19.4	19.9	20.1	20.1	20.1	20.1	20.1	20.1
77.5°	14.2	14.7	15.1	15.2	15.2	15.5	15.9	16.2	15.7	15.2	15.7
80°	11.6	12.1	12.6	12.7	12.7	12.9	13.4	13.6	13.2	12.7	13.2
82.5°	9.1	9.6	10.0	10.2	10.2	10.2	10.3	10.3	10.3	10.2	10.3
85°	5.3	5.3	5.3	5.3	5.3	5.5	6.0	6.4	6.4	6.4	6.4
87.5°	4.7	4.7	4.7	4.7	4.4	4.6	4.6	4.1	3.1	2.1	3.1
90°	14.8	14.8	14.8	14.8	13.7	13.7	11.6	8.5	5.3	2.1	5.3
92.5°	18.2	18.2	17.3	17.3	16.3	14.6	12.5	11.8	12.9	7.2	13.7
95°	15.9	15.9	15.9	15.9	18.0	24.3	33.8	35.9	24.3	21.1	29.6
97.5°	37.4	39.9	43.5	52.4	61.7	66.6	62.6	45.4	44.0	42.1	56.2
100°	77.1	77.1	82.4	88.8	101.5	83.5	63.4	62.4	59.2	58.1	74.0
102.5°	122.0	124.5	127.2	128.5	99.8	90.3	87.1	81.0	76.1	75.0	91.7
105°	163.8	156.4	134.2	121.5	121.5	123.6	121.5	114.1	103.6	100.4	118.4
107.5°	160.2	157.0	159.8	161.1	166.1	164.7	160.2	146.7	131.9	129.1	145.0
110°	188.1	189.2	190.2	192.3	196.6	193.4	188.1	171.2	152.2	146.9	162.8

TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	100°
112.5°	221.1	220.5	223.2	224.5	224.5	223.0	214.3	193.2	172.5	166.3	180.5
115°	267.4	269.5	270.5	271.6	270.5	268.4	252.6	229.3	204.0	193.4	206.1
117.5°	320.6	315.8	317.3	318.1	318.7	311.1	293.8	266.3	236.9	221.3	231.0
120°	351.9	348.8	347.7	347.7	346.6	338.2	319.2	291.7	258.9	239.9	246.2
122.5°	379.8	379.2	379.0	378.1	377.9	366.1	345.4	316.2	282.6	259.3	261.5
125°	424.8	425.9	422.7	418.5	417.4	406.9	384.7	354.0	318.1	288.5	285.3
127.5°	467.5	469.7	466.3	463.9	458.2	443.7	422.5	391.9	351.7	318.5	308.2
130°	494.6	496.7	492.5	489.3	481.9	468.2	447.0	416.4	376.2	337.1	323.4
132.5°	521.6	522.1	517.8	513.8	505.6	491.8	470.7	440.9	398.2	359.1	341.1
135°	559.1	560.1	554.8	549.5	536.9	526.3	506.2	476.6	433.3	392.1	367.8
137.5°	589.9	590.1	585.5	577.7	569.2	555.7	537.1	509.2	469.2	424.8	394.0
140°	607.7	608.7	602.4	597.1	588.6	576.0	559.1	529.5	490.4	446.0	414.3
142.5°	622.9	623.9	619.3	614.0	605.6	592.9	577.7	549.8	511.5	468.0	433.7
145°	643.6	646.8	642.5	637.3	629.9	618.2	602.4	577.0	542.1	499.9	461.8
147.5°	665.6	665.8	662.6	659.5	651.0	638.5	627.1	601.8	568.6	531.4	491.6
150°	677.4	678.5	675.3	672.1	663.7	652.1	641.5	616.1	585.5	551.7	513.6
152.5°	687.6	689.5	687.1	683.1	675.5	663.1	653.3	629.7	601.5	569.4	533.1
155°	701.7	704.9	702.8	698.6	690.1	678.5	669.0	648.9	622.5	593.9	561.2
157.5°	715.3	718.2	715.9	710.8	702.2	691.8	682.7	663.7	641.3	616.3	586.3
160°	722.9	725.0	721.8	717.6	708.1	698.6	691.2	672.1	653.1	629.9	602.4
162.5°	727.1	730.1	726.9	721.8	712.3	703.6	697.1	679.7	661.6	640.9	616.8
165°	732.4	733.4	731.3	727.1	716.5	709.1	703.8	690.1	673.2	656.3	637.3
167.5°	732.0	736.2	733.0	729.0	717.6	712.3	707.4	695.2	682.7	668.5	654.4
170°	730.3	734.5	731.3	728.2	717.6	712.3	709.1	698.6	686.9	675.3	663.7
172.5°	726.0	729.4	727.1	723.9	714.2	709.8	708.3	699.4	689.5	680.4	670.4
175°	714.4	718.6	717.6	714.4	706.0	703.8	704.9	698.6	692.2	686.9	679.5
177.5°	699.8	704.1	702.4	700.7	694.8	693.9	697.3	693.9	690.5	688.8	685.5
180°	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0

TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°
0°	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7	2207.7
2.5°	2213.5	2206.9	2199.0	2199.2	2207.5	2213.2	2211.3	2209.4
5°	2212.8	2205.3	2196.3	2198.4	2211.6	2221.1	2219.7	2218.3
7.5°	2214.2	2208.7	2201.9	2203.4	2213.4	2220.3	2218.2	2216.0
10°	2217.1	2209.9	2200.0	2200.2	2210.6	2218.0	2216.6	2215.1
12.5°	2223.1	2213.2	2198.8	2195.7	2203.8	2209.0	2205.7	2202.4
15°	2224.9	2211.6	2191.4	2181.3	2181.3	2180.1	2175.4	2170.7
17.5°	2204.2	2186.2	2159.2	2142.1	2134.8	2128.0	2122.2	2116.5
20°	2178.0	2156.6	2125.1	2103.4	2091.7	2082.3	2079.9	2077.6
22.5°	2138.0	2115.1	2081.3	2058.0	2045.1	2034.5	2030.6	2026.8
25°	2055.6	2031.7	1997.4	1975.5	1966.1	1957.7	1952.6	1947.4
27.5°	1944.6	1921.6	1889.4	1867.9	1857.2	1847.4	1840.2	1833.1
30°	1853.8	1835.2	1809.8	1790.0	1775.9	1762.5	1751.2	1739.9
32.5°	1751.3	1735.0	1712.6	1694.7	1681.4	1669.1	1660.1	1651.0
35°	1571.9	1561.4	1547.8	1533.2	1517.7	1503.7	1494.3	1484.9
37.5°	1359.0	1351.2	1340.4	1328.9	1316.7	1305.1	1295.6	1286.1
40°	1208.4	1201.9	1193.0	1179.6	1161.7	1147.7	1145.4	1143.0
42.5°	1051.9	1046.2	1033.8	1020.8	1007.1	994.0	983.0	972.0
45°	782.0	792.7	792.7	784.5	768.0	744.4	699.2	654.1
47.5°	490.7	522.8	549.2	538.0	489.0	438.6	383.8	328.9
50°	313.5	354.5	398.3	386.3	318.6	263.2	244.8	226.5
52.5°	209.2	247.9	293.9	288.3	231.1	185.8	176.1	166.4
55°	121.2	140.1	163.1	161.7	135.8	115.5	111.7	108.0
57.5°	77.4	85.7	94.8	94.8	85.7	77.5	71.5	65.6
60°	54.8	61.7	69.3	68.3	58.9	50.6	45.4	40.2
62.5°	42.9	48.2	54.6	54.0	46.5	40.4	38.6	36.8
65°	34.8	35.3	35.7	35.5	34.6	33.6	32.7	31.8
67.5°	30.8	30.6	30.2	30.0	29.9	29.6	28.8	27.9
70°	27.4	27.5	27.5	27.3	26.8	26.3	25.9	25.4
72.5°	24.9	24.7	24.3	24.1	24.0	23.7	22.9	22.0
75°	20.1	20.1	20.1	19.9	19.4	18.9	18.5	18.0
77.5°	16.2	15.9	15.5	15.2	15.2	15.1	14.7	14.2
80°	13.6	13.4	12.9	12.7	12.7	12.6	12.1	11.6
82.5°	10.3	10.3	10.2	10.2	10.2	10.0	9.6	9.1
85°	6.4	6.0	5.5	5.3	5.3	5.3	5.3	5.3
87.5°	3.9	4.6	5.3	6.1	7.0	7.4	7.8	8.0
90°	7.4	11.6	16.9	22.2	26.4	28.5	30.6	31.7
92.5°	19.2	26.0	33.8	39.9	46.7	51.4	53.5	53.7
95°	44.4	53.9	65.5	76.1	84.5	90.9	95.1	96.2
97.5°	68.3	86.0	98.9	111.2	123.4	131.0	135.9	136.5
100°	87.7	104.6	122.6	133.2	148.0	156.4	159.6	162.8
102.5°	108.9	123.2	142.9	158.5	172.5	180.1	186.6	189.8
105°	138.4	156.4	173.3	191.3	207.1	215.6	221.9	225.1
107.5°	166.6	188.5	205.4	223.0	236.9	247.3	254.9	258.1
110°	186.0	207.1	228.3	244.1	258.9	268.4	276.9	280.1



TEST NUMBER: P709342

CATALOG NUMBER: DL2W-WB-M-050U-075D-940-UNV-STD-W-WM-4

**CANDELA DISTRIBUTION (continued):**

	110°	120°	130°	140°	150°	160°	170°	180°
112.5°	204.6	226.6	249.4	267.0	280.9	293.0	298.9	304.6
115°	230.4	254.7	277.9	300.1	314.9	323.4	328.7	332.9
117.5°	253.2	277.7	301.6	323.8	339.0	346.0	349.2	353.2
120°	268.4	293.8	316.0	338.2	355.1	364.6	367.8	370.9
122.5°	282.8	307.3	330.4	351.7	368.6	379.0	383.8	386.2
125°	302.3	326.6	349.8	370.9	385.7	398.4	404.8	406.9
127.5°	318.3	342.6	367.1	387.4	403.1	413.6	420.0	422.9
130°	331.8	351.9	377.3	398.4	413.2	423.8	430.1	432.2
132.5°	343.7	360.4	384.0	406.0	421.7	433.1	437.7	440.7
135°	364.6	373.1	393.1	416.4	433.3	442.8	448.1	451.3
137.5°	384.9	387.2	399.9	421.2	438.2	448.7	454.0	456.1
140°	398.4	397.4	405.8	423.8	440.7	451.3	456.5	458.7
142.5°	413.6	410.0	414.3	427.2	442.4	453.0	459.1	460.4
145°	438.6	429.1	425.9	433.3	444.9	454.4	459.7	460.8
147.5°	466.5	451.9	442.8	444.1	450.6	457.4	461.4	462.3
150°	485.1	467.1	455.5	453.4	456.5	460.8	463.9	463.9
152.5°	502.0	484.9	469.0	465.2	464.2	466.7	469.0	468.2
155°	531.6	510.4	492.5	486.1	480.9	479.8	478.7	477.7
157.5°	561.2	538.1	517.8	508.3	502.6	499.2	496.9	494.2
160°	578.1	555.9	534.8	525.2	517.8	513.6	510.4	509.4
162.5°	594.1	574.5	554.2	541.3	534.8	528.8	527.4	523.8
165°	617.2	601.3	579.1	566.5	561.2	556.9	553.8	549.5
167.5°	640.0	625.2	606.6	594.4	588.4	584.2	580.6	578.3
170°	651.0	640.4	623.5	613.0	608.7	604.5	599.2	596.0
172.5°	662.0	653.1	639.6	629.9	628.2	623.1	621.2	617.2
175°	675.3	670.0	659.5	654.2	654.2	652.1	652.1	646.8
177.5°	684.6	682.9	676.2	672.8	675.3	675.3	674.5	671.9
180°	688.0	688.0	688.0	688.0	688.0	688.0	688.0	688.0

(END OF REPORT)