

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356779

Luminaire Tested: 1ASL4-5HE-2-G52-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 1ASL4-5HE-2-G52-UNV
Description: 1FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND G52 LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 276.0 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 0.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	76	74	74	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	60	60	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	50	50	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	42	42	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	36	36	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	32	32	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	28	28	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	25	25	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	22	22	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	20	20	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2652	2652	2652
5°	2611	2585	2591
10°	2577	2527	2526
15°	2536	2464	2476
20°	2487	2386	2407
25°	2420	2312	2344
30°	2339	2228	2284
35°	2274	2151	2213
40°	2197	2065	2139
45°	2120	1993	2086
50°	2026	1900	2004
55°	1932	1798	1940
60°	1816	1687	1870
65°	1652	1580	1818
70°	1470	1478	1769
75°	1222	1392	1753
80°	865	1311	1747
85°	427	1268	1796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2120 cd/sqm

TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.6	2.8
10°-20°	21.9	7.9
20°-30°	33.2	12.0
30°-40°	40.2	14.6
40°-50°	42.3	15.3
50°-60°	39.5	14.3
60°-70°	32.6	11.8
70°-80°	23.7	8.6
80°-90°	15.0	5.4
90°-100°	8.9	3.2
100°-110°	5.1	1.9
110°-120°	2.9	1.1
120°-130°	1.7	0.6
130°-140°	0.9	0.3
140°-150°	0.4	0.1
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	62.7	22.7
0°-40°	102.9	37.3
0°-60°	184.8	66.9
0°-90°	256.0	92.8
90°-120°	17.0	6.1
90°-150°	19.9	7.2
90°-180°	20.0	7.2
0°-180°	276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	80	80	80	80	80	
5°	80	80	80	80	80	8
15°	76	77	78	78	79	22
25°	70	71	72	73	74	32
35°	61	62	64	66	67	38
45°	50	52	55	58	59	39
55°	39	41	44	48	49	35
65°	26	29	33	37	39	26
75°	13	17	23	28	30	14
85°	2	8	15	20	22	3
90°	0	5	11	16	18	0
95°	0	3	9	13	15	0
105°	0	1	5	8	10	0
115°	0	0	3	5	6	0
125°	0	0	2	3	4	0
135°	0	0	1	2	2	0
145°	0	0	0	1	2	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	80.4	80.4	80.4	80.4	80.4
2.5°	79.9	80.6	80.4	80.1	80.1
5°	79.6	80.4	80.1	80.1	80.4
7.5°	79.1	79.9	79.9	79.9	80.1
10°	78.4	79.4	79.4	79.4	79.6
12.5°	77.6	78.4	78.6	78.9	79.1
15°	76.4	77.4	77.9	78.1	78.6
17.5°	75.1	75.8	76.6	77.4	77.6
20°	73.6	74.6	75.3	76.1	76.4
22.5°	71.8	72.8	73.8	74.6	75.1
25°	69.8	70.8	72.3	73.3	73.8
27.5°	67.8	68.8	70.5	71.8	72.3
30°	65.2	66.7	68.5	70.0	70.8
32.5°	63.0	64.5	66.5	68.3	68.8
35°	60.7	62.2	64.5	66.2	67.0
37.5°	58.1	59.9	62.2	64.2	65.0
40°	55.6	57.4	59.9	62.2	62.7
42.5°	53.1	54.9	57.9	59.9	60.7
45°	50.3	52.3	55.4	57.6	58.7
47.5°	47.5	49.6	52.6	55.1	56.1
50°	44.5	46.8	50.1	52.6	53.6
52.5°	41.7	44.0	47.3	50.1	51.3
55°	38.7	41.0	44.5	47.5	48.8
57.5°	35.6	37.9	41.7	45.0	46.3
60°	32.6	34.9	38.7	42.5	43.7
62.5°	29.3	31.9	35.9	39.7	41.2
65°	26.0	28.8	33.1	37.2	38.9
67.5°	23.0	25.8	30.3	34.9	36.4
70°	19.7	22.8	27.8	32.4	34.1
72.5°	16.4	19.7	25.3	30.1	31.9
75°	13.4	16.9	23.0	27.8	29.8
77.5°	10.1	14.4	20.7	25.8	27.6
80°	7.3	11.9	18.5	23.8	25.5
82.5°	4.8	9.6	16.4	21.7	23.5
85°	2.5	7.8	14.7	19.7	21.7
87.5°	0.8	6.1	12.9	18.0	19.7
90°	0.0	4.8	11.4	16.2	18.2
92.5°	0.0	3.8	9.9	14.7	16.4
95°	0.0	3.0	8.6	13.1	14.9
97.5°	0.0	2.5	7.6	11.9	13.4
100°	0.0	2.0	6.6	10.6	12.1
102.5°	0.0	1.5	5.6	9.4	10.9
105°	0.0	1.0	4.8	8.3	9.6
107.5°	0.0	0.8	4.0	7.3	8.6
110°	0.0	0.8	3.8	6.3	7.6

TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.5	3.3	5.8	6.8
115°	0.0	0.5	2.8	5.1	6.1
117.5°	0.0	0.5	2.5	4.6	5.6
120°	0.0	0.5	2.3	4.0	4.8
122.5°	0.0	0.3	2.0	3.5	4.3
125°	0.0	0.3	1.8	3.3	3.8
127.5°	0.0	0.3	1.5	3.0	3.5
130°	0.0	0.3	1.5	2.8	3.3
132.5°	0.0	0.0	1.3	2.5	3.0
135°	0.0	0.0	1.0	2.0	2.5
137.5°	0.0	0.0	1.0	1.8	2.3
140°	0.0	0.0	0.8	1.8	2.0
142.5°	0.0	0.0	0.5	1.5	1.8
145°	0.0	0.0	0.5	1.3	1.5
147.5°	0.0	0.0	0.3	1.0	1.3
150°	0.0	0.0	0.3	0.8	1.0
152.5°	0.0	0.0	0.0	0.5	0.8
155°	0.0	0.0	0.0	0.3	0.5
157.5°	0.0	0.0	0.0	0.0	0.3
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356779

CATALOG NUMBER: 1ASL4-5HE-2-G52-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.60	14.14	13.07	14.60	15.09	14.43	15.96	14.90	16.42	16.91
	3H	14.11	15.51	14.60	15.98	16.51	16.78	18.18	17.26	18.65	19.18
	4H	14.60	15.92	15.10	16.41	16.95	17.90	19.23	18.41	19.72	20.26
	6H	14.87	16.11	15.39	16.61	17.17	19.05	20.28	19.57	20.79	21.35
	8H	14.93	16.11	15.46	16.64	17.20	19.61	20.79	20.14	21.32	21.89
	12H	14.94	16.08	15.48	16.60	17.19	20.19	21.33	20.73	21.85	22.45
4H	2H	13.44	14.76	13.94	15.25	15.79	14.87	16.20	15.37	16.68	17.23
	3H	15.18	16.32	15.70	16.85	17.41	17.45	18.58	17.97	19.11	19.68
	4H	15.79	16.83	16.33	17.37	17.97	18.75	19.79	19.29	20.33	20.93
	6H	16.20	17.11	16.76	17.68	18.29	20.10	21.01	20.65	21.58	22.19
	8H	16.30	17.16	16.86	17.72	18.35	20.76	21.63	21.33	22.19	22.82
	12H	16.34	17.13	16.93	17.72	18.35	21.47	22.25	22.06	22.85	23.48
8H	4H	16.44	17.30	17.00	17.86	18.49	18.98	19.85	19.55	20.41	21.04
	6H	17.02	17.75	17.62	18.36	18.99	20.50	21.24	21.10	21.84	22.48
	8H	17.21	17.87	17.82	18.49	19.13	21.32	21.98	21.92	22.60	23.24
	12H	17.33	17.92	17.94	18.53	19.24	22.21	22.80	22.82	23.40	24.11
12H	4H	16.61	17.39	17.20	17.99	18.62	18.99	19.78	19.58	20.37	21.00
	6H	17.29	17.95	17.90	18.57	19.22	20.55	21.21	21.15	21.83	22.47
	8H	17.58	18.17	18.19	18.77	19.48	21.43	22.02	22.04	22.63	23.34

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-8

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-G520-UNV-OPL-1_600mA


Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-G520-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND GREEN 520NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K):	7535	CRI (Ra):	-11.7		
CIE u':	0.0718	R1:	-30.6	R9:	-351.9
CIE v':	0.5710	R2:	5.1	R10:	-75.5
Duv:	0.1461	R3:	5.6	R11:	-78.0
CIE x:	0.1962	R4:	-51.7	R12:	-14.7
CIE y:	0.6931	R5:	-6.4	R13:	-32.5
CIE z:	0.1107	R6:	-0.6	R14:	52.7
Peak Wavelength (nm):	524	R7:	10.9	R15:	-37.0
Dominant Wavelength (nm):	529	R8:	-25.8		
Purity:	75.95236				
Rf:	NR				
Rg:	NR				



Test Conditions


Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-8


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-8

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2511-597-8

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.63

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.87

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			


REPORT NUMBER: SP1-2511-597-8

TM-30-18





Summary

$R_f = 0$
 $R_g = 0$
 $CIE R_a = -11.7$
 $R_g = -351.9$

Spectral Power Distribution Comparison



Color Vector Graphics




REPORT NUMBER: SP1-2511-597-8

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	





REPORT NUMBER: SP1-2511-597-8

TM-30-18

Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)