

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356762

Luminaire Tested: 1ASL4-35VHE-3-R63-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 1ASL4-35VHE-3-R63-UNV
Description: 1FT 3500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND R63 LEDS 3 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 906.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 0.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8789	8789	8789
5°	8649	8580	8588
10°	8540	8373	8370
15°	8385	8129	8185
20°	8197	7898	7979
25°	7991	7616	7743
30°	7771	7369	7542
35°	7513	7092	7320
40°	7268	6838	7084
45°	7006	6538	6851
50°	6712	6219	6606
55°	6389	5911	6389
60°	5987	5554	6162
65°	5490	5206	5981
70°	4880	4859	5837
75°	4041	4527	5735
80°	2890	4238	5693
85°	1417	4064	5777

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7006 cd/sqm

TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	2.8
10°-20°	72.5	8.0
20°-30°	109.7	12.1
30°-40°	132.8	14.7
40°-50°	139.5	15.4
50°-60°	130.2	14.4
60°-70°	107.6	11.9
70°-80°	77.4	8.5
80°-90°	48.1	5.3
90°-100°	28.2	3.1
100°-110°	16.1	1.8
110°-120°	9.1	1.0
120°-130°	5.2	0.6
130°-140°	2.8	0.3
140°-150°	1.2	0.1
150°-160°	0.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.5	22.9
0°-40°	340.3	37.6
0°-60°	610.0	67.3
0°-90°	843.1	93.1
90°-120°	53.4	5.9
90°-150°	62.7	6.9
90°-180°	63.0	7.0
0°-180°	906.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	266	266	266	266	266	
5°	264	266	266	266	266	25
15°	253	256	257	259	260	71
25°	230	234	238	242	244	106
35°	200	206	213	219	222	126
45°	166	172	182	190	193	128
55°	128	135	146	157	161	114
65°	86	95	109	123	128	86
75°	44	55	75	91	98	47
85°	8	25	47	64	70	10
90°	0	15	36	52	58	0
95°	0	9	27	42	48	0
105°	0	3	15	26	30	0
115°	0	2	9	16	19	0
125°	0	1	6	10	12	0
135°	0	0	3	7	8	0
145°	0	0	2	4	4	0
155°	0	0	0	1	2	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	266.5	266.5	266.5	266.5	266.5
2.5°	265.4	267.0	267.0	265.4	265.4
5°	263.7	265.9	265.9	265.9	266.5
7.5°	262.0	264.8	264.8	264.8	265.9
10°	259.8	262.6	263.1	263.1	263.7
12.5°	256.5	259.8	260.4	260.9	261.5
15°	252.6	255.9	257.0	258.7	259.8
17.5°	248.2	252.1	254.3	255.9	257.0
20°	242.6	246.5	249.3	251.5	253.2
22.5°	237.1	240.4	243.8	246.5	248.2
25°	230.5	234.3	238.2	241.5	243.8
27.5°	223.3	227.7	232.7	236.6	238.8
30°	216.6	221.0	226.6	231.6	233.8
32.5°	208.9	213.8	219.9	224.9	227.7
35°	200.5	206.1	212.7	218.8	221.6
37.5°	192.2	197.8	206.1	212.2	214.9
40°	183.9	189.5	198.3	205.0	207.7
42.5°	175.1	180.6	190.0	197.2	200.5
45°	166.2	172.3	181.7	189.5	192.8
47.5°	157.3	163.4	173.4	181.7	185.0
50°	147.4	154.0	164.0	173.4	176.7
52.5°	137.9	144.6	155.7	165.1	168.4
55°	128.0	135.2	146.3	156.8	160.7
57.5°	118.0	125.2	136.8	147.9	152.3
60°	107.5	115.2	127.4	139.1	144.0
62.5°	96.9	105.3	118.6	130.7	135.7
65°	86.4	94.7	109.1	123.0	128.0
67.5°	75.9	84.8	100.3	114.7	120.8
70°	65.4	74.8	91.4	106.4	112.5
72.5°	54.8	64.8	83.1	98.6	104.7
75°	44.3	55.4	74.8	90.9	97.5
77.5°	33.8	46.5	67.6	83.7	90.3
80°	24.4	38.8	59.8	76.4	83.1
82.5°	15.5	31.0	53.2	69.8	76.4
85°	8.3	24.9	47.1	63.7	69.8
87.5°	2.8	19.4	41.0	57.6	63.7
90°	0.0	15.0	36.0	51.5	58.2
92.5°	0.0	11.6	31.6	46.5	52.6
95°	0.0	9.4	27.1	41.5	47.6
97.5°	0.0	7.8	23.8	37.1	42.7
100°	0.0	6.1	20.5	33.2	38.2
102.5°	0.0	5.0	17.7	29.4	34.3
105°	0.0	3.3	15.0	26.0	30.5
107.5°	0.0	2.8	12.7	23.3	27.1
110°	0.0	2.2	11.6	19.9	23.8



TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	1.7	10.5	17.7	21.6
115°	0.0	1.7	8.9	16.1	18.8
117.5°	0.0	1.7	7.8	14.4	17.2
120°	0.0	1.1	7.2	12.7	15.5
122.5°	0.0	1.1	6.1	11.6	13.8
125°	0.0	1.1	5.5	10.5	12.2
127.5°	0.0	0.6	5.0	9.4	11.1
130°	0.0	0.6	4.4	8.3	10.0
132.5°	0.0	0.6	3.9	7.8	9.4
135°	0.0	0.0	3.3	6.6	8.3
137.5°	0.0	0.0	2.8	6.1	7.2
140°	0.0	0.0	2.2	5.0	6.6
142.5°	0.0	0.0	1.7	4.4	5.5
145°	0.0	0.0	1.7	3.9	4.4
147.5°	0.0	0.0	1.1	2.8	3.9
150°	0.0	0.0	0.6	2.2	2.8
152.5°	0.0	0.0	0.0	1.7	2.2
155°	0.0	0.0	0.0	1.1	1.7
157.5°	0.0	0.0	0.0	0.0	0.6
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356762

CATALOG NUMBER: 1ASL4-35VHE-3-R63-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.79	18.33	17.26	18.79	19.27	18.58	20.12	19.05	20.57	21.05
	3H	18.29	19.70	18.78	20.16	20.69	20.94	22.34	21.42	22.81	23.33
	4H	18.78	20.11	19.28	20.59	21.13	22.06	23.39	22.56	23.87	24.41
	6H	19.06	20.30	19.57	20.79	21.35	23.18	24.42	23.70	24.92	25.47
	8H	19.11	20.30	19.64	20.82	21.38	23.73	24.92	24.26	25.44	26.00
	12H	19.12	20.26	19.66	20.78	21.37	24.30	25.44	24.84	25.96	26.55
4H	2H	17.62	18.95	18.12	19.43	19.97	19.02	20.35	19.53	20.84	21.37
	3H	19.36	20.49	19.88	21.02	21.58	21.61	22.75	22.13	23.27	23.83
	4H	19.97	21.00	20.50	21.54	22.13	22.90	23.94	23.44	24.48	25.07
	6H	20.37	21.28	20.92	21.85	22.45	24.22	25.14	24.77	25.70	26.31
	8H	20.46	21.33	21.02	21.89	22.51	24.88	25.74	25.44	26.30	26.92
	12H	20.51	21.29	21.09	21.88	22.51	25.57	26.35	26.15	26.94	27.56
8H	4H	20.60	21.46	21.16	22.02	22.64	23.13	23.99	23.69	24.55	25.17
	6H	21.17	21.90	21.76	22.51	23.13	24.62	25.35	25.21	25.95	26.58
	8H	21.35	22.02	21.96	22.63	23.27	25.41	26.08	26.02	26.69	27.33
	12H	21.47	22.06	22.08	22.66	23.37	26.29	26.88	26.89	27.48	28.19
12H	4H	20.76	21.55	21.35	22.14	22.76	23.14	23.92	23.72	24.51	25.14
	6H	21.43	22.10	22.04	22.71	23.35	24.66	25.32	25.26	25.93	26.57
	8H	21.71	22.30	22.32	22.90	23.61	25.53	26.12	26.13	26.72	27.42

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-7

Test Date: 01/21/2026

Luminaire Tested: 4ASL-2-R630-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-R630-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND RED 630NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 0
 CIE u': 0.5395
 CIE v': 0.5190
 Duv: 0.0000
 CIE x: 0.7004
 CIE y: 0.2995
 CIE z: 0.0001
 Peak Wavelength (nm): 638
 Dominant Wavelength (nm): 624
 Purity: 99.9862
 Rf: NR
 Rg: NR

CRI (Ra): 0.0
 R1: 0.0
 R2: 0.0
 R3: 0.0
 R4: 0.0
 R5: 0.0
 R6: 0.0
 R7: 0.0
 R8: 0.0
 R9: 0.0
 R10: 0.0
 R11: 0.0
 R12: 0.0
 R13: 0.0
 R14: 0.0
 R15: 0.0




REPORT NUMBER: SP1-2511-597-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies outside the range

REPORT NUMBER: SP1-2511-597-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.05

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 0.02


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7





TM-30-18

Summary

$R_f = 0$
 $R_g = 0$
 CIE $R_a = 0.0$
 $R_9 = 0.0$



Color Vector Graphics




REPORT NUMBER: SP1-2511-597-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	




REPORT NUMBER: SP1-2511-597-7

TM-30-18

Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)