

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356988

Luminaire Tested: 3ASL4-10HE-2-27-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 3ASL4-10HE-2-27-UNV
Description: 3FT 1000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2838.1 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 2.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 24.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107		101	101	101		95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84		86	83	80		81	79	77	74
2	95	86	79	72	92	84	77	71	79	73	68		74	70	65		70	66	63	60
3	86	75	66	59	83	73	65	58	69	62	56		65	59	55		62	57	53	50
4	79	66	57	50	76	64	56	49	61	54	48		58	51	46		55	49	45	42
5	72	59	50	43	70	57	49	42	54	47	41		52	45	40		49	43	39	36
6	67	53	44	37	64	52	43	37	49	41	36		47	40	35		44	39	34	32
7	62	48	39	33	60	47	38	32	45	37	32		43	36	31		41	35	30	28
8	58	44	35	29	56	43	34	29	41	33	28		39	32	28		37	31	27	25
9	54	40	32	26	52	39	31	26	37	30	25		36	29	25		34	29	24	22
10	50	37	29	24	49	36	28	23	35	28	23		33	27	22		32	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8961	8961	8961
5°	8883	8778	8756
10°	8816	8612	8543
15°	8728	8430	8372
20°	8617	8203	8131
25°	8444	7978	7924
30°	8228	7722	7718
35°	8058	7484	7479
40°	7862	7228	7227
45°	7662	7006	7044
50°	7406	6714	6771
55°	7158	6400	6555
60°	6856	6048	6325
65°	6389	5721	6147
70°	5864	5411	5983
75°	5105	5169	5931
80°	3928	4950	5913
85°	2310	4925	6082

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7662 cd/sqm

TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	2.8
10°-20°	225.4	7.9
20°-30°	341.5	12.0
30°-40°	413.0	14.6
40°-50°	435.4	15.3
50°-60°	406.3	14.3
60°-70°	335.5	11.8
70°-80°	243.4	8.6
80°-90°	153.8	5.4
90°-100°	91.8	3.2
100°-110°	52.6	1.9
110°-120°	29.9	1.1
120°-130°	17.0	0.6
130°-140°	9.2	0.3
140°-150°	4.0	0.1
150°-160°	0.7	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.2	22.7
0°-40°	1058.2	37.3
0°-60°	1900.0	66.9
0°-90°	2632.7	92.8
90°-120°	174.3	6.1
90°-150°	204.6	7.2
90°-180°	205.0	7.2
0°-180°	2838.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	819	827	824	824	827	78
15°	785	796	801	803	808	222
25°	718	728	744	754	759	331
35°	624	640	663	681	689	390
45°	517	538	569	593	603	399
55°	398	421	458	489	502	355
65°	268	296	341	382	400	266
75°	138	174	237	286	307	145
85°	26	81	151	203	224	32
90°	0	49	117	166	187	1
95°	0	31	88	135	153	0
105°	0	10	49	86	99	0
115°	0	5	29	52	62	0
125°	0	3	18	34	39	0
135°	0	0	10	21	26	0
145°	0	0	5	13	16	0
155°	0	0	0	3	5	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.7	826.7	826.7	826.7	826.7
2.5°	821.5	829.3	826.7	824.1	824.1
5°	818.9	826.7	824.1	824.1	826.7
7.5°	813.7	821.5	821.5	821.5	824.1
10°	805.9	816.3	816.3	816.3	818.9
12.5°	798.1	805.9	808.5	811.1	813.7
15°	785.1	795.5	800.7	803.3	808.5
17.5°	772.1	779.9	787.7	795.5	798.1
20°	756.5	766.9	774.7	782.5	785.1
22.5°	738.3	748.7	759.1	766.9	772.1
25°	717.5	727.9	743.5	753.9	759.1
27.5°	696.7	707.1	725.3	738.3	743.5
30°	670.7	686.3	704.5	720.1	727.9
32.5°	647.3	662.9	683.7	701.9	707.1
35°	623.9	639.5	662.9	681.1	688.9
37.5°	597.9	616.1	639.5	660.3	668.1
40°	571.9	590.1	616.1	639.5	644.7
42.5°	545.9	564.1	595.3	616.1	623.9
45°	517.3	538.1	569.3	592.7	603.1
47.5°	488.7	509.5	540.7	566.7	577.1
50°	457.5	480.9	514.7	540.7	551.1
52.5°	428.9	452.3	486.1	514.7	527.7
55°	397.7	421.1	457.5	488.7	501.7
57.5°	366.5	389.9	428.9	462.7	475.7
60°	335.4	358.7	397.7	436.7	449.7
62.5°	301.6	327.6	369.1	408.1	423.7
65°	267.8	296.4	340.6	382.1	400.3
67.5°	236.6	265.2	312.0	358.7	374.3
70°	202.8	234.0	286.0	332.8	350.9
72.5°	169.0	202.8	260.0	309.4	327.6
75°	137.8	174.2	236.6	286.0	306.8
77.5°	104.0	148.2	213.2	265.2	283.4
80°	75.4	122.2	189.8	244.4	262.6
82.5°	49.4	98.8	169.0	223.6	241.8
85°	26.0	80.6	150.8	202.8	223.6
87.5°	7.8	62.4	132.6	184.6	202.8
90°	0.0	49.4	117.0	166.4	187.2
92.5°	0.0	39.0	101.4	150.8	169.0
95°	0.0	31.2	88.4	135.2	153.4
97.5°	0.0	26.0	78.0	122.2	137.8
100°	0.0	20.8	67.6	109.2	124.8
102.5°	0.0	15.6	57.2	96.2	111.8
105°	0.0	10.4	49.4	85.8	98.8
107.5°	0.0	7.8	41.6	75.4	88.4
110°	0.0	7.8	39.0	65.0	78.0



TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	5.2	33.8	59.8	70.2
115°	0.0	5.2	28.6	52.0	62.4
117.5°	0.0	5.2	26.0	46.8	57.2
120°	0.0	5.2	23.4	41.6	49.4
122.5°	0.0	2.6	20.8	36.4	44.2
125°	0.0	2.6	18.2	33.8	39.0
127.5°	0.0	2.6	15.6	31.2	36.4
130°	0.0	2.6	15.6	28.6	33.8
132.5°	0.0	0.0	13.0	26.0	31.2
135°	0.0	0.0	10.4	20.8	26.0
137.5°	0.0	0.0	10.4	18.2	23.4
140°	0.0	0.0	7.8	18.2	20.8
142.5°	0.0	0.0	5.2	15.6	18.2
145°	0.0	0.0	5.2	13.0	15.6
147.5°	0.0	0.0	2.6	10.4	13.0
150°	0.0	0.0	2.6	7.8	10.4
152.5°	0.0	0.0	0.0	5.2	7.8
155°	0.0	0.0	0.0	2.6	5.2
157.5°	0.0	0.0	0.0	0.0	2.6
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356988

CATALOG NUMBER: 3ASL4-10HE-2-27-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.92	18.45	17.39	18.92	19.41	18.95	20.49	19.42	20.95	21.44
	3H	18.42	19.82	18.91	20.29	20.82	21.39	22.79	21.88	23.26	23.79
	4H	18.90	20.23	19.41	20.72	21.26	22.59	23.92	23.10	24.41	24.95
	6H	19.18	20.42	19.70	20.92	21.48	23.84	25.08	24.36	25.58	26.14
	8H	19.23	20.42	19.76	20.94	21.51	24.49	25.67	25.02	26.20	26.77
	12H	19.25	20.39	19.79	20.90	21.50	25.20	26.33	25.73	26.85	27.45
4H	2H	17.79	19.12	18.30	19.61	20.15	19.38	20.71	19.89	21.20	21.74
	3H	19.54	20.67	20.06	21.20	21.77	22.05	23.18	22.57	23.72	24.28
	4H	20.15	21.18	20.69	21.72	22.32	23.43	24.46	23.97	25.00	25.60
	6H	20.55	21.46	21.11	22.03	22.64	24.88	25.80	25.44	26.36	26.97
	8H	20.65	21.51	21.21	22.07	22.70	25.63	26.49	26.20	27.06	27.69
	12H	20.69	21.48	21.28	22.07	22.70	26.46	27.25	27.05	27.84	28.47
8H	4H	20.84	21.70	21.40	22.26	22.89	23.65	24.51	24.21	25.08	25.70
	6H	21.42	22.15	22.02	22.76	23.39	25.28	26.01	25.87	26.62	27.25
	8H	21.61	22.27	22.22	22.89	23.53	26.17	26.83	26.78	27.45	28.10
	12H	21.73	22.32	22.34	22.93	23.64	27.19	27.78	27.80	28.39	29.10
12H	4H	21.03	21.82	21.62	22.41	23.04	23.66	24.44	24.24	25.04	25.67
	6H	21.72	22.38	22.33	23.00	23.65	25.32	25.98	25.92	26.60	27.24
	8H	22.01	22.60	22.62	23.21	23.92	26.28	26.87	26.89	27.48	28.19

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-2

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-27-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-27-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 2696
 CIE u' : 0.2632
 CIE v' : 0.5245
 Duv: -0.0020
 CIE x: 0.4568
 CIE y: 0.4045
 CIE z: 0.1387
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 58.52757
 R_f: 90.1
 R_g: 103.5

CRI (Ra): 94.4
 R1: 97.5
 R2: 97.8
 R3: 96.9
 R4: 95.3
 R5: 97.2
 R6: 96.5
 R7: 91.2
 R8: 83.2
 R9: 61.8
 R10: 93.6
 R11: 93.7
 R12: 94.1
 R13: 97.6
 R14: 96.8
 R15: 91.9



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.45


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2





TM-30-18

Summary

$R_f = 90.1$
 $R_g = 103.5$
 $CIE R_a = 94.4$
 $R_9 = 61.8$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 89	CES51 = 92	CES76 = 90
CES02 = 64	CES27 = 97	CES52 = 92	CES77 = 84
CES03 = 32	CES28 = 96	CES53 = 88	CES78 = 87
CES04 = 71	CES29 = 83	CES54 = 97	CES79 = 88
CES05 = 51	CES30 = 85	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 69
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 95
CES08 = 43	CES33 = 84	CES58 = 88	CES83 = 91
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 96	CES60 = 99	CES85 = 81
CES11 = 59	CES36 = 98	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 45	CES38 = 89	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 92	CES90 = 93
CES16 = 48	CES41 = 89	CES66 = 92	CES91 = 91
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 97	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 72
CES20 = 68	CES45 = 90	CES70 = 93	CES95 = 88
CES21 = 87	CES46 = 89	CES71 = 95	CES96 = 92
CES22 = 79	CES47 = 79	CES72 = 98	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 89	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 88	CES99 = 92
CES25 = 72	CES50 = 92	CES75 = 94	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)