

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357042

Luminaire Tested: 3ASL4-25VHE-3-27-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 3ASL4-25VHE-3-27-UNV
Description: 3FT 2500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS 3 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6936.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 2.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 64.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357042
CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357042
 CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22112	22112	22112
5°	21899	21684	21606
10°	21759	21252	21059
15°	21500	20719	20596
20°	21158	20207	20074
25°	20762	19569	19480
30°	20345	19013	18976
35°	19830	18387	18417
40°	19355	17811	17829
45°	18844	17118	17237
50°	18262	16375	16623
55°	17634	15664	16070
60°	16819	14834	15510
65°	15785	14034	15045
70°	14472	13240	14680
75°	12570	12507	14430
80°	9720	11945	14325
85°	5651	11773	14537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18844 cd/sqm



TEST NUMBER: P1357042
 CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.4	2.8
10°-20°	555.4	8.0
20°-30°	839.7	12.1
30°-40°	1016.8	14.7
40°-50°	1067.9	15.4
50°-60°	996.3	14.4
60°-70°	823.4	11.9
70°-80°	592.9	8.5
80°-90°	368.4	5.3
90°-100°	215.9	3.1
100°-110°	123.5	1.8
110°-120°	69.7	1.0
120°-130°	40.1	0.6
130°-140°	21.6	0.3
140°-150°	9.1	0.1
150°-160°	1.7	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1588.6	22.9
0°-40°	2605.4	37.6
0°-60°	4669.7	67.3
0°-90°	6454.4	93.1
90°-120°	409.1	5.9
90°-150°	479.9	6.9
90°-180°	482.0	6.9
0°-180°	6936.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2040	2040	2040	2040	2040	
5°	2019	2036	2036	2036	2040	192
15°	1934	1959	1968	1981	1989	545
25°	1764	1794	1824	1849	1866	813
35°	1535	1578	1629	1675	1696	961
45°	1272	1319	1391	1450	1476	982
55°	980	1035	1120	1200	1230	875
65°	662	725	836	942	980	655
75°	339	424	572	696	746	359
85°	64	191	360	488	534	78
90°	0	114	276	394	445	3
95°	0	72	208	318	365	0
105°	0	25	114	199	233	0
115°	0	13	68	123	144	0
125°	0	8	42	81	93	0
135°	0	0	25	51	64	0
145°	0	0	13	30	34	0
155°	0	0	0	8	13	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357042

CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2040.0	2040.0	2040.0	2040.0	2040.0
2.5°	2031.5	2044.2	2044.2	2031.5	2031.5
5°	2018.8	2035.7	2035.7	2035.7	2040.0
7.5°	2006.0	2027.2	2027.2	2027.2	2035.7
10°	1989.1	2010.3	2014.5	2014.5	2018.8
12.5°	1963.6	1989.1	1993.3	1997.6	2001.8
15°	1933.9	1959.4	1967.9	1980.6	1989.1
17.5°	1900.0	1929.7	1946.7	1959.4	1967.9
20°	1857.6	1887.3	1908.5	1925.5	1938.2
22.5°	1815.2	1840.6	1866.1	1887.3	1900.0
25°	1764.3	1794.0	1823.7	1849.1	1866.1
27.5°	1709.2	1743.1	1781.3	1811.0	1827.9
30°	1658.3	1692.2	1734.6	1772.8	1789.7
32.5°	1598.9	1637.1	1683.7	1721.9	1743.1
35°	1535.3	1577.7	1628.6	1675.2	1696.4
37.5°	1471.7	1514.1	1577.7	1624.3	1645.5
40°	1408.0	1450.5	1518.3	1569.2	1590.4
42.5°	1340.2	1382.6	1454.7	1509.8	1535.3
45°	1272.3	1319.0	1391.1	1450.5	1475.9
47.5°	1204.5	1251.1	1327.5	1391.1	1416.5
50°	1128.1	1179.0	1255.4	1327.5	1352.9
52.5°	1056.0	1106.9	1191.8	1263.8	1289.3
55°	979.7	1034.8	1119.7	1200.2	1229.9
57.5°	903.4	958.5	1047.6	1132.4	1166.3
60°	822.8	882.1	975.5	1064.5	1102.7
62.5°	742.2	805.8	907.6	1000.9	1039.1
65°	661.6	725.2	835.5	941.5	979.7
67.5°	581.0	648.9	767.6	877.9	924.6
70°	500.5	572.5	699.8	814.3	860.9
72.5°	419.9	496.2	636.2	754.9	801.6
75°	339.3	424.1	572.5	695.5	746.4
77.5°	258.7	356.3	517.4	640.4	691.3
80°	186.6	296.9	458.0	585.3	636.2
82.5°	118.8	237.5	407.1	534.4	585.3
85°	63.6	190.8	360.5	487.7	534.4
87.5°	21.2	148.4	313.8	441.1	487.7
90°	0.0	114.5	275.7	394.4	445.3
92.5°	0.0	89.1	241.7	356.3	402.9
95°	0.0	72.1	207.8	318.1	364.7
97.5°	0.0	59.4	182.4	284.2	326.6
100°	0.0	46.7	156.9	254.5	292.6
102.5°	0.0	38.2	135.7	224.8	262.9
105°	0.0	25.4	114.5	199.3	233.3
107.5°	0.0	21.2	97.5	178.1	207.8
110°	0.0	17.0	89.1	152.7	182.4



TEST NUMBER: P1357042

CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	12.7	80.6	135.7	165.4
115°	0.0	12.7	67.9	123.0	144.2
117.5°	0.0	12.7	59.4	110.3	131.5
120°	0.0	8.5	55.1	97.5	118.8
122.5°	0.0	8.5	46.7	89.1	106.0
125°	0.0	8.5	42.4	80.6	93.3
127.5°	0.0	4.2	38.2	72.1	84.8
130°	0.0	4.2	33.9	63.6	76.3
132.5°	0.0	4.2	29.7	59.4	72.1
135°	0.0	0.0	25.4	50.9	63.6
137.5°	0.0	0.0	21.2	46.7	55.1
140°	0.0	0.0	17.0	38.2	50.9
142.5°	0.0	0.0	12.7	33.9	42.4
145°	0.0	0.0	12.7	29.7	33.9
147.5°	0.0	0.0	8.5	21.2	29.7
150°	0.0	0.0	4.2	17.0	21.2
152.5°	0.0	0.0	0.0	12.7	17.0
155°	0.0	0.0	0.0	8.5	12.7
157.5°	0.0	0.0	0.0	0.0	4.2
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357042
 CATALOG NUMBER: 3ASL4-25VHE-3-27-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.08	21.62	20.55	22.07	22.56	22.08	23.62	22.55	24.07	24.56
	3H	21.58	22.98	22.06	23.45	23.97	24.53	25.93	25.01	26.40	26.92
	4H	22.06	23.39	22.56	23.87	24.41	25.72	27.05	26.22	27.53	28.07
	6H	22.33	23.57	22.85	24.07	24.62	26.95	28.19	27.47	28.69	29.24
	8H	22.39	23.57	22.91	24.09	24.65	27.58	28.77	28.11	29.29	29.85
	12H	22.40	23.54	22.93	24.05	24.64	28.27	29.41	28.81	29.93	30.52
4H	2H	20.95	22.28	21.45	22.76	23.30	22.51	23.85	23.02	24.33	24.87
	3H	22.69	23.82	23.20	24.35	24.91	25.19	26.32	25.71	26.85	27.41
	4H	23.29	24.33	23.83	24.87	25.46	26.55	27.59	27.08	28.12	28.72
	6H	23.69	24.61	24.24	25.17	25.77	27.98	28.89	28.53	29.46	30.06
	8H	23.78	24.65	24.34	25.21	25.83	28.72	29.58	29.28	30.14	30.76
	12H	23.83	24.61	24.41	25.20	25.83	29.53	30.31	30.11	30.90	31.53
8H	4H	23.97	24.83	24.53	25.39	26.01	26.77	27.63	27.33	28.19	28.81
	6H	24.54	25.28	25.14	25.88	26.51	28.36	29.10	28.96	29.70	30.32
	8H	24.73	25.39	25.33	26.00	26.64	29.24	29.90	29.85	30.52	31.16
	12H	24.84	25.43	25.45	26.03	26.74	30.24	30.83	30.85	31.44	32.14
12H	4H	24.16	24.94	24.74	25.53	26.15	26.77	27.56	27.36	28.15	28.77
	6H	24.83	25.50	25.44	26.11	26.75	28.40	29.06	29.01	29.68	30.31
	8H	25.11	25.70	25.72	26.31	27.01	29.35	29.94	29.96	30.54	31.25

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-2

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-27-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-27-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 2696
 CIE u': 0.2632
 CIE v': 0.5245
 Duv: -0.0020
 CIE x: 0.4568
 CIE y: 0.4045
 CIE z: 0.1387
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 58.52757
 Rf: 90.1
 Rg: 103.5

CRI (Ra):	94.4		
R1:	97.5	R9:	61.8
R2:	97.8	R10:	93.6
R3:	96.9	R11:	93.7
R4:	95.3	R12:	94.1
R5:	97.2	R13:	97.6
R6:	96.5	R14:	96.8
R7:	91.2	R15:	91.9
R8:	83.2		



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.45



λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

Summary

$R_f = 90.1$
 $R_g = 103.5$
 $CIE R_a = 94.4$
 $R_9 = 61.8$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 89	CES51 = 92	CES76 = 90
CES02 = 64	CES27 = 97	CES52 = 92	CES77 = 84
CES03 = 32	CES28 = 96	CES53 = 88	CES78 = 87
CES04 = 71	CES29 = 83	CES54 = 97	CES79 = 88
CES05 = 51	CES30 = 85	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 69
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 95
CES08 = 43	CES33 = 84	CES58 = 88	CES83 = 91
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 96	CES60 = 99	CES85 = 81
CES11 = 59	CES36 = 98	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 45	CES38 = 89	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 92	CES90 = 93
CES16 = 48	CES41 = 89	CES66 = 92	CES91 = 91
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 97	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 72
CES20 = 68	CES45 = 90	CES70 = 93	CES95 = 88
CES21 = 87	CES46 = 89	CES71 = 95	CES96 = 92
CES22 = 79	CES47 = 79	CES72 = 98	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 89	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 88	CES99 = 92
CES25 = 72	CES50 = 92	CES75 = 94	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)