

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357061

Luminaire Tested: 3ASL4-35VHE-3-30-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 3ASL4-35VHE-3-30-UNV
Description: 3FT 3500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3000K LEDS 3 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10083.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 2.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 94.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357061
CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357061
 CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32144	32144	32144
5°	31834	31523	31408
10°	31631	30895	30614
15°	31256	30119	29941
20°	30757	29376	29182
25°	30182	28447	28318
30°	29576	27640	27587
35°	28827	26729	26775
40°	28137	25893	25918
45°	27395	24884	25059
50°	26549	23805	24166
55°	25634	22770	23362
60°	24449	21564	22547
65°	22948	20402	21871
70°	21035	19247	21342
75°	18271	18183	20978
80°	14132	17367	20823
85°	8219	17115	21131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27395 cd/sqm



TEST NUMBER: P1357061
 CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.2	2.8
10°-20°	807.4	8.0
20°-30°	1220.7	12.1
30°-40°	1478.1	14.7
40°-50°	1552.5	15.4
50°-60°	1448.4	14.4
60°-70°	1197.0	11.9
70°-80°	861.9	8.5
80°-90°	535.6	5.3
90°-100°	313.8	3.1
100°-110°	179.5	1.8
110°-120°	101.4	1.0
120°-130°	58.3	0.6
130°-140°	31.4	0.3
140°-150°	13.2	0.1
150°-160°	2.4	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2309.4	22.9
0°-40°	3787.5	37.6
0°-60°	6788.4	67.3
0°-90°	9382.9	93.1
90°-120°	594.7	5.9
90°-150°	697.7	6.9
90°-180°	700.0	6.9
0°-180°	10083.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2966	2966	2966	2966	2966	
5°	2935	2959	2959	2959	2966	279
15°	2811	2848	2861	2879	2892	793
25°	2565	2608	2651	2688	2713	1181
35°	2232	2294	2368	2435	2466	1397
45°	1850	1917	2022	2109	2146	1427
55°	1424	1504	1628	1745	1788	1273
65°	962	1054	1215	1369	1424	952
75°	493	616	832	1011	1085	522
85°	92	277	524	709	777	113
90°	0	166	401	573	647	4
95°	0	105	302	462	530	0
105°	0	37	166	290	339	0
115°	0	18	99	179	210	0
125°	0	12	62	117	136	0
135°	0	0	37	74	92	0
145°	0	0	18	43	49	0
155°	0	0	0	12	18	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357061
 CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2965.5	2965.5	2965.5	2965.5	2965.5
2.5°	2953.2	2971.7	2971.7	2953.2	2953.2
5°	2934.7	2959.4	2959.4	2959.4	2965.5
7.5°	2916.2	2947.0	2947.0	2947.0	2959.4
10°	2891.6	2922.4	2928.6	2928.6	2934.7
12.5°	2854.6	2891.6	2897.7	2903.9	2910.1
15°	2811.4	2848.4	2860.7	2879.2	2891.6
17.5°	2762.1	2805.2	2829.9	2848.4	2860.7
20°	2700.4	2743.6	2774.4	2799.1	2817.6
22.5°	2638.8	2675.8	2712.8	2743.6	2762.1
25°	2564.8	2608.0	2651.1	2688.1	2712.8
27.5°	2484.6	2534.0	2589.5	2632.6	2657.3
30°	2410.7	2460.0	2521.6	2577.1	2601.8
32.5°	2324.3	2379.8	2447.7	2503.1	2534.0
35°	2231.9	2293.5	2367.5	2435.3	2466.2
37.5°	2139.4	2201.0	2293.5	2361.3	2392.2
40°	2046.9	2108.6	2207.2	2281.2	2312.0
42.5°	1948.3	2009.9	2114.7	2194.9	2231.9
45°	1849.6	1917.4	2022.2	2108.6	2145.6
47.5°	1751.0	1818.8	1929.8	2022.2	2059.2
50°	1640.0	1714.0	1825.0	1929.8	1966.8
52.5°	1535.2	1609.2	1732.5	1837.3	1874.3
55°	1424.2	1504.4	1627.7	1744.8	1788.0
57.5°	1313.2	1393.4	1522.8	1646.2	1695.5
60°	1196.1	1282.4	1418.0	1547.5	1603.0
62.5°	1078.9	1171.4	1319.4	1455.0	1510.5
65°	961.8	1054.3	1214.6	1368.7	1424.2
67.5°	844.7	943.3	1115.9	1276.2	1344.1
70°	727.5	832.3	1017.3	1183.8	1251.6
72.5°	610.4	721.3	924.8	1097.4	1165.3
75°	493.2	616.5	832.3	1011.1	1085.1
77.5°	376.1	517.9	752.2	931.0	1005.0
80°	271.3	431.6	665.9	850.8	924.8
82.5°	172.6	345.3	591.9	776.8	850.8
85°	92.5	277.4	524.1	709.0	776.8
87.5°	30.8	215.8	456.2	641.2	709.0
90°	0.0	166.5	400.7	573.4	647.4
92.5°	0.0	129.5	351.4	517.9	585.7
95°	0.0	104.8	302.1	462.4	530.2
97.5°	0.0	86.3	265.1	413.1	474.7
100°	0.0	67.8	228.1	369.9	425.4
102.5°	0.0	55.5	197.3	326.8	382.3
105°	0.0	37.0	166.5	289.8	339.1
107.5°	0.0	30.8	141.8	258.9	302.1
110°	0.0	24.7	129.5	222.0	265.1



TEST NUMBER: P1357061
 CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	18.5	117.1	197.3	240.4
115°	0.0	18.5	98.6	178.8	209.6
117.5°	0.0	18.5	86.3	160.3	191.1
120°	0.0	12.3	80.1	141.8	172.6
122.5°	0.0	12.3	67.8	129.5	154.1
125°	0.0	12.3	61.7	117.1	135.6
127.5°	0.0	6.2	55.5	104.8	123.3
130°	0.0	6.2	49.3	92.5	111.0
132.5°	0.0	6.2	43.2	86.3	104.8
135°	0.0	0.0	37.0	74.0	92.5
137.5°	0.0	0.0	30.8	67.8	80.1
140°	0.0	0.0	24.7	55.5	74.0
142.5°	0.0	0.0	18.5	49.3	61.7
145°	0.0	0.0	18.5	43.2	49.3
147.5°	0.0	0.0	12.3	30.8	43.2
150°	0.0	0.0	6.2	24.7	30.8
152.5°	0.0	0.0	0.0	18.5	24.7
155°	0.0	0.0	0.0	12.3	18.5
157.5°	0.0	0.0	0.0	0.0	6.2
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357061
 CATALOG NUMBER: 3ASL4-35VHE-3-30-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.38	22.92	21.85	23.37	23.86	23.38	24.92	23.85	25.37	25.86
	3H	22.88	24.28	23.36	24.75	25.27	25.83	27.23	26.31	27.70	28.22
	4H	23.36	24.69	23.86	25.17	25.71	27.02	28.35	27.52	28.83	29.37
	6H	23.63	24.87	24.15	25.37	25.92	28.25	29.49	28.77	29.99	30.54
	8H	23.69	24.87	24.21	25.39	25.95	28.88	30.07	29.41	30.59	31.15
	12H	23.70	24.84	24.23	25.35	25.94	29.57	30.71	30.11	31.22	31.82
4H	2H	22.25	23.58	22.75	24.06	24.60	23.81	25.15	24.32	25.63	26.17
	3H	23.99	25.12	24.50	25.65	26.21	26.49	27.62	27.01	28.15	28.71
	4H	24.59	25.63	25.13	26.17	26.76	27.85	28.89	28.38	29.42	30.02
	6H	24.99	25.91	25.54	26.47	27.07	29.28	30.19	29.83	30.76	31.36
	8H	25.08	25.95	25.64	26.51	27.13	30.01	30.88	30.58	31.44	32.06
	12H	25.13	25.91	25.71	26.50	27.13	30.83	31.61	31.41	32.20	32.83
8H	4H	25.27	26.13	25.83	26.69	27.31	28.07	28.93	28.63	29.49	30.11
	6H	25.84	26.58	26.44	27.18	27.81	29.66	30.40	30.26	31.00	31.62
	8H	26.03	26.69	26.63	27.30	27.94	30.54	31.20	31.15	31.82	32.46
	12H	26.14	26.73	26.75	27.33	28.04	31.54	32.13	32.15	32.74	33.44
12H	4H	25.46	26.24	26.04	26.83	27.45	28.07	28.86	28.66	29.45	30.07
	6H	26.13	26.80	26.74	27.41	28.05	29.70	30.36	30.31	30.98	31.61
	8H	26.41	27.00	27.02	27.61	28.31	30.65	31.24	31.26	31.84	32.55

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-3

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-30-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-30-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3000K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 3005
 CIE u': 0.2513
 CIE v': 0.5178
 Duv: -0.0025
 CIE x: 0.4330
 CIE y: 0.3966
 CIE z: 0.1704
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 49.00645
 Rf: 90.1
 Rg: 103.3

CRI (Ra):	93.9		
R1:	96.5	R9:	62.0
R2:	96.6	R10:	90.8
R3:	95.5	R11:	94.1
R4:	94.4	R12:	88.9
R5:	96.0	R13:	96.4
R6:	96.4	R14:	96.3
R7:	91.7	R15:	91.9
R8:	84.0		



Test Conditions

Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.42

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.76


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

Summary

$R_f = 90.1$
 $R_g = 103.3$
 CIE $R_a = 93.9$
 $R_9 = 62.0$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 93	CES76 = 86
CES02 = 63	CES27 = 97	CES52 = 93	CES77 = 87
CES03 = 32	CES28 = 95	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 98	CES79 = 91
CES05 = 51	CES30 = 87	CES55 = 97	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 90	CES81 = 75
CES07 = 44	CES32 = 80	CES57 = 89	CES82 = 96
CES08 = 42	CES33 = 85	CES58 = 89	CES83 = 92
CES09 = 29	CES34 = 89	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 59	CES36 = 96	CES61 = 98	CES86 = 78
CES12 = 65	CES37 = 92	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 92	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 94	CES89 = 82
CES15 = 72	CES40 = 91	CES65 = 91	CES90 = 94
CES16 = 48	CES41 = 91	CES66 = 93	CES91 = 87
CES17 = 50	CES42 = 88	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 94	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 74
CES20 = 67	CES45 = 90	CES70 = 90	CES95 = 87
CES21 = 86	CES46 = 89	CES71 = 91	CES96 = 92
CES22 = 79	CES47 = 82	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 89	CES73 = 85	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 91	CES99 = 93
CES25 = 72	CES50 = 93	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)