

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357125

Luminaire Tested: 4ASL4-10HE-2-R63-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 4ASL4-10HE-2-R63-UNV
Description: 4FT 1000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND R63 LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1063.9 lumens
Efficiency: N/A
Efficacy: 43.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 3.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 24.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2515	2515	2515
5°	2495	2466	2457
10°	2478	2419	2398
15°	2455	2370	2350
20°	2426	2307	2282
25°	2380	2245	2224
30°	2322	2174	2166
35°	2276	2108	2100
40°	2222	2038	2029
45°	2170	1976	1977
50°	2100	1896	1901
55°	2034	1808	1840
60°	1952	1710	1775
65°	1825	1620	1726
70°	1682	1534	1680
75°	1477	1469	1665
80°	1152	1409	1659
85°	695	1408	1707

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2170 cd/sqm

TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.4	2.8
10°-20°	84.5	7.9
20°-30°	128.0	12.0
30°-40°	154.8	14.6
40°-50°	163.2	15.3
50°-60°	152.4	14.3
60°-70°	125.8	11.8
70°-80°	91.3	8.6
80°-90°	57.6	5.4
90°-100°	34.4	3.2
100°-110°	19.7	1.9
110°-120°	11.2	1.1
120°-130°	6.4	0.6
130°-140°	3.5	0.3
140°-150°	1.5	0.1
150°-160°	0.3	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.9	22.7
0°-40°	396.7	37.3
0°-60°	712.3	67.0
0°-90°	987.0	92.8
90°-120°	65.3	6.1
90°-150°	76.7	7.2
90°-180°	77.0	7.2
0°-180°	1063.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	310	310	310	310	310	
5°	307	310	309	309	310	29
15°	294	298	300	301	303	83
25°	269	273	279	283	285	124
35°	234	240	248	255	258	146
45°	194	202	213	222	226	150
55°	149	158	172	183	188	133
65°	100	111	128	143	150	100
75°	52	65	89	107	115	54
85°	10	30	56	76	84	12
90°	0	18	44	62	70	0
95°	0	12	33	51	58	0
105°	0	4	18	32	37	0
115°	0	2	11	20	23	0
125°	0	1	7	13	15	0
135°	0	0	4	8	10	0
145°	0	0	2	5	6	0
155°	0	0	0	1	2	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	309.9	309.9	309.9	309.9	309.9
2.5°	308.0	310.9	309.9	309.0	309.0
5°	307.0	309.9	309.0	309.0	309.9
7.5°	305.1	308.0	308.0	308.0	309.0
10°	302.1	306.0	306.0	306.0	307.0
12.5°	299.2	302.1	303.1	304.1	305.1
15°	294.3	298.2	300.2	301.2	303.1
17.5°	289.5	292.4	295.3	298.2	299.2
20°	283.6	287.5	290.4	293.4	294.3
22.5°	276.8	280.7	284.6	287.5	289.5
25°	269.0	272.9	278.7	282.6	284.6
27.5°	261.2	265.1	271.9	276.8	278.7
30°	251.5	257.3	264.1	270.0	272.9
32.5°	242.7	248.5	256.3	263.1	265.1
35°	233.9	239.8	248.5	255.4	258.3
37.5°	224.2	231.0	239.8	247.6	250.5
40°	214.4	221.2	231.0	239.8	241.7
42.5°	204.7	211.5	223.2	231.0	233.9
45°	194.0	201.7	213.4	222.2	226.1
47.5°	183.2	191.0	202.7	212.5	216.4
50°	171.5	180.3	193.0	202.7	206.6
52.5°	160.8	169.6	182.3	193.0	197.8
55°	149.1	157.9	171.5	183.2	188.1
57.5°	137.4	146.2	160.8	173.5	178.4
60°	125.7	134.5	149.1	163.7	168.6
62.5°	113.1	122.8	138.4	153.0	158.9
65°	100.4	111.1	127.7	143.3	150.1
67.5°	88.7	99.4	117.0	134.5	140.3
70°	76.0	87.7	107.2	124.8	131.6
72.5°	63.4	76.0	97.5	116.0	122.8
75°	51.7	65.3	88.7	107.2	115.0
77.5°	39.0	55.6	79.9	99.4	106.2
80°	28.3	45.8	71.1	91.6	98.4
82.5°	18.5	37.0	63.4	83.8	90.6
85°	9.7	30.2	56.5	76.0	83.8
87.5°	2.9	23.4	49.7	69.2	76.0
90°	0.0	18.5	43.9	62.4	70.2
92.5°	0.0	14.6	38.0	56.5	63.4
95°	0.0	11.7	33.1	50.7	57.5
97.5°	0.0	9.7	29.2	45.8	51.7
100°	0.0	7.8	25.3	40.9	46.8
102.5°	0.0	5.8	21.4	36.1	41.9
105°	0.0	3.9	18.5	32.2	37.0
107.5°	0.0	2.9	15.6	28.3	33.1
110°	0.0	2.9	14.6	24.4	29.2



TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	1.9	12.7	22.4	26.3
115°	0.0	1.9	10.7	19.5	23.4
117.5°	0.0	1.9	9.7	17.5	21.4
120°	0.0	1.9	8.8	15.6	18.5
122.5°	0.0	1.0	7.8	13.6	16.6
125°	0.0	1.0	6.8	12.7	14.6
127.5°	0.0	1.0	5.8	11.7	13.6
130°	0.0	1.0	5.8	10.7	12.7
132.5°	0.0	0.0	4.9	9.7	11.7
135°	0.0	0.0	3.9	7.8	9.7
137.5°	0.0	0.0	3.9	6.8	8.8
140°	0.0	0.0	2.9	6.8	7.8
142.5°	0.0	0.0	1.9	5.8	6.8
145°	0.0	0.0	1.9	4.9	5.8
147.5°	0.0	0.0	1.0	3.9	4.9
150°	0.0	0.0	1.0	2.9	3.9
152.5°	0.0	0.0	0.0	1.9	2.9
155°	0.0	0.0	0.0	1.0	1.9
157.5°	0.0	0.0	0.0	0.0	1.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357125

CATALOG NUMBER: 4ASL4-10HE-2-R63-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.52	14.05	12.99	14.51	15.00	14.58	16.11	15.05	16.57	17.06
	3H	14.02	15.42	14.50	15.89	16.42	17.03	18.43	17.51	18.90	19.43
	4H	14.50	15.83	15.01	16.32	16.86	18.24	19.57	18.74	20.05	20.60
	6H	14.77	16.01	15.29	16.51	17.07	19.51	20.74	20.03	21.24	21.81
	8H	14.83	16.01	15.36	16.54	17.10	20.17	21.35	20.70	21.88	22.44
	12H	14.84	15.98	15.38	16.50	17.10	20.90	22.03	21.43	22.55	23.15
4H	2H	13.40	14.72	13.90	15.21	15.76	15.01	16.34	15.51	16.82	17.37
	3H	15.14	16.27	15.66	16.80	17.37	17.69	18.82	18.21	19.35	19.92
	4H	15.75	16.78	16.29	17.33	17.92	19.07	20.11	19.61	20.65	21.25
	6H	16.15	17.07	16.71	17.63	18.24	20.54	21.46	21.10	22.02	22.64
	8H	16.25	17.11	16.81	17.68	18.30	21.31	22.17	21.87	22.74	23.36
	12H	16.29	17.08	16.88	17.67	18.30	22.16	22.94	22.75	23.54	24.17
8H	4H	16.44	17.30	17.01	17.87	18.50	19.29	20.15	19.86	20.72	21.35
	6H	17.03	17.76	17.63	18.37	19.00	20.94	21.67	21.53	22.28	22.91
	8H	17.22	17.88	17.83	18.50	19.14	21.85	22.51	22.46	23.13	23.77
	12H	17.34	17.93	17.95	18.54	19.25	22.89	23.48	23.50	24.08	24.79
12H	4H	16.64	17.43	17.23	18.02	18.65	19.30	20.08	19.89	20.68	21.31
	6H	17.33	17.99	17.94	18.61	19.26	20.97	21.64	21.58	22.25	22.90
	8H	17.62	18.21	18.23	18.82	19.53	21.96	22.55	22.57	23.15	23.86

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-7

Test Date: 01/21/2026

Luminaire Tested: 4ASL-2-R630-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-R630-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND RED 630NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 0
 CIE u' : 0.5395
 CIE v' : 0.5190
 Duv: 0.0000
 CIE x: 0.7004
 CIE y: 0.2995
 CIE z: 0.0001
 Peak Wavelength (nm): 638
 Dominant Wavelength (nm): 624
 Purity: 99.9862
 Rf: NR
 Rg: NR

CRI (Ra): 0.0
 R1: 0.0
 R2: 0.0
 R3: 0.0
 R4: 0.0
 R5: 0.0
 R6: 0.0
 R7: 0.0
 R8: 0.0
 R9: 0.0
 R10: 0.0
 R11: 0.0
 R12: 0.0
 R13: 0.0
 R14: 0.0
 R15: 0.0



Test Conditions


Stabilization Time: 69M
 Operation Time: 2H 9M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies outside the range

REPORT NUMBER: SP1-2511-597-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.05

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 0.02


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7





TM-30-18

Summary

$R_f = 0$
 $R_g = 0$
 $CIE R_a = 0.0$
 $R_9 = 0.0$



Color Vector Graphics




REPORT NUMBER: SP1-2511-597-7




TM-30-18

Individual Sample Fidelity Index (R_{fi})

CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)