

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357174

Luminaire Tested: 4ASL4-20HE-2-40-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 4ASL4-20HE-2-40-UNV
Description: 4FT 2000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 4000K LEDS 2 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8356.0 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 3.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 71.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357174
CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357174
 CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19753	19753	19753
5°	19597	19360	19300
10°	19463	19003	18831
15°	19285	18612	18454
20°	19054	18119	17924
25°	18688	17633	17467
30°	18230	17077	17014
35°	17871	16559	16487
40°	17455	16002	15931
45°	17035	15521	15528
50°	16493	14885	14927
55°	15972	14202	14451
60°	15331	13435	13945
65°	14334	12721	13552
70°	13215	12050	13191
75°	11589	11532	13073
80°	9034	11074	13033
85°	5483	11059	13407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17035 cd/sqm



TEST NUMBER: P1357174
 CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.8	2.8
10°-20°	663.5	7.9
20°-30°	1005.4	12.0
30°-40°	1216.0	14.6
40°-50°	1282.0	15.3
50°-60°	1196.5	14.3
60°-70°	987.8	11.8
70°-80°	716.6	8.6
80°-90°	452.8	5.4
90°-100°	270.2	3.2
100°-110°	154.9	1.9
110°-120°	88.0	1.1
120°-130°	50.2	0.6
130°-140°	27.2	0.3
140°-150°	11.9	0.1
150°-160°	2.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1899.8	22.7
0°-40°	3115.8	37.3
0°-60°	5594.2	66.9
0°-90°	7751.4	92.8
90°-120°	513.2	6.1
90°-150°	602.4	7.2
90°-180°	605.0	7.2
0°-180°	8356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2434	2434	2434	2434	2434	
5°	2411	2434	2426	2426	2434	229
15°	2312	2342	2358	2365	2380	652
25°	2112	2143	2189	2220	2235	973
35°	1837	1883	1952	2005	2028	1148
45°	1523	1584	1676	1745	1776	1175
55°	1171	1240	1347	1439	1477	1047
65°	788	873	1003	1125	1179	783
75°	406	513	696	842	903	427
85°	76	237	444	597	658	94
90°	0	145	344	490	551	3
95°	0	92	260	398	452	0
105°	0	31	145	253	291	0
115°	0	15	84	153	184	0
125°	0	8	54	100	115	0
135°	0	0	31	61	76	0
145°	0	0	15	38	46	0
155°	0	0	0	8	15	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357174

CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2434.0	2434.0	2434.0	2434.0	2434.0
2.5°	2418.7	2441.7	2434.0	2426.4	2426.4
5°	2411.1	2434.0	2426.4	2426.4	2434.0
7.5°	2395.7	2418.7	2418.7	2418.7	2426.4
10°	2372.8	2403.4	2403.4	2403.4	2411.1
12.5°	2349.8	2372.8	2380.4	2388.1	2395.7
15°	2311.5	2342.2	2357.5	2365.1	2380.4
17.5°	2273.3	2296.2	2319.2	2342.2	2349.8
20°	2227.4	2258.0	2280.9	2303.9	2311.5
22.5°	2173.8	2204.4	2235.0	2258.0	2273.3
25°	2112.5	2143.2	2189.1	2219.7	2235.0
27.5°	2051.3	2081.9	2135.5	2173.8	2189.1
30°	1974.8	2020.7	2074.3	2120.2	2143.2
32.5°	1905.9	1951.8	2013.0	2066.6	2081.9
35°	1837.0	1882.9	1951.8	2005.4	2028.3
37.5°	1760.5	1814.0	1882.9	1944.2	1967.1
40°	1683.9	1737.5	1814.0	1882.9	1898.2
42.5°	1607.4	1660.9	1752.8	1814.0	1837.0
45°	1523.2	1584.4	1676.3	1745.1	1775.8
47.5°	1439.0	1500.2	1592.1	1668.6	1699.2
50°	1347.1	1416.0	1515.5	1592.1	1622.7
52.5°	1262.9	1331.8	1431.3	1515.5	1553.8
55°	1171.1	1240.0	1347.1	1439.0	1477.2
57.5°	1079.2	1148.1	1262.9	1362.4	1400.7
60°	987.4	1056.3	1171.1	1285.9	1324.2
62.5°	887.9	964.4	1086.9	1201.7	1247.6
65°	788.4	872.6	1002.7	1125.2	1178.7
67.5°	696.5	780.7	918.5	1056.3	1102.2
70°	597.0	688.9	842.0	979.7	1033.3
72.5°	497.5	597.0	765.4	910.8	964.4
75°	405.7	512.8	696.5	842.0	903.2
77.5°	306.2	436.3	627.6	780.7	834.3
80°	222.0	359.7	558.8	719.5	773.1
82.5°	145.4	290.9	497.5	658.3	711.8
85°	76.5	237.3	443.9	597.0	658.3
87.5°	23.0	183.7	390.4	543.4	597.0
90°	0.0	145.4	344.4	489.9	551.1
92.5°	0.0	114.8	298.5	443.9	497.5
95°	0.0	91.8	260.2	398.0	451.6
97.5°	0.0	76.5	229.6	359.7	405.7
100°	0.0	61.2	199.0	321.5	367.4
102.5°	0.0	45.9	168.4	283.2	329.1
105°	0.0	30.6	145.4	252.6	290.9
107.5°	0.0	23.0	122.5	222.0	260.2
110°	0.0	23.0	114.8	191.4	229.6



TEST NUMBER: P1357174

CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	15.3	99.5	176.0	206.7
115°	0.0	15.3	84.2	153.1	183.7
117.5°	0.0	15.3	76.5	137.8	168.4
120°	0.0	15.3	68.9	122.5	145.4
122.5°	0.0	7.7	61.2	107.2	130.1
125°	0.0	7.7	53.6	99.5	114.8
127.5°	0.0	7.7	45.9	91.8	107.2
130°	0.0	7.7	45.9	84.2	99.5
132.5°	0.0	0.0	38.3	76.5	91.8
135°	0.0	0.0	30.6	61.2	76.5
137.5°	0.0	0.0	30.6	53.6	68.9
140°	0.0	0.0	23.0	53.6	61.2
142.5°	0.0	0.0	15.3	45.9	53.6
145°	0.0	0.0	15.3	38.3	45.9
147.5°	0.0	0.0	7.7	30.6	38.3
150°	0.0	0.0	7.7	23.0	30.6
152.5°	0.0	0.0	0.0	15.3	23.0
155°	0.0	0.0	0.0	7.7	15.3
157.5°	0.0	0.0	0.0	0.0	7.7
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357174
 CATALOG NUMBER: 4ASL4-20HE-2-40-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.68	21.21	20.15	21.67	22.16	21.74	23.27	22.21	23.73	24.22
	3H	21.18	22.58	21.66	23.05	23.58	24.19	25.59	24.67	26.06	26.59
	4H	21.66	22.99	22.17	23.47	24.02	25.40	26.73	25.90	27.21	27.76
	6H	21.93	23.17	22.45	23.67	24.23	26.67	27.91	27.19	28.41	28.97
	8H	21.99	23.17	22.52	23.70	24.26	27.33	28.51	27.86	29.04	29.60
	12H	22.00	23.14	22.54	23.66	24.26	28.06	29.19	28.59	29.71	30.31
4H	2H	20.56	21.88	21.06	22.37	22.92	22.17	23.49	22.67	23.98	24.53
	3H	22.30	23.43	22.82	23.96	24.53	24.85	25.98	25.37	26.51	27.08
	4H	22.91	23.94	23.45	24.49	25.08	26.23	27.27	26.77	27.81	28.41
	6H	23.31	24.23	23.87	24.79	25.40	27.70	28.62	28.26	29.18	29.80
	8H	23.41	24.27	23.97	24.84	25.46	28.47	29.33	29.03	29.90	30.52
	12H	23.45	24.24	24.04	24.83	25.46	29.32	30.11	29.91	30.70	31.33
8H	4H	23.60	24.46	24.17	25.03	25.66	26.45	27.31	27.02	27.88	28.51
	6H	24.19	24.92	24.79	25.53	26.16	28.10	28.83	28.69	29.44	30.07
	8H	24.38	25.04	24.99	25.66	26.30	29.01	29.67	29.62	30.29	30.93
	12H	24.50	25.09	25.11	25.70	26.41	30.05	30.64	30.66	31.25	31.96
12H	4H	23.80	24.59	24.39	25.18	25.81	26.46	27.24	27.05	27.84	28.47
	6H	24.49	25.15	25.10	25.77	26.42	28.14	28.80	28.74	29.42	30.06
	8H	24.78	25.37	25.39	25.98	26.69	29.12	29.71	29.73	30.31	31.02

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-4

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-40-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-40-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 4000K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 4015
 CIE u': 0.2259
 CIE v': 0.4990
 Duv: -0.0019
 CIE x: 0.3785
 CIE y: 0.3715
 CIE z: 0.2500
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 580
 Purity: 25.06827
 R_f: 90.7
 R_g: 100.2

CRI (Ra):	93.9		
R1:	95.7	R9:	66.3
R2:	96.3	R10:	89.1
R3:	94.8	R11:	95.0
R4:	95.2	R12:	73.8
R5:	94.6	R13:	96.0
R6:	93.5	R14:	96.4
R7:	94.0	R15:	93.2
R8:	87.2		



Test Conditions


Stabilization Time: 23M
 Operation Time: 1H 23M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4015K
 CIE x = 0.3785
 CIE y = 0.3715
 Duv = -0.0019

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.79

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-4

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.74




λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

Summary

$R_f = 90.7$
 $R_g = 100.2$
 CIE $R_a = 93.9$
 $R_9 = 66.3$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 92	CES51 = 98	CES76 = 84
CES02 = 62	CES27 = 91	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 95	CES53 = 97	CES78 = 81
CES04 = 69	CES29 = 95	CES54 = 93	CES79 = 94
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 92
CES06 = 50	CES31 = 95	CES56 = 95	CES81 = 81
CES07 = 42	CES32 = 87	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 97	CES84 = 93
CES10 = 74	CES35 = 95	CES60 = 92	CES85 = 81
CES11 = 57	CES36 = 80	CES61 = 92	CES86 = 84
CES12 = 63	CES37 = 93	CES62 = 85	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 92	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 85
CES15 = 71	CES40 = 97	CES65 = 88	CES90 = 98
CES16 = 47	CES41 = 97	CES66 = 86	CES91 = 71
CES17 = 49	CES42 = 91	CES67 = 85	CES92 = 77
CES18 = 56	CES43 = 91	CES68 = 87	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 76
CES20 = 66	CES45 = 95	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 96	CES71 = 78	CES96 = 92
CES22 = 78	CES47 = 94	CES72 = 93	CES97 = 95
CES23 = 91	CES48 = 92	CES73 = 78	CES98 = 95
CES24 = 90	CES49 = 95	CES74 = 91	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)