

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357098

Luminaire Tested: 4ASL4-10-1-35-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-6)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 4ASL4-10-1-35-UNV
Description: 4FT 1000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS 1 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4032.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 3.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357098
CATALOG NUMBER: 4ASL4-10-1-35-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357098

CATALOG NUMBER: 4ASL4-10-1-35-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	94		
1	106	100	95	91	102	97	93	89	92	88	85	87	84	81	82	80	78	75		
2	95	86	79	73	92	84	77	71	79	74	69	75	70	66	71	67	64	61		
3	87	76	67	60	84	73	65	59	69	63	57	66	60	55	62	58	54	51		
4	79	67	57	50	76	65	56	50	62	54	48	58	52	47	56	50	46	43		
5	73	59	50	43	70	58	49	43	55	47	42	52	46	41	50	44	40	37		
6	67	53	44	38	65	52	43	37	50	42	36	47	41	35	45	39	35	32		
7	62	48	39	33	60	47	39	33	45	37	32	43	36	31	41	35	31	29		
8	58	44	35	29	56	43	35	29	41	34	29	39	33	28	38	32	27	25		
9	54	40	32	26	52	39	32	26	38	31	26	36	30	25	35	29	25	23		
10	51	37	29	24	49	36	29	24	35	28	23	34	27	23	32	27	22	21		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9773	9773	9773
5°	9678	9577	9528
10°	9622	9382	9278
15°	9525	9175	9083
20°	9382	8939	8842
25°	9207	8658	8582
30°	9017	8400	8339
35°	8827	8137	8095
40°	8614	7871	7844
45°	8410	7581	7588
50°	8174	7279	7319
55°	7878	6937	7050
60°	7552	6580	6814
65°	7134	6205	6579
70°	6483	5810	6349
75°	5641	5459	6172
80°	4492	5157	6064
85°	2637	4955	6104

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8410 cd/sqm

TEST NUMBER: P1357098

CATALOG NUMBER: 4ASL4-10-1-35-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	2.8
10°-20°	327.4	8.1
20°-30°	495.0	12.3
30°-40°	598.3	14.8
40°-50°	629.1	15.6
50°-60°	586.0	14.5
60°-70°	481.5	11.9
70°-80°	341.8	8.5
80°-90°	206.1	5.1
90°-100°	115.4	2.9
100°-110°	63.9	1.6
110°-120°	35.6	0.9
120°-130°	20.5	0.5
130°-140°	11.2	0.3
140°-150°	5.0	0.1
150°-160°	1.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.4	23.2
0°-40°	1534.7	38.1
0°-60°	2749.8	68.2
0°-90°	3779.1	93.7
90°-120°	215.0	5.3
90°-150°	251.8	6.2
90°-180°	253.0	6.3
0°-180°	4032.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1204	1204	1204	1204	1204	
5°	1191	1202	1200	1199	1202	113
15°	1142	1157	1162	1168	1172	322
25°	1041	1060	1075	1090	1098	480
35°	907	930	959	984	996	567
45°	752	779	819	853	868	580
55°	578	610	658	702	721	517
65°	392	428	489	546	572	387
75°	198	248	330	398	426	211
85°	37	106	199	272	300	46
90°	0	63	148	218	244	1
95°	0	37	109	172	196	0
105°	0	14	57	104	123	0
115°	0	7	35	63	75	0
125°	0	4	22	41	48	0
135°	0	1	14	26	33	0
145°	1	0	5	15	19	1
155°	1	1	0	4	5	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357098

CATALOG NUMBER: 4ASL4-10-1-35-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1204.3	1204.3	1204.3	1204.3	1204.3
2.5°	1196.2	1207.0	1204.3	1198.9	1198.9
5°	1190.7	1201.6	1200.2	1198.9	1201.6
7.5°	1183.9	1194.8	1194.8	1196.2	1198.9
10°	1173.0	1186.6	1186.6	1186.6	1188.0
12.5°	1159.4	1173.0	1175.7	1177.1	1179.8
15°	1141.7	1156.6	1162.1	1167.5	1171.6
17.5°	1121.2	1136.2	1145.7	1152.6	1159.4
20°	1096.7	1113.0	1125.3	1133.5	1140.3
22.5°	1070.8	1087.2	1099.4	1111.7	1119.9
25°	1040.8	1059.9	1074.9	1089.9	1098.1
27.5°	1010.9	1029.9	1049.0	1066.7	1076.3
30°	976.8	998.6	1020.4	1040.8	1050.4
32.5°	941.4	964.5	990.4	1012.2	1023.1
35°	907.3	930.5	959.1	983.6	995.9
37.5°	870.5	893.7	926.4	953.7	965.9
40°	831.0	856.9	892.3	921.0	934.6
42.5°	792.9	818.8	856.9	888.3	901.9
45°	752.0	779.3	818.8	852.8	867.8
47.5°	709.8	738.4	780.6	816.1	832.4
50°	667.6	697.5	741.1	779.3	795.6
52.5°	622.6	653.9	700.3	741.1	758.8
55°	577.6	610.3	658.0	701.6	720.7
57.5°	532.7	565.4	617.1	663.5	683.9
60°	486.4	520.4	573.6	624.0	647.1
62.5°	438.7	474.1	530.0	584.5	609.0
65°	392.4	427.8	489.1	546.3	572.2
67.5°	343.3	381.5	446.9	506.8	534.0
70°	292.9	336.5	406.0	470.0	497.3
72.5°	247.9	292.9	367.8	433.2	461.8
75°	197.5	247.9	329.7	397.8	426.4
77.5°	153.9	208.4	294.3	363.7	392.4
80°	110.4	170.3	260.2	331.1	359.7
82.5°	70.8	136.2	228.9	301.1	328.3
85°	36.8	106.3	198.9	272.5	299.7
87.5°	10.9	81.7	171.7	243.9	271.1
90°	0.0	62.7	148.5	218.0	243.9
92.5°	0.0	47.7	128.1	194.8	220.7
95°	0.0	36.8	109.0	171.7	196.2
97.5°	0.0	28.6	94.0	151.2	175.7
100°	0.0	23.2	80.4	133.5	156.7
102.5°	0.0	19.1	69.5	118.5	139.0
105°	0.0	13.6	57.2	103.5	122.6
107.5°	0.0	9.5	50.4	91.3	107.6
110°	0.0	8.2	45.0	79.0	95.4

TEST NUMBER: P1357098

CATALOG NUMBER: 4ASL4-10-1-35-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	6.8	39.5	70.8	84.5
115°	0.0	6.8	35.4	62.7	74.9
117.5°	0.0	5.4	30.0	55.9	66.8
120°	0.0	5.4	27.2	50.4	59.9
122.5°	0.0	4.1	24.5	45.0	54.5
125°	0.0	4.1	21.8	40.9	47.7
127.5°	0.0	2.7	19.1	36.8	43.6
130°	0.0	2.7	17.7	32.7	39.5
132.5°	0.0	1.4	16.3	30.0	35.4
135°	0.0	1.4	13.6	25.9	32.7
137.5°	0.0	0.0	12.3	23.2	28.6
140°	0.0	0.0	9.5	20.4	25.9
142.5°	1.4	0.0	8.2	17.7	21.8
145°	1.4	0.0	5.4	15.0	19.1
147.5°	1.4	1.4	4.1	12.3	15.0
150°	1.4	1.4	2.7	8.2	12.3
152.5°	1.4	1.4	1.4	5.4	8.2
155°	1.4	1.4	0.0	4.1	5.4
157.5°	1.4	1.4	0.0	1.4	2.7
160°	1.4	1.4	0.0	0.0	1.4
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357098

CATALOG NUMBER: 4ASL4-10-1-35-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.33	18.88	17.79	19.32	19.79	19.31	20.86	19.77	21.30	21.77
	3H	18.82	20.23	19.29	20.68	21.19	21.72	23.13	22.19	23.58	24.09
	4H	19.29	20.63	19.78	21.10	21.63	22.88	24.22	23.38	24.69	25.22
	6H	19.57	20.82	20.08	21.30	21.84	24.09	25.34	24.60	25.82	26.36
	8H	19.62	20.82	20.14	21.33	21.87	24.71	25.91	25.23	26.42	26.96
	12H	19.63	20.78	20.16	21.28	21.86	25.39	26.54	25.92	27.04	27.62
4H	2H	18.19	19.53	18.68	20.00	20.52	19.74	21.08	20.24	21.55	22.08
	3H	19.92	21.06	20.42	21.57	22.12	22.38	23.52	22.88	24.03	24.58
	4H	20.52	21.56	21.04	22.09	22.66	23.71	24.75	24.23	25.28	25.86
	6H	20.91	21.83	21.46	22.39	22.98	25.11	26.03	25.65	26.58	27.17
	8H	21.01	21.87	21.56	22.42	23.03	25.83	26.70	26.38	27.25	27.85
	12H	21.05	21.84	21.62	22.42	23.03	26.64	27.42	27.21	28.00	28.61
8H	4H	21.17	22.03	21.72	22.59	23.19	23.92	24.79	24.47	25.34	25.94
	6H	21.74	22.47	22.32	23.06	23.68	25.48	26.22	26.07	26.81	27.42
	8H	21.91	22.58	22.51	23.18	23.80	26.35	27.01	26.94	27.62	28.24
	12H	22.02	22.61	22.62	23.21	23.90	27.34	27.93	27.93	28.52	29.21
12H	4H	21.35	22.14	21.92	22.72	23.33	23.93	24.72	24.50	25.30	25.91
	6H	22.01	22.67	22.61	23.28	23.90	25.52	26.18	26.12	26.79	27.41
	8H	22.28	22.87	22.88	23.46	24.16	26.45	27.04	27.05	27.64	28.33

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-1

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-35-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-35-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 3487
 CIE u' : 0.2366
 CIE v' : 0.5099
 Duv: -0.0012
 CIE x: 0.4047
 CIE y: 0.3876
 CIE z: 0.2077
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.79273
 R_f: 90
 R_g: 102.4

CRI (Ra): 92.5
 R1: 94.7
 R2: 94.3
 R3: 92.9
 R4: 93.3
 R5: 93.9
 R6: 93.4
 R7: 92.5
 R8: 85.2
 R9: 61.3
 R10: 85.5
 R11: 93.7
 R12: 80.8
 R13: 94.3
 R14: 95.1
 R15: 90.9



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.15


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1





TM-30-18

Summary

$R_f = 90$
 $R_g = 102.4$
 $CIE R_a = 92.5$
 $R_9 = 61.3$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 87	CES51 = 95	CES76 = 82
CES02 = 62	CES27 = 96	CES52 = 94	CES77 = 89
CES03 = 31	CES28 = 93	CES53 = 90	CES78 = 79
CES04 = 70	CES29 = 84	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 89	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 91	CES81 = 81
CES07 = 43	CES32 = 80	CES57 = 90	CES82 = 96
CES08 = 41	CES33 = 86	CES58 = 91	CES83 = 94
CES09 = 29	CES34 = 88	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 93	CES60 = 97	CES85 = 84
CES11 = 58	CES36 = 93	CES61 = 96	CES86 = 82
CES12 = 64	CES37 = 91	CES62 = 98	CES87 = 90
CES13 = 43	CES38 = 95	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 93	CES89 = 83
CES15 = 71	CES40 = 92	CES65 = 90	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 91	CES91 = 83
CES17 = 49	CES42 = 87	CES67 = 91	CES92 = 80
CES18 = 56	CES43 = 85	CES68 = 91	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 75
CES20 = 66	CES45 = 90	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 90	CES71 = 85	CES96 = 91
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 90
CES23 = 91	CES48 = 91	CES73 = 80	CES98 = 91
CES24 = 90	CES49 = 88	CES74 = 94	CES99 = 92
CES25 = 71	CES50 = 94	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)