

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357217

Luminaire Tested: 4ASL4-30VHE-3-30-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 4ASL4-30VHE-3-30-UNV
Description: 4FT 3000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3000K LEDS 3 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11540.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 3.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 105.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357217
CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357217
 CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27544	27544	27544
5°	27299	27025	26913
10°	27146	26501	26233
15°	26845	25849	25656
20°	26439	25224	25005
25°	25967	24440	24265
30°	25469	23759	23638
35°	24851	22989	22942
40°	24285	22283	22209
45°	23675	21431	21472
50°	22980	20515	20707
55°	22231	19640	20018
60°	21254	18618	19319
65°	20014	17636	18741
70°	18430	16662	18286
75°	16125	15772	17975
80°	12635	15103	17842
85°	7582	14944	18107

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23675 cd/sqm



TEST NUMBER: P1357217
 CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.8	2.8
10°-20°	924.1	8.0
20°-30°	1397.1	12.1
30°-40°	1691.7	14.7
40°-50°	1776.8	15.4
50°-60°	1657.7	14.4
60°-70°	1370.0	11.9
70°-80°	986.4	8.5
80°-90°	613.0	5.3
90°-100°	359.2	3.1
100°-110°	205.5	1.8
110°-120°	116.0	1.0
120°-130°	66.8	0.6
130°-140°	36.0	0.3
140°-150°	15.1	0.1
150°-160°	2.8	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2643.1	22.9
0°-40°	4334.8	37.6
0°-60°	7769.3	67.3
0°-90°	10738.7	93.1
90°-120°	680.7	5.9
90°-150°	798.5	6.9
90°-180°	801.0	6.9
0°-180°	11540.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3394	3394	3394	3394	3394	
5°	3359	3387	3387	3387	3394	319
15°	3218	3260	3274	3295	3309	907
25°	2935	2985	3034	3076	3105	1352
35°	2554	2625	2710	2787	2822	1599
45°	2117	2194	2314	2413	2456	1633
55°	1630	1722	1863	1997	2046	1456
65°	1101	1207	1390	1566	1630	1089
75°	564	706	953	1157	1242	597
85°	106	318	600	812	889	129
90°	0	190	459	656	741	5
95°	0	120	346	529	607	0
105°	0	42	190	332	388	0
115°	0	21	113	205	240	0
125°	0	14	71	134	155	0
135°	0	0	42	85	106	0
145°	0	0	21	49	56	0
155°	0	0	0	14	21	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357217
 CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3394.1	3394.1	3394.1	3394.1	3394.1
2.5°	3380.0	3401.1	3401.1	3380.0	3380.0
5°	3358.8	3387.0	3387.0	3387.0	3394.1
7.5°	3337.6	3372.9	3372.9	3372.9	3387.0
10°	3309.4	3344.7	3351.7	3351.7	3358.8
12.5°	3267.1	3309.4	3316.4	3323.5	3330.6
15°	3217.7	3260.0	3274.1	3295.3	3309.4
17.5°	3161.2	3210.6	3238.8	3260.0	3274.1
20°	3090.6	3140.0	3175.3	3203.5	3224.7
22.5°	3020.1	3062.4	3104.8	3140.0	3161.2
25°	2935.4	2984.8	3034.2	3076.5	3104.8
27.5°	2843.7	2900.1	2963.6	3013.0	3041.3
30°	2759.0	2815.5	2886.0	2949.5	2977.7
32.5°	2660.2	2723.7	2801.3	2864.8	2900.1
35°	2554.4	2624.9	2709.6	2787.2	2822.5
37.5°	2448.5	2519.1	2624.9	2702.6	2737.8
40°	2342.7	2413.2	2526.1	2610.8	2646.1
42.5°	2229.8	2300.3	2420.3	2512.0	2554.4
45°	2116.9	2194.5	2314.5	2413.2	2455.6
47.5°	2004.0	2081.6	2208.6	2314.5	2356.8
50°	1877.0	1961.6	2088.7	2208.6	2251.0
52.5°	1757.0	1841.7	1982.8	2102.8	2145.1
55°	1630.0	1721.7	1862.9	1996.9	2046.3
57.5°	1503.0	1594.7	1742.9	1884.0	1940.5
60°	1368.9	1467.7	1622.9	1771.1	1834.6
62.5°	1234.8	1340.7	1510.0	1665.3	1728.8
65°	1100.8	1206.6	1390.1	1566.5	1630.0
67.5°	966.7	1079.6	1277.2	1460.6	1538.3
70°	832.6	952.6	1164.3	1354.8	1432.4
72.5°	698.6	825.6	1058.4	1256.0	1333.6
75°	564.5	705.6	952.6	1157.2	1241.9
77.5°	430.4	592.7	860.9	1065.5	1150.2
80°	310.5	493.9	762.1	973.8	1058.4
82.5°	197.6	395.2	677.4	889.1	973.8
85°	105.8	317.5	599.8	811.5	889.1
87.5°	35.3	247.0	522.2	733.9	811.5
90°	0.0	190.5	458.7	656.2	740.9
92.5°	0.0	148.2	402.2	592.7	670.3
95°	0.0	120.0	345.8	529.2	606.8
97.5°	0.0	98.8	303.4	472.8	543.3
100°	0.0	77.6	261.1	423.4	486.9
102.5°	0.0	63.5	225.8	374.0	437.5
105°	0.0	42.3	190.5	331.6	388.1
107.5°	0.0	35.3	162.3	296.4	345.8
110°	0.0	28.2	148.2	254.0	303.4



TEST NUMBER: P1357217
 CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	21.2	134.1	225.8	275.2
115°	0.0	21.2	112.9	204.6	239.9
117.5°	0.0	21.2	98.8	183.5	218.7
120°	0.0	14.1	91.7	162.3	197.6
122.5°	0.0	14.1	77.6	148.2	176.4
125°	0.0	14.1	70.6	134.1	155.2
127.5°	0.0	7.1	63.5	120.0	141.1
130°	0.0	7.1	56.5	105.8	127.0
132.5°	0.0	7.1	49.4	98.8	120.0
135°	0.0	0.0	42.3	84.7	105.8
137.5°	0.0	0.0	35.3	77.6	91.7
140°	0.0	0.0	28.2	63.5	84.7
142.5°	0.0	0.0	21.2	56.5	70.6
145°	0.0	0.0	21.2	49.4	56.5
147.5°	0.0	0.0	14.1	35.3	49.4
150°	0.0	0.0	7.1	28.2	35.3
152.5°	0.0	0.0	0.0	21.2	28.2
155°	0.0	0.0	0.0	14.1	21.2
157.5°	0.0	0.0	0.0	0.0	7.1
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357217
 CATALOG NUMBER: 4ASL4-30VHE-3-30-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.85	22.39	21.32	22.85	23.33	22.88	24.42	23.35	24.87	25.36
	3H	22.35	23.75	22.83	24.22	24.74	25.34	26.75	25.82	27.21	27.74
	4H	22.83	24.16	23.33	24.64	25.18	26.54	27.87	27.04	28.35	28.89
	6H	23.11	24.35	23.62	24.84	25.40	27.79	29.03	28.31	29.53	30.08
	8H	23.16	24.35	23.69	24.87	25.43	28.44	29.63	28.97	30.15	30.71
	12H	23.17	24.31	23.71	24.82	25.41	29.15	30.29	29.68	30.80	31.39
4H	2H	21.73	23.06	22.23	23.54	24.08	23.31	24.65	23.82	25.13	25.67
	3H	23.46	24.60	23.98	25.12	25.69	26.00	27.14	26.52	27.66	28.22
	4H	24.07	25.11	24.60	25.64	26.24	27.37	28.41	27.91	28.95	29.54
	6H	24.47	25.38	25.02	25.95	26.55	28.82	29.73	29.37	30.29	30.90
	8H	24.56	25.42	25.12	25.99	26.61	29.57	30.43	30.13	30.99	31.61
	12H	24.61	25.39	25.19	25.98	26.60	30.40	31.19	30.98	31.78	32.40
8H	4H	24.75	25.61	25.31	26.18	26.79	27.59	28.45	28.15	29.01	29.63
	6H	25.33	26.06	25.92	26.66	27.29	29.20	29.93	29.79	30.54	31.16
	8H	25.51	26.17	26.12	26.79	27.42	30.09	30.76	30.70	31.37	32.01
	12H	25.63	26.22	26.23	26.82	27.52	31.12	31.71	31.72	32.31	33.01
12H	4H	24.94	25.73	25.53	26.32	26.94	27.60	28.38	28.18	28.97	29.59
	6H	25.62	26.28	26.23	26.90	27.54	29.24	29.90	29.84	30.51	31.15
	8H	25.90	26.49	26.51	27.10	27.80	30.20	30.79	30.81	31.39	32.10

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-3

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-30-UNV-OPL-1_600mA


Data in this report applies to families of products including 4ASL

REPORT NUMBER: SP1-2511-597-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.42

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.76



λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

Summary

$R_f = 90.1$
 $R_g = 103.3$
 CIE $R_a = 93.9$
 $R_9 = 62.0$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 88	CES51 = 93	CES76 = 86
CES02 = 63	CES27 = 97	CES52 = 93	CES77 = 87
CES03 = 32	CES28 = 95	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 98	CES79 = 91
CES05 = 51	CES30 = 87	CES55 = 97	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 90	CES81 = 75
CES07 = 44	CES32 = 80	CES57 = 89	CES82 = 96
CES08 = 42	CES33 = 85	CES58 = 89	CES83 = 92
CES09 = 29	CES34 = 89	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 59	CES36 = 96	CES61 = 98	CES86 = 78
CES12 = 65	CES37 = 92	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 92	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 94	CES89 = 82
CES15 = 72	CES40 = 91	CES65 = 91	CES90 = 94
CES16 = 48	CES41 = 91	CES66 = 93	CES91 = 87
CES17 = 50	CES42 = 88	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 94	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 74
CES20 = 67	CES45 = 90	CES70 = 90	CES95 = 87
CES21 = 86	CES46 = 89	CES71 = 91	CES96 = 92
CES22 = 79	CES47 = 82	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 89	CES73 = 85	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 91	CES99 = 93
CES25 = 72	CES50 = 93	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)