

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357341

Luminaire Tested: 6ASL4-20VHE-3-35-UNV

Issue Date: 2/17/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1357341  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: 6ASL4-20VHE-3-35-UNV  
Description: 6FT 2000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS 3 ROW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12000.0 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 5.98' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 100.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1357341  
CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P1357341  
 CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19061	19061	19061
5°	18906	18712	18625
10°	18815	18358	18154
15°	18621	17916	17755
20°	18355	17492	17304
25°	18043	16957	16792
30°	17714	16494	16358
35°	17302	15968	15877
40°	16928	15488	15369
45°	16525	14905	14860
50°	16066	14279	14330
55°	15573	13681	13853
60°	14926	12983	13370
65°	14102	12313	12969
70°	13047	11650	12655
75°	11501	11050	12440
80°	9140	10610	12347
85°	5690	10541	12530

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16525 cd/sqm



TEST NUMBER: P1357341  
 CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	334.7	2.8
10°-20°	960.9	8.0
20°-30°	1452.8	12.1
30°-40°	1759.2	14.7
40°-50°	1847.6	15.4
50°-60°	1723.8	14.4
60°-70°	1424.6	11.9
70°-80°	1025.7	8.5
80°-90°	637.4	5.3
90°-100°	373.5	3.1
100°-110°	213.7	1.8
110°-120°	120.6	1.0
120°-130°	69.4	0.6
130°-140°	37.4	0.3
140°-150°	15.7	0.1
150°-160°	2.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2748.4	22.9
0°-40°	4507.6	37.6
0°-60°	8079.0	67.3
0°-90°	11166.8	93.1
90°-120°	707.8	5.9
90°-150°	830.3	6.9
90°-180°	833.0	6.9
0°-180°	12000.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3529	3529	3529	3529	3529	
5°	3493	3522	3522	3522	3529	332
15°	3346	3390	3405	3427	3441	943
25°	3052	3104	3155	3199	3228	1406
35°	2656	2730	2818	2898	2935	1663
45°	2201	2282	2407	2509	2554	1698
55°	1695	1790	1937	2076	2128	1514
65°	1145	1255	1446	1629	1695	1133
75°	587	734	991	1203	1291	621
85°	110	330	624	844	924	135
90°	0	198	477	682	770	5
95°	0	125	360	550	631	0
105°	0	44	198	345	404	0
115°	0	22	117	213	250	0
125°	0	15	73	139	161	0
135°	0	0	44	88	110	0
145°	0	0	22	51	59	0
155°	0	0	0	15	22	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357341  
 CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3529.4	3529.4	3529.4	3529.4	3529.4
2.5°	3514.7	3536.7	3536.7	3514.7	3514.7
5°	3492.7	3522.0	3522.0	3522.0	3529.4
7.5°	3470.7	3507.3	3507.3	3507.3	3522.0
10°	3441.3	3478.0	3485.3	3485.3	3492.7
12.5°	3397.3	3441.3	3448.6	3456.0	3463.3
15°	3345.9	3389.9	3404.6	3426.6	3441.3
17.5°	3287.2	3338.6	3367.9	3389.9	3404.6
20°	3213.8	3265.2	3301.9	3331.2	3353.3
22.5°	3140.5	3184.5	3228.5	3265.2	3287.2
25°	3052.4	3103.8	3155.1	3199.2	3228.5
27.5°	2957.0	3015.7	3081.8	3133.1	3162.5
30°	2869.0	2927.7	3001.1	3067.1	3096.4
32.5°	2766.3	2832.3	2913.0	2979.0	3015.7
35°	2656.2	2729.6	2817.6	2898.3	2935.0
37.5°	2546.1	2619.5	2729.6	2810.3	2847.0
40°	2436.1	2509.4	2626.8	2714.9	2751.6
42.5°	2318.7	2392.0	2516.8	2612.2	2656.2
45°	2201.3	2282.0	2406.7	2509.4	2553.5
47.5°	2083.9	2164.6	2296.7	2406.7	2450.7
50°	1951.8	2039.8	2171.9	2296.7	2340.7
52.5°	1827.0	1915.1	2061.9	2186.6	2230.6
55°	1695.0	1790.4	1937.1	2076.5	2127.9
57.5°	1562.9	1658.3	1812.4	1959.1	2017.8
60°	1423.5	1526.2	1687.6	1841.7	1907.8
62.5°	1284.1	1394.1	1570.2	1731.7	1797.7
65°	1144.7	1254.7	1445.5	1628.9	1695.0
67.5°	1005.2	1122.6	1328.1	1518.9	1599.6
70°	865.8	990.6	1210.7	1408.8	1489.5
72.5°	726.4	858.5	1100.6	1306.1	1386.8
75°	587.0	733.8	990.6	1203.4	1291.4
77.5°	447.6	616.4	895.2	1108.0	1196.0
80°	322.9	513.6	792.5	1012.6	1100.6
82.5°	205.5	410.9	704.4	924.5	1012.6
85°	110.1	330.2	623.7	843.8	924.5
87.5°	36.7	256.8	543.0	763.1	843.8
90°	0.0	198.1	476.9	682.4	770.4
92.5°	0.0	154.1	418.2	616.4	697.1
95°	0.0	124.7	359.5	550.3	631.0
97.5°	0.0	102.7	315.5	491.6	565.0
100°	0.0	80.7	271.5	440.3	506.3
102.5°	0.0	66.0	234.8	388.9	454.9
105°	0.0	44.0	198.1	344.9	403.6
107.5°	0.0	36.7	168.8	308.2	359.5
110°	0.0	29.4	154.1	264.2	315.5



TEST NUMBER: P1357341  
 CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	22.0	139.4	234.8	286.2
115°	0.0	22.0	117.4	212.8	249.5
117.5°	0.0	22.0	102.7	190.8	227.5
120°	0.0	14.7	95.4	168.8	205.5
122.5°	0.0	14.7	80.7	154.1	183.4
125°	0.0	14.7	73.4	139.4	161.4
127.5°	0.0	7.3	66.0	124.7	146.8
130°	0.0	7.3	58.7	110.1	132.1
132.5°	0.0	7.3	51.4	102.7	124.7
135°	0.0	0.0	44.0	88.1	110.1
137.5°	0.0	0.0	36.7	80.7	95.4
140°	0.0	0.0	29.4	66.0	88.1
142.5°	0.0	0.0	22.0	58.7	73.4
145°	0.0	0.0	22.0	51.4	58.7
147.5°	0.0	0.0	14.7	36.7	51.4
150°	0.0	0.0	7.3	29.4	36.7
152.5°	0.0	0.0	0.0	22.0	29.4
155°	0.0	0.0	0.0	14.7	22.0
157.5°	0.0	0.0	0.0	0.0	7.3
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357341  
 CATALOG NUMBER: 6ASL4-20VHE-3-35-UNV

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.58	21.12	20.05	21.58	22.06	21.64	23.18	22.11	23.63	24.12
	3H	21.08	22.48	21.56	22.95	23.47	24.11	25.52	24.60	25.98	26.51
	4H	21.56	22.89	22.06	23.37	23.91	25.32	26.65	25.82	27.14	27.67
	6H	21.84	23.08	22.35	23.57	24.13	26.59	27.83	27.11	28.33	28.88
	8H	21.89	23.08	22.42	23.60	24.16	27.26	28.44	27.78	28.96	29.52
	12H	21.90	23.04	22.44	23.55	24.14	27.99	29.13	28.52	29.64	30.23
4H	2H	20.47	21.80	20.97	22.28	22.82	22.07	23.40	22.57	23.89	24.42
	3H	22.20	23.34	22.72	23.86	24.42	24.77	25.91	25.29	26.43	26.99
	4H	22.81	23.84	23.34	24.38	24.97	26.15	27.19	26.69	27.73	28.32
	6H	23.20	24.12	23.76	24.68	25.29	27.61	28.53	28.17	29.09	29.70
	8H	23.30	24.16	23.86	24.72	25.34	28.38	29.24	28.94	29.81	30.43
	12H	23.34	24.13	23.92	24.72	25.34	29.24	30.02	29.82	30.61	31.24
8H	4H	23.49	24.36	24.05	24.92	25.54	26.37	27.23	26.93	27.79	28.41
	6H	24.07	24.80	24.66	25.41	26.03	28.00	28.73	28.59	29.33	29.96
	8H	24.25	24.91	24.86	25.53	26.17	28.91	29.57	29.51	30.18	30.82
	12H	24.37	24.96	24.98	25.56	26.27	29.95	30.54	30.56	31.14	31.85
12H	4H	23.69	24.47	24.27	25.06	25.69	26.38	27.16	26.96	27.75	28.37
	6H	24.37	25.03	24.97	25.65	26.28	28.04	28.70	28.64	29.31	29.95
	8H	24.65	25.24	25.26	25.84	26.55	29.01	29.60	29.62	30.20	30.91

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-1

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-35-UNV-OPL-1\_600mA

Data in this report applies to families of products including 4ASL

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2511-597-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 11/18/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Fail-Safe  
 Catalog Number: **4ASL-2-35-UNV-OPL-1\_600mA**  
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDs with 1 rows at 600mA

**Spectral Parameters**

CCT (K): 3487  
 CIE u': 0.2366  
 CIE v': 0.5099  
 Duv: -0.0012  
 CIE x: 0.4047  
 CIE y: 0.3876  
 CIE z: 0.2077  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 37.79273  
 R<sub>f</sub>: 90  
 R<sub>g</sub>: 102.4

CRI (Ra):	92.5		
R1:	94.7	R9:	61.3
R2:	94.3	R10:	85.5
R3:	92.9	R11:	93.7
R4:	93.3	R12:	80.8
R5:	93.9	R13:	94.3
R6:	93.4	R14:	95.1
R7:	92.5	R15:	90.9
R8:	85.2		



**Test Conditions**


Stabilization Time: 31M  
 Operation Time: 1H 31M  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-1

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.58**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 3.15**


λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

**Summary**

$R_f = 90$   
 $R_g = 102.4$   
 CIE  $R_a = 92.5$   
 $R_9 = 61.3$



**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 86	CES26 = 87	CES51 = 95	CES76 = 82
CES02 = 62	CES27 = 96	CES52 = 94	CES77 = 89
CES03 = 31	CES28 = 93	CES53 = 90	CES78 = 79
CES04 = 70	CES29 = 84	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 89	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 91	CES81 = 81
CES07 = 43	CES32 = 80	CES57 = 90	CES82 = 96
CES08 = 41	CES33 = 86	CES58 = 91	CES83 = 94
CES09 = 29	CES34 = 88	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 93	CES60 = 97	CES85 = 84
CES11 = 58	CES36 = 93	CES61 = 96	CES86 = 82
CES12 = 64	CES37 = 91	CES62 = 98	CES87 = 90
CES13 = 43	CES38 = 95	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 93	CES89 = 83
CES15 = 71	CES40 = 92	CES65 = 90	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 91	CES91 = 83
CES17 = 49	CES42 = 87	CES67 = 91	CES92 = 80
CES18 = 56	CES43 = 85	CES68 = 91	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 75
CES20 = 66	CES45 = 90	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 90	CES71 = 85	CES96 = 91
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 90
CES23 = 91	CES48 = 91	CES73 = 80	CES98 = 91
CES24 = 90	CES49 = 88	CES74 = 94	CES99 = 92
CES25 = 71	CES50 = 94	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)