

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357364

Luminaire Tested: 6ASL4-30VHE-3-G52-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 6ASL4-30VHE-3-G52-UNV
Description: 6FT 3000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND G52 LEDS 3 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8922.0 lumens
Efficiency: N/A
Efficacy: 49.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 5.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 181.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357364
CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357364

CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14172	14172	14172
5°	14057	13912	13848
10°	13989	13649	13497
15°	13845	13321	13201
20°	13647	13005	12865
25°	13415	12608	12485
30°	13170	12263	12163
35°	12864	11872	11804
40°	12585	11516	11427
45°	12286	11082	11048
50°	11945	10616	10654
55°	11578	10172	10300
60°	11097	9653	9940
65°	10485	9154	9642
70°	9700	8662	9409
75°	8550	8216	9249
80°	6793	7888	9180
85°	4227	7837	9317

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12286 cd/sqm



TEST NUMBER: P1357364
 CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.8	2.8
10°-20°	714.4	8.0
20°-30°	1080.2	12.1
30°-40°	1307.9	14.7
40°-50°	1373.7	15.4
50°-60°	1281.6	14.4
60°-70°	1059.2	11.9
70°-80°	762.6	8.5
80°-90°	473.9	5.3
90°-100°	277.7	3.1
100°-110°	158.8	1.8
110°-120°	89.7	1.0
120°-130°	51.6	0.6
130°-140°	27.8	0.3
140°-150°	11.7	0.1
150°-160°	2.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2043.5	22.9
0°-40°	3351.4	37.6
0°-60°	6006.7	67.3
0°-90°	8302.5	93.1
90°-120°	526.3	5.9
90°-150°	617.4	6.9
90°-180°	620.0	6.9
0°-180°	8922.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2624	2624	2624	2624	2624	
5°	2597	2619	2619	2619	2624	247
15°	2488	2520	2531	2548	2559	701
25°	2270	2308	2346	2379	2400	1045
35°	1975	2029	2095	2155	2182	1236
45°	1637	1697	1789	1866	1898	1263
55°	1260	1331	1440	1544	1582	1126
65°	851	933	1075	1211	1260	842
75°	436	546	736	895	960	462
85°	82	246	464	627	687	100
90°	0	147	355	507	573	4
95°	0	93	267	409	469	0
105°	0	33	147	256	300	0
115°	0	16	87	158	186	0
125°	0	11	55	104	120	0
135°	0	0	33	66	82	0
145°	0	0	16	38	44	0
155°	0	0	0	11	16	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357364

CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2624.1	2624.1	2624.1	2624.1	2624.1
2.5°	2613.2	2629.5	2629.5	2613.2	2613.2
5°	2596.8	2618.6	2618.6	2618.6	2624.1
7.5°	2580.4	2607.7	2607.7	2607.7	2618.6
10°	2558.6	2585.9	2591.3	2591.3	2596.8
12.5°	2525.9	2558.6	2564.1	2569.5	2575.0
15°	2487.7	2520.4	2531.3	2547.7	2558.6
17.5°	2444.0	2482.2	2504.1	2520.4	2531.3
20°	2389.5	2427.7	2455.0	2476.8	2493.1
22.5°	2334.9	2367.7	2400.4	2427.7	2444.0
25°	2269.5	2307.7	2345.9	2378.6	2400.4
27.5°	2198.6	2242.2	2291.3	2329.5	2351.3
30°	2133.1	2176.7	2231.3	2280.4	2302.2
32.5°	2056.7	2105.8	2165.8	2214.9	2242.2
35°	1974.9	2029.4	2094.9	2154.9	2182.2
37.5°	1893.0	1947.6	2029.4	2089.4	2116.7
40°	1811.2	1865.8	1953.1	2018.5	2045.8
42.5°	1723.9	1778.5	1871.2	1942.1	1974.9
45°	1636.6	1696.7	1789.4	1865.8	1898.5
47.5°	1549.4	1609.4	1707.6	1789.4	1822.1
50°	1451.2	1516.6	1614.8	1707.6	1740.3
52.5°	1358.4	1423.9	1533.0	1625.7	1658.5
55°	1260.2	1331.1	1440.2	1543.9	1582.1
57.5°	1162.0	1232.9	1347.5	1456.6	1500.3
60°	1058.4	1134.7	1254.8	1369.3	1418.4
62.5°	954.7	1036.5	1167.5	1287.5	1336.6
65°	851.1	932.9	1074.7	1211.1	1260.2
67.5°	747.4	834.7	987.4	1129.3	1189.3
70°	643.7	736.5	900.2	1047.4	1107.5
72.5°	540.1	638.3	818.3	971.1	1031.1
75°	436.4	545.5	736.5	894.7	960.2
77.5°	332.8	458.3	665.6	823.8	889.2
80°	240.0	381.9	589.2	752.9	818.3
82.5°	152.8	305.5	523.7	687.4	752.9
85°	81.8	245.5	463.7	627.4	687.4
87.5°	27.3	190.9	403.7	567.4	627.4
90°	0.0	147.3	354.6	507.4	572.8
92.5°	0.0	114.6	311.0	458.3	518.3
95°	0.0	92.7	267.3	409.2	469.2
97.5°	0.0	76.4	234.6	365.5	420.1
100°	0.0	60.0	201.9	327.3	376.4
102.5°	0.0	49.1	174.6	289.1	338.2
105°	0.0	32.7	147.3	256.4	300.1
107.5°	0.0	27.3	125.5	229.1	267.3
110°	0.0	21.8	114.6	196.4	234.6



TEST NUMBER: P1357364
 CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	16.4	103.7	174.6	212.8
115°	0.0	16.4	87.3	158.2	185.5
117.5°	0.0	16.4	76.4	141.8	169.1
120°	0.0	10.9	70.9	125.5	152.8
122.5°	0.0	10.9	60.0	114.6	136.4
125°	0.0	10.9	54.6	103.7	120.0
127.5°	0.0	5.5	49.1	92.7	109.1
130°	0.0	5.5	43.6	81.8	98.2
132.5°	0.0	5.5	38.2	76.4	92.7
135°	0.0	0.0	32.7	65.5	81.8
137.5°	0.0	0.0	27.3	60.0	70.9
140°	0.0	0.0	21.8	49.1	65.5
142.5°	0.0	0.0	16.4	43.6	54.6
145°	0.0	0.0	16.4	38.2	43.6
147.5°	0.0	0.0	10.9	27.3	38.2
150°	0.0	0.0	5.5	21.8	27.3
152.5°	0.0	0.0	0.0	16.4	21.8
155°	0.0	0.0	0.0	10.9	16.4
157.5°	0.0	0.0	0.0	0.0	5.5
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357364
 CATALOG NUMBER: 6ASL4-30VHE-3-G52-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.55	20.09	19.02	20.55	21.03	20.61	22.15	21.08	22.60	23.09
	3H	20.05	21.45	20.53	21.92	22.44	23.08	24.49	23.57	24.95	25.48
	4H	20.53	21.86	21.03	22.34	22.88	24.29	25.62	24.79	26.11	26.64
	6H	20.81	22.05	21.32	22.54	23.10	25.56	26.80	26.08	27.30	27.85
	8H	20.86	22.05	21.39	22.57	23.13	26.23	27.41	26.75	27.93	28.49
	12H	20.87	22.01	21.41	22.52	23.11	26.96	28.10	27.49	28.61	29.20
4H	2H	19.44	20.77	19.94	21.25	21.79	21.04	22.37	21.55	22.86	23.39
	3H	21.17	22.31	21.69	22.83	23.39	23.74	24.88	24.26	25.40	25.96
	4H	21.78	22.81	22.31	23.35	23.94	25.12	26.16	25.66	26.70	27.29
	6H	22.17	23.09	22.73	23.65	24.26	26.58	27.50	27.14	28.06	28.67
	8H	22.27	23.13	22.83	23.69	24.31	27.35	28.21	27.91	28.78	29.40
	12H	22.31	23.10	22.89	23.69	24.31	28.21	28.99	28.79	29.58	30.21
8H	4H	22.46	23.33	23.02	23.89	24.51	25.34	26.20	25.90	26.76	27.38
	6H	23.04	23.77	23.63	24.38	25.00	26.97	27.70	27.56	28.30	28.93
	8H	23.22	23.88	23.83	24.50	25.14	27.88	28.54	28.48	29.15	29.79
	12H	23.34	23.93	23.95	24.53	25.24	28.92	29.51	29.53	30.11	30.82
12H	4H	22.66	23.44	23.24	24.03	24.66	25.35	26.13	25.93	26.72	27.34
	6H	23.34	24.00	23.94	24.62	25.25	27.01	27.67	27.61	28.28	28.92
	8H	23.62	24.21	24.23	24.81	25.52	27.98	28.57	28.59	29.18	29.88

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-8

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-G520-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-G520-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND GREEN 520NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 7535
 CIE u': 0.0718
 CIE v': 0.5710
 Duv: 0.1461
 CIE x: 0.1962
 CIE y: 0.6931
 CIE z: 0.1107
 Peak Wavelength (nm): 524
 Dominant Wavelength (nm): 529
 Purity: 75.95236
 Rf: NR
 Rg: NR

CRI (Ra):	-11.7		
R1:	-30.6	R9:	-351.9
R2:	5.1	R10:	-75.5
R3:	5.6	R11:	-78.0
R4:	-51.7	R12:	-14.7
R5:	-6.4	R13:	-32.5
R6:	-0.6	R14:	52.7
R7:	10.9	R15:	-37.0
R8:	-25.8		



Test Conditions

Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-8

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies outside the range

REPORT NUMBER: SP1-2511-597-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.63

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR


M/P: 4.87

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			





Summary

$R_f = 0$
 $R_g = 0$
 $CIE R_a = -11.7$
 $R_g = -351.9$

Spectral Power Distribution Comparison



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)