

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357373

Luminaire Tested: 6ASL4-35VHE-3-G52-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 6ASL4-35VHE-3-G52-UNV
Description: 6FT 3500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND G52 LEDS 3 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10395.1 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 5.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 218.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357373
CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357373

CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16512	16512	16512
5°	16377	16210	16134
10°	16298	15903	15726
15°	16130	15520	15380
20°	15900	15153	14990
25°	15630	14689	14546
30°	15345	14288	14171
35°	14987	13833	13753
40°	14663	13416	13314
45°	14314	12911	12872
50°	13916	12369	12413
55°	13490	11851	12001
60°	12929	11246	11582
65°	12216	10666	11235
70°	11302	10092	10962
75°	9963	9572	10776
80°	7917	9191	10696
85°	4925	9131	10855

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14314 cd/sqm



TEST NUMBER: P1357373
 CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.9	2.8
10°-20°	832.4	8.0
20°-30°	1258.5	12.1
30°-40°	1523.9	14.7
40°-50°	1600.5	15.4
50°-60°	1493.2	14.4
60°-70°	1234.1	11.9
70°-80°	888.5	8.5
80°-90°	552.2	5.3
90°-100°	323.5	3.1
100°-110°	185.1	1.8
110°-120°	104.5	1.0
120°-130°	60.1	0.6
130°-140°	32.4	0.3
140°-150°	13.6	0.1
150°-160°	2.5	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2380.8	22.9
0°-40°	3904.7	37.6
0°-60°	6998.5	67.3
0°-90°	9673.2	93.1
90°-120°	613.1	5.9
90°-150°	719.3	6.9
90°-180°	722.0	6.9
0°-180°	10395.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3057	3057	3057	3057	3057	
5°	3026	3051	3051	3051	3057	288
15°	2898	2936	2949	2968	2981	817
25°	2644	2689	2733	2771	2797	1218
35°	2301	2364	2441	2511	2542	1440
45°	1907	1977	2085	2174	2212	1471
55°	1468	1551	1678	1799	1843	1312
65°	992	1087	1252	1411	1468	981
75°	508	636	858	1042	1119	538
85°	95	286	540	731	801	117
90°	0	172	413	591	667	4
95°	0	108	312	477	547	0
105°	0	38	172	299	350	0
115°	0	19	102	184	216	0
125°	0	13	64	121	140	0
135°	0	0	38	76	95	0
145°	0	0	19	44	51	0
155°	0	0	0	13	19	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357373

CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3057.3	3057.3	3057.3	3057.3	3057.3
2.5°	3044.6	3063.7	3063.7	3044.6	3044.6
5°	3025.5	3051.0	3051.0	3051.0	3057.3
7.5°	3006.5	3038.2	3038.2	3038.2	3051.0
10°	2981.0	3012.8	3019.2	3019.2	3025.5
12.5°	2942.9	2981.0	2987.4	2993.7	3000.1
15°	2898.4	2936.5	2949.3	2968.3	2981.0
17.5°	2847.6	2892.0	2917.5	2936.5	2949.3
20°	2784.0	2828.5	2860.3	2885.7	2904.8
22.5°	2720.4	2758.6	2796.7	2828.5	2847.6
25°	2644.2	2688.7	2733.1	2771.3	2796.7
27.5°	2561.5	2612.4	2669.6	2714.1	2739.5
30°	2485.3	2536.1	2599.7	2656.9	2682.3
32.5°	2396.3	2453.5	2523.4	2580.6	2612.4
35°	2300.9	2364.5	2440.8	2510.7	2542.5
37.5°	2205.6	2269.1	2364.5	2434.4	2466.2
40°	2110.2	2173.8	2275.5	2351.8	2383.6
42.5°	2008.5	2072.1	2180.2	2262.8	2300.9
45°	1906.8	1976.8	2084.8	2173.8	2211.9
47.5°	1805.1	1875.1	1989.5	2084.8	2123.0
50°	1690.7	1767.0	1881.4	1989.5	2027.6
52.5°	1582.7	1659.0	1786.1	1894.1	1932.3
55°	1468.3	1550.9	1678.0	1798.8	1843.3
57.5°	1353.9	1436.5	1570.0	1697.1	1747.9
60°	1233.1	1322.1	1461.9	1595.4	1652.6
62.5°	1112.3	1207.7	1360.2	1500.1	1557.3
65°	991.6	1086.9	1252.2	1411.1	1468.3
67.5°	870.8	972.5	1150.5	1315.7	1385.6
70°	750.0	858.1	1048.8	1220.4	1290.3
72.5°	629.3	743.7	953.4	1131.4	1201.3
75°	508.5	635.6	858.1	1042.4	1118.7
77.5°	387.7	533.9	775.5	959.8	1036.1
80°	279.7	444.9	686.5	877.1	953.4
82.5°	178.0	355.9	610.2	800.9	877.1
85°	95.3	286.0	540.3	731.0	800.9
87.5°	31.8	222.5	470.4	661.0	731.0
90°	0.0	171.6	413.1	591.1	667.4
92.5°	0.0	133.5	362.3	533.9	603.8
95°	0.0	108.1	311.5	476.7	546.6
97.5°	0.0	89.0	273.3	425.9	489.4
100°	0.0	69.9	235.2	381.4	438.6
102.5°	0.0	57.2	203.4	336.9	394.1
105°	0.0	38.1	171.6	298.7	349.6
107.5°	0.0	31.8	146.2	267.0	311.5
110°	0.0	25.4	133.5	228.8	273.3



TEST NUMBER: P1357373
 CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	19.1	120.8	203.4	247.9
115°	0.0	19.1	101.7	184.3	216.1
117.5°	0.0	19.1	89.0	165.3	197.0
120°	0.0	12.7	82.6	146.2	178.0
122.5°	0.0	12.7	69.9	133.5	158.9
125°	0.0	12.7	63.6	120.8	139.8
127.5°	0.0	6.4	57.2	108.1	127.1
130°	0.0	6.4	50.8	95.3	114.4
132.5°	0.0	6.4	44.5	89.0	108.1
135°	0.0	0.0	38.1	76.3	95.3
137.5°	0.0	0.0	31.8	69.9	82.6
140°	0.0	0.0	25.4	57.2	76.3
142.5°	0.0	0.0	19.1	50.8	63.6
145°	0.0	0.0	19.1	44.5	50.8
147.5°	0.0	0.0	12.7	31.8	44.5
150°	0.0	0.0	6.4	25.4	31.8
152.5°	0.0	0.0	0.0	19.1	25.4
155°	0.0	0.0	0.0	12.7	19.1
157.5°	0.0	0.0	0.0	0.0	6.4
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357373
 CATALOG NUMBER: 6ASL4-35VHE-3-G52-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.09	20.63	19.55	21.08	21.56	21.14	22.68	21.61	23.13	23.62
	3H	20.58	21.99	21.06	22.45	22.98	23.62	25.02	24.10	25.49	26.01
	4H	21.06	22.39	21.56	22.88	23.41	24.82	26.16	25.33	26.64	27.18
	6H	21.34	22.58	21.85	23.07	23.63	26.09	27.33	26.61	27.83	28.38
	8H	21.39	22.58	21.92	23.10	23.66	26.76	27.94	27.28	28.46	29.02
	12H	21.40	22.54	21.94	23.06	23.65	27.49	28.63	28.02	29.14	29.73
4H	2H	19.97	21.30	20.47	21.78	22.32	21.57	22.90	22.08	23.39	23.92
	3H	21.70	22.84	22.22	23.36	23.92	24.27	25.41	24.79	25.93	26.49
	4H	22.31	23.34	22.84	23.88	24.47	25.65	26.69	26.19	27.23	27.82
	6H	22.70	23.62	23.26	24.18	24.79	27.12	28.03	27.67	28.59	29.20
	8H	22.80	23.66	23.36	24.22	24.84	27.88	28.75	28.44	29.31	29.93
	12H	22.84	23.63	23.42	24.22	24.84	28.74	29.53	29.32	30.12	30.74
8H	4H	22.99	23.86	23.55	24.42	25.04	25.87	26.73	26.43	27.29	27.91
	6H	23.57	24.30	24.17	24.91	25.53	27.50	28.23	28.09	28.84	29.46
	8H	23.75	24.41	24.36	25.03	25.67	28.41	29.07	29.01	29.68	30.32
	12H	23.87	24.46	24.48	25.06	25.77	29.45	30.04	30.06	30.65	31.35
12H	4H	23.19	23.97	23.77	24.56	25.19	25.88	26.66	26.46	27.25	27.87
	6H	23.87	24.53	24.48	25.15	25.78	27.54	28.20	28.14	28.81	29.45
	8H	24.15	24.74	24.76	25.34	26.05	28.51	29.10	29.12	29.71	30.41

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-8

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-G520-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-G520-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND GREEN 520NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 7535
 CIE u': 0.0718
 CIE v': 0.5710
 Duv: 0.1461
 CIE x: 0.1962
 CIE y: 0.6931
 CIE z: 0.1107
 Peak Wavelength (nm): 524
 Dominant Wavelength (nm): 529
 Purity: 75.95236
 Rf: NR
 Rg: NR

CRI (Ra):	-11.7		
R1:	-30.6	R9:	-351.9
R2:	5.1	R10:	-75.5
R3:	5.6	R11:	-78.0
R4:	-51.7	R12:	-14.7
R5:	-6.4	R13:	-32.5
R6:	-0.6	R14:	52.7
R7:	10.9	R15:	-37.0
R8:	-25.8		



Test Conditions

Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-8

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies outside the range

REPORT NUMBER: SP1-2511-597-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.63

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR


M/P: 4.87

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			





Summary

$R_f = 0$
 $R_g = 0$
 $CIE R_a = -11.7$
 $R_g = -351.9$

Spectral Power Distribution Comparison




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)