

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357417

Luminaire Tested: 8ASL4-10HE-2-27-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-10HE-2-27-UNV
Description: 8FT 1000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7568.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 66.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8922	8922	8922
5°	8861	8751	8717
10°	8811	8597	8505
15°	8741	8426	8335
20°	8647	8209	8096
25°	8492	7995	7889
30°	8295	7749	7685
35°	8146	7521	7447
40°	7970	7275	7196
45°	7794	7063	7013
50°	7564	6782	6742
55°	7346	6479	6527
60°	7078	6137	6298
65°	6651	5822	6121
70°	6176	5528	5958
75°	5478	5305	5904
80°	4362	5116	5886
85°	2800	5142	6055

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7794 cd/sqm

TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.1	2.8
10°-20°	600.9	7.9
20°-30°	910.6	12.0
30°-40°	1101.3	14.6
40°-50°	1161.1	15.3
50°-60°	1083.6	14.3
60°-70°	894.7	11.8
70°-80°	649.0	8.6
80°-90°	410.1	5.4
90°-100°	244.8	3.2
100°-110°	140.3	1.9
110°-120°	79.7	1.1
120°-130°	45.5	0.6
130°-140°	24.6	0.3
140°-150°	10.8	0.1
150°-160°	1.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.6	22.7
0°-40°	2821.9	37.3
0°-60°	5066.7	66.9
0°-90°	7020.4	92.8
90°-120°	464.8	6.1
90°-150°	545.6	7.2
90°-180°	548.0	7.2
0°-180°	7568.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2204	2204	2204	2204	2204	
5°	2184	2204	2198	2198	2204	207
15°	2094	2121	2135	2142	2156	591
25°	1913	1941	1983	2010	2024	881
35°	1664	1705	1768	1816	1837	1040
45°	1380	1435	1518	1581	1608	1064
55°	1061	1123	1220	1303	1338	948
65°	714	790	908	1019	1068	709
75°	367	464	631	763	818	386
85°	69	215	402	541	596	85
90°	0	132	312	444	499	3
95°	0	83	236	360	409	0
105°	0	28	132	229	263	0
115°	0	14	76	139	166	0
125°	0	7	48	90	104	0
135°	0	0	28	56	69	0
145°	0	0	14	35	42	0
155°	0	0	0	7	14	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2204.5	2204.5	2204.5	2204.5	2204.5
2.5°	2190.6	2211.4	2204.5	2197.5	2197.5
5°	2183.7	2204.5	2197.5	2197.5	2204.5
7.5°	2169.8	2190.6	2190.6	2190.6	2197.5
10°	2149.0	2176.8	2176.8	2176.8	2183.7
12.5°	2128.2	2149.0	2156.0	2162.9	2169.8
15°	2093.6	2121.3	2135.2	2142.1	2156.0
17.5°	2058.9	2079.7	2100.5	2121.3	2128.2
20°	2017.3	2045.0	2065.8	2086.6	2093.6
22.5°	1968.8	1996.5	2024.2	2045.0	2058.9
25°	1913.3	1941.1	1982.6	2010.4	2024.2
27.5°	1857.9	1885.6	1934.1	1968.8	1982.6
30°	1788.5	1830.1	1878.7	1920.3	1941.1
32.5°	1726.1	1767.7	1823.2	1871.7	1885.6
35°	1663.8	1705.4	1767.7	1816.3	1837.1
37.5°	1594.4	1643.0	1705.4	1760.8	1781.6
40°	1525.1	1573.6	1643.0	1705.4	1719.2
42.5°	1455.8	1504.3	1587.5	1643.0	1663.8
45°	1379.5	1435.0	1518.2	1580.6	1608.3
47.5°	1303.3	1358.7	1441.9	1511.2	1539.0
50°	1220.1	1282.5	1372.6	1441.9	1469.7
52.5°	1143.8	1206.2	1296.3	1372.6	1407.3
55°	1060.6	1123.0	1220.1	1303.3	1337.9
57.5°	977.5	1039.8	1143.8	1234.0	1268.6
60°	894.3	956.7	1060.6	1164.6	1199.3
62.5°	804.1	873.5	984.4	1088.4	1130.0
65°	714.0	790.3	908.1	1019.1	1067.6
67.5°	630.8	707.1	831.9	956.7	998.3
70°	540.7	623.9	762.6	887.3	935.9
72.5°	450.6	540.7	693.2	824.9	873.5
75°	367.4	464.5	630.8	762.6	818.0
77.5°	277.3	395.1	568.5	707.1	755.6
80°	201.0	325.8	506.1	651.6	700.2
82.5°	131.7	263.4	450.6	596.2	644.7
85°	69.3	214.9	402.1	540.7	596.2
87.5°	20.8	166.4	353.5	492.2	540.7
90°	0.0	131.7	312.0	443.7	499.1
92.5°	0.0	104.0	270.4	402.1	450.6
95°	0.0	83.2	235.7	360.5	409.0
97.5°	0.0	69.3	208.0	325.8	367.4
100°	0.0	55.5	180.2	291.2	332.8
102.5°	0.0	41.6	152.5	256.5	298.1
105°	0.0	27.7	131.7	228.8	263.4
107.5°	0.0	20.8	110.9	201.0	235.7
110°	0.0	20.8	104.0	173.3	208.0

TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	13.9	90.1	159.4	187.2
115°	0.0	13.9	76.3	138.6	166.4
117.5°	0.0	13.9	69.3	124.8	152.5
120°	0.0	13.9	62.4	110.9	131.7
122.5°	0.0	6.9	55.5	97.1	117.8
125°	0.0	6.9	48.5	90.1	104.0
127.5°	0.0	6.9	41.6	83.2	97.1
130°	0.0	6.9	41.6	76.3	90.1
132.5°	0.0	0.0	34.7	69.3	83.2
135°	0.0	0.0	27.7	55.5	69.3
137.5°	0.0	0.0	27.7	48.5	62.4
140°	0.0	0.0	20.8	48.5	55.5
142.5°	0.0	0.0	13.9	41.6	48.5
145°	0.0	0.0	13.9	34.7	41.6
147.5°	0.0	0.0	6.9	27.7	34.7
150°	0.0	0.0	6.9	20.8	27.7
152.5°	0.0	0.0	0.0	13.9	20.8
155°	0.0	0.0	0.0	6.9	13.9
157.5°	0.0	0.0	0.0	0.0	6.9
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357417

CATALOG NUMBER: 8ASL4-10HE-2-27-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.93	18.47	17.40	18.93	19.42	19.03	20.57	19.51	21.03	21.52
	3H	18.43	19.83	18.92	20.30	20.83	21.50	22.90	21.99	23.37	23.90
	4H	18.91	20.24	19.42	20.73	21.27	22.73	24.06	23.24	24.54	25.09
	6H	19.19	20.42	19.71	20.92	21.48	24.03	25.27	24.55	25.77	26.33
	8H	19.24	20.43	19.77	20.95	21.52	24.71	25.90	25.24	26.42	26.99
	12H	19.25	20.39	19.79	20.91	21.51	25.48	26.61	26.02	27.13	27.73
4H	2H	17.82	19.15	18.33	19.63	20.18	19.46	20.79	19.97	21.28	21.82
	3H	19.56	20.69	20.08	21.22	21.79	22.16	23.29	22.68	23.82	24.39
	4H	20.17	21.21	20.71	21.75	22.35	23.56	24.60	24.10	25.14	25.74
	6H	20.57	21.49	21.13	22.05	22.67	25.06	25.97	25.62	26.54	27.15
	8H	20.67	21.53	21.23	22.10	22.72	25.85	26.71	26.41	27.28	27.90
	12H	20.71	21.50	21.30	22.09	22.72	26.74	27.52	27.33	28.12	28.75
8H	4H	20.87	21.74	21.44	22.30	22.93	23.78	24.64	24.34	25.21	25.83
	6H	21.46	22.19	22.06	22.80	23.43	25.45	26.18	26.05	26.79	27.42
	8H	21.65	22.31	22.26	22.93	23.57	26.38	27.04	26.99	27.66	28.31
	12H	21.77	22.36	22.38	22.97	23.68	27.46	28.05	28.07	28.66	29.37
12H	4H	21.08	21.86	21.67	22.46	23.09	23.79	24.57	24.37	25.17	25.80
	6H	21.77	22.43	22.38	23.05	23.69	25.49	26.15	26.10	26.77	27.41
	8H	22.06	22.65	22.67	23.26	23.97	26.49	27.08	27.10	27.69	28.40

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-2

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-27-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-27-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 2696
 CIE u' : 0.2632
 CIE v' : 0.5245
 Duv: -0.0020
 CIE x: 0.4568
 CIE y: 0.4045
 CIE z: 0.1387
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 58.52757
 R_f: 90.1
 R_g: 103.5

CRI (Ra): 94.4
 R1: 97.5
 R2: 97.8
 R3: 96.9
 R4: 95.3
 R5: 97.2
 R6: 96.5
 R7: 91.2
 R8: 83.2
 R9: 61.8
 R10: 93.6
 R11: 93.7
 R12: 94.1
 R13: 97.6
 R14: 96.8
 R15: 91.9



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.45


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2





TM-30-18

Summary

$R_f = 90.1$
 $R_g = 103.5$
 $CIE R_a = 94.4$
 $R_9 = 61.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 89	CES51 = 92	CES76 = 90
CES02 = 64	CES27 = 97	CES52 = 92	CES77 = 84
CES03 = 32	CES28 = 96	CES53 = 88	CES78 = 87
CES04 = 71	CES29 = 83	CES54 = 97	CES79 = 88
CES05 = 51	CES30 = 85	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 69
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 95
CES08 = 43	CES33 = 84	CES58 = 88	CES83 = 91
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 96	CES60 = 99	CES85 = 81
CES11 = 59	CES36 = 98	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 45	CES38 = 89	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 92	CES90 = 93
CES16 = 48	CES41 = 89	CES66 = 92	CES91 = 91
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 97	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 72
CES20 = 68	CES45 = 90	CES70 = 93	CES95 = 88
CES21 = 87	CES46 = 89	CES71 = 95	CES96 = 92
CES22 = 79	CES47 = 79	CES72 = 98	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 89	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 88	CES99 = 92
CES25 = 72	CES50 = 92	CES75 = 94	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)