

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357461

Luminaire Tested: 8ASL4-15HE-2-R63-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-15HE-2-R63-UNV
Description: 8FT 1500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND R63 LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3199.0 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3771	3771	3771
5°	3745	3699	3685
10°	3724	3634	3595
15°	3695	3562	3523
20°	3655	3470	3422
25°	3590	3380	3335
30°	3506	3276	3248
35°	3443	3179	3148
40°	3369	3075	3042
45°	3294	2985	2964
50°	3197	2867	2850
55°	3105	2738	2759
60°	2992	2594	2662
65°	2811	2461	2588
70°	2611	2336	2519
75°	2316	2243	2496
80°	1844	2162	2488
85°	1184	2174	2559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3294 cd/sqm

TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.8
10°-20°	254.0	7.9
20°-30°	384.9	12.0
30°-40°	465.5	14.6
40°-50°	490.8	15.3
50°-60°	458.1	14.3
60°-70°	378.2	11.8
70°-80°	274.3	8.6
80°-90°	173.3	5.4
90°-100°	103.5	3.2
100°-110°	59.3	1.9
110°-120°	33.7	1.1
120°-130°	19.2	0.6
130°-140°	10.4	0.3
140°-150°	4.6	0.1
150°-160°	0.8	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.3	22.7
0°-40°	1192.8	37.3
0°-60°	2141.7	66.9
0°-90°	2967.6	92.8
90°-120°	196.5	6.1
90°-150°	230.7	7.2
90°-180°	231.0	7.2
0°-180°	3199.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	932	932	932	932	932	
5°	923	932	929	929	932	88
15°	885	897	902	906	911	250
25°	809	820	838	850	856	373
35°	703	721	747	768	776	440
45°	583	607	642	668	680	450
55°	448	475	516	551	566	401
65°	302	334	384	431	451	300
75°	155	196	267	322	346	163
85°	29	91	170	229	252	36
90°	0	56	132	188	211	1
95°	0	35	100	152	173	0
105°	0	12	56	97	111	0
115°	0	6	32	59	70	0
125°	0	3	20	38	44	0
135°	0	0	12	23	29	0
145°	0	0	6	15	18	0
155°	0	0	0	3	6	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	931.8	931.8	931.8	931.8	931.8
2.5°	926.0	934.8	931.8	928.9	928.9
5°	923.0	931.8	928.9	928.9	931.8
7.5°	917.2	926.0	926.0	926.0	928.9
10°	908.4	920.1	920.1	920.1	923.0
12.5°	899.6	908.4	911.3	914.3	917.2
15°	885.0	896.7	902.5	905.5	911.3
17.5°	870.3	879.1	887.9	896.7	899.6
20°	852.7	864.4	873.2	882.0	885.0
22.5°	832.2	843.9	855.6	864.4	870.3
25°	808.8	820.5	838.1	849.8	855.6
27.5°	785.3	797.0	817.6	832.2	838.1
30°	756.0	773.6	794.1	811.7	820.5
32.5°	729.6	747.2	770.7	791.2	797.0
35°	703.3	720.9	747.2	767.7	776.5
37.5°	674.0	694.5	720.9	744.3	753.1
40°	644.7	665.2	694.5	720.9	726.7
42.5°	615.4	635.9	671.0	694.5	703.3
45°	583.1	606.6	641.7	668.1	679.8
47.5°	550.9	574.3	609.5	638.8	650.5
50°	515.7	542.1	580.2	609.5	621.2
52.5°	483.5	509.9	548.0	580.2	594.9
55°	448.3	474.7	515.7	550.9	565.5
57.5°	413.2	439.5	483.5	521.6	536.2
60°	378.0	404.4	448.3	492.3	506.9
62.5°	339.9	369.2	416.1	460.1	477.6
65°	301.8	334.1	383.9	430.8	451.3
67.5°	266.7	298.9	351.6	404.4	422.0
70°	228.6	263.7	322.3	375.1	395.6
72.5°	190.5	228.6	293.0	348.7	369.2
75°	155.3	196.3	266.7	322.3	345.8
77.5°	117.2	167.0	240.3	298.9	319.4
80°	85.0	137.7	213.9	275.4	296.0
82.5°	55.7	111.4	190.5	252.0	272.5
85°	29.3	90.8	170.0	228.6	252.0
87.5°	8.8	70.3	149.4	208.1	228.6
90°	0.0	55.7	131.9	187.5	211.0
92.5°	0.0	44.0	114.3	170.0	190.5
95°	0.0	35.2	99.6	152.4	172.9
97.5°	0.0	29.3	87.9	137.7	155.3
100°	0.0	23.4	76.2	123.1	140.7
102.5°	0.0	17.6	64.5	108.4	126.0
105°	0.0	11.7	55.7	96.7	111.4
107.5°	0.0	8.8	46.9	85.0	99.6
110°	0.0	8.8	44.0	73.3	87.9



TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	5.9	38.1	67.4	79.1
115°	0.0	5.9	32.2	58.6	70.3
117.5°	0.0	5.9	29.3	52.7	64.5
120°	0.0	5.9	26.4	46.9	55.7
122.5°	0.0	2.9	23.4	41.0	49.8
125°	0.0	2.9	20.5	38.1	44.0
127.5°	0.0	2.9	17.6	35.2	41.0
130°	0.0	2.9	17.6	32.2	38.1
132.5°	0.0	0.0	14.7	29.3	35.2
135°	0.0	0.0	11.7	23.4	29.3
137.5°	0.0	0.0	11.7	20.5	26.4
140°	0.0	0.0	8.8	20.5	23.4
142.5°	0.0	0.0	5.9	17.6	20.5
145°	0.0	0.0	5.9	14.7	17.6
147.5°	0.0	0.0	2.9	11.7	14.7
150°	0.0	0.0	2.9	8.8	11.7
152.5°	0.0	0.0	0.0	5.9	8.8
155°	0.0	0.0	0.0	2.9	5.9
157.5°	0.0	0.0	0.0	0.0	2.9
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357461

CATALOG NUMBER: 8ASL4-15HE-2-R63-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.94	15.47	14.41	15.93	16.42	16.04	17.58	16.51	18.04	18.53
	3H	15.44	16.84	15.93	17.31	17.84	18.51	19.91	19.00	20.38	20.91
	4H	15.92	17.25	16.43	17.74	18.28	19.74	21.07	20.24	21.55	22.10
	6H	16.19	17.43	16.71	17.93	18.49	21.04	22.27	21.56	22.77	23.33
	8H	16.25	17.43	16.78	17.96	18.52	21.72	22.90	22.25	23.43	23.99
	12H	16.26	17.40	16.80	17.92	18.52	22.49	23.62	23.02	24.14	24.74
4H	2H	14.83	16.15	15.33	16.64	17.19	16.47	17.80	16.98	18.28	18.83
	3H	16.57	17.70	17.09	18.23	18.80	19.17	20.30	19.69	20.83	21.40
	4H	17.18	18.21	17.72	18.75	19.35	20.57	21.61	21.11	22.15	22.75
	6H	17.58	18.49	18.14	19.06	19.67	22.07	22.98	22.63	23.55	24.16
	8H	17.68	18.54	18.24	19.10	19.73	22.86	23.72	23.42	24.28	24.91
	12H	17.72	18.51	18.31	19.10	19.73	23.75	24.53	24.33	25.13	25.76
8H	4H	17.88	18.74	18.45	19.31	19.94	20.79	21.65	21.35	22.22	22.84
	6H	18.47	19.20	19.07	19.81	20.44	22.46	23.19	23.06	23.80	24.43
	8H	18.66	19.32	19.27	19.94	20.58	23.39	24.05	24.00	24.67	25.31
	12H	18.78	19.37	19.39	19.97	20.68	24.47	25.06	25.08	25.67	26.38
12H	4H	18.09	18.87	18.67	19.47	20.10	20.80	21.58	21.38	22.17	22.81
	6H	18.78	19.44	19.39	20.06	20.70	22.50	23.16	23.11	23.78	24.42
	8H	19.07	19.66	19.68	20.26	20.97	23.50	24.09	24.11	24.70	25.41

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-7

Test Date: 01/21/2026

Luminaire Tested: 4ASL-2-R630-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-R630-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND RED 630NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 0
 CIE u': 0.5395
 CIE v': 0.5190
 Duv: 0.0000
 CIE x: 0.7004
 CIE y: 0.2995
 CIE z: 0.0001
 Peak Wavelength (nm): 638
 Dominant Wavelength (nm): 624
 Purity: 99.9862
 Rf: NR
 Rg: NR

CRI (Ra): 0.0
 R1: 0.0
 R2: 0.0
 R3: 0.0
 R4: 0.0
 R5: 0.0
 R6: 0.0
 R7: 0.0
 R8: 0.0
 R9: 0.0
 R10: 0.0
 R11: 0.0
 R12: 0.0
 R13: 0.0
 R14: 0.0
 R15: 0.0



Test Conditions


Stabilization Time: 69M
 Operation Time: 2H 9M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2511-597-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.05

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 0.02

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	248	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	409	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	630	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	903	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	960	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	535	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	212	NR	780	0	NR	910	0	NR
395	0	NR	525	0	NR	655	88	NR	785	0	NR	915	0	NR
400	0	NR	530	0	NR	660	38	NR	790	0	NR	920	0	NR
405	0	NR	535	0	NR	665	19	NR	795	0	NR	925	0	NR
410	0	NR	540	0	NR	670	10	NR	800	0	NR	930	0	NR
415	0	NR	545	0	NR	675	6	NR	805	0	NR	935	0	NR
420	0	NR	550	0	NR	680	4	NR	810	0	NR	940	0	NR
425	0	NR	555	0	NR	685	2	NR	815	0	NR	945	0	NR
430	0	NR	560	0	NR	690	2	NR	820	0	NR	950	0	NR
435	0	NR	565	1	NR	695	1	NR	825	0	NR	955	0	NR
440	0	NR	570	2	NR	700	1	NR	830	0	NR	960	0	NR
445	0	NR	575	3	NR	705	1	NR	835	0	NR	965	0	NR
450	0	NR	580	4	NR	710	1	NR	840	0	NR	970	0	NR
455	0	NR	585	7	NR	715	1	NR	845	0	NR	975	0	NR
460	0	NR	590	12	NR	720	1	NR	850	0	NR	980	0	NR
465	0	NR	595	20	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	34	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	56	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	92	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	152	NR	745	0	NR	875	0	NR			


REPORT NUMBER: SP1-2511-597-7

TM-30-18





Summary

$R_f = 0$
 $R_g = 0$
 CIE $R_a = 0.0$
 $R_9 = 0.0$

Spectral Power Distribution Comparison



Color Vector Graphics




REPORT NUMBER: SP1-2511-597-7




TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)