

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357505

Luminaire Tested: 8ASL4-20VHE-3-G52-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-20VHE-3-G52-UNV
Description: 8FT 2000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND G52 LEDS 3 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7983.0 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 154.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	117	117	117	117	114	114	114	114	107	107	107		101	101	101		96
1	105	100	95	91	102	97	92	88	91	88	84		86	83	80		81
2	95	86	79	72	92	84	77	71	79	73	68		75	70	66		71
3	86	75	67	60	83	73	65	59	69	62	57		65	60	55		62
4	79	66	57	50	76	65	56	49	61	54	48		58	52	47		55
5	73	59	50	43	70	58	49	42	55	47	41		52	45	40		49
6	67	53	44	37	64	52	43	37	49	42	36		47	40	35		45
7	62	48	39	33	60	47	38	32	45	37	32		43	36	31		41
8	58	44	35	29	56	43	35	29	41	34	28		39	32	28		37
9	54	40	32	26	52	39	31	26	38	30	25		36	30	25		35
10	50	37	29	24	49	36	29	23	35	28	23		33	27	23		32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9502	9502	9502
5°	9428	9331	9285
10°	9386	9157	9050
15°	9294	8938	8851
20°	9164	8729	8626
25°	9013	8464	8371
30°	8852	8235	8155
35°	8651	7975	7915
40°	8469	7738	7662
45°	8273	7449	7407
50°	8050	7139	7143
55°	7811	6843	6906
60°	7496	6497	6665
65°	7094	6165	6465
70°	6580	5838	6309
75°	5822	5543	6201
80°	4661	5329	6155
85°	2958	5306	6246

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8273 cd/sqm

TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.6	2.8
10°-20°	639.3	8.0
20°-30°	966.5	12.1
30°-40°	1170.3	14.7
40°-50°	1229.1	15.4
50°-60°	1146.7	14.4
60°-70°	947.7	11.9
70°-80°	682.4	8.5
80°-90°	424.0	5.3
90°-100°	248.5	3.1
100°-110°	142.1	1.8
110°-120°	80.2	1.0
120°-130°	46.2	0.6
130°-140°	24.9	0.3
140°-150°	10.5	0.1
150°-160°	1.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1828.4	22.9
0°-40°	2998.7	37.6
0°-60°	5374.5	67.3
0°-90°	7428.7	93.1
90°-120°	470.8	5.9
90°-150°	552.4	6.9
90°-180°	554.0	6.9
0°-180°	7983.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2348	2348	2348	2348	2348	
5°	2324	2343	2343	2343	2348	221
15°	2226	2255	2265	2280	2289	628
25°	2031	2065	2099	2128	2148	935
35°	1767	1816	1874	1928	1952	1106
45°	1464	1518	1601	1669	1699	1130
55°	1128	1191	1289	1381	1416	1008
65°	762	835	962	1084	1128	754
75°	390	488	659	800	859	413
85°	73	220	415	561	615	90
90°	0	132	317	454	512	3
95°	0	83	239	366	420	0
105°	0	29	132	229	268	0
115°	0	15	78	142	166	0
125°	0	10	49	93	107	0
135°	0	0	29	59	73	0
145°	0	0	15	34	39	0
155°	0	0	0	10	15	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2347.9	2347.9	2347.9	2347.9	2347.9
2.5°	2338.1	2352.8	2352.8	2338.1	2338.1
5°	2323.5	2343.0	2343.0	2343.0	2347.9
7.5°	2308.9	2333.3	2333.3	2333.3	2343.0
10°	2289.3	2313.7	2318.6	2318.6	2323.5
12.5°	2260.0	2289.3	2294.2	2299.1	2304.0
15°	2225.9	2255.2	2264.9	2279.6	2289.3
17.5°	2186.8	2221.0	2240.5	2255.2	2264.9
20°	2138.0	2172.2	2196.6	2216.1	2230.8
22.5°	2089.2	2118.5	2147.8	2172.2	2186.8
25°	2030.6	2064.8	2099.0	2128.2	2147.8
27.5°	1967.2	2006.2	2050.1	2084.3	2103.8
30°	1908.6	1947.6	1996.5	2040.4	2059.9
32.5°	1840.3	1884.2	1937.9	1981.8	2006.2
35°	1767.0	1815.8	1874.4	1928.1	1952.5
37.5°	1693.8	1742.6	1815.8	1869.5	1893.9
40°	1620.6	1669.4	1747.5	1806.1	1830.5
42.5°	1542.5	1591.3	1674.3	1737.7	1767.0
45°	1464.4	1518.1	1601.1	1669.4	1698.7
47.5°	1386.3	1440.0	1527.8	1601.1	1630.4
50°	1298.4	1357.0	1444.9	1527.8	1557.1
52.5°	1215.4	1274.0	1371.6	1454.6	1483.9
55°	1127.6	1191.0	1288.7	1381.4	1415.6
57.5°	1039.7	1103.2	1205.7	1303.3	1342.4
60°	947.0	1015.3	1122.7	1225.2	1269.1
62.5°	854.2	927.4	1044.6	1152.0	1195.9
65°	761.5	834.7	961.6	1083.6	1127.6
67.5°	668.7	746.8	883.5	1010.4	1064.1
70°	576.0	659.0	805.4	937.2	990.9
72.5°	483.2	571.1	732.2	868.9	922.6
75°	390.5	488.1	659.0	800.5	859.1
77.5°	297.8	410.0	595.5	737.1	795.7
80°	214.8	341.7	527.2	673.6	732.2
82.5°	136.7	273.4	468.6	615.0	673.6
85°	73.2	219.7	414.9	561.4	615.0
87.5°	24.4	170.8	361.2	507.7	561.4
90°	0.0	131.8	317.3	454.0	512.5
92.5°	0.0	102.5	278.2	410.0	463.7
95°	0.0	83.0	239.2	366.1	419.8
97.5°	0.0	68.3	209.9	327.0	375.9
100°	0.0	53.7	180.6	292.9	336.8
102.5°	0.0	43.9	156.2	258.7	302.6
105°	0.0	29.3	131.8	229.4	268.5
107.5°	0.0	24.4	112.3	205.0	239.2
110°	0.0	19.5	102.5	175.7	209.9

TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	14.6	92.7	156.2	190.4
115°	0.0	14.6	78.1	141.6	166.0
117.5°	0.0	14.6	68.3	126.9	151.3
120°	0.0	9.8	63.5	112.3	136.7
122.5°	0.0	9.8	53.7	102.5	122.0
125°	0.0	9.8	48.8	92.7	107.4
127.5°	0.0	4.9	43.9	83.0	97.6
130°	0.0	4.9	39.1	73.2	87.9
132.5°	0.0	4.9	34.2	68.3	83.0
135°	0.0	0.0	29.3	58.6	73.2
137.5°	0.0	0.0	24.4	53.7	63.5
140°	0.0	0.0	19.5	43.9	58.6
142.5°	0.0	0.0	14.6	39.1	48.8
145°	0.0	0.0	14.6	34.2	39.1
147.5°	0.0	0.0	9.8	24.4	34.2
150°	0.0	0.0	4.9	19.5	24.4
152.5°	0.0	0.0	0.0	14.6	19.5
155°	0.0	0.0	0.0	9.8	14.6
157.5°	0.0	0.0	0.0	0.0	4.9
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357505

CATALOG NUMBER: 8ASL4-20VHE-3-G52-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.17	18.71	17.64	19.17	19.65	19.24	20.78	19.71	21.23	21.72
	3H	18.67	20.07	19.15	20.54	21.06	21.72	23.13	22.20	23.59	24.12
	4H	19.15	20.48	19.65	20.96	21.50	22.94	24.27	23.44	24.75	25.29
	6H	19.42	20.66	19.94	21.16	21.71	24.22	25.46	24.73	25.95	26.51
	8H	19.47	20.66	20.00	21.18	21.74	24.89	26.07	25.41	26.59	27.15
	12H	19.49	20.63	20.02	21.14	21.73	25.63	26.77	26.17	27.28	27.88
4H	2H	18.06	19.39	18.56	19.87	20.41	19.67	21.00	20.17	21.49	22.02
	3H	19.79	20.92	20.31	21.45	22.01	22.38	23.51	22.89	24.04	24.60
	4H	20.39	21.43	20.93	21.97	22.56	23.76	24.80	24.30	25.34	25.93
	6H	20.79	21.71	21.35	22.27	22.88	25.24	26.15	25.79	26.71	27.32
	8H	20.89	21.75	21.45	22.31	22.93	26.01	26.87	26.57	27.44	28.05
	12H	20.93	21.71	21.51	22.30	22.93	26.88	27.67	27.46	28.26	28.88
8H	4H	21.08	21.95	21.65	22.51	23.13	23.98	24.84	24.54	25.40	26.02
	6H	21.66	22.40	22.26	23.00	23.62	25.62	26.35	26.21	26.95	27.58
	8H	21.85	22.51	22.45	23.12	23.76	26.53	27.19	27.14	27.81	28.45
	12H	21.96	22.55	22.57	23.15	23.86	27.59	28.18	28.20	28.78	29.49
12H	4H	21.28	22.07	21.87	22.66	23.28	23.99	24.77	24.57	25.36	25.98
	6H	21.96	22.63	22.57	23.24	23.88	25.65	26.32	26.26	26.93	27.57
	8H	22.24	22.83	22.85	23.44	24.14	26.64	27.23	27.25	27.83	28.54

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-8

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-G520-UNV-OPL-1_600mA


Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-G520-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND GREEN 520NM LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K):	7535	CRI (Ra):	-11.7		
CIE u':	0.0718	R1:	-30.6	R9:	-351.9
CIE v':	0.5710	R2:	5.1	R10:	-75.5
Duv:	0.1461	R3:	5.6	R11:	-78.0
CIE x:	0.1962	R4:	-51.7	R12:	-14.7
CIE y:	0.6931	R5:	-6.4	R13:	-32.5
CIE z:	0.1107	R6:	-0.6	R14:	52.7
Peak Wavelength (nm):	524	R7:	10.9	R15:	-37.0
Dominant Wavelength (nm):	529	R8:	-25.8		
Purity:	75.95236				
Rf:	NR				
Rg:	NR				



Test Conditions


Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-8


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-8

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2511-597-8

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.63

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.87

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	7	NR	750	0	NR	880	0	NR
365	0	NR	495	249	NR	625	6	NR	755	0	NR	885	0	NR
370	0	NR	500	356	NR	630	4	NR	760	0	NR	890	0	NR
375	0	NR	505	502	NR	635	4	NR	765	0	NR	895	0	NR
380	0	NR	510	674	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	853	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	976	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	996	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	920	NR	660	2	NR	790	0	NR	920	0	NR
405	0	NR	535	792	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	642	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	511	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	394	NR	680	1	NR	810	0	NR	940	0	NR
425	1	NR	555	300	NR	685	1	NR	815	0	NR	945	0	NR
430	1	NR	560	224	NR	690	1	NR	820	0	NR	950	0	NR
435	1	NR	565	166	NR	695	1	NR	825	0	NR	955	0	NR
440	2	NR	570	122	NR	700	1	NR	830	0	NR	960	0	NR
445	3	NR	575	90	NR	705	1	NR	835	0	NR	965	0	NR
450	4	NR	580	66	NR	710	1	NR	840	0	NR	970	0	NR
455	7	NR	585	48	NR	715	0	NR	845	0	NR	975	0	NR
460	12	NR	590	36	NR	720	0	NR	850	0	NR	980	0	NR
465	19	NR	595	27	NR	725	0	NR	855	0	NR	985	0	NR
470	31	NR	600	21	NR	730	0	NR	860	0	NR	990	0	NR
475	49	NR	605	16	NR	735	0	NR	865	0	NR	995	0	NR
480	75	NR	610	12	NR	740	0	NR	870	0	NR	1000	0	NR
485	115	NR	615	9	NR	745	0	NR	875	0	NR			


REPORT NUMBER: SP1-2511-597-8

TM-30-18





Summary

$R_f = 0$
 $R_g = 0$
 $CIE R_a = -11.7$
 $R_g = -351.9$

Spectral Power Distribution Comparison




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 0	CES26 = 0	CES51 = 0	CES76 = 0
CES02 = 0	CES27 = 0	CES52 = 0	CES77 = 0
CES03 = 0	CES28 = 0	CES53 = 0	CES78 = 0
CES04 = 0	CES29 = 0	CES54 = 0	CES79 = 0
CES05 = 0	CES30 = 0	CES55 = 0	CES80 = 0
CES06 = 0	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 0	CES32 = 0	CES57 = 0	CES82 = 0
CES08 = 0	CES33 = 0	CES58 = 0	CES83 = 0
CES09 = 0	CES34 = 0	CES59 = 0	CES84 = 0
CES10 = 0	CES35 = 0	CES60 = 0	CES85 = 0
CES11 = 0	CES36 = 0	CES61 = 0	CES86 = 0
CES12 = 0	CES37 = 0	CES62 = 0	CES87 = 0
CES13 = 0	CES38 = 0	CES63 = 0	CES88 = 0
CES14 = 0	CES39 = 0	CES64 = 0	CES89 = 0
CES15 = 0	CES40 = 0	CES65 = 0	CES90 = 0
CES16 = 0	CES41 = 0	CES66 = 0	CES91 = 0
CES17 = 0	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 0	CES43 = 0	CES68 = 0	CES93 = 0
CES19 = 0	CES44 = 0	CES69 = 0	CES94 = 0
CES20 = 0	CES45 = 0	CES70 = 0	CES95 = 0
CES21 = 0	CES46 = 0	CES71 = 0	CES96 = 0
CES22 = 0	CES47 = 0	CES72 = 0	CES97 = 0
CES23 = 0	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 0	CES49 = 0	CES74 = 0	CES99 = 0
CES25 = 0	CES50 = 0	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)