

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357526

Luminaire Tested: 8ASL4-30VHE-3-50-UNV

Issue Date: 2/17/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1357526  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: 8ASL4-30VHE-3-50-UNV  
Description: 8FT 3000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 5000K LEDS 3 ROW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 24504.0 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 210.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1357526  
CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P1357526  
 CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	29167	29167	29167
5°	28941	28641	28499
10°	28812	28107	27778
15°	28527	27436	27168
20°	28130	26793	26478
25°	27665	25981	25694
30°	27173	25278	25031
35°	26554	24480	24294
40°	25995	23750	23517
45°	25395	22864	22737
50°	24709	21912	21927
55°	23974	21004	21198
60°	23008	19942	20459
65°	21774	18924	19845
70°	20196	17919	19364
75°	17873	17012	19035
80°	14306	16358	18894
85°	9079	16286	19174

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25395 cd/sqm



TEST NUMBER: P1357526  
 CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	683.4	2.8
10°-20°	1962.2	8.0
20°-30°	2966.7	12.1
30°-40°	3592.2	14.7
40°-50°	3772.9	15.4
50°-60°	3519.9	14.4
60°-70°	2909.0	11.9
70°-80°	2094.5	8.5
80°-90°	1301.6	5.3
90°-100°	762.7	3.1
100°-110°	436.3	1.8
110°-120°	246.3	1.0
120°-130°	141.8	0.6
130°-140°	76.4	0.3
140°-150°	32.1	0.1
150°-160°	5.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5612.3	22.9
0°-40°	9204.5	37.6
0°-60°	16497.3	67.3
0°-90°	22802.5	93.1
90°-120°	1445.3	5.9
90°-150°	1695.5	6.9
90°-180°	1701.0	6.9
0°-180°	24504.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	7207	7207	7207	7207	7207	
5°	7132	7192	7192	7192	7207	678
15°	6832	6922	6952	6997	7027	1926
25°	6233	6338	6443	6533	6593	2871
35°	5424	5574	5754	5918	5993	3395
45°	4495	4660	4914	5124	5214	3468
55°	3461	3656	3956	4240	4345	3093
65°	2337	2562	2952	3326	3461	2313
75°	1199	1498	2023	2457	2637	1268
85°	225	674	1274	1723	1888	275
90°	0	404	974	1393	1573	10
95°	0	255	734	1124	1289	0
105°	0	90	404	704	824	0
115°	0	45	240	434	509	0
125°	0	30	150	285	330	0
135°	0	0	90	180	225	0
145°	0	0	45	105	120	0
155°	0	0	0	30	45	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357526  
 CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	7207.0	7207.0	7207.0	7207.0	7207.0
2.5°	7177.0	7221.9	7221.9	7177.0	7177.0
5°	7132.0	7192.0	7192.0	7192.0	7207.0
7.5°	7087.1	7162.0	7162.0	7162.0	7192.0
10°	7027.2	7102.1	7117.1	7117.1	7132.0
12.5°	6937.3	7027.2	7042.1	7057.1	7072.1
15°	6832.4	6922.3	6952.2	6997.2	7027.2
17.5°	6712.5	6817.4	6877.3	6922.3	6952.2
20°	6562.7	6667.6	6742.5	6802.4	6847.4
22.5°	6412.8	6502.7	6592.6	6667.6	6712.5
25°	6233.0	6337.9	6442.8	6532.7	6592.6
27.5°	6038.3	6158.1	6293.0	6397.9	6457.8
30°	5858.5	5978.3	6128.2	6263.0	6322.9
32.5°	5648.7	5783.5	5948.4	6083.2	6158.1
35°	5423.9	5573.8	5753.6	5918.4	5993.3
37.5°	5199.2	5349.0	5573.8	5738.6	5813.5
40°	4974.4	5124.3	5364.0	5543.8	5618.7
42.5°	4734.7	4884.5	5139.3	5334.0	5423.9
45°	4495.0	4659.8	4914.5	5124.3	5214.2
47.5°	4255.3	4420.1	4689.8	4914.5	5004.4
50°	3985.6	4165.4	4435.0	4689.8	4779.7
52.5°	3730.8	3910.6	4210.3	4465.0	4554.9
55°	3461.1	3655.9	3955.6	4240.3	4345.1
57.5°	3191.4	3386.2	3700.9	4000.5	4120.4
60°	2906.8	3116.5	3446.2	3760.8	3895.7
62.5°	2622.1	2846.8	3206.4	3536.1	3670.9
65°	2337.4	2562.1	2951.7	3326.3	3461.1
67.5°	2052.7	2292.4	2712.0	3101.5	3266.4
70°	1768.0	2022.7	2472.2	2876.8	3041.6
72.5°	1483.3	1753.0	2247.5	2667.0	2831.8
75°	1198.7	1498.3	2022.7	2457.3	2637.1
77.5°	914.0	1258.6	1828.0	2262.5	2442.3
80°	659.3	1048.8	1618.2	2067.7	2247.5
82.5°	419.5	839.1	1438.4	1887.9	2067.7
85°	224.7	674.2	1273.6	1723.1	1887.9
87.5°	74.9	524.4	1108.8	1558.3	1723.1
90°	0.0	404.5	973.9	1393.4	1573.2
92.5°	0.0	314.6	854.0	1258.6	1423.4
95°	0.0	254.7	734.2	1123.7	1288.6
97.5°	0.0	209.8	644.3	1003.9	1153.7
100°	0.0	164.8	554.4	899.0	1033.8
102.5°	0.0	134.8	479.5	794.1	929.0
105°	0.0	89.9	404.5	704.2	824.1
107.5°	0.0	74.9	344.6	629.3	734.2
110°	0.0	59.9	314.6	539.4	644.3



TEST NUMBER: P1357526  
 CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	44.9	284.7	479.5	584.3
115°	0.0	44.9	239.7	434.5	509.4
117.5°	0.0	44.9	209.8	389.6	464.5
120°	0.0	30.0	194.8	344.6	419.5
122.5°	0.0	30.0	164.8	314.6	374.6
125°	0.0	30.0	149.8	284.7	329.6
127.5°	0.0	15.0	134.8	254.7	299.7
130°	0.0	15.0	119.9	224.7	269.7
132.5°	0.0	15.0	104.9	209.8	254.7
135°	0.0	0.0	89.9	179.8	224.7
137.5°	0.0	0.0	74.9	164.8	194.8
140°	0.0	0.0	59.9	134.8	179.8
142.5°	0.0	0.0	44.9	119.9	149.8
145°	0.0	0.0	44.9	104.9	119.9
147.5°	0.0	0.0	30.0	74.9	104.9
150°	0.0	0.0	15.0	59.9	74.9
152.5°	0.0	0.0	0.0	44.9	59.9
155°	0.0	0.0	0.0	30.0	44.9
157.5°	0.0	0.0	0.0	0.0	15.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357526  
 CATALOG NUMBER: 8ASL4-30VHE-3-50-UNV

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.07	22.61	21.54	23.06	23.55	23.14	24.68	23.60	25.13	25.61
	3H	22.56	23.97	23.04	24.43	24.96	25.62	27.02	26.10	27.49	28.01
	4H	23.04	24.37	23.55	24.86	25.39	26.83	28.16	27.33	28.65	29.18
	6H	23.32	24.56	23.83	25.05	25.61	28.11	29.35	28.63	29.85	30.40
	8H	23.37	24.56	23.90	25.08	25.64	28.78	29.97	29.31	30.49	31.05
	12H	23.38	24.52	23.92	25.04	25.63	29.53	30.67	30.06	31.18	31.77
4H	2H	21.95	23.28	22.45	23.77	24.30	23.57	24.90	24.07	25.38	25.92
	3H	23.69	24.82	24.20	25.35	25.91	26.28	27.41	26.79	27.94	28.50
	4H	24.29	25.33	24.83	25.86	26.46	27.66	28.70	28.20	29.23	29.83
	6H	24.69	25.61	25.24	26.17	26.77	29.13	30.05	29.69	30.61	31.22
	8H	24.78	25.64	25.34	26.21	26.83	29.91	30.77	30.47	31.33	31.95
	12H	24.83	25.61	25.41	26.20	26.83	30.78	31.56	31.36	32.15	32.78
8H	4H	24.98	25.84	25.54	26.41	27.03	27.88	28.74	28.44	29.30	29.92
	6H	25.56	26.29	26.15	26.90	27.52	29.52	30.25	30.11	30.85	31.48
	8H	25.74	26.40	26.35	27.02	27.65	30.43	31.09	31.04	31.71	32.34
	12H	25.86	26.45	26.46	27.05	27.75	31.49	32.08	32.09	32.68	33.39
12H	4H	25.18	25.96	25.76	26.55	27.18	27.88	28.67	28.46	29.26	29.88
	6H	25.86	26.52	26.47	27.14	27.77	29.55	30.21	30.16	30.83	31.47
	8H	26.14	26.73	26.75	27.33	28.04	30.54	31.13	31.14	31.73	32.43

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-5

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-50-UNV-OPL-1\_600mA

Data in this report applies to families of products including 4ASL

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2511-597-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 11/18/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Fail-Safe  
 Catalog Number: **4ASL-2-50-UNV-OPL-1\_600mA**  
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 5000K LEDs with 1 rows at 600mA

**Spectral Parameters**

CCT (K): 5076  
 CIE u': 0.2110  
 CIE v': 0.4830  
 Duv: -0.0005  
 CIE x: 0.3429  
 CIE y: 0.3489  
 CIE z: 0.3082  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 572  
 Purity: 7.553016  
 R<sub>f</sub>: 90.4  
 R<sub>g</sub>: 99

CRI (Ra):	94.9		
R1:	96.7	R9:	74.0
R2:	98.2	R10:	93.9
R3:	96.6	R11:	96.2
R4:	95.6	R12:	72.4
R5:	95.1	R13:	98.1
R6:	93.6	R14:	97.8
R7:	94.0	R15:	95.6
R8:	89.6		



**Test Conditions**

Stabilization Time: 24M  
 Operation Time: 1H 24M  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-5

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-5

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.12

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-5

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 4.65**





λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

**Summary**

$R_f = 90.4$   
 $R_g = 99$   
 $CIE R_a = 94.9$   
 $R_9 = 74.0$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 85	CES26 = 95	CES51 = 95	CES76 = 87
CES02 = 61	CES27 = 89	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 84
CES04 = 69	CES29 = 95	CES54 = 90	CES79 = 94
CES05 = 48	CES30 = 84	CES55 = 88	CES80 = 93
CES06 = 50	CES31 = 96	CES56 = 91	CES81 = 81
CES07 = 41	CES32 = 92	CES57 = 89	CES82 = 97
CES08 = 40	CES33 = 94	CES58 = 89	CES83 = 95
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 93
CES10 = 73	CES35 = 96	CES60 = 90	CES85 = 82
CES11 = 56	CES36 = 76	CES61 = 90	CES86 = 85
CES12 = 62	CES37 = 95	CES62 = 80	CES87 = 93
CES13 = 42	CES38 = 79	CES63 = 90	CES88 = 97
CES14 = 74	CES39 = 98	CES64 = 86	CES89 = 87
CES15 = 71	CES40 = 99	CES65 = 87	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 83	CES91 = 70
CES17 = 48	CES42 = 94	CES67 = 82	CES92 = 78
CES18 = 56	CES43 = 95	CES68 = 85	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 86	CES94 = 79
CES20 = 65	CES45 = 99	CES70 = 84	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 76	CES96 = 93
CES22 = 77	CES47 = 93	CES72 = 92	CES97 = 96
CES23 = 91	CES48 = 86	CES73 = 80	CES98 = 95
CES24 = 90	CES49 = 98	CES74 = 89	CES99 = 93
CES25 = 70	CES50 = 96	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)