

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357542

Luminaire Tested: 8ASL4-35VHE-3-65-UNV

Issue Date: 2/17/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1357542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: 8ASL4-35VHE-3-65-UNV  
Description: 8FT 3500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 6500K LEDS 3 ROW  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 27992.0 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')  
CIE Type: Direct

Input Watts (W): 252.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1357542  
CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P1357542  
 CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	33319	33319	33319
5°	33060	32717	32556
10°	32913	32107	31732
15°	32587	31342	31035
20°	32134	30607	30247
25°	31603	29679	29352
30°	31040	28876	28595
35°	30334	27965	27752
40°	29696	27131	26865
45°	29010	26119	25974
50°	28226	25031	25048
55°	27387	23994	24215
60°	26282	22781	23371
65°	24873	21618	22670
70°	23071	20470	22121
75°	20416	19435	21744
80°	16342	18686	21583
85°	10372	18605	21903

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29010 cd/sqm



TEST NUMBER: P1357542  
 CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	780.7	2.8
10°-20°	2241.5	8.0
20°-30°	3389.0	12.1
30°-40°	4103.5	14.7
40°-50°	4309.9	15.4
50°-60°	4021.0	14.4
60°-70°	3323.1	11.9
70°-80°	2392.7	8.5
80°-90°	1486.8	5.3
90°-100°	871.2	3.1
100°-110°	498.4	1.8
110°-120°	281.4	1.0
120°-130°	161.9	0.6
130°-140°	87.2	0.3
140°-150°	36.7	0.1
150°-160°	6.8	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6411.2	22.9
0°-40°	10514.7	37.6
0°-60°	18845.6	67.3
0°-90°	26048.3	93.1
90°-120°	1651.0	5.9
90°-150°	1936.9	6.9
90°-180°	1944.0	6.9
0°-180°	27992.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	8233	8233	8233	8233	8233	
5°	8147	8216	8216	8216	8233	774
15°	7805	7908	7942	7993	8027	2201
25°	7120	7240	7360	7463	7531	3280
35°	6196	6367	6573	6761	6846	3879
45°	5135	5323	5614	5854	5956	3962
55°	3954	4176	4519	4844	4964	3533
65°	2670	2927	3372	3800	3954	2642
75°	1369	1712	2311	2807	3012	1448
85°	257	770	1455	1968	2157	314
90°	0	462	1112	1592	1797	12
95°	0	291	839	1284	1472	0
105°	0	103	462	804	941	0
115°	0	51	274	496	582	0
125°	0	34	171	325	377	0
135°	0	0	103	205	257	0
145°	0	0	51	120	137	0
155°	0	0	0	34	51	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357542  
 CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	8232.8	8232.8	8232.8	8232.8	8232.8
2.5°	8198.6	8249.9	8249.9	8198.6	8198.6
5°	8147.2	8215.7	8215.7	8215.7	8232.8
7.5°	8095.9	8181.5	8181.5	8181.5	8215.7
10°	8027.4	8113.0	8130.1	8130.1	8147.2
12.5°	7924.7	8027.4	8044.5	8061.7	8078.8
15°	7804.9	7907.6	7941.9	7993.2	8027.4
17.5°	7668.0	7787.8	7856.3	7907.6	7941.9
20°	7496.8	7616.6	7702.2	7770.7	7822.0
22.5°	7325.7	7428.4	7531.1	7616.6	7668.0
25°	7120.3	7240.1	7359.9	7462.6	7531.1
27.5°	6897.8	7034.7	7188.7	7308.6	7377.0
30°	6692.4	6829.3	7000.5	7154.5	7223.0
32.5°	6452.8	6606.8	6795.1	6949.1	7034.7
35°	6196.0	6367.2	6572.6	6760.8	6846.4
37.5°	5939.3	6110.4	6367.2	6555.4	6641.0
40°	5682.5	5853.7	6127.5	6332.9	6418.5
42.5°	5408.7	5579.8	5870.8	6093.3	6196.0
45°	5134.8	5323.1	5614.1	5853.7	5956.4
47.5°	4861.0	5049.2	5357.3	5614.1	5716.8
50°	4552.9	4758.3	5066.4	5357.3	5460.0
52.5°	4261.9	4467.3	4809.6	5100.6	5203.3
55°	3953.8	4176.3	4518.6	4843.8	4963.7
57.5°	3645.7	3868.2	4227.7	4570.0	4706.9
60°	3320.5	3560.1	3936.7	4296.1	4450.2
62.5°	2995.3	3252.1	3662.8	4039.4	4193.4
65°	2670.1	2926.8	3371.9	3799.8	3953.8
67.5°	2344.9	2618.8	3098.0	3543.0	3731.3
70°	2019.7	2310.7	2824.1	3286.3	3474.6
72.5°	1694.5	2002.6	2567.4	3046.7	3234.9
75°	1369.3	1711.6	2310.7	2807.0	3012.4
77.5°	1044.1	1437.7	2088.2	2584.5	2789.9
80°	753.1	1198.1	1848.5	2362.0	2567.4
82.5°	479.2	958.5	1643.1	2156.6	2362.0
85°	256.7	770.2	1454.9	1968.3	2156.6
87.5°	85.6	599.1	1266.6	1780.1	1968.3
90°	0.0	462.1	1112.5	1591.8	1797.2
92.5°	0.0	359.4	975.6	1437.7	1626.0
95°	0.0	291.0	838.7	1283.7	1472.0
97.5°	0.0	239.6	736.0	1146.8	1317.9
100°	0.0	188.3	633.3	1027.0	1181.0
102.5°	0.0	154.0	547.7	907.2	1061.2
105°	0.0	102.7	462.1	804.5	941.4
107.5°	0.0	85.6	393.7	718.9	838.7
110°	0.0	68.5	359.4	616.2	736.0



TEST NUMBER: P1357542  
 CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	51.3	325.2	547.7	667.5
115°	0.0	51.3	273.9	496.4	581.9
117.5°	0.0	51.3	239.6	445.0	530.6
120°	0.0	34.2	222.5	393.7	479.2
122.5°	0.0	34.2	188.3	359.4	427.9
125°	0.0	34.2	171.2	325.2	376.6
127.5°	0.0	17.1	154.0	291.0	342.3
130°	0.0	17.1	136.9	256.7	308.1
132.5°	0.0	17.1	119.8	239.6	291.0
135°	0.0	0.0	102.7	205.4	256.7
137.5°	0.0	0.0	85.6	188.3	222.5
140°	0.0	0.0	68.5	154.0	205.4
142.5°	0.0	0.0	51.3	136.9	171.2
145°	0.0	0.0	51.3	119.8	136.9
147.5°	0.0	0.0	34.2	85.6	119.8
150°	0.0	0.0	17.1	68.5	85.6
152.5°	0.0	0.0	0.0	51.3	68.5
155°	0.0	0.0	0.0	34.2	51.3
157.5°	0.0	0.0	0.0	0.0	17.1
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357542  
 CATALOG NUMBER: 8ASL4-35VHE-3-65-UNV

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.53	23.07	22.00	23.52	24.01	23.60	25.14	24.07	25.59	26.08
	3H	23.03	24.43	23.51	24.89	25.42	26.08	27.49	26.56	27.95	28.47
	4H	23.51	24.84	24.01	25.32	25.86	27.29	28.63	27.80	29.11	29.65
	6H	23.78	25.02	24.30	25.52	26.07	28.57	29.81	29.09	30.31	30.86
	8H	23.83	25.02	24.36	25.54	26.10	29.24	30.43	29.77	30.95	31.51
	12H	23.85	24.99	24.38	25.50	26.09	29.99	31.13	30.52	31.64	32.23
4H	2H	22.41	23.75	22.92	24.23	24.77	24.03	25.36	24.53	25.84	26.38
	3H	24.15	25.28	24.66	25.81	26.37	26.74	27.87	27.25	28.40	28.96
	4H	24.75	25.79	25.29	26.33	26.92	28.12	29.16	28.66	29.70	30.29
	6H	25.15	26.07	25.71	26.63	27.24	29.59	30.51	30.15	31.07	31.68
	8H	25.24	26.11	25.80	26.67	27.29	30.37	31.23	30.93	31.79	32.41
	12H	25.29	26.07	25.87	26.66	27.29	31.24	32.03	31.82	32.62	33.24
8H	4H	25.44	26.31	26.00	26.87	27.49	28.34	29.20	28.90	29.76	30.38
	6H	26.02	26.75	26.62	27.36	27.98	29.98	30.71	30.57	31.31	31.94
	8H	26.20	26.86	26.81	27.48	28.12	30.89	31.55	31.50	32.17	32.81
	12H	26.32	26.91	26.93	27.51	28.22	31.95	32.54	32.56	33.14	33.85
12H	4H	25.64	26.43	26.22	27.02	27.64	28.35	29.13	28.93	29.72	30.34
	6H	26.32	26.98	26.93	27.60	28.24	30.01	30.68	30.62	31.29	31.93
	8H	26.60	27.19	27.21	27.80	28.50	31.00	31.59	31.60	32.19	32.90

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-6

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-65-UNV-OPL-1\_600mA

Data in this report applies to families of products including 4ASL


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2511-597-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 11/18/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Fail-Safe  
 Catalog Number: **4ASL-2-65-UNV-OPL-1\_600mA**  
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 6500K LEDs with 1 rows at 600mA

**Spectral Parameters**

CCT (K): 6972  
 CIE u': 0.1979  
 CIE v': 0.4612  
 Duv: 0.0005  
 CIE x: 0.3066  
 CIE y: 0.3177  
 CIE z: 0.3758  
 Peak Wavelength (nm): 455  
 Dominant Wavelength (nm): 483  
 Purity: 10.33335  
 Rf: 88.2  
 Rg: 97.1

CRI (Ra):	94.3		
R1:	96.1	R9:	82.6
R2:	98.8	R10:	95.4
R3:	96.4	R11:	95.2
R4:	92.8	R12:	63.5
R5:	92.9	R13:	99.3
R6:	92.2	R14:	98.1
R7:	93.5	R15:	93.7
R8:	91.4		



**Test Conditions**


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 6500K 7-step quadrangle

REPORT NUMBER: SP1-2511-597-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	260	NR	620	255	NR	750	6	NR	880	0	NR
365	0	NR	495	274	NR	625	252	NR	755	6	NR	885	0	NR
370	0	NR	500	297	NR	630	778	NR	760	5	NR	890	0	NR
375	0	NR	505	320	NR	635	431	NR	765	4	NR	895	0	NR
380	1	NR	510	337	NR	640	160	NR	770	4	NR	900	0	NR
385	2	NR	515	349	NR	645	165	NR	775	3	NR	905	0	NR
390	2	NR	520	354	NR	650	135	NR	780	3	NR	910	0	NR
395	3	NR	525	356	NR	655	115	NR	785	2	NR	915	0	NR
400	5	NR	530	356	NR	660	99	NR	790	2	NR	920	0	NR
405	6	NR	535	355	NR	665	84	NR	795	2	NR	925	0	NR
410	8	NR	540	354	NR	670	77	NR	800	2	NR	930	0	NR
415	12	NR	545	351	NR	675	64	NR	805	1	NR	935	0	NR
420	19	NR	550	350	NR	680	55	NR	810	1	NR	940	0	NR
425	33	NR	555	348	NR	685	47	NR	815	1	NR	945	0	NR
430	60	NR	560	344	NR	690	41	NR	820	1	NR	950	0	NR
435	113	NR	565	339	NR	695	35	NR	825	1	NR	955	0	NR
440	206	NR	570	331	NR	700	30	NR	830	1	NR	960	0	NR
445	392	NR	575	323	NR	705	26	NR	835	1	NR	965	0	NR
450	764	NR	580	315	NR	710	22	NR	840	1	NR	970	0	NR
455	1000	NR	585	307	NR	715	19	NR	845	0	NR	975	0	NR
460	736	NR	590	299	NR	720	16	NR	850	0	NR	980	0	NR
465	513	NR	595	290	NR	725	14	NR	855	0	NR	985	0	NR
470	430	NR	600	282	NR	730	12	NR	860	0	NR	990	0	NR
475	325	NR	605	276	NR	735	10	NR	865	0	NR	995	0	NR
480	256	NR	610	287	NR	740	9	NR	870	0	NR	1000	0	NR
485	250	NR	615	284	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-6

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 2.48**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	260	NR	620	255	NR	750	6	NR	880	0	NR
365	0	NR	495	274	NR	625	252	NR	755	6	NR	885	0	NR
370	0	NR	500	297	NR	630	778	NR	760	5	NR	890	0	NR
375	0	NR	505	320	NR	635	431	NR	765	4	NR	895	0	NR
380	1	NR	510	337	NR	640	160	NR	770	4	NR	900	0	NR
385	2	NR	515	349	NR	645	165	NR	775	3	NR	905	0	NR
390	2	NR	520	354	NR	650	135	NR	780	3	NR	910	0	NR
395	3	NR	525	356	NR	655	115	NR	785	2	NR	915	0	NR
400	5	NR	530	356	NR	660	99	NR	790	2	NR	920	0	NR
405	6	NR	535	355	NR	665	84	NR	795	2	NR	925	0	NR
410	8	NR	540	354	NR	670	77	NR	800	2	NR	930	0	NR
415	12	NR	545	351	NR	675	64	NR	805	1	NR	935	0	NR
420	19	NR	550	350	NR	680	55	NR	810	1	NR	940	0	NR
425	33	NR	555	348	NR	685	47	NR	815	1	NR	945	0	NR
430	60	NR	560	344	NR	690	41	NR	820	1	NR	950	0	NR
435	113	NR	565	339	NR	695	35	NR	825	1	NR	955	0	NR
440	206	NR	570	331	NR	700	30	NR	830	1	NR	960	0	NR
445	392	NR	575	323	NR	705	26	NR	835	1	NR	965	0	NR
450	764	NR	580	315	NR	710	22	NR	840	1	NR	970	0	NR
455	1000	NR	585	307	NR	715	19	NR	845	0	NR	975	0	NR
460	736	NR	590	299	NR	720	16	NR	850	0	NR	980	0	NR
465	513	NR	595	290	NR	725	14	NR	855	0	NR	985	0	NR
470	430	NR	600	282	NR	730	12	NR	860	0	NR	990	0	NR
475	325	NR	605	276	NR	735	10	NR	865	0	NR	995	0	NR
480	256	NR	610	287	NR	740	9	NR	870	0	NR	1000	0	NR
485	250	NR	615	284	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-6

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 5.67





$\lambda$ (nm)	Power $W^{\wedge}/nm$	Lumens ( $\phi/nm$ )	$\lambda$ (nm)	Power $W^{\wedge}/nm$	Lumens ( $\phi/nm$ )	$\lambda$ (nm)	Power $W^{\wedge}/nm$	Lumens ( $\phi/nm$ )	$\lambda$ (nm)	Power $W^{\wedge}/nm$	Lumens ( $\phi/nm$ )	$\lambda$ (nm)	Power $W^{\wedge}/nm$	Lumens ( $\phi/nm$ )
360	0	NR	490	260	NR	620	255	NR	750	6	NR	880	0	NR
365	0	NR	495	274	NR	625	252	NR	755	6	NR	885	0	NR
370	0	NR	500	297	NR	630	778	NR	760	5	NR	890	0	NR
375	0	NR	505	320	NR	635	431	NR	765	4	NR	895	0	NR
380	1	NR	510	337	NR	640	160	NR	770	4	NR	900	0	NR
385	2	NR	515	349	NR	645	165	NR	775	3	NR	905	0	NR
390	2	NR	520	354	NR	650	135	NR	780	3	NR	910	0	NR
395	3	NR	525	356	NR	655	115	NR	785	2	NR	915	0	NR
400	5	NR	530	356	NR	660	99	NR	790	2	NR	920	0	NR
405	6	NR	535	355	NR	665	84	NR	795	2	NR	925	0	NR
410	8	NR	540	354	NR	670	77	NR	800	2	NR	930	0	NR
415	12	NR	545	351	NR	675	64	NR	805	1	NR	935	0	NR
420	19	NR	550	350	NR	680	55	NR	810	1	NR	940	0	NR
425	33	NR	555	348	NR	685	47	NR	815	1	NR	945	0	NR
430	60	NR	560	344	NR	690	41	NR	820	1	NR	950	0	NR
435	113	NR	565	339	NR	695	35	NR	825	1	NR	955	0	NR
440	206	NR	570	331	NR	700	30	NR	830	1	NR	960	0	NR
445	392	NR	575	323	NR	705	26	NR	835	1	NR	965	0	NR
450	764	NR	580	315	NR	710	22	NR	840	1	NR	970	0	NR
455	1000	NR	585	307	NR	715	19	NR	845	0	NR	975	0	NR
460	736	NR	590	299	NR	720	16	NR	850	0	NR	980	0	NR
465	513	NR	595	290	NR	725	14	NR	855	0	NR	985	0	NR
470	430	NR	600	282	NR	730	12	NR	860	0	NR	990	0	NR
475	325	NR	605	276	NR	735	10	NR	865	0	NR	995	0	NR
480	256	NR	610	287	NR	740	9	NR	870	0	NR	1000	0	NR
485	250	NR	615	284	NR	745	7	NR	875	0	NR			

**Summary**

$R_f = 88.2$   
 $R_g = 97.1$   
 $CIE R_a = 94.3$   
 $R_9 = 82.6$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 85	CES26 = 97	CES51 = 91	CES76 = 88
CES02 = 60	CES27 = 83	CES52 = 96	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 92	CES78 = 83
CES04 = 68	CES29 = 88	CES54 = 86	CES79 = 94
CES05 = 47	CES30 = 74	CES55 = 82	CES80 = 93
CES06 = 49	CES31 = 90	CES56 = 86	CES81 = 81
CES07 = 40	CES32 = 96	CES57 = 83	CES82 = 96
CES08 = 39	CES33 = 86	CES58 = 83	CES83 = 94
CES09 = 29	CES34 = 96	CES59 = 94	CES84 = 91
CES10 = 72	CES35 = 97	CES60 = 87	CES85 = 80
CES11 = 55	CES36 = 67	CES61 = 87	CES86 = 86
CES12 = 61	CES37 = 96	CES62 = 72	CES87 = 93
CES13 = 42	CES38 = 68	CES63 = 86	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 81	CES89 = 88
CES15 = 71	CES40 = 96	CES65 = 83	CES90 = 90
CES16 = 46	CES41 = 88	CES66 = 76	CES91 = 60
CES17 = 48	CES42 = 97	CES67 = 76	CES92 = 77
CES18 = 55	CES43 = 97	CES68 = 82	CES93 = 85
CES19 = 69	CES44 = 99	CES69 = 82	CES94 = 81
CES20 = 64	CES45 = 98	CES70 = 82	CES95 = 80
CES21 = 84	CES46 = 93	CES71 = 68	CES96 = 93
CES22 = 76	CES47 = 87	CES72 = 91	CES97 = 95
CES23 = 91	CES48 = 79	CES73 = 77	CES98 = 93
CES24 = 89	CES49 = 95	CES74 = 86	CES99 = 91
CES25 = 69	CES50 = 92	CES75 = 74	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)