

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356742

Luminaire Tested: 1ASL4-25VHE-3-A59-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 1ASL4-25VHE-3-A59-UNV
Description: 1FT 2500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND A59 LEDS 3 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 509.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 0.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 14.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	117	117	117	117	114	114	114	114	107	107	107		101	101	101		96
1	105	100	95	91	102	97	92	88	91	88	84		86	83	80		81
2	95	86	79	72	92	84	77	71	79	73	68		75	70	66		71
3	86	75	67	60	83	73	65	59	69	62	57		65	60	55		62
4	79	66	57	50	76	65	56	49	61	54	48		58	52	47		55
5	73	59	50	43	70	58	49	42	55	47	41		52	45	40		49
6	67	53	44	37	64	52	43	37	49	42	36		47	40	35		45
7	62	48	39	33	60	47	38	32	45	37	32		43	36	31		41
8	58	44	35	29	56	43	35	29	41	34	28		39	32	28		37
9	54	40	32	26	52	39	31	26	38	30	25		36	30	25		35
10	50	37	29	24	49	36	29	23	35	28	23		33	27	23		32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4937	4937	4937
5°	4858	4821	4824
10°	4799	4704	4701
15°	4711	4568	4600
20°	4605	4438	4481
25°	4490	4278	4348
30°	4366	4140	4236
35°	4223	3985	4112
40°	4083	3841	3980
45°	3937	3674	3848
50°	3770	3492	3712
55°	3589	3321	3590
60°	3364	3121	3462
65°	3088	2925	3359
70°	2738	2733	3279
75°	2271	2542	3223
80°	1623	2381	3199
85°	803	2286	3244

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3937 cd/sqm

TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.2	2.8
10°-20°	40.8	8.0
20°-30°	61.6	12.1
30°-40°	74.6	14.7
40°-50°	78.4	15.4
50°-60°	73.1	14.4
60°-70°	60.4	11.9
70°-80°	43.5	8.5
80°-90°	27.0	5.3
90°-100°	15.8	3.1
100°-110°	9.1	1.8
110°-120°	5.1	1.0
120°-130°	2.9	0.6
130°-140°	1.6	0.3
140°-150°	0.7	0.1
150°-160°	0.1	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.6	22.9
0°-40°	191.2	37.6
0°-60°	342.7	67.3
0°-90°	473.7	93.1
90°-120°	30.0	5.9
90°-150°	35.2	6.9
90°-180°	35.0	6.9
0°-180°	509.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	150	150	150	150	150	
5°	148	149	149	149	150	14
15°	142	144	144	145	146	40
25°	130	132	134	136	137	60
35°	113	116	120	123	124	71
45°	93	97	102	106	108	72
55°	72	76	82	88	90	64
65°	49	53	61	69	72	48
75°	25	31	42	51	55	26
85°	5	14	26	36	39	6
90°	0	8	20	29	33	0
95°	0	5	15	23	27	0
105°	0	2	8	15	17	0
115°	0	1	5	9	11	0
125°	0	1	3	6	7	0
135°	0	0	2	4	5	0
145°	0	0	1	2	2	0
155°	0	0	0	1	1	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	149.7	149.7	149.7	149.7	149.7
2.5°	149.1	150.0	150.0	149.1	149.1
5°	148.1	149.4	149.4	149.4	149.7
7.5°	147.2	148.8	148.8	148.8	149.4
10°	146.0	147.5	147.8	147.8	148.1
12.5°	144.1	146.0	146.3	146.6	146.9
15°	141.9	143.8	144.4	145.3	146.0
17.5°	139.4	141.6	142.9	143.8	144.4
20°	136.3	138.5	140.1	141.3	142.2
22.5°	133.2	135.1	136.9	138.5	139.4
25°	129.5	131.7	133.8	135.7	136.9
27.5°	125.4	127.9	130.7	132.9	134.1
30°	121.7	124.2	127.3	130.1	131.3
32.5°	117.3	120.1	123.6	126.4	127.9
35°	112.7	115.8	119.5	122.9	124.5
37.5°	108.0	111.1	115.8	119.2	120.8
40°	103.3	106.4	111.4	115.2	116.7
42.5°	98.4	101.5	106.8	110.8	112.7
45°	93.4	96.8	102.1	106.4	108.3
47.5°	88.4	91.8	97.4	102.1	104.0
50°	82.8	86.5	92.1	97.4	99.3
52.5°	77.5	81.2	87.5	92.7	94.6
55°	71.9	75.9	82.2	88.1	90.3
57.5°	66.3	70.3	76.9	83.1	85.6
60°	60.4	64.7	71.6	78.1	80.9
62.5°	54.5	59.1	66.6	73.5	76.3
65°	48.6	53.2	61.3	69.1	71.9
67.5°	42.6	47.6	56.3	64.4	67.8
70°	36.7	42.0	51.4	59.8	63.2
72.5°	30.8	36.4	46.7	55.4	58.8
75°	24.9	31.1	42.0	51.0	54.8
77.5°	19.0	26.1	38.0	47.0	50.7
80°	13.7	21.8	33.6	43.0	46.7
82.5°	8.7	17.4	29.9	39.2	43.0
85°	4.7	14.0	26.5	35.8	39.2
87.5°	1.6	10.9	23.0	32.4	35.8
90°	0.0	8.4	20.2	28.9	32.7
92.5°	0.0	6.5	17.7	26.1	29.6
95°	0.0	5.3	15.3	23.3	26.8
97.5°	0.0	4.4	13.4	20.9	24.0
100°	0.0	3.4	11.5	18.7	21.5
102.5°	0.0	2.8	10.0	16.5	19.3
105°	0.0	1.9	8.4	14.6	17.1
107.5°	0.0	1.6	7.2	13.1	15.3
110°	0.0	1.2	6.5	11.2	13.4

TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.9	5.9	10.0	12.1
115°	0.0	0.9	5.0	9.0	10.6
117.5°	0.0	0.9	4.4	8.1	9.6
120°	0.0	0.6	4.0	7.2	8.7
122.5°	0.0	0.6	3.4	6.5	7.8
125°	0.0	0.6	3.1	5.9	6.8
127.5°	0.0	0.3	2.8	5.3	6.2
130°	0.0	0.3	2.5	4.7	5.6
132.5°	0.0	0.3	2.2	4.4	5.3
135°	0.0	0.0	1.9	3.7	4.7
137.5°	0.0	0.0	1.6	3.4	4.0
140°	0.0	0.0	1.2	2.8	3.7
142.5°	0.0	0.0	0.9	2.5	3.1
145°	0.0	0.0	0.9	2.2	2.5
147.5°	0.0	0.0	0.6	1.6	2.2
150°	0.0	0.0	0.3	1.2	1.6
152.5°	0.0	0.0	0.0	0.9	1.2
155°	0.0	0.0	0.0	0.6	0.9
157.5°	0.0	0.0	0.0	0.0	0.3
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356742

CATALOG NUMBER: 1ASL4-25VHE-3-A59-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.78	16.32	15.25	16.78	17.26	16.57	18.11	17.04	18.57	19.05
	3H	16.29	17.69	16.77	18.16	18.68	18.94	20.34	19.42	20.80	21.33
	4H	16.77	18.10	17.27	18.59	19.12	20.05	21.38	20.55	21.87	22.40
	6H	17.05	18.29	17.57	18.79	19.34	21.18	22.42	21.69	22.91	23.47
	8H	17.10	18.29	17.63	18.81	19.37	21.73	22.92	22.26	23.44	24.00
	12H	17.12	18.26	17.65	18.77	19.36	22.30	23.44	22.83	23.95	24.54
4H	2H	15.62	16.95	16.12	17.43	17.97	17.02	18.35	17.52	18.83	19.37
	3H	17.35	18.49	17.87	19.01	19.57	19.61	20.74	20.12	21.27	21.83
	4H	17.96	19.00	18.50	19.53	20.13	20.90	21.94	21.43	22.47	23.06
	6H	18.36	19.28	18.92	19.84	20.45	22.22	23.13	22.77	23.70	24.30
	8H	18.46	19.32	19.02	19.88	20.50	22.87	23.74	23.43	24.30	24.92
	12H	18.50	19.29	19.09	19.88	20.50	23.56	24.35	24.15	24.94	25.56
8H	4H	18.59	19.45	19.15	20.01	20.63	21.12	21.99	21.68	22.55	23.17
	6H	19.17	19.90	19.76	20.50	21.13	22.61	23.35	23.21	23.95	24.58
	8H	19.35	20.01	19.95	20.62	21.26	23.41	24.07	24.02	24.69	25.33
	12H	19.47	20.06	20.07	20.66	21.36	24.29	24.88	24.89	25.48	26.18
12H	4H	18.76	19.54	19.34	20.13	20.76	21.13	21.92	21.72	22.51	23.13
	6H	19.43	20.09	20.03	20.71	21.34	22.66	23.32	23.26	23.93	24.57
	8H	19.71	20.30	20.31	20.90	21.60	23.52	24.11	24.13	24.72	25.42

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-9

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-A590-UNV-OPL-1_600mA


Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-A590-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND AMBER 590 LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K):	1535	CRI (Ra):	-20.0		
CIE u':	0.3534	R1:	-32.1	R9:	-380.5
CIE v':	0.5468	R2:	53.1	R10:	29.9
Duv:	0.0117	R3:	18.5	R11:	-92.0
CIE x:	0.5921	R4:	-65.7	R12:	-8.5
CIE y:	0.4072	R5:	-38.6	R13:	-13.5
CIE z:	0.0007	R6:	42.8	R14:	47.1
Peak Wavelength (nm):	598	R7:	-6.2	R15:	-65.4
Dominant Wavelength (nm):	592	R8:	-132.3		
Purity:	99.97894				
Rf:	1.3				
Rg:	0.1				



Test Conditions


Stabilization Time: 77M
 Operation Time: 2H 17M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-9

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.22

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 0.12


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9





TM-30-18

Summary

$R_f = 1.3$
 $R_g = 0.1$
 $CIE\ R_a = -20.0$
 $R_g = -380.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 90	CES26 = 0	CES51 = 19	CES76 = 0
CES02 = 70	CES27 = 32	CES52 = 2	CES77 = 0
CES03 = 31	CES28 = 25	CES53 = 0	CES78 = 0
CES04 = 77	CES29 = 1	CES54 = 13	CES79 = 2
CES05 = 52	CES30 = 31	CES55 = 7	CES80 = 1
CES06 = 56	CES31 = 1	CES56 = 0	CES81 = 0
CES07 = 41	CES32 = 0	CES57 = 0	CES82 = 51
CES08 = 39	CES33 = 21	CES58 = 0	CES83 = 21
CES09 = 29	CES34 = 0	CES59 = 10	CES84 = 55
CES10 = 87	CES35 = 24	CES60 = 60	CES85 = 10
CES11 = 70	CES36 = 77	CES61 = 14	CES86 = 0
CES12 = 76	CES37 = 6	CES62 = 53	CES87 = 2
CES13 = 47	CES38 = 42	CES63 = 68	CES88 = 2
CES14 = 77	CES39 = 75	CES64 = 0	CES89 = 0
CES15 = 74	CES40 = 49	CES65 = 0	CES90 = 2
CES16 = 49	CES41 = 75	CES66 = 0	CES91 = 57
CES17 = 56	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 60	CES43 = 0	CES68 = 0	CES93 = 3
CES19 = 80	CES44 = 95	CES69 = 28	CES94 = 0
CES20 = 71	CES45 = 1	CES70 = 0	CES95 = 0
CES21 = 94	CES46 = 6	CES71 = 0	CES96 = 2
CES22 = 87	CES47 = 70	CES72 = 42	CES97 = 1
CES23 = 94	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 95	CES49 = 6	CES74 = 62	CES99 = 0
CES25 = 79	CES50 = 10	CES75 = 0	





Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2511-597-9

TM-30-18

Measure Comparisons



(END OF REPORT)