

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356934

Luminaire Tested: 2ASL4-5-1-27-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-6)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 2ASL4-5-1-27-UNV
Description: 2FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS 1 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 932.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 1.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 8.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	118	118	118	118	114	114	114	114	108	108	108		102	102	102		96
1	106	100	95	91	102	97	93	89	92	88	85		87	84	81		82
2	95	86	79	73	92	84	77	71	79	74	69		75	70	66		71
3	87	76	67	60	84	73	65	59	69	63	57		66	60	55		62
4	79	67	57	50	76	65	56	50	62	54	48		58	52	47		56
5	73	59	50	43	70	58	49	43	55	47	42		52	46	41		50
6	67	53	44	38	65	52	43	37	50	42	36		47	41	35		45
7	62	48	39	33	60	47	39	33	45	37	32		43	36	31		41
8	58	44	35	29	56	43	35	29	41	34	29		39	33	28		38
9	54	40	32	26	52	39	32	26	38	31	26		36	30	25		35
10	51	37	29	24	49	36	29	24	35	28	23		34	27	23		32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4542	4542	4542
5°	4487	4443	4429
10°	4450	4347	4312
15°	4396	4243	4221
20°	4319	4128	4109
25°	4228	3993	3988
30°	4129	3868	3875
35°	4028	3740	3762
40°	3918	3612	3645
45°	3810	3472	3527
50°	3685	3325	3401
55°	3532	3161	3277
60°	3361	2990	3167
65°	3147	2810	3058
70°	2822	2618	2949
75°	2408	2446	2869
80°	1845	2292	2816
85°	994	2179	2838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3810 cd/sqm

TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.4	2.8
10°-20°	75.7	8.1
20°-30°	114.4	12.3
30°-40°	138.3	14.8
40°-50°	145.4	15.6
50°-60°	135.5	14.5
60°-70°	111.3	11.9
70°-80°	79.0	8.5
80°-90°	47.6	5.1
90°-100°	26.7	2.9
100°-110°	14.8	1.6
110°-120°	8.2	0.9
120°-130°	4.7	0.5
130°-140°	2.6	0.3
140°-150°	1.1	0.1
150°-160°	0.3	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.5	23.2
0°-40°	354.8	38.1
0°-60°	635.6	68.2
0°-90°	873.6	93.7
90°-120°	49.7	5.3
90°-150°	58.2	6.2
90°-180°	58.0	6.2
0°-180°	932.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	278	278	278	278	278	
5°	275	278	277	277	278	26
15°	264	267	269	270	271	74
25°	241	245	248	252	254	111
35°	210	215	222	227	230	131
45°	174	180	189	197	201	134
55°	134	141	152	162	167	119
65°	91	99	113	126	132	89
75°	46	57	76	92	99	49
85°	8	25	46	63	69	11
90°	0	14	34	50	56	0
95°	0	8	25	40	45	0
105°	0	3	13	24	28	0
115°	0	2	8	14	17	0
125°	0	1	5	9	11	0
135°	0	0	3	6	8	0
145°	0	0	1	4	4	0
155°	0	0	0	1	1	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	278.4	278.4	278.4	278.4	278.4
2.5°	276.5	279.0	278.4	277.1	277.1
5°	275.2	277.8	277.4	277.1	277.8
7.5°	273.7	276.2	276.2	276.5	277.1
10°	271.1	274.3	274.3	274.3	274.6
12.5°	268.0	271.1	271.8	272.1	272.7
15°	263.9	267.4	268.6	269.9	270.8
17.5°	259.2	262.6	264.8	266.4	268.0
20°	253.5	257.3	260.1	262.0	263.6
22.5°	247.5	251.3	254.1	257.0	258.9
25°	240.6	245.0	248.5	251.9	253.8
27.5°	233.7	238.1	242.5	246.6	248.8
30°	225.8	230.8	235.9	240.6	242.8
32.5°	217.6	223.0	228.9	234.0	236.5
35°	209.7	215.1	221.7	227.4	230.2
37.5°	201.2	206.6	214.1	220.4	223.3
40°	192.1	198.1	206.3	212.9	216.0
42.5°	183.3	189.3	198.1	205.3	208.5
45°	173.8	180.1	189.3	197.1	200.6
47.5°	164.1	170.7	180.4	188.6	192.4
50°	154.3	161.2	171.3	180.1	183.9
52.5°	143.9	151.2	161.9	171.3	175.4
55°	133.5	141.1	152.1	162.2	166.6
57.5°	123.1	130.7	142.7	153.4	158.1
60°	112.4	120.3	132.6	144.2	149.6
62.5°	101.4	109.6	122.5	135.1	140.8
65°	90.7	98.9	113.1	126.3	132.3
67.5°	79.4	88.2	103.3	117.1	123.4
70°	67.7	77.8	93.8	108.6	114.9
72.5°	57.3	67.7	85.0	100.1	106.8
75°	45.7	57.3	76.2	92.0	98.6
77.5°	35.6	48.2	68.0	84.1	90.7
80°	25.5	39.4	60.1	76.5	83.1
82.5°	16.4	31.5	52.9	69.6	75.9
85°	8.5	24.6	46.0	63.0	69.3
87.5°	2.5	18.9	39.7	56.4	62.7
90°	0.0	14.5	34.3	50.4	56.4
92.5°	0.0	11.0	29.6	45.0	51.0
95°	0.0	8.5	25.2	39.7	45.3
97.5°	0.0	6.6	21.7	35.0	40.6
100°	0.0	5.4	18.6	30.9	36.2
102.5°	0.0	4.4	16.1	27.4	32.1
105°	0.0	3.1	13.2	23.9	28.3
107.5°	0.0	2.2	11.7	21.1	24.9
110°	0.0	1.9	10.4	18.3	22.0



TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	1.6	9.1	16.4	19.5
115°	0.0	1.6	8.2	14.5	17.3
117.5°	0.0	1.3	6.9	12.9	15.4
120°	0.0	1.3	6.3	11.7	13.9
122.5°	0.0	0.9	5.7	10.4	12.6
125°	0.0	0.9	5.0	9.4	11.0
127.5°	0.0	0.6	4.4	8.5	10.1
130°	0.0	0.6	4.1	7.6	9.1
132.5°	0.0	0.3	3.8	6.9	8.2
135°	0.0	0.3	3.1	6.0	7.6
137.5°	0.0	0.0	2.8	5.4	6.6
140°	0.0	0.0	2.2	4.7	6.0
142.5°	0.3	0.0	1.9	4.1	5.0
145°	0.3	0.0	1.3	3.5	4.4
147.5°	0.3	0.3	0.9	2.8	3.5
150°	0.3	0.3	0.6	1.9	2.8
152.5°	0.3	0.3	0.3	1.3	1.9
155°	0.3	0.3	0.0	0.9	1.3
157.5°	0.3	0.3	0.0	0.3	0.6
160°	0.3	0.3	0.0	0.0	0.3
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356934

CATALOG NUMBER: 2ASL4-5-1-27-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.63	16.18	15.09	16.63	17.09	16.53	18.08	16.99	18.53	18.99
	3H	16.13	17.54	16.60	17.99	18.50	18.90	20.32	19.38	20.77	21.28
	4H	16.60	17.94	17.10	18.41	18.94	20.04	21.38	20.53	21.85	22.38
	6H	16.88	18.13	17.39	18.61	19.15	21.20	22.45	21.71	22.93	23.47
	8H	16.93	18.13	17.45	18.64	19.18	21.79	22.98	22.30	23.49	24.03
	12H	16.95	18.09	17.47	18.60	19.17	22.41	23.56	22.94	24.06	24.63
4H	2H	15.48	16.82	15.97	17.29	17.81	16.97	18.31	17.46	18.78	19.31
	3H	17.21	18.35	17.72	18.87	19.41	19.57	20.71	20.07	21.22	21.77
	4H	17.81	18.85	18.34	19.38	19.96	20.87	21.92	21.40	22.44	23.02
	6H	18.21	19.13	18.75	19.68	20.27	22.22	23.14	22.77	23.70	24.29
	8H	18.30	19.17	18.85	19.72	20.32	22.91	23.78	23.46	24.33	24.93
	12H	18.35	19.13	18.92	19.71	20.32	23.66	24.44	24.23	25.02	25.63
8H	4H	18.44	19.31	18.99	19.86	20.47	21.09	21.96	21.64	22.51	23.11
	6H	19.01	19.75	19.59	20.34	20.95	22.61	23.34	23.19	23.93	24.54
	8H	19.19	19.85	19.78	20.46	21.08	23.43	24.09	24.03	24.70	25.32
	12H	19.30	19.89	19.90	20.48	21.17	24.36	24.95	24.96	25.55	26.24
12H	4H	18.62	19.40	19.19	19.98	20.59	21.10	21.88	21.67	22.46	23.07
	6H	19.27	19.94	19.87	20.54	21.17	22.64	23.31	23.24	23.91	24.53
	8H	19.54	20.13	20.14	20.73	21.42	23.54	24.13	24.13	24.72	25.41

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-2

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-27-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-27-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 2696
 CIE u' : 0.2632
 CIE v' : 0.5245
 Duv: -0.0020
 CIE x: 0.4568
 CIE y: 0.4045
 CIE z: 0.1387
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 58.52757
 R_f: 90.1
 R_g: 103.5

CRI (Ra): 94.4
 R1: 97.5
 R2: 97.8
 R3: 96.9
 R4: 95.3
 R5: 97.2
 R6: 96.5
 R7: 91.2
 R8: 83.2
 R9: 61.8
 R10: 93.6
 R11: 93.7
 R12: 94.1
 R13: 97.6
 R14: 96.8
 R15: 91.9



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.45


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2





TM-30-18

Summary

$R_f = 90.1$
 $R_g = 103.5$
 $CIE R_a = 94.4$
 $R_9 = 61.8$







Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 89	CES51 = 92	CES76 = 90
CES02 = 64	CES27 = 97	CES52 = 92	CES77 = 84
CES03 = 32	CES28 = 96	CES53 = 88	CES78 = 87
CES04 = 71	CES29 = 83	CES54 = 97	CES79 = 88
CES05 = 51	CES30 = 85	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 69
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 95
CES08 = 43	CES33 = 84	CES58 = 88	CES83 = 91
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 96	CES60 = 99	CES85 = 81
CES11 = 59	CES36 = 98	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 45	CES38 = 89	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 92	CES90 = 93
CES16 = 48	CES41 = 89	CES66 = 92	CES91 = 91
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 97	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 72
CES20 = 68	CES45 = 90	CES70 = 93	CES95 = 88
CES21 = 87	CES46 = 89	CES71 = 95	CES96 = 92
CES22 = 79	CES47 = 79	CES72 = 98	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 89	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 88	CES99 = 92
CES25 = 72	CES50 = 92	CES75 = 94	





Color Rendition by Hue-Angle Bin


REPORT NUMBER: SP1-2511-597-2

TM-30-18

Measure Comparisons



(END OF REPORT)