

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356935

Luminaire Tested: 2ASL4-5-1-30-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-6)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 2ASL4-5-1-30-UNV
Description: 2FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3000K LEDS 1 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 1.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 8.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356935
CATALOG NUMBER: 2ASL4-5-1-30-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1356935
 CATALOG NUMBER: 2ASL4-5-1-30-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	96	94
1	106	100	95	91	102	97	93	89	92	88	85	87	84	81	82	80	78	82	80	78	75
2	95	86	79	73	92	84	77	71	79	74	69	75	70	66	71	67	64	71	67	64	61
3	87	76	67	60	84	73	65	59	69	63	57	66	60	55	62	58	54	62	58	54	51
4	79	67	57	50	76	65	56	50	62	54	48	58	52	47	56	50	46	56	50	46	43
5	73	59	50	43	70	58	49	43	55	47	42	52	46	41	50	44	40	50	44	40	37
6	67	53	44	38	65	52	43	37	50	42	36	47	41	35	45	39	35	45	39	35	32
7	62	48	39	33	60	47	39	33	45	37	32	43	36	31	41	35	31	41	35	31	29
8	58	44	35	29	56	43	35	29	41	34	29	39	33	28	38	32	27	38	32	27	25
9	54	40	32	26	52	39	32	26	38	31	26	36	30	25	35	29	25	35	29	25	23
10	51	37	29	24	49	36	29	24	35	28	23	34	27	23	32	27	22	32	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4737	4737	4737
5°	4679	4634	4619
10°	4642	4534	4497
15°	4584	4425	4402
20°	4505	4306	4286
25°	4409	4163	4159
30°	4306	4033	4041
35°	4201	3900	3924
40°	4086	3766	3802
45°	3974	3620	3678
50°	3843	3469	3547
55°	3686	3296	3416
60°	3505	3118	3303
65°	3282	2930	3188
70°	2942	2732	3077
75°	2508	2552	2992
80°	1925	2391	2938
85°	1040	2274	2960

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3974 cd/sqm



TEST NUMBER: P1356935
 CATALOG NUMBER: 2ASL4-5-1-30-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.5	2.8
10°-20°	78.9	8.1
20°-30°	119.3	12.3
30°-40°	144.2	14.8
40°-50°	151.7	15.6
50°-60°	141.3	14.5
60°-70°	116.1	11.9
70°-80°	82.4	8.5
80°-90°	49.7	5.1
90°-100°	27.8	2.9
100°-110°	15.4	1.6
110°-120°	8.6	0.9
120°-130°	5.0	0.5
130°-140°	2.7	0.3
140°-150°	1.2	0.1
150°-160°	0.3	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.7	23.2
0°-40°	370.0	38.1
0°-60°	662.9	68.2
0°-90°	911.0	93.7
90°-120°	51.8	5.3
90°-150°	60.7	6.2
90°-180°	61.0	6.3
0°-180°	972.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	290	290	290	290	290	
5°	287	290	289	289	290	27
15°	275	279	280	282	282	78
25°	251	256	259	263	265	116
35°	219	224	231	237	240	137
45°	181	188	197	206	209	140
55°	139	147	159	169	174	125
65°	95	103	118	132	138	93
75°	48	60	80	96	103	51
85°	9	26	48	66	72	11
90°	0	15	36	52	59	0
95°	0	9	26	41	47	0
105°	0	3	14	25	30	0
115°	0	2	8	15	18	0
125°	0	1	5	10	12	0
135°	0	0	3	6	8	0
145°	0	0	1	4	5	0
155°	0	0	0	1	1	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1356935

CATALOG NUMBER: 2ASL4-5-1-30-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	290.3	290.3	290.3	290.3	290.3
2.5°	288.4	291.0	290.3	289.0	289.0
5°	287.0	289.7	289.3	289.0	289.7
7.5°	285.4	288.0	288.0	288.4	289.0
10°	282.8	286.1	286.1	286.1	286.4
12.5°	279.5	282.8	283.4	283.8	284.4
15°	275.2	278.8	280.1	281.5	282.4
17.5°	270.3	273.9	276.2	277.8	279.5
20°	264.4	268.3	271.3	273.3	274.9
22.5°	258.1	262.1	265.0	268.0	270.0
25°	250.9	255.5	259.1	262.7	264.7
27.5°	243.7	248.3	252.9	257.2	259.5
30°	235.5	240.7	246.0	250.9	253.2
32.5°	226.9	232.5	238.8	244.0	246.6
35°	218.7	224.3	231.2	237.1	240.1
37.5°	209.9	215.4	223.3	229.9	232.9
40°	200.3	206.6	215.1	222.0	225.3
42.5°	191.1	197.4	206.6	214.1	217.4
45°	181.3	187.9	197.4	205.6	209.2
47.5°	171.1	178.0	188.2	196.7	200.7
50°	160.9	168.2	178.7	187.9	191.8
52.5°	150.1	157.6	168.8	178.7	182.9
55°	139.3	147.1	158.6	169.1	173.7
57.5°	128.4	136.3	148.8	159.9	164.9
60°	117.2	125.5	138.3	150.4	156.0
62.5°	105.8	114.3	127.8	140.9	146.8
65°	94.6	103.1	117.9	131.7	137.9
67.5°	82.8	92.0	107.7	122.2	128.7
70°	70.6	81.1	97.9	113.3	119.9
72.5°	59.8	70.6	88.7	104.4	111.3
75°	47.6	59.8	79.5	95.9	102.8
77.5°	37.1	50.2	70.9	87.7	94.6
80°	26.6	41.1	62.7	79.8	86.7
82.5°	17.1	32.8	55.2	72.6	79.2
85°	8.9	25.6	48.0	65.7	72.3
87.5°	2.6	19.7	41.4	58.8	65.4
90°	0.0	15.1	35.8	52.5	58.8
92.5°	0.0	11.5	30.9	47.0	53.2
95°	0.0	8.9	26.3	41.4	47.3
97.5°	0.0	6.9	22.7	36.5	42.4
100°	0.0	5.6	19.4	32.2	37.8
102.5°	0.0	4.6	16.7	28.6	33.5
105°	0.0	3.3	13.8	25.0	29.6
107.5°	0.0	2.3	12.2	22.0	25.9
110°	0.0	2.0	10.8	19.0	23.0



TEST NUMBER: P1356935
 CATALOG NUMBER: 2ASL4-5-1-30-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	1.6	9.5	17.1	20.4
115°	0.0	1.6	8.5	15.1	18.1
117.5°	0.0	1.3	7.2	13.5	16.1
120°	0.0	1.3	6.6	12.2	14.5
122.5°	0.0	1.0	5.9	10.8	13.1
125°	0.0	1.0	5.3	9.9	11.5
127.5°	0.0	0.7	4.6	8.9	10.5
130°	0.0	0.7	4.3	7.9	9.5
132.5°	0.0	0.3	3.9	7.2	8.5
135°	0.0	0.3	3.3	6.2	7.9
137.5°	0.0	0.0	3.0	5.6	6.9
140°	0.0	0.0	2.3	4.9	6.2
142.5°	0.3	0.0	2.0	4.3	5.3
145°	0.3	0.0	1.3	3.6	4.6
147.5°	0.3	0.3	1.0	3.0	3.6
150°	0.3	0.3	0.7	2.0	3.0
152.5°	0.3	0.3	0.3	1.3	2.0
155°	0.3	0.3	0.0	1.0	1.3
157.5°	0.3	0.3	0.0	0.3	0.7
160°	0.3	0.3	0.0	0.0	0.3
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1356935
 CATALOG NUMBER: 2ASL4-5-1-30-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.78	16.33	15.24	16.77	17.24	16.68	18.23	17.14	18.67	19.14
	3H	16.27	17.69	16.74	18.14	18.65	19.05	20.47	19.52	20.92	21.43
	4H	16.75	18.09	17.24	18.56	19.08	20.19	21.53	20.68	22.00	22.52
	6H	17.03	18.27	17.53	18.76	19.30	21.35	22.60	21.85	23.08	23.62
	8H	17.08	18.27	17.60	18.78	19.33	21.93	23.13	22.45	23.64	24.18
	12H	17.09	18.24	17.62	18.74	19.32	22.56	23.70	23.08	24.21	24.78
4H	2H	15.63	16.97	16.12	17.44	17.96	17.12	18.46	17.61	18.93	19.45
	3H	17.36	18.50	17.86	19.01	19.56	19.71	20.86	20.22	21.37	21.91
	4H	17.96	19.00	18.48	19.53	20.10	21.02	22.06	21.54	22.59	23.17
	6H	18.35	19.28	18.90	19.83	20.42	22.37	23.29	22.91	23.84	24.43
	8H	18.45	19.31	19.00	19.87	20.47	23.06	23.92	23.61	24.47	25.08
	12H	18.49	19.28	19.06	19.86	20.47	23.80	24.59	24.38	25.17	25.78
8H	4H	18.59	19.46	19.14	20.01	20.61	21.23	22.10	21.79	22.65	23.26
	6H	19.16	19.89	19.74	20.48	21.10	22.75	23.49	23.33	24.08	24.69
	8H	19.33	20.00	19.93	20.60	21.22	23.58	24.24	24.17	24.85	25.47
	12H	19.44	20.03	20.04	20.63	21.32	24.51	25.10	25.11	25.69	26.38
12H	4H	18.76	19.55	19.33	20.13	20.74	21.24	22.03	21.82	22.61	23.22
	6H	19.42	20.08	20.02	20.69	21.31	22.79	23.45	23.38	24.06	24.68
	8H	19.69	20.28	20.29	20.87	21.56	23.68	24.28	24.28	24.87	25.56

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-3

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-30-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-30-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3000K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 3005
 CIE u': 0.2513
 CIE v': 0.5178
 Duv: -0.0025
 CIE x: 0.4330
 CIE y: 0.3966
 CIE z: 0.1704
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 49.00645
 Rf: 90.1
 Rg: 103.3

CRI (Ra):	93.9		
R1:	96.5	R9:	62.0
R2:	96.6	R10:	90.8
R3:	95.5	R11:	94.1
R4:	94.4	R12:	88.9
R5:	96.0	R13:	96.4
R6:	96.4	R14:	96.3
R7:	91.7	R15:	91.9
R8:	84.0		



Test Conditions

Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.42

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.76


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	92	NR	620	304	NR	750	8	NR	880	0	NR
365	0	NR	495	114	NR	625	309	NR	755	7	NR	885	0	NR
370	0	NR	500	136	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	154	NR	635	582	NR	765	5	NR	895	0	NR
380	0	NR	510	169	NR	640	200	NR	770	4	NR	900	0	NR
385	0	NR	515	181	NR	645	207	NR	775	4	NR	905	0	NR
390	1	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	148	NR	785	3	NR	915	0	NR
400	2	NR	530	199	NR	660	127	NR	790	2	NR	920	0	NR
405	3	NR	535	203	NR	665	108	NR	795	2	NR	925	0	NR
410	5	NR	540	208	NR	670	100	NR	800	2	NR	930	0	NR
415	9	NR	545	214	NR	675	83	NR	805	2	NR	935	0	NR
420	16	NR	550	221	NR	680	71	NR	810	1	NR	940	0	NR
425	28	NR	555	228	NR	685	61	NR	815	1	NR	945	0	NR
430	48	NR	560	236	NR	690	53	NR	820	1	NR	950	0	NR
435	80	NR	565	244	NR	695	45	NR	825	1	NR	955	0	NR
440	135	NR	570	251	NR	700	38	NR	830	1	NR	960	0	NR
445	202	NR	575	259	NR	705	33	NR	835	1	NR	965	0	NR
450	195	NR	580	266	NR	710	28	NR	840	1	NR	970	0	NR
455	130	NR	585	274	NR	715	24	NR	845	1	NR	975	0	NR
460	101	NR	590	281	NR	720	20	NR	850	0	NR	980	0	NR
465	82	NR	595	286	NR	725	17	NR	855	0	NR	985	0	NR
470	62	NR	600	292	NR	730	15	NR	860	0	NR	990	0	NR
475	58	NR	605	298	NR	735	13	NR	865	0	NR	995	0	NR
480	62	NR	610	328	NR	740	11	NR	870	0	NR	1000	0	NR
485	74	NR	615	342	NR	745	9	NR	875	0	NR			

Summary

$R_f = 90.1$
 $R_g = 103.3$
 CIE $R_a = 93.9$
 $R_9 = 62.0$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 93	CES76 = 86
CES02 = 63	CES27 = 97	CES52 = 93	CES77 = 87
CES03 = 32	CES28 = 95	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 98	CES79 = 91
CES05 = 51	CES30 = 87	CES55 = 97	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 90	CES81 = 75
CES07 = 44	CES32 = 80	CES57 = 89	CES82 = 96
CES08 = 42	CES33 = 85	CES58 = 89	CES83 = 92
CES09 = 29	CES34 = 89	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 59	CES36 = 96	CES61 = 98	CES86 = 78
CES12 = 65	CES37 = 92	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 92	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 94	CES89 = 82
CES15 = 72	CES40 = 91	CES65 = 91	CES90 = 94
CES16 = 48	CES41 = 91	CES66 = 93	CES91 = 87
CES17 = 50	CES42 = 88	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 94	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 74
CES20 = 67	CES45 = 90	CES70 = 90	CES95 = 87
CES21 = 86	CES46 = 89	CES71 = 91	CES96 = 92
CES22 = 79	CES47 = 82	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 89	CES73 = 85	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 91	CES99 = 93
CES25 = 72	CES50 = 93	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)