

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356897

Luminaire Tested: 2ASL4-25VHE-3-35-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 2ASL4-25VHE-3-35-UNV
Description: 2FT 2500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS 3 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4964.0 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 1.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 42.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23821	23821	23821
5°	23555	23334	23276
10°	23369	22847	22687
15°	23054	22251	22189
20°	22650	21679	21625
25°	22187	20972	20985
30°	21700	20354	20444
35°	21108	19662	19841
40°	20555	19022	19206
45°	19961	18259	18570
50°	19285	17438	17909
55°	18552	16653	17312
60°	17608	15741	16709
65°	16426	14859	16209
70°	14929	13976	15816
75°	12793	13156	15546
80°	9667	12499	15431
85°	5318	12224	15658

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19961 cd/sqm

TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	2.8
10°-20°	397.5	8.0
20°-30°	601.0	12.1
30°-40°	727.7	14.7
40°-50°	764.3	15.4
50°-60°	713.1	14.4
60°-70°	589.3	11.9
70°-80°	424.3	8.5
80°-90°	263.7	5.3
90°-100°	154.5	3.1
100°-110°	88.4	1.8
110°-120°	49.9	1.0
120°-130°	28.7	0.6
130°-140°	15.5	0.3
140°-150°	6.5	0.1
150°-160°	1.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1136.9	22.9
0°-40°	1864.6	37.6
0°-60°	3342.0	67.3
0°-90°	4619.3	93.1
90°-120°	292.8	5.9
90°-150°	343.5	6.9
90°-180°	345.0	7.0
0°-180°	4964.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1460	1460	1460	1460	1460	
5°	1445	1457	1457	1457	1460	137
15°	1384	1402	1408	1418	1424	390
25°	1263	1284	1305	1323	1336	582
35°	1099	1129	1166	1199	1214	688
45°	911	944	996	1038	1056	703
55°	701	741	801	859	880	626
65°	474	519	598	674	701	469
75°	243	304	410	498	534	257
85°	46	137	258	349	382	56
90°	0	82	197	282	319	2
95°	0	52	149	228	261	0
105°	0	18	82	143	167	0
115°	0	9	49	88	103	0
125°	0	6	30	58	67	0
135°	0	0	18	36	46	0
145°	0	0	9	21	24	0
155°	0	0	0	6	9	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1460.0	1460.0	1460.0	1460.0	1460.0
2.5°	1453.9	1463.0	1463.0	1453.9	1453.9
5°	1444.8	1456.9	1456.9	1456.9	1460.0
7.5°	1435.7	1450.9	1450.9	1450.9	1456.9
10°	1423.6	1438.7	1441.8	1441.8	1444.8
12.5°	1405.3	1423.6	1426.6	1429.6	1432.7
15°	1384.1	1402.3	1408.4	1417.5	1423.6
17.5°	1359.8	1381.1	1393.2	1402.3	1408.4
20°	1329.5	1350.7	1365.9	1378.0	1387.1
22.5°	1299.1	1317.3	1335.5	1350.7	1359.8
25°	1262.7	1283.9	1305.2	1323.4	1335.5
27.5°	1223.2	1247.5	1274.8	1296.1	1308.2
30°	1186.8	1211.1	1241.4	1268.8	1280.9
32.5°	1144.3	1171.6	1205.0	1232.3	1247.5
35°	1098.8	1129.1	1165.6	1198.9	1214.1
37.5°	1053.2	1083.6	1129.1	1162.5	1177.7
40°	1007.7	1038.1	1086.6	1123.1	1138.2
42.5°	959.2	989.5	1041.1	1080.6	1098.8
45°	910.6	944.0	995.6	1038.1	1056.3
47.5°	862.0	895.4	950.0	995.6	1013.8
50°	807.4	843.8	898.4	950.0	968.3
52.5°	755.8	792.2	852.9	904.5	922.7
55°	701.2	740.6	801.3	859.0	880.2
57.5°	646.5	686.0	749.7	810.4	834.7
60°	588.8	631.3	698.1	761.9	789.2
62.5°	531.2	576.7	649.6	716.3	743.6
65°	473.5	519.0	598.0	673.8	701.2
67.5°	415.8	464.4	549.4	628.3	661.7
70°	358.2	409.8	500.8	582.8	616.2
72.5°	300.5	355.1	455.3	540.3	573.7
75°	242.8	303.5	409.8	497.8	534.2
77.5°	185.2	255.0	370.3	458.3	494.8
80°	133.6	212.5	327.8	418.9	455.3
82.5°	85.0	170.0	291.4	382.4	418.9
85°	45.5	136.6	258.0	349.1	382.4
87.5°	15.2	106.2	224.6	315.7	349.1
90°	0.0	82.0	197.3	282.3	318.7
92.5°	0.0	63.7	173.0	255.0	288.4
95°	0.0	51.6	148.7	227.6	261.0
97.5°	0.0	42.5	130.5	203.4	233.7
100°	0.0	33.4	112.3	182.1	209.4
102.5°	0.0	27.3	97.1	160.9	188.2
105°	0.0	18.2	82.0	142.7	166.9
107.5°	0.0	15.2	69.8	127.5	148.7
110°	0.0	12.1	63.7	109.3	130.5

TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	9.1	57.7	97.1	118.4
115°	0.0	9.1	48.6	88.0	103.2
117.5°	0.0	9.1	42.5	78.9	94.1
120°	0.0	6.1	39.5	69.8	85.0
122.5°	0.0	6.1	33.4	63.7	75.9
125°	0.0	6.1	30.4	57.7	66.8
127.5°	0.0	3.0	27.3	51.6	60.7
130°	0.0	3.0	24.3	45.5	54.6
132.5°	0.0	3.0	21.2	42.5	51.6
135°	0.0	0.0	18.2	36.4	45.5
137.5°	0.0	0.0	15.2	33.4	39.5
140°	0.0	0.0	12.1	27.3	36.4
142.5°	0.0	0.0	9.1	24.3	30.4
145°	0.0	0.0	9.1	21.2	24.3
147.5°	0.0	0.0	6.1	15.2	21.2
150°	0.0	0.0	3.0	12.1	15.2
152.5°	0.0	0.0	0.0	9.1	12.1
155°	0.0	0.0	0.0	6.1	9.1
157.5°	0.0	0.0	0.0	0.0	3.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356897

CATALOG NUMBER: 2ASL4-25VHE-3-35-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.32	21.86	20.79	22.31	22.80	22.26	23.80	22.73	24.26	24.74
	3H	21.82	23.22	22.30	23.69	24.21	24.69	26.09	25.17	26.56	27.08
	4H	22.30	23.63	22.80	24.11	24.65	25.86	27.19	26.36	27.67	28.21
	6H	22.57	23.81	23.09	24.31	24.86	27.06	28.30	27.57	28.79	29.35
	8H	22.63	23.82	23.15	24.34	24.89	27.67	28.86	28.20	29.38	29.94
	12H	22.64	23.78	23.17	24.29	24.88	28.32	29.46	28.85	29.97	30.56
4H	2H	21.18	22.51	21.68	22.99	23.53	22.70	24.03	23.20	24.51	25.05
	3H	22.91	24.05	23.43	24.57	25.14	25.35	26.49	25.87	27.01	27.57
	4H	23.52	24.56	24.05	25.09	25.69	26.69	27.73	27.23	28.27	28.86
	6H	23.92	24.84	24.47	25.40	26.00	28.09	29.01	28.64	29.57	30.17
	8H	24.01	24.88	24.57	25.44	26.06	28.80	29.67	29.36	30.23	30.85
	12H	24.06	24.84	24.64	25.43	26.06	29.58	30.36	30.16	30.95	31.58
8H	4H	24.18	25.05	24.74	25.61	26.23	26.91	27.77	27.47	28.34	28.96
	6H	24.76	25.49	25.35	26.10	26.72	28.48	29.21	29.07	29.81	30.44
	8H	24.94	25.60	25.55	26.22	26.86	29.33	30.00	29.94	30.61	31.25
	12H	25.06	25.65	25.67	26.25	26.96	30.30	30.88	30.90	31.49	32.19
12H	4H	24.37	25.15	24.95	25.74	26.36	26.92	27.70	27.50	28.29	28.92
	6H	25.04	25.70	25.65	26.32	26.96	28.52	29.18	29.12	29.79	30.43
	8H	25.32	25.91	25.93	26.51	27.22	29.44	30.03	30.05	30.64	31.34

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-1

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-35-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-35-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 3487
 CIE u' : 0.2366
 CIE v' : 0.5099
 Duv: -0.0012
 CIE x: 0.4047
 CIE y: 0.3876
 CIE z: 0.2077
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.79273
 R_f: 90
 R_g: 102.4

CRI (Ra): 92.5
 R1: 94.7
 R2: 94.3
 R3: 92.9
 R4: 93.3
 R5: 93.9
 R6: 93.4
 R7: 92.5
 R8: 85.2
 R9: 61.3
 R10: 85.5
 R11: 93.7
 R12: 80.8
 R13: 94.3
 R14: 95.1
 R15: 90.9



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.15


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1





TM-30-18

Summary

$R_f = 90$
 $R_g = 102.4$
 $CIE R_a = 92.5$
 $R_9 = 61.3$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 87	CES51 = 95	CES76 = 82
CES02 = 62	CES27 = 96	CES52 = 94	CES77 = 89
CES03 = 31	CES28 = 93	CES53 = 90	CES78 = 79
CES04 = 70	CES29 = 84	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 89	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 91	CES81 = 81
CES07 = 43	CES32 = 80	CES57 = 90	CES82 = 96
CES08 = 41	CES33 = 86	CES58 = 91	CES83 = 94
CES09 = 29	CES34 = 88	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 93	CES60 = 97	CES85 = 84
CES11 = 58	CES36 = 93	CES61 = 96	CES86 = 82
CES12 = 64	CES37 = 91	CES62 = 98	CES87 = 90
CES13 = 43	CES38 = 95	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 93	CES89 = 83
CES15 = 71	CES40 = 92	CES65 = 90	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 91	CES91 = 83
CES17 = 49	CES42 = 87	CES67 = 91	CES92 = 80
CES18 = 56	CES43 = 85	CES68 = 91	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 75
CES20 = 66	CES45 = 90	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 90	CES71 = 85	CES96 = 91
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 90
CES23 = 91	CES48 = 91	CES73 = 80	CES98 = 91
CES24 = 90	CES49 = 88	CES74 = 94	CES99 = 92
CES25 = 71	CES50 = 94	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)