

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1356914

Luminaire Tested: 2ASL4-30VHE-3-50-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1356914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-12)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 2ASL4-30VHE-3-50-UNV
Description: 2FT 3000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 5000K LEDS 3 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6126.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 1.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 52.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	93
1	105	100	95	91	102	97	92	88	91	88	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	75	70	66	71	67	63	63	63	61
3	86	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	50	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	35	29	41	34	28	39	32	28	37	32	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	30	25	35	29	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	29396	29396	29396
5°	29069	28798	28723
10°	28838	28195	27997
15°	28451	27459	27382
20°	27952	26753	26687
25°	27382	25881	25898
30°	26779	25119	25229
35°	26049	24264	24485
40°	25367	23476	23703
45°	24632	22532	22916
50°	23799	21522	22100
55°	22894	20552	21365
60°	21732	19425	20619
65°	20270	18336	20002
70°	18422	17250	19517
75°	15791	16235	19186
80°	11925	15423	19044
85°	6569	15086	19327

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24632 cd/sqm

TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.9	2.8
10°-20°	490.6	8.0
20°-30°	741.7	12.1
30°-40°	898.0	14.7
40°-50°	943.2	15.4
50°-60°	880.0	14.4
60°-70°	727.3	11.9
70°-80°	523.6	8.5
80°-90°	325.4	5.3
90°-100°	190.7	3.1
100°-110°	109.1	1.8
110°-120°	61.6	1.0
120°-130°	35.4	0.6
130°-140°	19.1	0.3
140°-150°	8.0	0.1
150°-160°	1.5	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1403.1	22.9
0°-40°	2301.1	37.6
0°-60°	4124.3	67.3
0°-90°	5700.6	93.1
90°-120°	361.3	5.9
90°-150°	423.9	6.9
90°-180°	425.0	6.9
0°-180°	6126.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1802	1802	1802	1802	1802	
5°	1783	1798	1798	1798	1802	169
15°	1708	1731	1738	1749	1757	482
25°	1558	1584	1611	1633	1648	718
35°	1356	1393	1438	1480	1498	849
45°	1124	1165	1229	1281	1304	867
55°	865	914	989	1060	1086	773
65°	584	640	738	832	865	578
75°	300	375	506	614	659	317
85°	56	169	318	431	472	69
90°	0	101	244	348	393	3
95°	0	64	184	281	322	0
105°	0	22	101	176	206	0
115°	0	11	60	109	127	0
125°	0	8	38	71	82	0
135°	0	0	22	45	56	0
145°	0	0	11	26	30	0
155°	0	0	0	8	11	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1801.7	1801.7	1801.7	1801.7	1801.7
2.5°	1794.2	1805.5	1805.5	1794.2	1794.2
5°	1783.0	1798.0	1798.0	1798.0	1801.7
7.5°	1771.8	1790.5	1790.5	1790.5	1798.0
10°	1756.8	1775.5	1779.3	1779.3	1783.0
12.5°	1734.3	1756.8	1760.5	1764.3	1768.0
15°	1708.1	1730.6	1738.1	1749.3	1756.8
17.5°	1678.1	1704.3	1719.3	1730.6	1738.1
20°	1640.7	1666.9	1685.6	1700.6	1711.8
22.5°	1603.2	1625.7	1648.2	1666.9	1678.1
25°	1558.3	1584.5	1610.7	1633.2	1648.2
27.5°	1509.6	1539.5	1573.2	1599.5	1614.4
30°	1464.6	1494.6	1532.0	1565.8	1580.7
32.5°	1412.2	1445.9	1487.1	1520.8	1539.5
35°	1356.0	1393.4	1438.4	1479.6	1498.3
37.5°	1299.8	1337.3	1393.4	1434.6	1453.4
40°	1243.6	1281.1	1341.0	1386.0	1404.7
42.5°	1183.7	1221.1	1284.8	1333.5	1356.0
45°	1123.7	1164.9	1228.6	1281.1	1303.5
47.5°	1063.8	1105.0	1172.4	1228.6	1251.1
50°	996.4	1041.3	1108.8	1172.4	1194.9
52.5°	932.7	977.7	1052.6	1116.3	1138.7
55°	865.3	914.0	988.9	1060.1	1086.3
57.5°	797.9	846.6	925.2	1000.1	1030.1
60°	726.7	779.1	861.5	940.2	973.9
62.5°	655.5	711.7	801.6	884.0	917.7
65°	584.3	640.5	737.9	831.6	865.3
67.5°	513.2	573.1	678.0	775.4	816.6
70°	442.0	505.7	618.1	719.2	760.4
72.5°	370.8	438.3	561.9	666.8	708.0
75°	299.7	374.6	505.7	614.3	659.3
77.5°	228.5	314.6	457.0	565.6	610.6
80°	164.8	262.2	404.5	516.9	561.9
82.5°	104.9	209.8	359.6	472.0	516.9
85°	56.2	168.6	318.4	430.8	472.0
87.5°	18.7	131.1	277.2	389.6	430.8
90°	0.0	101.1	243.5	348.4	393.3
92.5°	0.0	78.7	213.5	314.6	355.9
95°	0.0	63.7	183.5	280.9	322.1
97.5°	0.0	52.4	161.1	251.0	288.4
100°	0.0	41.2	138.6	224.7	258.5
102.5°	0.0	33.7	119.9	198.5	232.2
105°	0.0	22.5	101.1	176.1	206.0
107.5°	0.0	18.7	86.2	157.3	183.5
110°	0.0	15.0	78.7	134.8	161.1

TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	11.2	71.2	119.9	146.1
115°	0.0	11.2	59.9	108.6	127.4
117.5°	0.0	11.2	52.4	97.4	116.1
120°	0.0	7.5	48.7	86.2	104.9
122.5°	0.0	7.5	41.2	78.7	93.6
125°	0.0	7.5	37.5	71.2	82.4
127.5°	0.0	3.7	33.7	63.7	74.9
130°	0.0	3.7	30.0	56.2	67.4
132.5°	0.0	3.7	26.2	52.4	63.7
135°	0.0	0.0	22.5	44.9	56.2
137.5°	0.0	0.0	18.7	41.2	48.7
140°	0.0	0.0	15.0	33.7	44.9
142.5°	0.0	0.0	11.2	30.0	37.5
145°	0.0	0.0	11.2	26.2	30.0
147.5°	0.0	0.0	7.5	18.7	26.2
150°	0.0	0.0	3.7	15.0	18.7
152.5°	0.0	0.0	0.0	11.2	15.0
155°	0.0	0.0	0.0	7.5	11.2
157.5°	0.0	0.0	0.0	0.0	3.7
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1356914

CATALOG NUMBER: 2ASL4-30VHE-3-50-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.05	22.59	21.52	23.04	23.53	22.99	24.53	23.46	24.99	25.47
	3H	22.55	23.95	23.03	24.42	24.94	25.42	26.82	25.90	27.29	27.81
	4H	23.03	24.36	23.53	24.84	25.38	26.59	27.92	27.09	28.40	28.94
	6H	23.31	24.55	23.82	25.04	25.60	27.79	29.03	28.30	29.53	30.08
	8H	23.36	24.55	23.89	25.07	25.63	28.40	29.59	28.93	30.11	30.67
	12H	23.37	24.51	23.91	25.02	25.61	29.05	30.19	29.58	30.70	31.29
4H	2H	21.91	23.24	22.41	23.72	24.26	23.43	24.76	23.93	25.24	25.78
	3H	23.65	24.78	24.16	25.31	25.87	26.08	27.22	26.60	27.74	28.30
	4H	24.25	25.29	24.79	25.82	26.42	27.42	28.46	27.96	29.00	29.59
	6H	24.65	25.57	25.20	26.13	26.74	28.82	29.74	29.37	30.30	30.90
	8H	24.74	25.61	25.30	26.17	26.79	29.53	30.40	30.09	30.96	31.58
	12H	24.79	25.57	25.37	26.16	26.79	30.31	31.09	30.89	31.68	32.31
8H	4H	24.91	25.78	25.47	26.34	26.96	27.64	28.51	28.20	29.07	29.69
	6H	25.49	26.22	26.08	26.83	27.45	29.21	29.94	29.80	30.55	31.17
	8H	25.67	26.33	26.28	26.95	27.59	30.07	30.73	30.67	31.34	31.98
	12H	25.79	26.38	26.40	26.98	27.69	31.03	31.62	31.63	32.22	32.92
12H	4H	25.10	25.88	25.68	26.47	27.10	27.65	28.44	28.23	29.03	29.65
	6H	25.77	26.43	26.38	27.05	27.69	29.25	29.91	29.85	30.52	31.16
	8H	26.05	26.64	26.66	27.24	27.95	30.17	30.76	30.78	31.37	32.07

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-5

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-50-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-50-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 5000K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 5076
 CIE u' : 0.2110
 CIE v' : 0.4830
 Duv: -0.0005
 CIE x: 0.3429
 CIE y: 0.3489
 CIE z: 0.3082
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 572
 Purity: 7.553016
 R_f: 90.4
 R_g: 99

CRI (Ra): 94.9
 R1: 96.7
 R2: 98.2
 R3: 96.6
 R4: 95.6
 R5: 95.1
 R6: 93.6
 R7: 94.0
 R8: 89.6
 R9: 74.0
 R10: 93.9
 R11: 96.2
 R12: 72.4
 R13: 98.1
 R14: 97.8
 R15: 95.6



Test Conditions


Stabilization Time: 24M
 Operation Time: 1H 24M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-5

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.12

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-5

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 4.65


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	248	NR	620	337	NR	750	9	NR	880	0	NR
365	0	NR	495	269	NR	625	335	NR	755	8	NR	885	0	NR
370	0	NR	500	298	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	325	NR	635	580	NR	765	6	NR	895	0	NR
380	1	NR	510	346	NR	640	216	NR	770	5	NR	900	0	NR
385	1	NR	515	361	NR	645	221	NR	775	4	NR	905	0	NR
390	2	NR	520	369	NR	650	185	NR	780	4	NR	910	0	NR
395	3	NR	525	374	NR	655	158	NR	785	3	NR	915	0	NR
400	4	NR	530	376	NR	660	136	NR	790	3	NR	920	0	NR
405	6	NR	535	379	NR	665	116	NR	795	2	NR	925	0	NR
410	8	NR	540	381	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	381	NR	675	88	NR	805	2	NR	935	0	NR
420	22	NR	550	383	NR	680	76	NR	810	2	NR	940	0	NR
425	37	NR	555	386	NR	685	65	NR	815	1	NR	945	0	NR
430	66	NR	560	386	NR	690	56	NR	820	1	NR	950	0	NR
435	119	NR	565	385	NR	695	48	NR	825	1	NR	955	0	NR
440	203	NR	570	382	NR	700	41	NR	830	1	NR	960	0	NR
445	359	NR	575	379	NR	705	35	NR	835	1	NR	965	0	NR
450	620	NR	580	376	NR	710	30	NR	840	1	NR	970	0	NR
455	752	NR	585	372	NR	715	26	NR	845	1	NR	975	0	NR
460	576	NR	590	368	NR	720	22	NR	850	1	NR	980	0	NR
465	423	NR	595	363	NR	725	19	NR	855	0	NR	985	0	NR
470	354	NR	600	358	NR	730	16	NR	860	0	NR	990	0	NR
475	280	NR	605	355	NR	735	14	NR	865	0	NR	995	0	NR
480	232	NR	610	375	NR	740	12	NR	870	0	NR	1000	0	NR
485	232	NR	615	379	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-5





TM-30-18

Summary

$R_f = 90.4$
 $R_g = 99$
 $\text{CIE } R_a = 94.9$
 $R_9 = 74.0$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 95	CES51 = 95	CES76 = 87
CES02 = 61	CES27 = 89	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 84
CES04 = 69	CES29 = 95	CES54 = 90	CES79 = 94
CES05 = 48	CES30 = 84	CES55 = 88	CES80 = 93
CES06 = 50	CES31 = 96	CES56 = 91	CES81 = 81
CES07 = 41	CES32 = 92	CES57 = 89	CES82 = 97
CES08 = 40	CES33 = 94	CES58 = 89	CES83 = 95
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 93
CES10 = 73	CES35 = 96	CES60 = 90	CES85 = 82
CES11 = 56	CES36 = 76	CES61 = 90	CES86 = 85
CES12 = 62	CES37 = 95	CES62 = 80	CES87 = 93
CES13 = 42	CES38 = 79	CES63 = 90	CES88 = 97
CES14 = 74	CES39 = 98	CES64 = 86	CES89 = 87
CES15 = 71	CES40 = 99	CES65 = 87	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 83	CES91 = 70
CES17 = 48	CES42 = 94	CES67 = 82	CES92 = 78
CES18 = 56	CES43 = 95	CES68 = 85	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 86	CES94 = 79
CES20 = 65	CES45 = 99	CES70 = 84	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 76	CES96 = 93
CES22 = 77	CES47 = 93	CES72 = 92	CES97 = 96
CES23 = 91	CES48 = 86	CES73 = 80	CES98 = 95
CES24 = 90	CES49 = 98	CES74 = 89	CES99 = 93
CES25 = 70	CES50 = 96	CES75 = 79	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)