

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357071

Luminaire Tested: 3ASL4-5-1-35-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-6)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 3ASL4-5-1-35-UNV
Description: 3FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS 1 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1545.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 2.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 12.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357071
CATALOG NUMBER: 3ASL4-5-1-35-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357071
 CATALOG NUMBER: 3ASL4-5-1-35-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	96	94
1	106	100	95	91	102	97	93	89	92	88	85	87	84	81	82	80	78	82	80	78	75
2	95	86	79	73	92	84	77	71	79	74	69	75	70	66	71	67	64	71	67	64	61
3	87	76	67	60	84	73	65	59	69	63	57	66	60	55	62	58	54	62	58	54	51
4	79	67	57	50	76	65	56	50	62	54	48	58	52	47	56	50	46	56	50	46	43
5	73	59	50	43	70	58	49	43	55	47	42	52	46	41	50	44	40	50	44	40	37
6	67	53	44	38	65	52	43	37	50	42	36	47	41	35	45	39	35	45	39	35	32
7	62	48	39	33	60	47	39	33	45	37	32	43	36	31	41	35	31	41	35	31	29
8	58	44	35	29	56	43	35	29	41	34	29	39	33	28	38	32	27	38	32	27	25
9	54	40	32	26	52	39	32	26	38	31	26	36	30	25	35	29	25	35	29	25	23
10	51	37	29	24	49	36	29	24	35	28	23	34	27	23	32	27	22	32	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5002	5002	5002
5°	4950	4899	4876
10°	4917	4797	4749
15°	4864	4688	4648
20°	4786	4566	4525
25°	4693	4420	4393
30°	4592	4286	4268
35°	4491	4149	4143
40°	4377	4011	4014
45°	4269	3860	3883
50°	4141	3704	3746
55°	3983	3527	3609
60°	3810	3343	3488
65°	3586	3148	3368
70°	3244	2944	3248
75°	2804	2759	3159
80°	2203	2600	3103
85°	1253	2488	3123

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4269 cd/sqm



TEST NUMBER: P1357071
 CATALOG NUMBER: 3ASL4-5-1-35-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.7	2.8
10°-20°	125.4	8.1
20°-30°	189.7	12.3
30°-40°	229.3	14.8
40°-50°	241.0	15.6
50°-60°	224.6	14.5
60°-70°	184.5	11.9
70°-80°	131.0	8.5
80°-90°	78.9	5.1
90°-100°	44.2	2.9
100°-110°	24.5	1.6
110°-120°	13.7	0.9
120°-130°	7.9	0.5
130°-140°	4.3	0.3
140°-150°	1.9	0.1
150°-160°	0.4	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.8	23.2
0°-40°	588.1	38.1
0°-60°	1053.7	68.2
0°-90°	1448.1	93.7
90°-120°	82.4	5.3
90°-150°	96.5	6.2
90°-180°	97.0	6.3
0°-180°	1545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	456	460	460	459	460	43
15°	438	443	445	447	449	123
25°	399	406	412	418	421	184
35°	348	356	368	377	382	217
45°	288	299	314	327	332	222
55°	221	234	252	269	276	198
65°	150	164	187	209	219	148
75°	76	95	126	152	163	81
85°	14	41	76	104	115	18
90°	0	24	57	84	93	1
95°	0	14	42	66	75	0
105°	0	5	22	40	47	0
115°	0	3	14	24	29	0
125°	0	2	8	16	18	0
135°	0	0	5	10	12	0
145°	0	0	2	6	7	0
155°	0	0	0	2	2	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357071
 CATALOG NUMBER: 3ASL4-5-1-35-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.5	461.5	461.5	461.5	461.5
2.5°	458.3	462.5	461.5	459.4	459.4
5°	456.3	460.4	459.9	459.4	460.4
7.5°	453.6	457.8	457.8	458.3	459.4
10°	449.5	454.7	454.7	454.7	455.2
12.5°	444.3	449.5	450.5	451.0	452.1
15°	437.5	443.2	445.3	447.4	448.9
17.5°	429.6	435.4	439.0	441.6	444.3
20°	420.2	426.5	431.2	434.3	436.9
22.5°	410.3	416.6	421.3	426.0	429.1
25°	398.8	406.1	411.9	417.6	420.8
27.5°	387.3	394.7	402.0	408.8	412.4
30°	374.3	382.7	391.0	398.8	402.5
32.5°	360.7	369.6	379.5	387.9	392.0
35°	347.7	356.5	367.5	376.9	381.6
37.5°	333.6	342.5	355.0	365.4	370.1
40°	318.4	328.4	341.9	352.9	358.1
42.5°	303.8	313.7	328.4	340.4	345.6
45°	288.2	298.6	313.7	326.8	332.5
47.5°	272.0	282.9	299.1	312.7	319.0
50°	255.8	267.3	284.0	298.6	304.9
52.5°	238.6	250.6	268.3	284.0	290.8
55°	221.3	233.9	252.1	268.8	276.2
57.5°	204.1	216.6	236.5	254.2	262.1
60°	186.4	199.4	219.8	239.1	248.0
62.5°	168.1	181.7	203.1	224.0	233.3
65°	150.3	163.9	187.4	209.3	219.3
67.5°	131.6	146.2	171.2	194.2	204.6
70°	112.2	128.9	155.6	180.1	190.5
72.5°	95.0	112.2	140.9	166.0	177.0
75°	75.7	95.0	126.3	152.4	163.4
77.5°	59.0	79.9	112.8	139.4	150.3
80°	42.3	65.3	99.7	126.9	137.8
82.5°	27.1	52.2	87.7	115.4	125.8
85°	14.1	40.7	76.2	104.4	114.8
87.5°	4.2	31.3	65.8	93.4	103.9
90°	0.0	24.0	56.9	83.5	93.4
92.5°	0.0	18.3	49.1	74.7	84.6
95°	0.0	14.1	41.8	65.8	75.2
97.5°	0.0	11.0	36.0	57.9	67.3
100°	0.0	8.9	30.8	51.2	60.0
102.5°	0.0	7.3	26.6	45.4	53.2
105°	0.0	5.2	21.9	39.7	47.0
107.5°	0.0	3.7	19.3	35.0	41.2
110°	0.0	3.1	17.2	30.3	36.5



TEST NUMBER: P1357071
 CATALOG NUMBER: 3ASL4-5-1-35-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	2.6	15.1	27.1	32.4
115°	0.0	2.6	13.6	24.0	28.7
117.5°	0.0	2.1	11.5	21.4	25.6
120°	0.0	2.1	10.4	19.3	23.0
122.5°	0.0	1.6	9.4	17.2	20.9
125°	0.0	1.6	8.4	15.7	18.3
127.5°	0.0	1.0	7.3	14.1	16.7
130°	0.0	1.0	6.8	12.5	15.1
132.5°	0.0	0.5	6.3	11.5	13.6
135°	0.0	0.5	5.2	9.9	12.5
137.5°	0.0	0.0	4.7	8.9	11.0
140°	0.0	0.0	3.7	7.8	9.9
142.5°	0.5	0.0	3.1	6.8	8.4
145°	0.5	0.0	2.1	5.7	7.3
147.5°	0.5	0.5	1.6	4.7	5.7
150°	0.5	0.5	1.0	3.1	4.7
152.5°	0.5	0.5	0.5	2.1	3.1
155°	0.5	0.5	0.0	1.6	2.1
157.5°	0.5	0.5	0.0	0.5	1.0
160°	0.5	0.5	0.0	0.0	0.5
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357071
 CATALOG NUMBER: 3ASL4-5-1-35-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.99	16.54	15.45	16.98	17.45	16.94	18.49	17.40	18.94	19.40
	3H	16.48	17.89	16.95	18.35	18.86	19.34	20.75	19.81	21.21	21.72
	4H	16.96	18.30	17.45	18.77	19.29	20.50	21.84	20.99	22.31	22.83
	6H	17.23	18.48	17.74	18.97	19.50	21.69	22.93	22.19	23.42	23.96
	8H	17.29	18.48	17.80	18.99	19.53	22.29	23.49	22.81	24.00	24.54
	12H	17.30	18.45	17.82	18.95	19.52	22.95	24.10	23.48	24.60	25.18
4H	2H	15.85	17.19	16.34	17.66	18.18	17.38	18.72	17.87	19.19	19.71
	3H	17.58	18.72	18.08	19.23	19.78	20.00	21.14	20.50	21.65	22.20
	4H	18.17	19.22	18.70	19.74	20.32	21.32	22.37	21.85	22.89	23.47
	6H	18.57	19.49	19.12	20.04	20.64	22.70	23.62	23.25	24.18	24.77
	8H	18.66	19.53	19.22	20.08	20.69	23.41	24.28	23.97	24.83	25.44
	12H	18.71	19.49	19.28	20.07	20.68	24.20	24.99	24.77	25.57	26.18
8H	4H	18.82	19.69	19.37	20.24	20.84	21.54	22.40	22.09	22.95	23.56
	6H	19.39	20.12	19.97	20.72	21.33	23.08	23.82	23.67	24.41	25.02
	8H	19.56	20.23	20.16	20.83	21.46	23.93	24.60	24.53	25.20	25.82
	12H	19.67	20.27	20.27	20.86	21.55	24.90	25.49	25.50	26.09	26.78
12H	4H	19.00	19.78	19.57	20.36	20.97	21.54	22.33	22.12	22.91	23.52
	6H	19.66	20.32	20.25	20.93	21.55	23.12	23.78	23.71	24.39	25.01
	8H	19.93	20.52	20.52	21.11	21.80	24.04	24.63	24.64	25.22	25.91

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-1

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-35-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-35-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 3487
 CIE u': 0.2366
 CIE v': 0.5099
 Duv: -0.0012
 CIE x: 0.4047
 CIE y: 0.3876
 CIE z: 0.2077
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.79273
 R_f: 90
 R_g: 102.4

CRI (Ra):	92.5		
R1:	94.7	R9:	61.3
R2:	94.3	R10:	85.5
R3:	92.9	R11:	93.7
R4:	93.3	R12:	80.8
R5:	93.9	R13:	94.3
R6:	93.4	R14:	95.1
R7:	92.5	R15:	90.9
R8:	85.2		



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3487K
 CIE x = 0.4047
 CIE y = 0.3876
 Duv = -0.0012

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.15


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

Summary

$R_f = 90$
 $R_g = 102.4$
 CIE $R_a = 92.5$
 $R_9 = 61.3$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 87	CES51 = 95	CES76 = 82
CES02 = 62	CES27 = 96	CES52 = 94	CES77 = 89
CES03 = 31	CES28 = 93	CES53 = 90	CES78 = 79
CES04 = 70	CES29 = 84	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 89	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 91	CES81 = 81
CES07 = 43	CES32 = 80	CES57 = 90	CES82 = 96
CES08 = 41	CES33 = 86	CES58 = 91	CES83 = 94
CES09 = 29	CES34 = 88	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 93	CES60 = 97	CES85 = 84
CES11 = 58	CES36 = 93	CES61 = 96	CES86 = 82
CES12 = 64	CES37 = 91	CES62 = 98	CES87 = 90
CES13 = 43	CES38 = 95	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 93	CES89 = 83
CES15 = 71	CES40 = 92	CES65 = 90	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 91	CES91 = 83
CES17 = 49	CES42 = 87	CES67 = 91	CES92 = 80
CES18 = 56	CES43 = 85	CES68 = 91	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 75
CES20 = 66	CES45 = 90	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 90	CES71 = 85	CES96 = 91
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 90
CES23 = 91	CES48 = 91	CES73 = 80	CES98 = 91
CES24 = 90	CES49 = 88	CES74 = 94	CES99 = 92
CES25 = 71	CES50 = 94	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)