

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517207

Luminaire Tested: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517207
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-1-LD4-2HI-50-UNV-C-EDD-90
Description: 1 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2095.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 22.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517207

CATALOG NUMBER: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517207

CATALOG NUMBER: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	103	98	94	105	100	96	92	96	92	89		91	89	86		87
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	51		62	56	51		60
5	75	61	52	45	72	60	51	45	58	50	44		56	49	44		54
6	69	55	46	40	67	54	46	39	52	45	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7485	7485	7485
5°	7388	7355	7503
10°	7213	7436	7602
15°	7004	7217	7105
20°	6770	6743	6844
25°	6527	6435	6936
30°	6202	6183	7066
35°	5946	5945	6997
40°	5675	5761	7100
45°	5387	5530	7039
50°	5054	5287	7059
55°	4611	5028	7142
60°	4236	4679	6936
65°	3612	4268	6833
70°	2806	3742	6266
75°	1866	3113	5892
80°	934	2480	5516
85°	276	1832	5190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 55°

Luminance: 7142 cd/sqm

TEST NUMBER: P517207

CATALOG NUMBER: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	3.2
10°-20°	190.3	9.1
20°-30°	283.2	13.5
30°-40°	340.4	16.2
40°-50°	358.3	17.1
50°-60°	332.5	15.9
60°-70°	262.9	12.5
70°-80°	160.6	7.7
80°-90°	70.0	3.3
90°-100°	21.8	1.0
100°-110°	4.9	0.2
110°-120°	2.0	0.1
120°-130°	1.1	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.4	25.8
0°-40°	880.8	42.0
0°-60°	1571.5	75.0
0°-90°	2064.9	98.6
90°-120°	28.6	1.4
90°-150°	30.0	1.4
90°-180°	30.0	1.4
0°-180°	2095.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	694	692	695	702	704	66
15°	657	682	688	666	666	185
25°	592	630	601	619	629	272
35°	505	519	527	575	595	316
45°	413	415	449	520	540	318
55°	304	309	358	436	471	273
65°	192	199	252	334	364	191
75°	73	96	141	216	230	79
85°	6	23	55	106	122	10
90°	0	7	29	67	80	0
95°	0	2	13	37	45	0
105°	0	1	2	7	10	0
115°	0	1	2	3	3	0
125°	0	0	1	2	3	0
135°	0	0	0	1	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517207

CATALOG NUMBER: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.4	695.4	695.4	695.4	695.4
2.5°	696.3	694.4	690.6	694.3	695.3
5°	693.7	692.3	694.7	702.5	704.5
7.5°	687.9	693.3	699.7	713.8	718.4
10°	679.3	689.5	708.6	720.6	716.0
12.5°	668.8	686.1	711.7	688.2	677.3
15°	656.6	681.8	688.5	665.7	666.1
17.5°	642.3	678.3	657.7	657.2	653.1
20°	626.9	666.4	639.2	638.1	633.7
22.5°	610.3	650.7	622.8	620.5	632.4
25°	592.3	630.1	601.4	619.4	629.4
27.5°	569.8	603.2	583.5	609.0	621.6
30°	547.0	575.4	565.2	600.8	623.2
32.5°	525.6	546.4	550.2	597.7	601.4
35°	505.3	519.3	527.1	575.0	594.6
37.5°	483.1	486.9	507.6	565.5	584.4
40°	460.4	458.0	491.1	549.9	576.0
42.5°	436.0	435.2	473.7	542.1	555.2
45°	412.9	414.8	448.9	520.0	539.5
47.5°	389.3	391.7	425.4	495.8	519.9
50°	361.8	364.9	404.4	474.3	505.3
52.5°	332.1	338.0	384.0	453.9	485.2
55°	304.2	309.1	358.1	436.5	471.2
57.5°	278.7	281.6	331.4	414.5	440.7
60°	253.6	254.3	306.1	390.1	415.2
62.5°	224.8	226.1	280.2	361.4	395.0
65°	192.5	198.6	252.3	333.9	364.2
67.5°	162.3	173.0	223.8	308.7	324.6
70°	130.0	148.0	195.9	279.1	290.3
72.5°	100.4	121.5	167.3	245.9	261.7
75°	72.8	96.5	140.7	216.2	229.8
77.5°	49.0	73.1	115.7	183.3	201.3
80°	29.3	53.4	93.5	152.9	173.1
82.5°	15.0	35.8	72.5	128.2	146.3
85°	6.5	22.7	54.8	106.4	122.1
87.5°	1.8	12.9	40.4	86.0	99.3
90°	0.1	6.8	28.8	67.4	79.5
92.5°	0.1	3.3	20.3	51.0	60.2
95°	0.1	1.7	12.6	37.0	45.2
97.5°	0.1	1.0	7.6	26.2	33.1
100°	0.1	0.8	4.5	17.4	23.7
102.5°	0.1	1.0	3.1	11.0	15.4
105°	0.1	1.0	2.5	7.2	10.2
107.5°	0.3	1.0	2.3	5.4	7.1
110°	0.1	0.8	2.4	4.1	5.5

TEST NUMBER: P517207

CATALOG NUMBER: HVL12-1-LD4-2HI-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.7	2.3	3.4	4.1
115°	0.1	0.6	2.0	3.3	3.4
117.5°	0.3	0.4	1.6	3.3	3.4
120°	0.3	0.3	1.3	3.1	3.5
122.5°	0.3	0.3	1.0	2.8	3.4
125°	0.1	0.3	0.8	2.1	3.0
127.5°	0.3	0.3	0.7	1.7	2.3
130°	0.3	0.3	0.6	1.3	1.7
132.5°	0.3	0.3	0.4	1.0	1.3
135°	0.3	0.3	0.3	0.7	1.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)