

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357255

Luminaire Tested: 4ASL4-5HE-2-27-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 4ASL4-5HE-2-27-UNV
Description: 4FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1844.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 3.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4359	4359	4359
5°	4325	4272	4259
10°	4295	4194	4156
15°	4256	4107	4072
20°	4205	3999	3955
25°	4124	3891	3855
30°	4023	3768	3755
35°	3944	3654	3638
40°	3852	3531	3516
45°	3759	3425	3427
50°	3640	3284	3294
55°	3524	3134	3189
60°	3383	2964	3077
65°	3164	2808	2990
70°	2917	2659	2911
75°	2557	2545	2885
80°	1994	2444	2876
85°	1211	2442	2959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3759 cd/sqm

TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	2.8
10°-20°	146.4	7.9
20°-30°	221.9	12.0
30°-40°	268.3	14.6
40°-50°	282.9	15.3
50°-60°	264.0	14.3
60°-70°	218.0	11.8
70°-80°	158.1	8.6
80°-90°	99.9	5.4
90°-100°	59.6	3.2
100°-110°	34.2	1.9
110°-120°	19.4	1.1
120°-130°	11.1	0.6
130°-140°	6.0	0.3
140°-150°	2.6	0.1
150°-160°	0.5	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	419.2	22.7
0°-40°	687.6	37.3
0°-60°	1234.5	66.9
0°-90°	1710.6	92.8
90°-120°	113.3	6.1
90°-150°	132.9	7.2
90°-180°	133.0	7.2
0°-180°	1844.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	537	537	537	537	537	
5°	532	537	535	535	537	51
15°	510	517	520	522	525	144
25°	466	473	483	490	493	215
35°	405	416	431	442	448	253
45°	336	350	370	385	392	259
55°	258	274	297	318	326	231
65°	174	193	221	248	260	173
75°	90	113	154	186	199	94
85°	17	52	98	132	145	21
90°	0	32	76	108	122	1
95°	0	20	57	88	100	0
105°	0	7	32	56	64	0
115°	0	3	19	34	40	0
125°	0	2	12	22	25	0
135°	0	0	7	14	17	0
145°	0	0	3	8	10	0
155°	0	0	0	2	3	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.1	537.1	537.1	537.1	537.1
2.5°	533.8	538.8	537.1	535.4	535.4
5°	532.1	537.1	535.4	535.4	537.1
7.5°	528.7	533.8	533.8	533.8	535.4
10°	523.6	530.4	530.4	530.4	532.1
12.5°	518.6	523.6	525.3	527.0	528.7
15°	510.1	516.9	520.2	521.9	525.3
17.5°	501.7	506.7	511.8	516.9	518.6
20°	491.5	498.3	503.4	508.4	510.1
22.5°	479.7	486.5	493.2	498.3	501.7
25°	466.2	473.0	483.1	489.8	493.2
27.5°	452.7	459.4	471.3	479.7	483.1
30°	435.8	445.9	457.7	467.9	473.0
32.5°	420.6	430.7	444.2	456.1	459.4
35°	405.4	415.5	430.7	442.5	447.6
37.5°	388.5	400.3	415.5	429.0	434.1
40°	371.6	383.4	400.3	415.5	418.9
42.5°	354.7	366.5	386.8	400.3	405.4
45°	336.1	349.6	369.9	385.1	391.9
47.5°	317.6	331.1	351.3	368.2	375.0
50°	297.3	312.5	334.4	351.3	358.1
52.5°	278.7	293.9	315.9	334.4	342.9
55°	258.4	273.6	297.3	317.6	326.0
57.5°	238.2	253.4	278.7	300.7	309.1
60°	217.9	233.1	258.4	283.8	292.2
62.5°	195.9	212.8	239.9	265.2	275.3
65°	174.0	192.6	221.3	248.3	260.1
67.5°	153.7	172.3	202.7	233.1	243.2
70°	131.8	152.0	185.8	216.2	228.0
72.5°	109.8	131.8	168.9	201.0	212.8
75°	89.5	113.2	153.7	185.8	199.3
77.5°	67.6	96.3	138.5	172.3	184.1
80°	49.0	79.4	123.3	158.8	170.6
82.5°	32.1	64.2	109.8	145.3	157.1
85°	16.9	52.4	98.0	131.8	145.3
87.5°	5.1	40.5	86.1	119.9	131.8
90°	0.0	32.1	76.0	108.1	121.6
92.5°	0.0	25.3	65.9	98.0	109.8
95°	0.0	20.3	57.4	87.8	99.7
97.5°	0.0	16.9	50.7	79.4	89.5
100°	0.0	13.5	43.9	70.9	81.1
102.5°	0.0	10.1	37.2	62.5	72.6
105°	0.0	6.8	32.1	55.7	64.2
107.5°	0.0	5.1	27.0	49.0	57.4
110°	0.0	5.1	25.3	42.2	50.7



TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	3.4	22.0	38.8	45.6
115°	0.0	3.4	18.6	33.8	40.5
117.5°	0.0	3.4	16.9	30.4	37.2
120°	0.0	3.4	15.2	27.0	32.1
122.5°	0.0	1.7	13.5	23.6	28.7
125°	0.0	1.7	11.8	22.0	25.3
127.5°	0.0	1.7	10.1	20.3	23.6
130°	0.0	1.7	10.1	18.6	22.0
132.5°	0.0	0.0	8.4	16.9	20.3
135°	0.0	0.0	6.8	13.5	16.9
137.5°	0.0	0.0	6.8	11.8	15.2
140°	0.0	0.0	5.1	11.8	13.5
142.5°	0.0	0.0	3.4	10.1	11.8
145°	0.0	0.0	3.4	8.4	10.1
147.5°	0.0	0.0	1.7	6.8	8.4
150°	0.0	0.0	1.7	5.1	6.8
152.5°	0.0	0.0	0.0	3.4	5.1
155°	0.0	0.0	0.0	1.7	3.4
157.5°	0.0	0.0	0.0	0.0	1.7
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357255

CATALOG NUMBER: 4ASL4-5HE-2-27-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.43	15.96	14.90	16.42	16.91	16.49	18.02	16.96	18.48	18.97
	3H	15.93	17.33	16.42	17.80	18.33	18.94	20.34	19.42	20.81	21.34
	4H	16.41	17.74	16.92	18.23	18.77	20.15	21.48	20.65	21.96	22.51
	6H	16.69	17.92	17.20	18.42	18.98	21.42	22.65	21.94	23.16	23.72
	8H	16.74	17.92	17.27	18.45	19.02	22.08	23.26	22.61	23.79	24.35
	12H	16.75	17.89	17.29	18.41	19.01	22.81	23.94	23.34	24.46	25.06
4H	2H	15.31	16.64	15.81	17.12	17.67	16.92	18.25	17.42	18.73	19.28
	3H	17.05	18.18	17.57	18.71	19.28	19.60	20.73	20.12	21.26	21.83
	4H	17.66	18.70	18.20	19.24	19.83	20.98	22.02	21.52	22.56	23.16
	6H	18.06	18.98	18.62	19.54	20.16	22.45	23.37	23.01	23.93	24.55
	8H	18.16	19.02	18.72	19.59	20.21	23.22	24.08	23.78	24.65	25.27
	12H	18.21	18.99	18.79	19.58	20.21	24.07	24.86	24.66	25.45	26.08
8H	4H	18.35	19.22	18.92	19.78	20.41	21.20	22.06	21.77	22.63	23.26
	6H	18.94	19.67	19.54	20.28	20.91	22.85	23.58	23.44	24.19	24.82
	8H	19.13	19.79	19.74	20.41	21.05	23.76	24.42	24.37	25.04	25.68
	12H	19.25	19.84	19.86	20.45	21.16	24.80	25.39	25.41	26.00	26.71
12H	4H	18.55	19.34	19.14	19.93	20.56	21.21	21.99	21.80	22.59	23.22
	6H	19.24	19.91	19.85	20.52	21.17	22.89	23.55	23.49	24.17	24.81
	8H	19.53	20.12	20.14	20.73	21.44	23.87	24.46	24.48	25.06	25.77

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-2

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-27-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-27-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 2700K LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K): 2696
 CIE u' : 0.2632
 CIE v' : 0.5245
 Duv: -0.0020
 CIE x: 0.4568
 CIE y: 0.4045
 CIE z: 0.1387
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 58.52757
 R_f: 90.1
 R_g: 103.5

CRI (Ra): 94.4
 R1: 97.5
 R2: 97.8
 R3: 96.9
 R4: 95.3
 R5: 97.2
 R6: 96.5
 R7: 91.2
 R8: 83.2
 R9: 61.8
 R10: 93.6
 R11: 93.7
 R12: 94.1
 R13: 97.6
 R14: 96.8
 R15: 91.9



Test Conditions


Stabilization Time: 32M
 Operation Time: 1H 32M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.45


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	281	NR	750	7	NR	880	0	NR
365	0	NR	495	88	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	106	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	121	NR	635	581	NR	765	5	NR	895	0	NR
380	0	NR	510	133	NR	640	184	NR	770	4	NR	900	0	NR
385	0	NR	515	143	NR	645	191	NR	775	3	NR	905	0	NR
390	0	NR	520	149	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	155	NR	655	136	NR	785	2	NR	915	0	NR
400	1	NR	530	158	NR	660	116	NR	790	2	NR	920	0	NR
405	2	NR	535	163	NR	665	99	NR	795	2	NR	925	0	NR
410	3	NR	540	168	NR	670	92	NR	800	2	NR	930	0	NR
415	6	NR	545	173	NR	675	75	NR	805	1	NR	935	0	NR
420	11	NR	550	179	NR	680	65	NR	810	1	NR	940	0	NR
425	19	NR	555	187	NR	685	56	NR	815	1	NR	945	0	NR
430	32	NR	560	195	NR	690	48	NR	820	1	NR	950	0	NR
435	54	NR	565	203	NR	695	41	NR	825	1	NR	955	0	NR
440	90	NR	570	211	NR	700	35	NR	830	1	NR	960	0	NR
445	134	NR	575	219	NR	705	30	NR	835	1	NR	965	0	NR
450	128	NR	580	228	NR	710	26	NR	840	1	NR	970	0	NR
455	83	NR	585	237	NR	715	22	NR	845	0	NR	975	0	NR
460	67	NR	590	246	NR	720	19	NR	850	0	NR	980	0	NR
465	55	NR	595	251	NR	725	16	NR	855	0	NR	985	0	NR
470	42	NR	600	259	NR	730	13	NR	860	0	NR	990	0	NR
475	41	NR	605	266	NR	735	11	NR	865	0	NR	995	0	NR
480	46	NR	610	299	NR	740	10	NR	870	0	NR	1000	0	NR
485	55	NR	615	317	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-2





TM-30-18

Summary

$R_f = 90.1$
 $R_g = 103.5$
 $CIE R_a = 94.4$
 $R_9 = 61.8$




Color Vector Graphics







Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 89	CES51 = 92	CES76 = 90
CES02 = 64	CES27 = 97	CES52 = 92	CES77 = 84
CES03 = 32	CES28 = 96	CES53 = 88	CES78 = 87
CES04 = 71	CES29 = 83	CES54 = 97	CES79 = 88
CES05 = 51	CES30 = 85	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 69
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 95
CES08 = 43	CES33 = 84	CES58 = 88	CES83 = 91
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 96	CES60 = 99	CES85 = 81
CES11 = 59	CES36 = 98	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 45	CES38 = 89	CES63 = 90	CES88 = 94
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 92	CES90 = 93
CES16 = 48	CES41 = 89	CES66 = 92	CES91 = 91
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 85	CES68 = 97	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 72
CES20 = 68	CES45 = 90	CES70 = 93	CES95 = 88
CES21 = 87	CES46 = 89	CES71 = 95	CES96 = 92
CES22 = 79	CES47 = 79	CES72 = 98	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 89	CES98 = 91
CES24 = 91	CES49 = 87	CES74 = 88	CES99 = 92
CES25 = 72	CES50 = 92	CES75 = 94	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)