

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357479

Luminaire Tested: 8ASL4-20HE-2-35-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-20HE-2-35-UNV
Description: 8FT 2000 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDS 2 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16224.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 143.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357479
CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357479

CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19126	19126	19126
5°	18996	18761	18688
10°	18889	18428	18233
15°	18739	18064	17869
20°	18537	17599	17355
25°	18205	17140	16913
30°	17784	16613	16474
35°	17462	16124	15964
40°	17086	15595	15426
45°	16708	15142	15035
50°	16216	14538	14454
55°	15750	13889	13993
60°	15174	13158	13502
65°	14259	12481	13122
70°	13242	11849	12773
75°	11743	11375	12658
80°	9352	10967	12619
85°	6004	11023	12981

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16708 cd/sqm



TEST NUMBER: P1357479
 CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	448.2	2.8
10°-20°	1288.3	7.9
20°-30°	1952.1	12.0
30°-40°	2361.0	14.6
40°-50°	2489.1	15.3
50°-60°	2323.1	14.3
60°-70°	1918.0	11.8
70°-80°	1391.4	8.6
80°-90°	879.1	5.4
90°-100°	524.7	3.2
100°-110°	300.8	1.9
110°-120°	170.8	1.1
120°-130°	97.5	0.6
130°-140°	52.7	0.3
140°-150°	23.1	0.1
150°-160°	4.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3688.6	22.7
0°-40°	6049.6	37.3
0°-60°	10861.7	66.9
0°-90°	15050.1	92.8
90°-120°	996.4	6.1
90°-150°	1169.7	7.2
90°-180°	1174.0	7.2
0°-180°	16224.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4726	4726	4726	4726	4726	
5°	4681	4726	4711	4711	4726	445
15°	4488	4548	4577	4592	4622	1266
25°	4102	4161	4250	4310	4340	1889
35°	3567	3656	3790	3894	3938	2229
45°	2957	3076	3255	3388	3448	2281
55°	2274	2408	2616	2794	2868	2032
65°	1531	1694	1947	2185	2289	1520
75°	788	996	1352	1635	1754	828
85°	149	461	862	1159	1278	182
90°	0	282	669	951	1070	6
95°	0	178	505	773	877	0
105°	0	59	282	490	565	0
115°	0	30	164	297	357	0
125°	0	15	104	193	223	0
135°	0	0	59	119	149	0
145°	0	0	30	74	89	0
155°	0	0	0	15	30	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357479

CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4725.9	4725.9	4725.9	4725.9	4725.9
2.5°	4696.2	4740.7	4725.9	4711.0	4711.0
5°	4681.3	4725.9	4711.0	4711.0	4725.9
7.5°	4651.6	4696.2	4696.2	4696.2	4711.0
10°	4607.0	4666.4	4666.4	4666.4	4681.3
12.5°	4562.4	4607.0	4621.9	4636.7	4651.6
15°	4488.1	4547.5	4577.3	4592.1	4621.9
17.5°	4413.8	4458.4	4503.0	4547.5	4562.4
20°	4324.6	4384.1	4428.7	4473.2	4488.1
22.5°	4220.6	4280.0	4339.5	4384.1	4413.8
25°	4101.7	4161.2	4250.3	4309.8	4339.5
27.5°	3982.8	4042.3	4146.3	4220.6	4250.3
30°	3834.2	3923.4	4027.4	4116.6	4161.2
32.5°	3700.5	3789.6	3908.5	4012.5	4042.3
35°	3566.7	3655.9	3789.6	3893.7	3938.2
37.5°	3418.1	3522.1	3655.9	3774.8	3819.3
40°	3269.5	3373.5	3522.1	3655.9	3685.6
42.5°	3120.9	3224.9	3403.2	3522.1	3566.7
45°	2957.4	3076.3	3254.6	3388.4	3447.8
47.5°	2793.9	2912.8	3091.1	3239.8	3299.2
50°	2615.6	2749.3	2942.5	3091.1	3150.6
52.5°	2452.1	2585.9	2779.1	2942.5	3016.8
55°	2273.8	2407.5	2615.6	2793.9	2868.2
57.5°	2095.4	2229.2	2452.1	2645.3	2719.6
60°	1917.1	2050.9	2273.8	2496.7	2571.0
62.5°	1723.9	1872.5	2110.3	2333.2	2422.4
65°	1530.7	1694.2	1946.8	2184.6	2288.6
67.5°	1352.4	1515.8	1783.4	2050.9	2140.0
70°	1159.2	1337.5	1634.7	1902.2	2006.3
72.5°	966.0	1159.2	1486.1	1768.5	1872.5
75°	787.6	995.7	1352.4	1634.7	1753.6
77.5°	594.5	847.1	1218.6	1515.8	1619.9
80°	431.0	698.5	1084.9	1397.0	1501.0
82.5°	282.4	564.7	966.0	1278.1	1382.1
85°	148.6	460.7	862.0	1159.2	1278.1
87.5°	44.6	356.7	757.9	1055.1	1159.2
90°	0.0	282.4	668.8	951.1	1070.0
92.5°	0.0	222.9	579.6	862.0	966.0
95°	0.0	178.3	505.3	772.8	876.8
97.5°	0.0	148.6	445.8	698.5	787.6
100°	0.0	118.9	386.4	624.2	713.3
102.5°	0.0	89.2	326.9	549.9	639.0
105°	0.0	59.4	282.4	490.4	564.7
107.5°	0.0	44.6	237.8	431.0	505.3
110°	0.0	44.6	222.9	371.5	445.8



TEST NUMBER: P1357479

CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	29.7	193.2	341.8	401.3
115°	0.0	29.7	163.5	297.2	356.7
117.5°	0.0	29.7	148.6	267.5	326.9
120°	0.0	29.7	133.8	237.8	282.4
122.5°	0.0	14.9	118.9	208.1	252.6
125°	0.0	14.9	104.0	193.2	222.9
127.5°	0.0	14.9	89.2	178.3	208.1
130°	0.0	14.9	89.2	163.5	193.2
132.5°	0.0	0.0	74.3	148.6	178.3
135°	0.0	0.0	59.4	118.9	148.6
137.5°	0.0	0.0	59.4	104.0	133.8
140°	0.0	0.0	44.6	104.0	118.9
142.5°	0.0	0.0	29.7	89.2	104.0
145°	0.0	0.0	29.7	74.3	89.2
147.5°	0.0	0.0	14.9	59.4	74.3
150°	0.0	0.0	14.9	44.6	59.4
152.5°	0.0	0.0	0.0	29.7	44.6
155°	0.0	0.0	0.0	14.9	29.7
157.5°	0.0	0.0	0.0	0.0	14.9
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357479
 CATALOG NUMBER: 8ASL4-20HE-2-35-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.58	21.12	20.05	21.58	22.07	21.68	23.22	22.15	23.68	24.17
	3H	21.08	22.48	21.57	22.95	23.48	24.15	25.55	24.64	26.02	26.55
	4H	21.56	22.89	22.07	23.38	23.92	25.38	26.71	25.88	27.19	27.74
	6H	21.84	23.07	22.35	23.57	24.13	26.68	27.91	27.20	28.42	28.98
	8H	21.89	23.07	22.42	23.60	24.17	27.36	28.55	27.89	29.07	29.64
	12H	21.90	23.04	22.44	23.56	24.16	28.13	29.26	28.66	29.78	30.38
4H	2H	20.47	21.80	20.97	22.28	22.83	22.11	23.44	22.62	23.93	24.47
	3H	22.21	23.34	22.73	23.87	24.44	24.81	25.94	25.33	26.47	27.04
	4H	22.82	23.85	23.36	24.40	24.99	26.21	27.25	26.75	27.79	28.39
	6H	23.22	24.14	23.78	24.70	25.31	27.71	28.62	28.27	29.19	29.80
	8H	23.32	24.18	23.88	24.75	25.37	28.50	29.36	29.06	29.93	30.55
	12H	23.36	24.15	23.95	24.74	25.37	29.39	30.17	29.98	30.77	31.40
8H	4H	23.52	24.39	24.09	24.95	25.58	26.43	27.29	26.99	27.86	28.48
	6H	24.11	24.84	24.71	25.45	26.08	28.10	28.83	28.70	29.44	30.07
	8H	24.30	24.96	24.91	25.58	26.22	29.03	29.69	29.64	30.31	30.96
	12H	24.42	25.01	25.03	25.62	26.33	30.11	30.70	30.72	31.31	32.02
12H	4H	23.73	24.51	24.32	25.11	25.74	26.44	27.22	27.02	27.82	28.45
	6H	24.42	25.08	25.03	25.70	26.34	28.14	28.80	28.75	29.42	30.06
	8H	24.71	25.30	25.32	25.91	26.62	29.14	29.73	29.75	30.34	31.05

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-1

Test Date: 11/17/2025

Luminaire Tested: 4ASL-2-35-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-35-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 3500K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 3487
 CIE u': 0.2366
 CIE v': 0.5099
 Duv: -0.0012
 CIE x: 0.4047
 CIE y: 0.3876
 CIE z: 0.2077
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.79273
 R_f: 90
 R_g: 102.4

CRI (Ra):	92.5		
R1:	94.7	R9:	61.3
R2:	94.3	R10:	85.5
R3:	92.9	R11:	93.7
R4:	93.3	R12:	80.8
R5:	93.9	R13:	94.3
R6:	93.4	R14:	95.1
R7:	92.5	R15:	90.9
R8:	85.2		



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.15



λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	122	NR	620	322	NR	750	8	NR	880	0	NR
365	0	NR	495	152	NR	625	323	NR	755	7	NR	885	0	NR
370	0	NR	500	180	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	205	NR	635	589	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	210	NR	770	4	NR	900	0	NR
385	1	NR	515	238	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	247	NR	650	181	NR	780	3	NR	910	0	NR
395	2	NR	525	252	NR	655	155	NR	785	3	NR	915	0	NR
400	3	NR	530	258	NR	660	133	NR	790	2	NR	920	0	NR
405	5	NR	535	262	NR	665	113	NR	795	2	NR	925	0	NR
410	7	NR	540	267	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	271	NR	675	86	NR	805	2	NR	935	0	NR
420	24	NR	550	277	NR	680	74	NR	810	1	NR	940	0	NR
425	42	NR	555	284	NR	685	64	NR	815	1	NR	945	0	NR
430	72	NR	560	291	NR	690	55	NR	820	1	NR	950	0	NR
435	122	NR	565	296	NR	695	47	NR	825	1	NR	955	0	NR
440	207	NR	570	301	NR	700	40	NR	830	1	NR	960	0	NR
445	317	NR	575	306	NR	705	34	NR	835	1	NR	965	0	NR
450	304	NR	580	310	NR	710	29	NR	840	1	NR	970	0	NR
455	193	NR	585	315	NR	715	25	NR	845	1	NR	975	0	NR
460	149	NR	590	318	NR	720	21	NR	850	0	NR	980	0	NR
465	117	NR	595	320	NR	725	18	NR	855	0	NR	985	0	NR
470	85	NR	600	322	NR	730	15	NR	860	0	NR	990	0	NR
475	78	NR	605	325	NR	735	13	NR	865	0	NR	995	0	NR
480	84	NR	610	351	NR	740	11	NR	870	0	NR	1000	0	NR
485	98	NR	615	362	NR	745	10	NR	875	0	NR			

Summary

$R_f = 90$
 $R_g = 102.4$
 CIE $R_a = 92.5$
 $R_9 = 61.3$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 87	CES51 = 95	CES76 = 82
CES02 = 62	CES27 = 96	CES52 = 94	CES77 = 89
CES03 = 31	CES28 = 93	CES53 = 90	CES78 = 79
CES04 = 70	CES29 = 84	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 89	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 91	CES81 = 81
CES07 = 43	CES32 = 80	CES57 = 90	CES82 = 96
CES08 = 41	CES33 = 86	CES58 = 91	CES83 = 94
CES09 = 29	CES34 = 88	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 93	CES60 = 97	CES85 = 84
CES11 = 58	CES36 = 93	CES61 = 96	CES86 = 82
CES12 = 64	CES37 = 91	CES62 = 98	CES87 = 90
CES13 = 43	CES38 = 95	CES63 = 91	CES88 = 94
CES14 = 74	CES39 = 96	CES64 = 93	CES89 = 83
CES15 = 71	CES40 = 92	CES65 = 90	CES90 = 94
CES16 = 47	CES41 = 93	CES66 = 91	CES91 = 83
CES17 = 49	CES42 = 87	CES67 = 91	CES92 = 80
CES18 = 56	CES43 = 85	CES68 = 91	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 75
CES20 = 66	CES45 = 90	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 90	CES71 = 85	CES96 = 91
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 90
CES23 = 91	CES48 = 91	CES73 = 80	CES98 = 91
CES24 = 90	CES49 = 88	CES74 = 94	CES99 = 92
CES25 = 71	CES50 = 94	CES75 = 84	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)