

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357573

Luminaire Tested: 8ASL4-5HE-2-A59-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-7)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-5HE-2-A59-UNV
Description: 8FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND A59 LEDS 2 ROW
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 809.0 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 21.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

Luminous Intensity Polar Plot



TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	93
1	105	100	95	90	102	97	92	88	91	87	84	86	83	80	81	79	77	77	77	74
2	95	86	79	72	92	84	77	71	79	73	68	74	70	65	70	66	63	63	63	60
3	86	75	66	59	83	73	65	58	69	62	56	65	59	55	62	57	53	53	53	50
4	79	66	57	50	76	64	56	49	61	54	48	58	51	46	55	49	45	45	45	42
5	72	59	50	43	70	57	49	42	54	47	41	52	45	40	49	43	39	39	39	36
6	67	53	44	37	64	52	43	37	49	41	36	47	40	35	44	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	34	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	29	24	24	24	22
10	50	37	29	24	49	36	28	23	35	28	23	33	27	22	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	954	954	954
5°	947	935	932
10°	942	919	909
15°	934	901	891
20°	924	877	865
25°	908	854	843
30°	887	828	821
35°	871	804	796
40°	852	778	769
45°	833	755	750
50°	808	725	721
55°	785	692	698
60°	757	656	673
65°	711	623	654
70°	660	591	637
75°	586	567	631
80°	467	547	629
85°	299	550	647

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 833 cd/sqm

TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.3	2.8
10°-20°	64.2	7.9
20°-30°	97.3	12.0
30°-40°	117.7	14.6
40°-50°	124.1	15.3
50°-60°	115.8	14.3
60°-70°	95.6	11.8
70°-80°	69.4	8.6
80°-90°	43.8	5.4
90°-100°	26.2	3.2
100°-110°	15.0	1.9
110°-120°	8.5	1.1
120°-130°	4.9	0.6
130°-140°	2.6	0.3
140°-150°	1.1	0.1
150°-160°	0.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.9	22.7
0°-40°	301.7	37.3
0°-60°	541.6	66.9
0°-90°	750.5	92.8
90°-120°	49.7	6.1
90°-150°	58.3	7.2
90°-180°	59.0	7.3
0°-180°	809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	236	236	236	236	236	
5°	233	236	235	235	236	22
15°	224	227	228	229	230	63
25°	204	208	212	215	216	94
35°	178	182	189	194	196	111
45°	148	153	162	169	172	114
55°	113	120	130	139	143	101
65°	76	84	97	109	114	76
75°	39	50	67	82	87	41
85°	7	23	43	58	64	9
90°	0	14	33	47	53	0
95°	0	9	25	38	44	0
105°	0	3	14	24	28	0
115°	0	2	8	15	18	0
125°	0	1	5	10	11	0
135°	0	0	3	6	7	0
145°	0	0	2	4	4	0
155°	0	0	0	1	2	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	235.7	235.7	235.7	235.7	235.7
2.5°	234.2	236.4	235.7	234.9	234.9
5°	233.4	235.7	234.9	234.9	235.7
7.5°	231.9	234.2	234.2	234.2	234.9
10°	229.7	232.7	232.7	232.7	233.4
12.5°	227.5	229.7	230.5	231.2	231.9
15°	223.8	226.8	228.2	229.0	230.5
17.5°	220.1	222.3	224.5	226.8	227.5
20°	215.6	218.6	220.8	223.1	223.8
22.5°	210.5	213.4	216.4	218.6	220.1
25°	204.5	207.5	211.9	214.9	216.4
27.5°	198.6	201.6	206.8	210.5	211.9
30°	191.2	195.6	200.8	205.3	207.5
32.5°	184.5	189.0	194.9	200.1	201.6
35°	177.9	182.3	189.0	194.2	196.4
37.5°	170.4	175.6	182.3	188.2	190.4
40°	163.0	168.2	175.6	182.3	183.8
42.5°	155.6	160.8	169.7	175.6	177.9
45°	147.5	153.4	162.3	169.0	171.9
47.5°	139.3	145.2	154.1	161.5	164.5
50°	130.4	137.1	146.7	154.1	157.1
52.5°	122.3	128.9	138.6	146.7	150.4
55°	113.4	120.0	130.4	139.3	143.0
57.5°	104.5	111.2	122.3	131.9	135.6
60°	95.6	102.3	113.4	124.5	128.2
62.5°	86.0	93.4	105.2	116.3	120.8
65°	76.3	84.5	97.1	108.9	114.1
67.5°	67.4	75.6	88.9	102.3	106.7
70°	57.8	66.7	81.5	94.9	100.0
72.5°	48.2	57.8	74.1	88.2	93.4
75°	39.3	49.7	67.4	81.5	87.4
77.5°	29.6	42.2	60.8	75.6	80.8
80°	21.5	34.8	54.1	69.7	74.8
82.5°	14.1	28.2	48.2	63.7	68.9
85°	7.4	23.0	43.0	57.8	63.7
87.5°	2.2	17.8	37.8	52.6	57.8
90°	0.0	14.1	33.3	47.4	53.4
92.5°	0.0	11.1	28.9	43.0	48.2
95°	0.0	8.9	25.2	38.5	43.7
97.5°	0.0	7.4	22.2	34.8	39.3
100°	0.0	5.9	19.3	31.1	35.6
102.5°	0.0	4.4	16.3	27.4	31.9
105°	0.0	3.0	14.1	24.5	28.2
107.5°	0.0	2.2	11.9	21.5	25.2
110°	0.0	2.2	11.1	18.5	22.2



TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	1.5	9.6	17.0	20.0
115°	0.0	1.5	8.2	14.8	17.8
117.5°	0.0	1.5	7.4	13.3	16.3
120°	0.0	1.5	6.7	11.9	14.1
122.5°	0.0	0.7	5.9	10.4	12.6
125°	0.0	0.7	5.2	9.6	11.1
127.5°	0.0	0.7	4.4	8.9	10.4
130°	0.0	0.7	4.4	8.2	9.6
132.5°	0.0	0.0	3.7	7.4	8.9
135°	0.0	0.0	3.0	5.9	7.4
137.5°	0.0	0.0	3.0	5.2	6.7
140°	0.0	0.0	2.2	5.2	5.9
142.5°	0.0	0.0	1.5	4.4	5.2
145°	0.0	0.0	1.5	3.7	4.4
147.5°	0.0	0.0	0.7	3.0	3.7
150°	0.0	0.0	0.7	2.2	3.0
152.5°	0.0	0.0	0.0	1.5	2.2
155°	0.0	0.0	0.0	0.7	1.5
157.5°	0.0	0.0	0.0	0.0	0.7
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1357573

CATALOG NUMBER: 8ASL4-5HE-2-A59-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.16	10.70	9.64	11.16	11.65	11.26	12.80	11.74	13.26	13.75
	3H	10.67	12.07	11.15	12.54	13.07	13.74	15.14	14.22	15.61	16.14
	4H	11.15	12.47	11.65	12.96	13.51	14.96	16.29	15.47	16.78	17.32
	6H	11.42	12.66	11.94	13.16	13.72	16.26	17.50	16.78	18.00	18.56
	8H	11.47	12.66	12.00	13.18	13.75	16.94	18.13	17.47	18.65	19.22
	12H	11.49	12.63	12.03	13.14	13.74	17.71	18.85	18.25	19.36	19.96
4H	2H	10.05	11.38	10.56	11.87	12.41	11.69	13.02	12.20	13.51	14.05
	3H	11.79	12.93	12.31	13.46	14.02	14.39	15.53	14.91	16.06	16.62
	4H	12.40	13.44	12.94	13.98	14.58	15.79	16.83	16.33	17.37	17.97
	6H	12.80	13.72	13.36	14.29	14.90	17.29	18.21	17.85	18.77	19.39
	8H	12.90	13.76	13.46	14.33	14.95	18.08	18.94	18.64	19.51	20.13
	12H	12.95	13.73	13.53	14.33	14.96	18.97	19.75	19.56	20.35	20.98
8H	4H	13.11	13.97	13.67	14.54	15.16	16.01	16.87	16.58	17.44	18.07
	6H	13.69	14.42	14.29	15.03	15.66	17.68	18.41	18.28	19.02	19.65
	8H	13.88	14.54	14.49	15.16	15.80	18.62	19.28	19.22	19.89	20.54
	12H	14.00	14.59	14.61	15.20	15.91	19.69	20.28	20.30	20.89	21.60
12H	4H	13.31	14.10	13.90	14.69	15.32	16.02	16.80	16.61	17.40	18.03
	6H	14.00	14.67	14.61	15.28	15.93	17.72	18.38	18.33	19.00	19.64
	8H	14.29	14.88	14.90	15.49	16.20	18.72	19.31	19.33	19.92	20.63

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-9

Test Date: 01/22/2026

Luminaire Tested: 4ASL-2-A590-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/29/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-A590-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND AMBER 590 LEDS with 1 rows at 600mA

Spectral Parameters

CCT (K):	1535	CRI (Ra):	-20.0		
CIE u':	0.3534	R1:	-32.1	R9:	-380.5
CIE v':	0.5468	R2:	53.1	R10:	29.9
Duv:	0.0117	R3:	18.5	R11:	-92.0
CIE x:	0.5921	R4:	-65.7	R12:	-8.5
CIE y:	0.4072	R5:	-38.6	R13:	-13.5
CIE z:	0.0007	R6:	42.8	R14:	47.1
Peak Wavelength (nm):	598	R7:	-6.2	R15:	-65.4
Dominant Wavelength (nm):	592	R8:	-132.3		
Purity:	99.97894				
Rf:	1.3				
Rg:	0.1				



Test Conditions


Stabilization Time: 77M
 Operation Time: 2H 17M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2511-597-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-9

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.22

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9

Melanopic Flux vs. Wavelength

Melanopic Lumens: NR
M/P: 0.12

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	0	NR	620	35	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	17	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	9	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	5	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	3	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	2	NR	775	0	NR	905	0	NR
390	0	NR	520	0	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	1	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	1	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	2	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	4	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	7	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	12	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	22	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	38	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	66	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	115	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	203	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	354	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	596	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	923	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	909	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	447	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	183	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	75	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-9





TM-30-18

Summary

$R_f = 1.3$
 $R_g = 0.1$
 $CIE\ R_a = -20.0$
 $R_g = -380.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 90	CES26 = 0	CES51 = 19	CES76 = 0
CES02 = 70	CES27 = 32	CES52 = 2	CES77 = 0
CES03 = 31	CES28 = 25	CES53 = 0	CES78 = 0
CES04 = 77	CES29 = 1	CES54 = 13	CES79 = 2
CES05 = 52	CES30 = 31	CES55 = 7	CES80 = 1
CES06 = 56	CES31 = 1	CES56 = 0	CES81 = 0
CES07 = 41	CES32 = 0	CES57 = 0	CES82 = 51
CES08 = 39	CES33 = 21	CES58 = 0	CES83 = 21
CES09 = 29	CES34 = 0	CES59 = 10	CES84 = 55
CES10 = 87	CES35 = 24	CES60 = 60	CES85 = 10
CES11 = 70	CES36 = 77	CES61 = 14	CES86 = 0
CES12 = 76	CES37 = 6	CES62 = 53	CES87 = 2
CES13 = 47	CES38 = 42	CES63 = 68	CES88 = 2
CES14 = 77	CES39 = 75	CES64 = 0	CES89 = 0
CES15 = 74	CES40 = 49	CES65 = 0	CES90 = 2
CES16 = 49	CES41 = 75	CES66 = 0	CES91 = 57
CES17 = 56	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 60	CES43 = 0	CES68 = 0	CES93 = 3
CES19 = 80	CES44 = 95	CES69 = 28	CES94 = 0
CES20 = 71	CES45 = 1	CES70 = 0	CES95 = 0
CES21 = 94	CES46 = 6	CES71 = 0	CES96 = 2
CES22 = 87	CES47 = 70	CES72 = 42	CES97 = 1
CES23 = 94	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 95	CES49 = 6	CES74 = 62	CES99 = 0
CES25 = 79	CES50 = 10	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)