

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P1357549

Luminaire Tested: 8ASL4-5-1-40-UNV

Issue Date: 2/17/2026

Test Information

Test Method: LM-79-2019
Report Number: P1357549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2511-597-6)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: 8ASL4-5-1-40-UNV
Description: 8FT 500 LUMEN PER FOOT 4ASL LED LUMINAIRE WITH OPL LENS AND 4000K LEDS 1 ROW
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4128.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.3 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 7.98' x H: 0.1')
CIE Type: Direct

Input Watts (W): 33.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1357549
CATALOG NUMBER: 8ASL4-5-1-40-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P1357549
 CATALOG NUMBER: 8ASL4-5-1-40-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	96	94
1	106	100	95	91	102	97	93	89	92	88	85	87	84	81	82	80	78	82	80	78	75
2	95	86	79	73	92	84	77	71	79	74	69	75	70	66	71	67	64	71	67	64	61
3	87	76	67	60	84	73	65	59	69	63	57	66	60	55	62	58	54	62	58	54	51
4	79	67	57	50	76	65	56	50	62	54	48	58	52	47	56	50	46	56	50	46	43
5	73	59	50	43	70	58	49	43	55	47	42	52	46	41	50	44	40	50	44	40	37
6	67	53	44	38	65	52	43	37	50	42	36	47	41	35	45	39	35	45	39	35	32
7	62	48	39	33	60	47	39	33	45	37	32	43	36	31	41	35	31	41	35	31	29
8	58	44	35	29	56	43	35	29	41	34	29	39	33	28	38	32	27	38	32	27	25
9	54	40	32	26	52	39	32	26	38	31	26	36	30	25	35	29	25	35	29	25	23
10	51	37	29	24	49	36	29	24	35	28	23	34	27	23	32	27	22	32	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4990	4990	4990
5°	4947	4893	4865
10°	4924	4798	4737
15°	4880	4695	4637
20°	4813	4578	4514
25°	4730	4438	4382
30°	4639	4309	4257
35°	4548	4178	4133
40°	4446	4045	4005
45°	4350	3900	3874
50°	4237	3749	3737
55°	4096	3577	3599
60°	3941	3398	3479
65°	3742	3210	3359
70°	3426	3012	3241
75°	3015	2839	3151
80°	2452	2693	3095
85°	1523	2604	3117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4350 cd/sqm



TEST NUMBER: P1357549
 CATALOG NUMBER: 8ASL4-5-1-40-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	2.8
10°-20°	335.2	8.1
20°-30°	506.8	12.3
30°-40°	612.6	14.8
40°-50°	644.0	15.6
50°-60°	600.0	14.5
60°-70°	492.9	11.9
70°-80°	349.9	8.5
80°-90°	211.0	5.1
90°-100°	118.2	2.9
100°-110°	65.4	1.6
110°-120°	36.5	0.9
120°-130°	21.0	0.5
130°-140°	11.5	0.3
140°-150°	5.1	0.1
150°-160°	1.2	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	958.7	23.2
0°-40°	1571.3	38.1
0°-60°	2815.3	68.2
0°-90°	3869.1	93.7
90°-120°	220.1	5.3
90°-150°	257.7	6.2
90°-180°	259.0	6.3
0°-180°	4128.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1219	1230	1229	1227	1230	116
15°	1169	1184	1190	1195	1200	330
25°	1066	1085	1100	1116	1124	491
35°	929	953	982	1007	1020	581
45°	770	798	838	873	888	594
55°	591	625	674	718	738	529
65°	402	438	501	559	586	396
75°	202	254	338	407	437	216
85°	38	109	204	279	307	47
90°	0	64	152	223	250	2
95°	0	38	112	176	201	0
105°	0	14	59	106	126	0
115°	0	7	36	64	77	0
125°	0	4	22	42	49	0
135°	0	1	14	26	34	0
145°	1	0	6	15	20	1
155°	1	1	0	4	6	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P1357549

CATALOG NUMBER: 8ASL4-5-1-40-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1224.6	1235.8	1233.0	1227.4	1227.4
5°	1219.1	1230.2	1228.8	1227.4	1230.2
7.5°	1212.1	1223.2	1223.2	1224.6	1227.4
10°	1200.9	1214.9	1214.9	1214.9	1216.3
12.5°	1187.0	1200.9	1203.7	1205.1	1207.9
15°	1168.8	1184.2	1189.8	1195.3	1199.5
17.5°	1147.9	1163.3	1173.0	1180.0	1187.0
20°	1122.8	1139.5	1152.1	1160.5	1167.4
22.5°	1096.3	1113.0	1125.6	1138.2	1146.5
25°	1065.6	1085.2	1100.5	1115.8	1124.2
27.5°	1034.9	1054.5	1074.0	1092.1	1101.9
30°	1000.1	1022.4	1044.7	1065.6	1075.4
32.5°	963.8	987.5	1014.0	1036.3	1047.5
35°	928.9	952.6	981.9	1007.0	1019.6
37.5°	891.3	915.0	948.5	976.4	988.9
40°	850.8	877.3	913.6	942.9	956.8
42.5°	811.8	838.3	877.3	909.4	923.4
45°	769.9	797.8	838.3	873.1	888.5
47.5°	726.7	756.0	799.2	835.5	852.2
50°	683.4	714.1	758.8	797.8	814.6
52.5°	637.4	669.5	716.9	758.8	776.9
55°	591.4	624.9	673.7	718.3	737.8
57.5°	545.4	578.8	631.8	679.3	700.2
60°	497.9	532.8	587.2	638.8	662.5
62.5°	449.1	485.4	542.6	598.4	623.5
65°	401.7	438.0	500.7	559.3	585.8
67.5°	351.5	390.5	457.5	518.9	546.8
70°	299.9	344.5	415.6	481.2	509.1
72.5°	253.9	299.9	376.6	443.5	472.8
75°	202.2	253.9	337.5	407.3	436.6
77.5°	157.6	213.4	301.3	372.4	401.7
80°	113.0	174.3	266.4	338.9	368.2
82.5°	72.5	139.5	234.3	308.2	336.1
85°	37.7	108.8	203.6	279.0	306.9
87.5°	11.2	83.7	175.7	249.7	277.6
90°	0.0	64.2	152.0	223.2	249.7
92.5°	0.0	48.8	131.1	199.5	226.0
95°	0.0	37.7	111.6	175.7	200.9
97.5°	0.0	29.3	96.2	154.8	179.9
100°	0.0	23.7	82.3	136.7	160.4
102.5°	0.0	19.5	71.1	121.3	142.3
105°	0.0	13.9	58.6	106.0	125.5
107.5°	0.0	9.8	51.6	93.5	110.2
110°	0.0	8.4	46.0	80.9	97.6



TEST NUMBER: P1357549
 CATALOG NUMBER: 8ASL4-5-1-40-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	7.0	40.4	72.5	86.5
115°	0.0	7.0	36.3	64.2	76.7
117.5°	0.0	5.6	30.7	57.2	68.3
120°	0.0	5.6	27.9	51.6	61.4
122.5°	0.0	4.2	25.1	46.0	55.8
125°	0.0	4.2	22.3	41.8	48.8
127.5°	0.0	2.8	19.5	37.7	44.6
130°	0.0	2.8	18.1	33.5	40.4
132.5°	0.0	1.4	16.7	30.7	36.3
135°	0.0	1.4	13.9	26.5	33.5
137.5°	0.0	0.0	12.6	23.7	29.3
140°	0.0	0.0	9.8	20.9	26.5
142.5°	1.4	0.0	8.4	18.1	22.3
145°	1.4	0.0	5.6	15.3	19.5
147.5°	1.4	1.4	4.2	12.6	15.3
150°	1.4	1.4	2.8	8.4	12.6
152.5°	1.4	1.4	1.4	5.6	8.4
155°	1.4	1.4	0.0	4.2	5.6
157.5°	1.4	1.4	0.0	1.4	2.8
160°	1.4	1.4	0.0	0.0	1.4
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1357549
 CATALOG NUMBER: 8ASL4-5-1-40-UNV

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.01	16.56	15.46	17.00	17.47	17.03	18.58	17.49	19.02	19.49
	3H	16.50	17.91	16.97	18.36	18.87	19.46	20.87	19.93	21.33	21.84
	4H	16.97	18.31	17.46	18.78	19.30	20.64	21.98	21.13	22.45	22.97
	6H	17.25	18.50	17.75	18.98	19.52	21.88	23.12	22.38	23.61	24.15
	8H	17.30	18.50	17.82	19.00	19.55	22.52	23.71	23.04	24.22	24.77
	12H	17.31	18.46	17.84	18.96	19.54	23.24	24.38	23.76	24.89	25.46
4H	2H	15.88	17.22	16.37	17.69	18.21	17.46	18.80	17.96	19.27	19.80
	3H	17.61	18.75	18.11	19.26	19.81	20.11	21.26	20.62	21.77	22.32
	4H	18.20	19.25	18.73	19.77	20.35	21.46	22.51	21.99	23.03	23.61
	6H	18.60	19.52	19.15	20.07	20.66	22.89	23.81	23.43	24.36	24.95
	8H	18.69	19.56	19.24	20.11	20.72	23.63	24.50	24.18	25.05	25.66
	12H	18.74	19.52	19.31	20.10	20.71	24.48	25.26	25.05	25.84	26.45
8H	4H	18.86	19.73	19.42	20.28	20.89	21.67	22.54	22.23	23.09	23.70
	6H	19.43	20.17	20.02	20.76	21.37	23.26	24.00	23.85	24.59	25.20
	8H	19.61	20.27	20.21	20.88	21.50	24.15	24.81	24.74	25.42	26.04
	12H	19.72	20.31	20.32	20.90	21.59	25.17	25.76	25.77	26.36	27.05
12H	4H	19.05	19.84	19.62	20.42	21.03	21.68	22.47	22.26	23.05	23.66
	6H	19.71	20.38	20.31	20.98	21.60	23.30	23.96	23.89	24.57	25.19
	8H	19.98	20.57	20.58	21.17	21.86	24.25	24.84	24.85	25.43	26.12

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Fail-Safe

Report Number: SP1-2511-597-4

Test Date: 11/18/2025

Luminaire Tested: 4ASL-2-40-UNV-OPL-1_600mA

Data in this report applies to families of products including 4ASL


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2511-597-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/18/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Fail-Safe
 Catalog Number: **4ASL-2-40-UNV-OPL-1_600mA**
 Description: 2foot 4ASL LED LUMINAIRE WITH OPL LENS AND 4000K LEDs with 1 rows at 600mA

Spectral Parameters

CCT (K): 4015
 CIE u': 0.2259
 CIE v': 0.4990
 Duv: -0.0019
 CIE x: 0.3785
 CIE y: 0.3715
 CIE z: 0.2500
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 580
 Purity: 25.06827
 Rf: 90.7
 Rg: 100.2

CRI (Ra):	93.9		
R1:	95.7	R9:	66.3
R2:	96.3	R10:	89.1
R3:	94.8	R11:	95.0
R4:	95.2	R12:	73.8
R5:	94.6	R13:	96.0
R6:	93.5	R14:	96.4
R7:	94.0	R15:	93.2
R8:	87.2		



Test Conditions


Stabilization Time: 23M
 Operation Time: 1H 23M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2511-597-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2511-597-4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2511-597-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.79

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

REPORT NUMBER: SP1-2511-597-4

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.74




λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	343	NR	750	9	NR	880	0	NR
365	0	NR	495	197	NR	625	343	NR	755	8	NR	885	0	NR
370	0	NR	500	228	NR	630	1000	NR	760	7	NR	890	0	NR
375	0	NR	505	254	NR	635	591	NR	765	6	NR	895	0	NR
380	0	NR	510	274	NR	640	225	NR	770	5	NR	900	0	NR
385	1	NR	515	290	NR	645	229	NR	775	4	NR	905	0	NR
390	1	NR	520	300	NR	650	193	NR	780	4	NR	910	0	NR
395	2	NR	525	307	NR	655	165	NR	785	3	NR	915	0	NR
400	3	NR	530	311	NR	660	142	NR	790	3	NR	920	0	NR
405	5	NR	535	316	NR	665	122	NR	795	2	NR	925	0	NR
410	7	NR	540	320	NR	670	112	NR	800	2	NR	930	0	NR
415	11	NR	545	323	NR	675	93	NR	805	2	NR	935	0	NR
420	20	NR	550	329	NR	680	80	NR	810	2	NR	940	0	NR
425	35	NR	555	334	NR	685	69	NR	815	1	NR	945	0	NR
430	61	NR	560	340	NR	690	59	NR	820	1	NR	950	0	NR
435	108	NR	565	344	NR	695	51	NR	825	1	NR	955	0	NR
440	187	NR	570	346	NR	700	43	NR	830	1	NR	960	0	NR
445	329	NR	575	349	NR	705	37	NR	835	1	NR	965	0	NR
450	484	NR	580	351	NR	710	32	NR	840	1	NR	970	0	NR
455	433	NR	585	353	NR	715	27	NR	845	1	NR	975	0	NR
460	296	NR	590	354	NR	720	23	NR	850	1	NR	980	0	NR
465	237	NR	595	353	NR	725	20	NR	855	0	NR	985	0	NR
470	188	NR	600	354	NR	730	17	NR	860	0	NR	990	0	NR
475	146	NR	605	354	NR	735	15	NR	865	0	NR	995	0	NR
480	138	NR	610	378	NR	740	12	NR	870	0	NR	1000	0	NR
485	149	NR	615	385	NR	745	11	NR	875	0	NR			

Summary

$R_f = 90.7$
 $R_g = 100.2$
 CIE $R_a = 93.9$
 $R_9 = 66.3$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 92	CES51 = 98	CES76 = 84
CES02 = 62	CES27 = 91	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 95	CES53 = 97	CES78 = 81
CES04 = 69	CES29 = 95	CES54 = 93	CES79 = 94
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 92
CES06 = 50	CES31 = 95	CES56 = 95	CES81 = 81
CES07 = 42	CES32 = 87	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 97	CES84 = 93
CES10 = 74	CES35 = 95	CES60 = 92	CES85 = 81
CES11 = 57	CES36 = 80	CES61 = 92	CES86 = 84
CES12 = 63	CES37 = 93	CES62 = 85	CES87 = 91
CES13 = 43	CES38 = 87	CES63 = 92	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 90	CES89 = 85
CES15 = 71	CES40 = 97	CES65 = 88	CES90 = 98
CES16 = 47	CES41 = 97	CES66 = 86	CES91 = 71
CES17 = 49	CES42 = 91	CES67 = 85	CES92 = 77
CES18 = 56	CES43 = 91	CES68 = 87	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 76
CES20 = 66	CES45 = 95	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 96	CES71 = 78	CES96 = 92
CES22 = 78	CES47 = 94	CES72 = 93	CES97 = 95
CES23 = 91	CES48 = 92	CES73 = 78	CES98 = 95
CES24 = 90	CES49 = 95	CES74 = 91	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)