

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517519

Luminaire Tested: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517519
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-4-LD4-2STD-35-UNV-C-EDD-90
Description: 4 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7287.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 67.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517519

CATALOG NUMBER: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517519

CATALOG NUMBER: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6509	6509	6509
5°	6494	6444	6524
10°	6409	6564	6610
15°	6292	6418	6179
20°	6151	6043	5951
25°	6000	5811	6032
30°	5773	5630	6144
35°	5610	5460	6084
40°	5435	5341	6174
45°	5248	5179	6121
50°	5019	5010	6139
55°	4684	4828	6210
60°	4427	4566	6031
65°	3914	4246	5942
70°	3193	3817	5448
75°	2279	3282	5123
80°	1278	2745	4796
85°	475	2194	4513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 55°

Luminance: 6210 cd/sqm

TEST NUMBER: P517519

CATALOG NUMBER: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.5	3.2
10°-20°	662.1	9.1
20°-30°	985.1	13.5
30°-40°	1184.0	16.2
40°-50°	1246.3	17.1
50°-60°	1156.4	15.9
60°-70°	914.3	12.5
70°-80°	558.5	7.7
80°-90°	243.3	3.3
90°-100°	75.8	1.0
100°-110°	17.0	0.2
110°-120°	6.8	0.1
120°-130°	3.9	0.1
130°-140°	1.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.6	25.8
0°-40°	3063.6	42.0
0°-60°	5466.3	75.0
0°-90°	7182.5	98.6
90°-120°	99.6	1.4
90°-150°	104.5	1.4
90°-180°	104.0	1.4
0°-180°	7287.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2419	2419	2419	2419	2419	
5°	2413	2408	2416	2444	2450	229
15°	2284	2372	2395	2315	2317	643
25°	2060	2192	2092	2154	2189	946
35°	1758	1806	1834	2000	2068	1099
45°	1436	1443	1562	1809	1876	1107
55°	1058	1075	1246	1518	1639	951
65°	670	691	878	1161	1267	663
75°	253	336	489	752	799	276
85°	23	79	191	370	425	35
90°	0	24	100	234	276	1
95°	0	6	44	129	157	0
105°	0	3	9	25	36	1
115°	0	2	7	11	12	1
125°	0	1	3	7	10	1
135°	1	1	1	2	3	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517519

CATALOG NUMBER: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2418.9	2418.9	2418.9	2418.9	2418.9
2.5°	2421.8	2415.4	2402.1	2414.9	2418.4
5°	2413.0	2408.0	2416.4	2443.5	2450.4
7.5°	2392.8	2411.5	2433.7	2482.9	2498.7
10°	2362.7	2398.2	2464.7	2506.6	2490.3
12.5°	2326.3	2386.4	2475.6	2393.8	2355.8
15°	2283.9	2371.6	2394.7	2315.4	2316.9
17.5°	2234.1	2359.3	2287.8	2285.8	2271.6
20°	2180.4	2317.9	2223.3	2219.3	2204.1
22.5°	2122.7	2263.2	2166.1	2158.2	2199.6
25°	2060.2	2191.7	2091.7	2154.3	2189.3
27.5°	1981.8	2098.1	2029.6	2118.3	2162.2
30°	1902.5	2001.5	1966.1	2089.7	2167.6
32.5°	1828.1	1900.5	1913.8	2078.9	2091.7
35°	1757.6	1806.4	1833.5	2000.1	2068.1
37.5°	1680.3	1693.6	1765.5	1967.0	2032.6
40°	1601.4	1593.0	1708.3	1912.8	2003.5
42.5°	1516.7	1513.7	1647.7	1885.7	1931.1
45°	1436.4	1442.8	1561.5	1808.9	1876.4
47.5°	1354.1	1362.4	1479.7	1724.6	1808.4
50°	1258.5	1269.3	1406.8	1649.7	1757.6
52.5°	1155.0	1175.7	1335.8	1578.8	1687.7
55°	1057.9	1075.2	1245.7	1518.1	1638.9
57.5°	969.2	979.6	1152.5	1441.8	1532.9
60°	882.0	884.5	1064.8	1357.0	1444.2
62.5°	782.0	786.4	974.7	1257.0	1373.8
65°	669.6	690.8	877.6	1161.4	1266.8
67.5°	564.7	601.6	778.5	1073.7	1128.9
70°	452.3	514.9	681.5	970.7	1009.6
72.5°	349.4	422.8	581.9	855.4	910.1
75°	253.3	335.6	489.3	751.9	799.2
77.5°	170.5	254.3	402.6	637.6	700.2
80°	102.0	185.8	325.2	531.7	602.1
82.5°	52.2	124.7	252.3	445.9	509.0
85°	22.7	78.8	190.7	370.1	424.7
87.5°	6.4	44.8	140.4	299.1	345.4
90°	0.5	23.7	100.0	234.5	276.4
92.5°	0.5	11.3	70.5	177.4	209.4
95°	0.5	5.9	43.9	128.6	157.2
97.5°	0.5	3.4	26.6	91.2	115.3
100°	0.5	3.0	15.8	60.6	82.3
102.5°	0.5	3.4	10.8	38.4	53.7
105°	0.5	3.4	8.9	25.1	35.5
107.5°	1.0	3.4	7.9	18.7	24.6
110°	0.5	3.0	8.4	14.3	19.2

TEST NUMBER: P517519

CATALOG NUMBER: HVL12-4-LD4-2STD-35-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.0	2.5	7.9	11.8	14.3
115°	0.5	2.0	6.9	11.3	11.8
117.5°	1.0	1.5	5.4	11.3	11.8
120°	1.0	1.0	4.4	10.8	12.3
122.5°	1.0	1.0	3.4	9.9	11.8
125°	0.5	1.0	3.0	7.4	10.3
127.5°	1.0	1.0	2.5	5.9	7.9
130°	1.0	1.0	2.0	4.4	5.9
132.5°	1.0	1.0	1.5	3.4	4.4
135°	1.0	1.0	1.0	2.5	3.4
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)