

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517239

Luminaire Tested: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517239
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-1-LD4-2STD-50-UNV-C-EDD-90
Description: 1 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1628.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 16.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517239

CATALOG NUMBER: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517239

CATALOG NUMBER: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	103	98	94	105	100	96	92	96	92	89		91	89	86		87
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	51		62	56	51		60
5	75	61	52	45	72	60	51	45	58	50	44		56	49	44		54
6	69	55	46	39	67	54	46	39	52	45	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5817	5817	5817
5°	5741	5716	5831
10°	5605	5778	5908
15°	5442	5608	5521
20°	5260	5240	5318
25°	5073	5000	5390
30°	4819	4805	5491
35°	4621	4620	5436
40°	4411	4478	5518
45°	4187	4298	5469
50°	3928	4109	5486
55°	3583	3907	5549
60°	3292	3637	5391
65°	2807	3317	5310
70°	2182	2907	4870
75°	1451	2418	4579
80°	726	1928	4286
85°	217	1424	4034

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 55°

Luminance: 5549 cd/sqm

TEST NUMBER: P517239

CATALOG NUMBER: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	3.2
10°-20°	147.9	9.1
20°-30°	220.1	13.5
30°-40°	264.5	16.2
40°-50°	278.4	17.1
50°-60°	258.4	15.9
60°-70°	204.3	12.5
70°-80°	124.8	7.7
80°-90°	54.4	3.3
90°-100°	16.9	1.0
100°-110°	3.8	0.2
110°-120°	1.5	0.1
120°-130°	0.9	0.1
130°-140°	0.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	419.9	25.8
0°-40°	684.5	42.0
0°-60°	1221.2	75.0
0°-90°	1604.7	98.6
90°-120°	22.2	1.4
90°-150°	23.3	1.4
90°-180°	23.0	1.4
0°-180°	1628.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	540	540	540	540	540	
5°	539	538	540	546	548	51
15°	510	530	535	517	518	144
25°	460	490	467	481	489	211
35°	393	404	410	447	462	245
45°	321	322	349	404	419	247
55°	236	240	278	339	366	212
65°	150	154	196	260	283	148
75°	57	75	109	168	179	62
85°	5	18	43	83	95	8
90°	0	5	22	52	62	0
95°	0	1	10	29	35	0
105°	0	1	2	6	8	0
115°	0	0	2	2	3	0
125°	0	0	1	2	2	0
135°	0	0	0	1	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517239

CATALOG NUMBER: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	540.4	540.4	540.4	540.4	540.4
2.5°	541.1	539.6	536.7	539.5	540.3
5°	539.1	538.0	539.9	545.9	547.5
7.5°	534.6	538.8	543.7	554.7	558.2
10°	527.9	535.8	550.6	560.0	556.4
12.5°	519.7	533.1	553.1	534.8	526.3
15°	510.2	529.8	535.0	517.3	517.6
17.5°	499.1	527.1	511.1	510.7	507.5
20°	487.1	517.8	496.7	495.8	492.4
22.5°	474.2	505.6	483.9	482.2	491.4
25°	460.3	489.7	467.3	481.3	489.1
27.5°	442.8	468.7	453.4	473.3	483.1
30°	425.0	447.2	439.2	466.9	484.3
32.5°	408.4	424.6	427.6	464.4	467.3
35°	392.7	403.6	409.6	446.8	462.0
37.5°	375.4	378.4	394.4	439.5	454.1
40°	357.8	355.9	381.7	427.4	447.6
42.5°	338.8	338.2	368.1	421.3	431.4
45°	320.9	322.3	348.9	404.1	419.2
47.5°	302.5	304.4	330.6	385.3	404.0
50°	281.2	283.6	314.3	368.6	392.7
52.5°	258.0	262.7	298.4	352.7	377.0
55°	236.4	240.2	278.3	339.2	366.1
57.5°	216.5	218.8	257.5	322.1	342.5
60°	197.1	197.6	237.9	303.2	322.7
62.5°	174.7	175.7	217.7	280.8	306.9
65°	149.6	154.3	196.1	259.5	283.0
67.5°	126.2	134.4	173.9	239.9	252.2
70°	101.1	115.0	152.2	216.9	225.6
72.5°	78.1	94.5	130.0	191.1	203.3
75°	56.6	75.0	109.3	168.0	178.6
77.5°	38.1	56.8	89.9	142.5	156.4
80°	22.8	41.5	72.7	118.8	134.5
82.5°	11.7	27.9	56.4	99.6	113.7
85°	5.1	17.6	42.6	82.7	94.9
87.5°	1.4	10.0	31.4	66.8	77.2
90°	0.1	5.3	22.3	52.4	61.8
92.5°	0.1	2.5	15.7	39.6	46.8
95°	0.1	1.3	9.8	28.7	35.1
97.5°	0.1	0.8	5.9	20.4	25.8
100°	0.1	0.7	3.5	13.5	18.4
102.5°	0.1	0.8	2.4	8.6	12.0
105°	0.1	0.8	2.0	5.6	7.9
107.5°	0.2	0.8	1.8	4.2	5.5
110°	0.1	0.7	1.9	3.2	4.3

TEST NUMBER: P517239

CATALOG NUMBER: HVL12-1-LD4-2STD-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.2	0.6	1.8	2.6	3.2
115°	0.1	0.4	1.5	2.5	2.6
117.5°	0.2	0.3	1.2	2.5	2.6
120°	0.2	0.2	1.0	2.4	2.8
122.5°	0.2	0.2	0.8	2.2	2.6
125°	0.1	0.2	0.7	1.7	2.3
127.5°	0.2	0.2	0.6	1.3	1.8
130°	0.2	0.2	0.4	1.0	1.3
132.5°	0.2	0.2	0.3	0.8	1.0
135°	0.2	0.2	0.2	0.6	0.8
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)