

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517316

Luminaire Tested: HVL12-2-LD4-1LO-40-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517316
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-2-LD4-1LO-40-UNV-C-EDD
Description: 2 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1504.0 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 11.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517316

CATALOG NUMBER: HVL12-2-LD4-1LO-40-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517316

CATALOG NUMBER: HVL12-2-LD4-1LO-40-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2687	2687	2687
5°	2671	2653	2693
10°	2627	2696	2729
15°	2569	2630	2551
20°	2501	2469	2456
25°	2431	2368	2490
30°	2328	2288	2536
35°	2252	2212	2511
40°	2170	2157	2549
45°	2083	2085	2527
50°	1978	2008	2534
55°	1831	1926	2564
60°	1712	1811	2490
65°	1493	1672	2453
70°	1196	1490	2249
75°	830	1265	2115
80°	444	1038	1980
85°	149	805	1864

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 55°

Luminance: 2564 cd/sqm

TEST NUMBER: P517316

CATALOG NUMBER: HVL12-2-LD4-1LO-40-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	3.2
10°-20°	136.6	9.1
20°-30°	203.3	13.5
30°-40°	244.4	16.2
40°-50°	257.2	17.1
50°-60°	238.7	15.9
60°-70°	188.7	12.5
70°-80°	115.3	7.7
80°-90°	50.2	3.3
90°-100°	15.6	1.0
100°-110°	3.5	0.2
110°-120°	1.4	0.1
120°-130°	0.8	0.1
130°-140°	0.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.9	25.8
0°-40°	632.3	42.0
0°-60°	1128.2	75.0
0°-90°	1482.5	98.6
90°-120°	20.5	1.4
90°-150°	21.5	1.4
90°-180°	22.0	1.5
0°-180°	1504.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	499	499	499	499	499	
5°	498	497	499	504	506	47
15°	471	490	494	478	478	133
25°	425	452	432	445	452	195
35°	363	373	378	413	427	227
45°	296	298	322	373	387	229
55°	218	222	257	313	338	196
65°	138	143	181	240	262	137
75°	52	69	101	155	165	57
85°	5	16	39	76	88	7
90°	0	5	21	48	57	0
95°	0	1	9	26	32	0
105°	0	1	2	5	7	0
115°	0	0	1	2	2	0
125°	0	0	1	2	2	0
135°	0	0	0	0	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517316

CATALOG NUMBER: HVL12-2-LD4-1LO-40-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	499.2	499.2	499.2	499.2	499.2
2.5°	499.9	498.5	495.8	498.4	499.1
5°	498.0	497.0	498.7	504.3	505.8
7.5°	493.9	497.7	502.3	512.5	515.7
10°	487.7	495.0	508.7	517.3	514.0
12.5°	480.1	492.5	510.9	494.1	486.2
15°	471.4	489.5	494.3	477.9	478.2
17.5°	461.1	486.9	472.2	471.8	468.8
20°	450.0	478.4	458.9	458.1	454.9
22.5°	438.1	467.1	447.1	445.4	454.0
25°	425.2	452.4	431.7	444.6	451.9
27.5°	409.0	433.0	418.9	437.2	446.3
30°	392.7	413.1	405.8	431.3	447.4
32.5°	377.3	392.3	395.0	429.1	431.7
35°	362.8	372.8	378.4	412.8	426.8
37.5°	346.8	349.5	364.4	406.0	419.5
40°	330.5	328.8	352.6	394.8	413.5
42.5°	313.0	312.4	340.1	389.2	398.6
45°	296.5	297.8	322.3	373.3	387.3
47.5°	279.5	281.2	305.4	356.0	373.2
50°	259.7	262.0	290.4	340.5	362.8
52.5°	238.4	242.7	275.7	325.8	348.3
55°	218.4	221.9	257.1	313.3	338.3
57.5°	200.0	202.2	237.9	297.6	316.4
60°	182.0	182.6	219.8	280.1	298.1
62.5°	161.4	162.3	201.2	259.4	283.5
65°	138.2	142.6	181.1	239.7	261.5
67.5°	116.5	124.2	160.7	221.6	233.0
70°	93.4	106.3	140.7	200.3	208.4
72.5°	72.1	87.3	120.1	176.6	187.8
75°	52.3	69.3	101.0	155.2	165.0
77.5°	35.2	52.5	83.1	131.6	144.5
80°	21.1	38.3	67.1	109.7	124.3
82.5°	10.8	25.7	52.1	92.0	105.1
85°	4.7	16.3	39.4	76.4	87.7
87.5°	1.3	9.3	29.0	61.7	71.3
90°	0.1	4.9	20.6	48.4	57.1
92.5°	0.1	2.3	14.5	36.6	43.2
95°	0.1	1.2	9.1	26.5	32.4
97.5°	0.1	0.7	5.5	18.8	23.8
100°	0.1	0.6	3.3	12.5	17.0
102.5°	0.1	0.7	2.2	7.9	11.1
105°	0.1	0.7	1.8	5.2	7.3
107.5°	0.2	0.7	1.6	3.9	5.1
110°	0.1	0.6	1.7	2.9	4.0

TEST NUMBER: P517316

CATALOG NUMBER: HVL12-2-LD4-1LO-40-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.2	0.5	1.6	2.4	2.9
115°	0.1	0.4	1.4	2.3	2.4
117.5°	0.2	0.3	1.1	2.3	2.4
120°	0.2	0.2	0.9	2.2	2.5
122.5°	0.2	0.2	0.7	2.0	2.4
125°	0.1	0.2	0.6	1.5	2.1
127.5°	0.2	0.2	0.5	1.2	1.6
130°	0.2	0.2	0.4	0.9	1.2
132.5°	0.2	0.2	0.3	0.7	0.9
135°	0.2	0.2	0.2	0.5	0.7
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)