

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517435

Luminaire Tested: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517435
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-4-LD4-1HI-30-UNV-C-EDD-90
Description: 4 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4705.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 44.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517435

CATALOG NUMBER: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517435

CATALOG NUMBER: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	103	98	94	105	100	96	92	96	92	89		91	89	86		87
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	51		62	56	51		60
5	75	61	52	45	72	60	51	45	58	50	44		56	49	44		54
6	69	55	46	39	67	54	46	39	52	45	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4203	4203	4203
5°	4193	4161	4212
10°	4138	4238	4268
15°	4063	4144	3989
20°	3971	3902	3842
25°	3874	3752	3894
30°	3727	3635	3967
35°	3622	3525	3928
40°	3510	3448	3987
45°	3388	3344	3952
50°	3241	3235	3963
55°	3025	3117	4010
60°	2859	2948	3894
65°	2527	2742	3837
70°	2062	2464	3518
75°	1471	2119	3307
80°	826	1773	3097
85°	305	1416	2914

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 55°

Luminance: 4010 cd/sqm

TEST NUMBER: P517435

CATALOG NUMBER: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.1	3.2
10°-20°	427.5	9.1
20°-30°	636.0	13.5
30°-40°	764.5	16.2
40°-50°	804.7	17.1
50°-60°	746.7	15.9
60°-70°	590.4	12.5
70°-80°	360.6	7.7
80°-90°	157.1	3.3
90°-100°	48.9	1.0
100°-110°	11.0	0.2
110°-120°	4.4	0.1
120°-130°	2.5	0.1
130°-140°	0.7	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1213.6	25.8
0°-40°	1978.1	42.0
0°-60°	3529.4	75.0
0°-90°	4637.5	98.6
90°-120°	64.3	1.4
90°-150°	67.4	1.4
90°-180°	67.0	1.4
0°-180°	4705.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1562	1562	1562	1562	1562	
5°	1558	1555	1560	1578	1582	148
15°	1475	1531	1546	1495	1496	415
25°	1330	1415	1351	1391	1414	611
35°	1135	1166	1184	1291	1335	709
45°	927	932	1008	1168	1212	715
55°	683	694	804	980	1058	614
65°	432	446	567	750	818	428
75°	164	217	316	486	516	178
85°	15	51	123	239	274	23
90°	0	15	65	151	178	1
95°	0	4	28	83	102	0
105°	0	2	6	16	23	0
115°	0	1	4	7	8	0
125°	0	1	2	5	7	0
135°	1	1	1	2	2	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517435

CATALOG NUMBER: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1561.8	1561.8	1561.8	1561.8	1561.8
2.5°	1563.7	1559.6	1551.0	1559.3	1561.5
5°	1558.0	1554.8	1560.2	1577.7	1582.2
7.5°	1544.9	1557.0	1571.3	1603.2	1613.3
10°	1525.5	1548.4	1591.4	1618.4	1607.9
12.5°	1502.0	1540.8	1598.4	1545.6	1521.1
15°	1474.6	1531.3	1546.2	1495.0	1495.9
17.5°	1442.5	1523.3	1477.2	1475.9	1466.7
20°	1407.8	1496.6	1435.5	1433.0	1423.1
22.5°	1370.6	1461.3	1398.6	1393.5	1420.2
25°	1330.2	1415.1	1350.6	1391.0	1413.5
27.5°	1279.6	1354.7	1310.5	1367.7	1396.0
30°	1228.4	1292.3	1269.4	1349.3	1399.5
32.5°	1180.3	1227.1	1235.7	1342.3	1350.6
35°	1134.8	1166.3	1183.8	1291.4	1335.3
37.5°	1084.9	1093.5	1139.9	1270.1	1312.4
40°	1034.0	1028.6	1103.0	1235.1	1293.6
42.5°	979.3	977.4	1063.9	1217.6	1246.8
45°	927.4	931.5	1008.2	1167.9	1211.5
47.5°	874.3	879.7	955.4	1113.5	1167.6
50°	812.6	819.6	908.3	1065.2	1134.8
52.5°	745.7	759.1	862.5	1019.4	1089.7
55°	683.1	694.2	804.3	980.2	1058.2
57.5°	625.8	632.5	744.2	930.9	989.8
60°	569.5	571.1	687.5	876.2	932.5
62.5°	504.9	507.8	629.3	811.6	887.0
65°	432.4	446.0	566.6	749.9	818.0
67.5°	364.6	388.5	502.7	693.3	728.9
70°	292.1	332.5	440.0	626.8	651.9
72.5°	225.6	273.0	375.7	552.3	587.6
75°	163.5	216.7	315.9	485.5	516.0
77.5°	110.1	164.2	259.9	411.7	452.1
80°	65.9	119.9	210.0	343.3	388.8
82.5°	33.7	80.5	162.9	287.9	328.7
85°	14.6	50.9	123.1	238.9	274.2
87.5°	4.1	29.0	90.7	193.1	223.0
90°	0.3	15.3	64.6	151.4	178.5
92.5°	0.3	7.3	45.5	114.5	135.2
95°	0.3	3.8	28.3	83.0	101.5
97.5°	0.3	2.2	17.2	58.9	74.4
100°	0.3	1.9	10.2	39.1	53.1
102.5°	0.3	2.2	7.0	24.8	34.7
105°	0.3	2.2	5.7	16.2	22.9
107.5°	0.6	2.2	5.1	12.1	15.9
110°	0.3	1.9	5.4	9.2	12.4

TEST NUMBER: P517435

CATALOG NUMBER: HVL12-4-LD4-1HI-30-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.6	1.6	5.1	7.6	9.2
115°	0.3	1.3	4.5	7.3	7.6
117.5°	0.6	1.0	3.5	7.3	7.6
120°	0.6	0.6	2.9	7.0	8.0
122.5°	0.6	0.6	2.2	6.4	7.6
125°	0.3	0.6	1.9	4.8	6.7
127.5°	0.6	0.6	1.6	3.8	5.1
130°	0.6	0.6	1.3	2.9	3.8
132.5°	0.6	0.6	1.0	2.2	2.9
135°	0.6	0.6	0.6	1.6	2.2
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)